

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582071

Luminaire Tested: **HCC6S25D010MW-HM60525927-61WWWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582071  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S25D010MW-HM60525927-61WWWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2008.7 lumens  
Efficiency: N/A  
Efficacy: 75.0 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582071  
CATALOG NUMBER: HCC6S25D010MW-HM60525927-61WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P582071

CATALOG NUMBER: HCC6S25D010MW-HM60525927-61WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	56229	56229	56229
5°	57451	56218	55211
10°	59201	55694	53818
15°	61079	54955	52486
20°	62043	52895	50358
25°	61026	49757	47470
30°	58098	46121	44355
35°	52990	41633	40977
40°	46330	37399	37205
45°	39865	32918	33678
50°	34651	28681	29278
55°	30259	25175	25452
60°	26884	21818	19976
65°	23984	18368	15268
70°	21109	15035	12791
75°	18110	11861	12179
80°	14585	10165	11933
85°	9686	8806	10567



TEST NUMBER: P582071  
 CATALOG NUMBER: HCC6S25D010MW-HM60525927-61WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	97.1	4.8
10°-20°	276.5	13.8
20°-30°	394.7	19.6
30°-40°	413.4	20.6
40°-50°	348.1	17.3
50°-60°	247.7	12.3
60°-70°	145.0	7.2
70°-80°	68.6	3.4
80°-90°	17.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	768.3	38.2
0°-40°	1181.7	58.8
0°-60°	1777.5	88.5
0°-90°	2008.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2008.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1026	1026	1026	1026	1026	
5°	1044	1036	1022	1008	1003	100
15°	1076	1037	968	929	925	304
25°	1009	938	823	783	785	462
35°	792	726	622	601	612	492
45°	514	476	425	426	434	399
55°	317	290	263	263	266	285
65°	185	164	142	119	118	184
75°	86	71	56	55	58	92
85°	15	13	14	17	17	20
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582071

CATALOG NUMBER: HCC6S25D010MW-HM60525927-61WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1025.7	1025.7	1025.7	1025.7	1025.7	1025.7	1025.7	1025.7	1025.7
2.5°	1027.1	1027.1	1025.7	1024.3	1021.6	1017.3	1014.6	1011.7	1011.7
5°	1044.0	1041.1	1035.5	1028.6	1021.6	1013.2	1007.5	1003.3	1003.3
7.5°	1057.9	1052.4	1041.1	1028.6	1015.9	1004.7	994.9	989.2	987.9
10°	1063.5	1056.5	1039.7	1020.1	1000.5	985.1	973.8	966.8	966.8
12.5°	1069.2	1060.8	1038.4	1010.3	985.1	964.1	952.9	947.3	945.9
15°	1076.2	1064.9	1037.0	1001.9	968.3	944.5	929.1	924.8	924.8
17.5°	1076.2	1062.2	1027.1	983.7	941.6	915.1	901.0	896.8	898.3
20°	1063.5	1048.1	1006.2	952.9	906.7	878.6	864.6	861.8	863.2
22.5°	1039.7	1021.6	973.8	916.4	865.9	836.5	824.0	824.0	822.6
25°	1008.9	989.2	937.5	877.2	822.6	793.1	783.3	784.8	784.8
27.5°	968.3	948.6	896.8	832.4	777.7	748.3	741.3	744.0	745.5
30°	917.8	896.8	842.1	779.1	728.6	699.2	695.0	699.2	700.7
32.5°	856.2	840.8	787.5	723.1	675.4	650.2	648.8	652.9	658.6
35°	791.8	774.9	725.9	667.0	622.1	601.2	601.2	608.2	612.3
37.5°	721.6	704.8	660.0	611.0	573.1	553.5	556.3	563.3	564.7
40°	647.4	634.8	596.9	555.0	522.6	507.2	511.5	518.5	519.9
42.5°	577.4	566.1	535.3	497.4	473.6	462.4	468.0	476.4	479.3
45°	514.2	501.7	476.4	444.2	424.6	419.0	426.0	431.5	434.4
47.5°	456.8	445.6	424.6	395.2	381.2	378.3	385.3	388.2	390.9
50°	406.3	395.2	374.1	347.5	336.3	336.3	341.9	344.7	343.3
52.5°	357.4	347.5	327.9	305.5	298.5	298.5	302.7	304.1	306.9
55°	316.6	306.9	290.1	269.0	263.4	260.6	263.4	263.4	266.3
57.5°	278.8	270.4	255.0	235.4	228.4	225.7	224.2	222.8	225.7
60°	245.2	238.2	221.4	204.6	199.0	192.0	186.3	180.8	182.2
62.5°	214.4	207.4	192.0	175.2	169.5	159.8	152.7	145.7	148.5
65°	184.9	177.9	163.9	150.0	141.6	130.3	119.2	114.9	117.7
67.5°	158.4	152.7	138.7	124.7	117.7	105.1	93.8	93.8	95.2
70°	131.7	126.1	114.9	102.2	93.8	82.7	78.4	79.8	79.8
72.5°	107.9	103.7	92.5	81.3	72.9	65.9	65.9	67.3	68.7
75°	85.5	82.7	71.4	61.6	56.0	51.9	54.6	56.0	57.5
77.5°	65.9	61.6	53.3	46.2	42.0	43.5	46.2	47.6	49.0
80°	46.2	44.9	37.8	33.6	32.2	33.6	36.5	37.8	37.8
82.5°	29.4	28.1	23.8	22.4	22.4	23.8	26.6	26.6	26.6
85°	15.4	14.0	12.7	12.7	14.0	15.4	16.8	16.8	16.8
87.5°	5.6	4.3	5.6	5.6	7.0	7.0	7.0	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)