

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582088

Luminaire Tested: **HCC6W25D010BZ-HM60525930-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W25D010BZ-HM60525930-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2117.9 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582088
CATALOG NUMBER: HCC6W25D010BZ-HM60525930-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582088

CATALOG NUMBER: HCC6W25D010BZ-HM60525930-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	62331	62331	62331
5°	65089	62145	59283
10°	66871	61071	55710
15°	68525	59751	52197
20°	68828	57043	47937
25°	67383	53410	43968
30°	63928	49115	40291
35°	58062	44142	36152
40°	50588	39309	32525
45°	43772	34407	28592
50°	38233	29619	25057
55°	33786	26035	21495
60°	30359	22816	18628
65°	27188	19846	18056
70°	24283	16926	16926
75°	21075	14255	15864
80°	16890	12060	14490
85°	11573	10567	12517



TEST NUMBER: P582088
 CATALOG NUMBER: HCC6W25D010BZ-HM60525930-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.9	5.0
10°-20°	297.0	14.0
20°-30°	414.0	19.5
30°-40°	426.5	20.1
40°-50°	353.5	16.7
50°-60°	254.0	12.0
60°-70°	161.8	7.6
70°-80°	83.1	3.9
80°-90°	21.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	817.8	38.6
0°-40°	1244.4	58.8
0°-60°	1851.9	87.4
0°-90°	2117.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2117.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1137	1137	1137	1137	1137	
5°	1183	1164	1129	1093	1077	113
15°	1207	1161	1053	956	920	340
25°	1114	1038	883	770	727	510
35°	868	797	660	572	540	539
45°	565	525	444	387	369	437
55°	354	324	272	242	225	318
65°	210	187	153	133	139	210
75°	100	86	67	70	75	106
85°	18	17	17	18	20	24
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582088

CATALOG NUMBER: HCC6W25D010BZ-HM60525930-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0
2.5°	1158.4	1153.8	1147.6	1141.6	1132.3	1121.7	1112.4	1109.4	1104.8
5°	1182.8	1176.7	1164.5	1149.3	1129.3	1109.4	1092.6	1081.8	1077.3
7.5°	1198.1	1190.5	1173.7	1147.6	1118.6	1089.5	1065.0	1049.8	1043.6
10°	1201.3	1193.6	1170.7	1135.5	1097.1	1057.4	1026.8	1008.4	1000.8
12.5°	1205.8	1195.1	1166.0	1124.7	1075.7	1029.8	991.6	968.7	960.9
15°	1207.4	1195.1	1161.4	1110.9	1052.8	997.8	956.4	928.8	919.7
17.5°	1201.3	1187.5	1147.6	1086.5	1020.7	962.6	913.6	884.5	872.2
20°	1179.8	1164.5	1118.6	1049.8	977.8	916.6	866.1	835.5	821.7
22.5°	1152.3	1132.3	1080.3	1006.9	931.9	867.6	817.1	786.5	772.7
25°	1114.0	1095.6	1037.5	959.4	883.0	815.6	769.7	737.5	726.9
27.5°	1069.7	1048.3	988.5	910.4	832.5	765.1	720.7	691.7	677.9
30°	1009.9	990.0	930.4	852.3	775.9	713.1	667.2	642.7	636.5
32.5°	939.5	922.7	864.6	791.1	717.7	659.6	621.2	595.3	589.2
35°	867.6	847.8	797.3	728.4	659.6	607.5	572.2	549.3	540.2
37.5°	789.6	771.2	728.4	667.2	606.0	557.0	526.4	506.5	497.3
40°	706.9	693.2	653.4	604.4	549.3	506.5	480.5	463.6	454.5
42.5°	630.5	616.7	589.2	543.2	497.3	459.1	436.2	420.8	413.1
45°	564.6	552.4	524.9	485.0	443.8	411.6	387.2	376.4	368.8
47.5°	498.8	492.7	468.2	431.5	393.3	365.8	348.8	336.7	330.5
50°	448.3	440.7	417.8	379.5	347.3	325.9	310.6	300.0	293.8
52.5°	396.3	388.7	367.3	335.2	309.1	289.2	273.9	264.8	258.6
55°	353.5	347.3	324.4	295.3	272.4	255.5	241.8	231.1	224.9
57.5°	313.8	307.6	286.2	258.6	238.7	223.4	211.1	202.0	194.3
60°	276.9	272.4	251.0	224.9	208.1	192.8	182.1	174.4	169.9
62.5°	244.8	235.7	217.3	194.3	179.1	166.8	156.1	151.5	154.5
65°	209.6	205.0	186.7	166.8	153.0	140.8	133.1	136.2	139.2
67.5°	180.6	174.4	159.1	140.8	128.6	119.4	114.8	120.9	122.4
70°	151.5	145.3	131.6	116.3	105.6	99.5	99.5	104.0	105.6
72.5°	123.9	119.4	107.1	94.9	87.2	82.6	85.7	88.7	90.3
75°	99.5	94.9	85.7	74.9	67.3	67.3	70.4	73.4	74.9
77.5°	76.6	73.4	64.3	56.6	53.5	53.5	56.6	58.1	59.6
80°	53.5	50.5	45.9	41.3	38.2	41.3	44.4	44.4	45.9
82.5°	35.2	33.7	30.6	27.6	27.6	29.1	30.6	32.1	32.1
85°	18.4	18.4	16.8	15.3	16.8	18.4	18.4	19.9	19.9
87.5°	6.1	6.1	6.1	6.1	7.6	7.6	7.6	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)