

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582141

Luminaire Tested: **HCC6W30D010MW-HM63040827-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010MW-HM63040827-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2593.7 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582141
CATALOG NUMBER: HCC6W30D010MW-HM63040827-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582141

CATALOG NUMBER: HCC6W30D010MW-HM63040827-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	79796	79796	79796
5°	81334	79650	77845
10°	84094	78628	75327
15°	86675	77265	72969
20°	88015	74049	69149
25°	86430	68974	64389
30°	82158	62845	59091
35°	73843	56169	53298
40°	63734	49221	47618
45°	53959	42376	41268
50°	46267	35794	35444
55°	40113	30126	28960
60°	35019	24472	20645
65°	30794	18848	11415
70°	26591	12470	5578
75°	22536	6079	2160
80°	17458	2589	1263
85°	10315	1258	1258



TEST NUMBER: P582141

CATALOG NUMBER: HCC6W30D010MW-HM63040827-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.4	5.3
10°-20°	388.4	15.0
20°-30°	547.0	21.1
30°-40°	558.9	21.5
40°-50°	450.6	17.4
50°-60°	302.2	11.7
60°-70°	152.9	5.9
70°-80°	48.9	1.9
80°-90°	7.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1072.8	41.4
0°-40°	1631.6	62.9
0°-60°	2384.4	91.9
0°-90°	2593.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2593.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1456	1456	1456	1456	1456	
5°	1478	1468	1447	1425	1415	142
15°	1527	1466	1361	1300	1286	431
25°	1429	1316	1140	1071	1064	654
35°	1103	1003	839	792	796	687
45°	696	641	547	528	532	541
55°	420	373	315	301	303	378
65°	237	196	145	96	88	237
75°	106	76	29	10	10	114
85°	16	8	2	2	2	22
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582141

CATALOG NUMBER: HCC6W30D010MW-HM63040827-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6
2.5°	1461.6	1459.6	1457.6	1453.4	1447.4	1441.2	1437.1	1433.0	1431.0
5°	1478.0	1474.0	1467.8	1459.6	1447.4	1433.0	1424.8	1416.6	1414.6
7.5°	1500.5	1492.4	1476.0	1457.6	1437.1	1416.6	1402.3	1394.1	1387.9
10°	1510.7	1496.5	1474.0	1443.2	1412.5	1387.9	1369.5	1357.2	1353.2
12.5°	1518.9	1502.7	1469.8	1428.9	1387.9	1355.2	1334.8	1324.5	1320.4
15°	1527.2	1510.7	1465.8	1412.5	1361.4	1322.4	1299.9	1289.7	1285.7
17.5°	1527.2	1504.7	1451.4	1383.9	1322.4	1275.3	1252.8	1242.6	1240.6
20°	1508.7	1484.2	1418.7	1338.8	1269.3	1216.0	1195.5	1189.4	1185.3
22.5°	1474.0	1445.3	1371.6	1281.5	1205.8	1154.6	1132.0	1128.0	1123.8
25°	1428.9	1400.3	1316.3	1220.2	1140.3	1089.1	1070.7	1066.5	1064.5
27.5°	1371.6	1340.8	1252.8	1154.6	1068.7	1019.4	1003.2	1003.2	1001.0
30°	1297.9	1263.1	1177.1	1078.9	992.8	947.9	935.5	935.5	933.5
32.5°	1207.8	1173.1	1095.2	1001.0	919.2	872.1	861.9	865.9	863.9
35°	1103.4	1074.7	1003.2	911.0	839.3	796.4	792.2	796.4	796.4
37.5°	999.0	972.4	911.0	831.1	763.6	724.7	724.7	730.9	728.7
40°	890.6	870.0	812.7	743.1	687.8	661.2	657.2	663.2	665.4
42.5°	788.2	771.8	722.7	665.4	616.1	589.6	595.7	599.9	601.9
45°	696.0	679.6	640.8	581.4	546.6	528.2	528.2	534.3	532.3
47.5°	614.1	601.9	563.0	505.7	474.9	466.8	470.8	474.9	474.9
50°	542.5	524.1	487.3	442.2	419.7	409.4	413.5	415.6	415.6
52.5°	474.9	462.6	425.8	384.9	364.4	358.2	358.2	360.3	360.3
55°	419.7	405.3	372.6	331.6	315.2	307.1	300.9	298.9	303.0
57.5°	366.4	354.2	323.4	284.5	266.1	257.9	245.6	241.6	245.6
60°	319.4	309.1	278.5	241.6	223.2	206.8	192.4	184.3	188.3
62.5°	278.5	266.1	235.4	204.7	184.3	165.9	143.3	131.0	137.2
65°	237.4	227.2	196.5	165.9	145.3	122.8	96.2	88.0	88.0
67.5°	200.6	190.4	161.7	135.1	110.6	83.9	59.3	57.3	59.3
70°	165.9	155.6	131.0	104.4	77.8	51.1	34.8	34.8	34.8
72.5°	137.2	124.8	102.4	75.7	49.1	26.6	18.4	20.5	20.5
75°	106.4	96.2	75.7	51.1	28.7	12.2	10.2	10.2	10.2
77.5°	79.8	71.7	53.3	32.7	14.4	4.0	4.0	4.0	4.0
80°	55.3	47.1	34.8	20.5	8.2	4.0	4.0	4.0	4.0
82.5°	32.7	28.7	20.5	10.2	4.0	2.0	2.0	2.0	2.0
85°	16.4	14.4	8.2	4.0	2.0	2.0	2.0	2.0	2.0
87.5°	4.0	4.0	2.0	2.0	0.0	2.0	2.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)