

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582171

Luminaire Tested: **HCC6S30D010BZ-HM63040835-61RWWH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582171  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S30D010BZ-HM63040835-61RWWH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3407.3 lumens  
Efficiency: N/A  
Efficacy: 121.7 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582171  
CATALOG NUMBER: HCC6S30D010BZ-HM63040835-61RWWH

### Luminous Intensity Polar Plot





TEST NUMBER: P582171

CATALOG NUMBER: HCC6S30D010BZ-HM63040835-61RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77				77
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67				67
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59				59
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53				53
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47				47
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	95327	95327	95327
5°	96318	95438	94816
10°	97682	95150	94131
15°	99978	94547	93644
20°	100914	91743	92005
25°	98703	87126	88777
30°	93489	80930	83671
35°	84651	73970	76714
40°	73717	66868	69316
45°	62541	59192	61309
50°	55401	51708	53064
55°	48801	44213	44003
60°	43725	37234	34230
65°	39018	29861	24542
70°	34349	21558	15339
75°	28954	13047	8684
80°	22288	5746	3599
85°	12957	1447	1447



TEST NUMBER: P582171  
 CATALOG NUMBER: HCC6S30D010BZ-HM63040835-61RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.1	4.8
10°-20°	474.4	13.9
20°-30°	685.8	20.1
30°-40°	721.6	21.2
40°-50°	606.6	17.8
50°-60°	425.7	12.5
60°-70°	234.2	6.9
70°-80°	83.2	2.4
80°-90°	10.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1325.2	38.9
0°-40°	2046.8	60.1
0°-60°	3079.1	90.4
0°-90°	3407.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3407.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1739	1739	1739	1739	1739	
5°	1750	1746	1734	1728	1723	167
15°	1762	1732	1666	1646	1650	497
25°	1632	1550	1440	1443	1468	747
35°	1265	1192	1105	1128	1146	784
45°	807	784	764	782	791	633
55°	511	483	463	463	460	459
65°	301	269	230	189	189	299
75°	137	109	62	41	41	147
85°	21	11	2	2	2	28
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582171

CATALOG NUMBER: HCC6S30D010BZ-HM63040835-61RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1738.9	1738.9	1738.9	1738.9	1738.9	1738.9	1738.9	1738.9	1738.9
2.5°	1738.9	1738.9	1736.7	1736.7	1732.0	1732.0	1729.8	1729.8	1729.8
5°	1750.3	1750.3	1745.7	1738.9	1734.3	1727.5	1727.5	1725.2	1723.0
7.5°	1757.1	1754.8	1747.9	1738.9	1727.5	1716.1	1711.6	1713.8	1711.6
10°	1754.8	1750.3	1741.2	1723.0	1709.3	1693.3	1691.0	1688.7	1691.0
12.5°	1759.4	1752.6	1734.3	1711.6	1688.7	1670.5	1668.3	1668.3	1670.5
15°	1761.6	1754.8	1732.0	1697.9	1665.9	1647.7	1645.5	1647.7	1650.0
17.5°	1754.8	1745.7	1711.6	1665.9	1629.5	1611.2	1611.2	1615.9	1620.4
20°	1729.8	1716.1	1668.3	1613.6	1572.6	1558.9	1563.4	1572.6	1577.1
22.5°	1684.2	1668.3	1613.6	1552.0	1508.7	1497.3	1508.7	1520.1	1524.7
25°	1631.8	1613.6	1549.7	1485.9	1440.4	1426.7	1442.6	1460.8	1467.7
27.5°	1561.2	1540.6	1481.4	1408.4	1362.8	1356.1	1374.2	1394.7	1399.3
30°	1476.9	1454.0	1387.9	1319.6	1278.5	1276.3	1296.7	1315.0	1321.8
32.5°	1374.2	1353.7	1296.7	1228.4	1192.0	1192.0	1212.4	1228.4	1235.3
35°	1264.9	1242.0	1192.0	1134.9	1105.3	1107.6	1128.1	1139.5	1146.3
37.5°	1134.9	1128.1	1089.4	1041.6	1021.0	1025.5	1041.6	1050.6	1057.5
40°	1030.1	1011.8	986.9	948.1	934.4	939.0	954.9	964.0	968.6
42.5°	916.1	904.7	884.3	856.9	847.8	854.7	868.3	875.1	872.8
45°	806.7	804.5	784.0	768.0	763.5	772.6	781.6	788.5	790.8
47.5°	727.0	717.9	699.6	688.3	683.7	692.8	702.0	706.5	706.5
50°	649.6	640.4	622.2	610.8	606.3	615.3	622.2	626.7	622.2
52.5°	572.0	562.9	546.9	533.3	531.0	535.5	537.9	540.2	544.7
55°	510.6	501.4	483.2	467.2	462.6	464.9	462.6	462.6	460.4
57.5°	451.2	442.1	423.9	405.7	398.8	396.5	389.8	387.4	385.1
60°	398.8	387.4	369.2	348.7	339.6	330.4	319.0	312.2	312.2
62.5°	348.7	337.3	316.7	298.6	284.9	269.0	250.6	241.6	241.6
65°	300.8	291.7	269.0	248.4	230.2	209.6	189.2	184.7	189.2
67.5°	255.3	246.1	223.3	202.8	180.0	154.9	136.7	136.7	141.3
70°	214.3	205.1	184.7	159.6	134.5	109.4	95.7	95.7	95.7
72.5°	175.5	166.3	143.6	120.8	95.7	70.6	63.8	66.1	63.8
75°	136.7	130.0	109.4	84.3	61.6	43.3	41.0	38.8	41.0
77.5°	102.6	95.7	77.5	54.7	34.2	25.1	22.8	22.8	22.8
80°	70.6	63.8	50.2	31.9	18.2	11.4	11.4	11.4	11.4
82.5°	43.3	36.5	27.3	15.9	6.9	6.9	6.9	6.9	6.9
85°	20.6	15.9	11.4	4.5	2.3	2.3	2.3	2.3	2.3
87.5°	4.5	4.5	2.3	2.3	0.0	2.3	2.3	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)