

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582188

Luminaire Tested: **HCC6W30D010MW-HM63040840-61RWWC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582188  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W30D010MW-HM63040840-61RWWC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3568.1 lumens  
Efficiency: N/A  
Efficacy: 127.4 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582188  
CATALOG NUMBER: HCC6W30D010MW-HM63040840-61RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P582188

CATALOG NUMBER: HCC6W30D010MW-HM63040840-61RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	96889	96889	96889
5°	97391	97914	97914
10°	100115	98384	97983
15°	103298	98945	98945
20°	104502	96678	98913
25°	102411	91844	96187
30°	96876	85349	90349
35°	87663	78052	81894
40°	76264	70604	73352
45°	65170	62937	65170
50°	57192	55145	57397
55°	49900	46469	48295
60°	44119	38604	38078
65°	39148	30444	26099
70°	34557	21494	15740
75°	29420	12158	7604
80°	21909	3788	2241
85°	12014	1510	1510



TEST NUMBER: P582188  
 CATALOG NUMBER: HCC6W30D010MW-HM63040840-61RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.5	4.8
10°-20°	496.0	13.9
20°-30°	724.5	20.3
30°-40°	759.8	21.3
40°-50°	640.1	17.9
50°-60°	448.5	12.6
60°-70°	240.4	6.7
70°-80°	80.6	2.3
80°-90°	8.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1390.0	39.0
0°-40°	2149.8	60.2
0°-60°	3238.3	90.8
0°-90°	3568.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3568.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1767	1767	1767	1767	1767	
5°	1770	1777	1779	1779	1779	170
15°	1820	1796	1743	1734	1743	513
25°	1693	1621	1518	1545	1590	776
35°	1310	1243	1166	1200	1224	813
45°	841	826	812	833	841	655
55°	522	505	486	496	505	470
65°	302	275	235	194	201	301
75°	139	108	57	36	36	147
85°	19	10	2	2	2	26
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582188

CATALOG NUMBER: HCC6W30D010MW-HM63040840-61RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1767.4	1767.4	1767.4	1767.4	1767.4	1767.4	1767.4	1767.4	1767.4
2.5°	1755.4	1755.4	1760.2	1765.0	1769.8	1769.8	1772.2	1774.6	1772.2
5°	1769.8	1769.8	1777.0	1779.3	1779.3	1777.0	1779.3	1779.3	1779.3
7.5°	1791.3	1786.6	1789.0	1784.2	1779.3	1777.0	1774.6	1774.6	1774.6
10°	1798.5	1793.7	1789.0	1779.3	1767.4	1760.2	1757.8	1760.2	1760.2
12.5°	1808.1	1803.4	1791.3	1772.2	1757.8	1745.8	1743.4	1748.2	1748.2
15°	1820.1	1815.2	1796.1	1765.0	1743.4	1731.4	1733.9	1738.7	1743.4
17.5°	1820.1	1810.5	1779.3	1738.7	1712.3	1700.4	1709.9	1721.9	1729.0
20°	1791.3	1781.7	1738.7	1688.4	1657.2	1650.1	1666.9	1688.4	1695.5
22.5°	1753.1	1733.9	1683.6	1623.7	1590.2	1590.2	1614.1	1640.5	1650.1
25°	1693.1	1678.7	1621.3	1551.9	1518.4	1516.0	1544.6	1580.5	1590.2
27.5°	1626.1	1606.9	1544.6	1472.8	1436.9	1439.3	1470.4	1506.3	1516.0
30°	1530.4	1506.3	1451.3	1381.9	1348.3	1357.8	1389.0	1415.4	1427.3
32.5°	1422.5	1401.0	1350.7	1286.0	1257.2	1266.9	1293.2	1317.2	1326.7
35°	1309.9	1286.0	1243.0	1185.4	1166.3	1175.9	1199.8	1219.0	1223.7
37.5°	1183.1	1166.3	1135.1	1089.6	1075.3	1087.2	1106.4	1118.4	1123.1
40°	1065.7	1051.3	1025.0	991.5	986.6	996.3	1015.4	1022.5	1025.0
42.5°	950.7	938.8	922.1	898.1	898.1	907.7	924.4	929.2	931.6
45°	840.6	833.4	826.2	807.1	811.8	823.9	833.4	840.6	840.6
47.5°	744.8	747.2	737.7	723.3	728.0	740.0	747.2	754.4	754.4
50°	670.6	663.3	653.8	639.4	646.6	656.2	665.7	670.6	673.0
52.5°	584.4	581.9	574.8	558.0	562.8	567.6	577.1	584.4	586.8
55°	522.1	514.8	505.3	486.2	486.2	490.9	495.7	500.6	505.3
57.5°	462.2	455.0	440.6	419.1	416.7	416.7	414.4	419.1	426.3
60°	402.4	400.0	378.3	359.2	352.1	344.8	335.3	337.7	347.3
62.5°	349.7	344.8	325.7	301.8	287.4	275.4	263.5	261.0	270.6
65°	301.8	297.0	275.4	251.5	234.7	213.2	193.9	193.9	201.2
67.5°	258.6	249.1	230.0	203.6	182.0	155.6	136.5	141.3	143.6
70°	215.6	208.3	186.8	160.4	134.1	107.7	95.8	98.2	98.2
72.5°	177.2	167.6	146.1	119.7	93.5	69.4	64.7	62.3	62.3
75°	138.9	129.4	107.7	81.4	57.4	40.7	35.9	35.9	35.9
77.5°	100.6	93.5	74.2	50.3	31.2	19.1	16.8	14.4	14.4
80°	69.4	62.3	45.5	26.4	12.0	7.1	7.1	7.1	7.1
82.5°	40.7	33.5	21.5	12.0	4.8	2.4	2.4	2.4	2.4
85°	19.1	14.4	9.6	4.8	2.4	2.4	2.4	2.4	2.4
87.5°	2.4	2.4	2.4	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)