

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582213

Luminaire Tested: **HCC6S30D010MW-HM63040927-61WWBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582213  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S30D010MW-HM63040927-61WWBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2190.1 lumens  
Efficiency: N/A  
Efficacy: 78.2 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582213  
CATALOG NUMBER: HCC6S30D010MW-HM63040927-61WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P582213

CATALOG NUMBER: HCC6S30D010MW-HM63040927-61WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	67374	67374	67374
5°	68677	67252	65727
10°	71013	66393	63598
15°	73184	65239	61612
20°	74317	62515	58385
25°	72978	58231	54372
30°	69371	53071	49894
35°	62352	47422	44999
40°	53808	41564	40204
45°	45563	35787	34841
50°	39061	30216	29927
55°	33863	25442	24458
60°	29570	20667	17433
65°	26008	15916	9638
70°	22456	10515	4712
75°	19042	5147	1843
80°	14743	2178	1073
85°	8680	1132	1132



TEST NUMBER: P582213  
 CATALOG NUMBER: HCC6S30D010MW-HM63040927-61WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.0	5.3
10°-20°	328.0	15.0
20°-30°	461.8	21.1
30°-40°	471.9	21.5
40°-50°	380.5	17.4
50°-60°	255.2	11.7
60°-70°	129.1	5.9
70°-80°	41.3	1.9
80°-90°	6.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	905.8	41.4
0°-40°	1377.7	62.9
0°-60°	2013.3	91.9
0°-90°	2190.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2190.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1229	1229	1229	1229	1229	
5°	1248	1239	1222	1203	1194	120
15°	1290	1238	1150	1098	1086	364
25°	1206	1112	963	904	899	552
35°	932	847	709	669	672	580
45°	588	541	462	446	449	457
55°	354	315	266	254	256	319
65°	200	166	123	81	74	200
75°	90	64	24	9	9	97
85°	14	7	2	2	2	19
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582213

CATALOG NUMBER: HCC6S30D010MW-HM63040927-61WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1229.0	1229.0	1229.0	1229.0	1229.0	1229.0	1229.0	1229.0	1229.0
2.5°	1234.2	1232.4	1230.7	1227.3	1222.1	1216.8	1213.4	1209.9	1208.3
5°	1248.0	1244.5	1239.3	1232.4	1222.1	1209.9	1203.0	1196.1	1194.4
7.5°	1267.0	1260.1	1246.3	1230.7	1213.4	1196.1	1184.0	1177.1	1172.0
10°	1275.7	1263.6	1244.5	1218.6	1192.7	1172.0	1156.4	1146.0	1142.5
12.5°	1282.6	1268.8	1241.1	1206.5	1172.0	1144.3	1127.1	1118.4	1114.9
15°	1289.5	1275.7	1237.6	1192.7	1149.5	1116.6	1097.6	1089.0	1085.6
17.5°	1289.5	1270.4	1225.5	1168.4	1116.6	1076.9	1057.9	1049.2	1047.5
20°	1273.9	1253.2	1197.9	1130.5	1071.6	1026.7	1009.5	1004.2	1000.8
22.5°	1244.5	1220.4	1158.1	1082.1	1018.1	974.9	955.8	952.4	948.9
25°	1206.5	1182.3	1111.5	1030.1	962.7	919.6	904.0	900.5	898.9
27.5°	1158.1	1132.2	1057.9	974.9	902.3	860.8	846.9	846.9	845.3
30°	1095.9	1066.5	993.9	910.9	838.4	800.3	790.0	790.0	788.2
32.5°	1019.8	990.4	924.8	845.3	776.1	736.3	727.7	731.1	729.5
35°	931.7	907.4	846.9	769.2	708.6	672.4	668.9	672.4	672.4
37.5°	843.5	821.0	769.2	701.7	644.8	611.9	611.9	617.1	615.3
40°	751.9	734.6	686.2	627.4	580.8	558.4	554.9	560.0	561.8
42.5°	665.5	651.7	610.2	561.8	520.3	497.8	502.9	506.5	508.2
45°	587.7	573.8	541.0	490.9	461.6	446.0	446.0	451.1	449.4
47.5°	518.5	508.2	475.4	427.0	401.0	394.2	397.6	401.0	401.0
50°	458.0	442.5	411.4	373.3	354.3	345.8	349.2	350.9	350.9
52.5°	401.0	390.7	359.6	325.0	307.7	302.5	302.5	304.3	304.3
55°	354.3	342.2	314.6	280.0	266.2	259.3	254.1	252.3	255.9
57.5°	309.4	299.0	273.1	240.3	224.7	217.8	207.5	203.9	207.5
60°	269.7	261.0	235.1	203.9	188.5	174.5	162.5	155.5	159.0
62.5°	235.1	224.7	198.8	172.9	155.5	140.1	121.0	110.6	115.8
65°	200.5	191.9	166.0	140.1	122.7	103.7	81.2	74.3	74.3
67.5°	169.4	160.8	136.5	114.0	93.3	70.9	50.2	48.4	50.2
70°	140.1	131.4	110.6	88.1	65.6	43.2	29.4	29.4	29.4
72.5°	115.8	105.5	86.4	64.0	41.5	22.5	15.6	17.2	17.2
75°	89.9	81.2	64.0	43.2	24.3	10.3	8.7	8.7	8.7
77.5°	67.4	60.5	44.9	27.7	12.1	3.4	3.4	3.4	3.4
80°	46.7	39.7	29.4	17.2	6.9	3.4	3.4	3.4	3.4
82.5°	27.7	24.3	17.2	8.7	3.4	1.8	1.8	1.8	1.8
85°	13.8	12.1	6.9	3.4	1.8	1.8	1.8	1.8	1.8
87.5°	3.4	3.4	1.8	1.8	0.0	1.8	1.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)