

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582243

Luminaire Tested: **HCC6W30D010MW-HM63040935-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010MW-HM63040935-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3043.5 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582243
CATALOG NUMBER: HCC6W30D010MW-HM63040935-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582243

CATALOG NUMBER: HCC6W30D010MW-HM63040935-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	85147	85147	85147
5°	86033	85246	84685
10°	87256	84991	84083
15°	89302	84450	83650
20°	90139	81942	82181
25°	88166	77817	79299
30°	83500	72290	74739
35°	75610	66073	68529
40°	65852	59733	61909
45°	55874	52866	54765
50°	49474	46182	47393
55°	43583	39502	39301
60°	39054	33254	30579
65°	34855	26670	21922
70°	30662	19250	13704
75°	25862	11628	7752
80°	19920	5146	3220
85°	11511	1258	1258



TEST NUMBER: P582243
 CATALOG NUMBER: HCC6W30D010MW-HM63040935-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.4	4.8
10°-20°	423.7	13.9
20°-30°	612.5	20.1
30°-40°	644.5	21.2
40°-50°	541.8	17.8
50°-60°	380.3	12.5
60°-70°	209.2	6.9
70°-80°	74.3	2.4
80°-90°	9.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1183.7	38.9
0°-40°	1828.2	60.1
0°-60°	2750.3	90.4
0°-90°	3043.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3043.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1553	1553	1553	1553	1553	
5°	1563	1559	1549	1543	1539	149
15°	1574	1547	1488	1470	1474	444
25°	1458	1384	1286	1289	1311	667
35°	1130	1065	987	1008	1024	700
45°	721	700	682	698	706	565
55°	456	432	413	413	411	410
65°	269	240	206	169	169	267
75°	122	98	55	37	37	131
85°	18	10	2	2	2	25
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582243

CATALOG NUMBER: HCC6W30D010MW-HM63040935-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1553.2	1553.2	1553.2	1553.2	1553.2	1553.2	1553.2	1553.2	1553.2
2.5°	1553.2	1553.2	1551.2	1551.2	1547.1	1547.1	1545.1	1545.1	1545.1
5°	1563.4	1563.4	1559.4	1553.2	1549.1	1543.1	1543.1	1541.1	1538.9
7.5°	1569.5	1567.5	1561.4	1553.2	1543.1	1532.9	1528.8	1530.8	1528.8
10°	1567.5	1563.4	1555.2	1538.9	1526.8	1512.5	1510.5	1508.5	1510.5
12.5°	1571.5	1565.4	1549.1	1528.8	1508.5	1492.2	1490.1	1490.1	1492.2
15°	1573.5	1567.5	1547.1	1516.6	1488.0	1471.7	1469.7	1471.7	1473.9
17.5°	1567.5	1559.4	1528.8	1488.0	1455.5	1439.2	1439.2	1443.3	1447.4
20°	1545.1	1532.9	1490.1	1441.3	1404.6	1392.4	1396.5	1404.6	1408.7
22.5°	1504.3	1490.1	1441.3	1386.3	1347.6	1337.4	1347.6	1357.8	1361.9
25°	1457.6	1441.3	1384.2	1327.3	1286.5	1274.4	1288.6	1304.8	1311.0
27.5°	1394.5	1376.1	1323.2	1258.1	1217.3	1211.2	1227.5	1245.8	1249.9
30°	1319.1	1298.7	1239.8	1178.7	1142.0	1140.0	1158.3	1174.6	1180.7
32.5°	1227.5	1209.2	1158.3	1097.2	1064.6	1064.6	1082.9	1097.2	1103.4
35°	1129.8	1109.5	1064.6	1013.7	987.3	989.4	1007.7	1017.8	1024.0
37.5°	1013.7	1007.7	973.1	930.3	912.0	916.0	930.3	938.5	944.5
40°	920.2	903.9	881.4	846.8	834.7	838.7	853.0	861.1	865.1
42.5°	818.4	808.2	789.9	765.4	757.3	763.3	775.6	781.6	779.6
45°	720.7	718.6	700.3	686.1	681.9	690.1	698.2	704.4	706.4
47.5°	649.4	641.2	624.9	614.8	610.7	618.9	627.0	631.0	631.0
50°	580.1	572.0	555.7	545.5	541.5	549.7	555.7	559.8	555.7
52.5°	510.9	502.8	488.6	476.3	474.3	478.3	480.5	482.5	486.5
55°	456.0	447.9	431.6	417.3	413.3	415.3	413.3	413.3	411.2
57.5°	403.1	394.9	378.6	362.4	356.2	354.2	348.1	346.1	344.0
60°	356.2	346.1	329.8	311.4	303.3	295.2	285.0	278.9	278.9
62.5°	311.4	301.3	283.0	266.7	254.4	240.2	223.9	215.8	215.8
65°	268.7	260.5	240.2	221.9	205.6	187.3	169.0	164.9	169.0
67.5°	228.1	219.8	199.5	181.2	160.9	138.4	122.1	122.1	126.2
70°	191.3	183.2	164.9	142.4	120.1	97.7	85.5	85.5	85.5
72.5°	156.7	148.6	128.3	107.8	85.5	63.1	57.0	59.1	57.0
75°	122.1	116.0	97.7	75.3	54.9	38.6	36.6	34.6	36.6
77.5°	91.6	85.5	69.2	48.9	30.6	22.4	20.3	20.3	20.3
80°	63.1	57.0	44.8	28.5	16.3	10.2	10.2	10.2	10.2
82.5°	38.6	32.6	24.4	14.3	6.1	6.1	6.1	6.1	6.1
85°	18.3	14.3	10.2	4.0	2.0	2.0	2.0	2.0	2.0
87.5°	4.0	4.0	2.0	2.0	0.0	2.0	2.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)