

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582285

Luminaire Tested: **HCC6S35D010MW-HM63040827-61WWBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582285  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S35D010MW-HM63040827-61WWBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3081.8 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582285  
CATALOG NUMBER: HCC6S35D010MW-HM63040827-61WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P582285

CATALOG NUMBER: HCC6S35D010MW-HM63040827-61WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	94806	94806	94806
5°	96637	94629	92488
10°	99926	93424	89500
15°	102980	91800	86692
20°	104577	87974	82158
25°	102695	81948	76504
30°	97616	74670	70207
35°	87736	66736	63323
40°	75713	58488	56570
45°	64107	50346	49028
50°	54966	42532	42114
55°	47664	35803	34407
60°	41598	29066	24527
65°	36606	22402	13568
70°	31576	14810	6620
75°	26794	7223	2563
80°	20741	3062	1547
85°	12265	1572	1572



TEST NUMBER: P582285  
 CATALOG NUMBER: HCC6S35D010MW-HM63040827-61WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.2	5.3
10°-20°	461.5	15.0
20°-30°	649.9	21.1
30°-40°	664.0	21.5
40°-50°	535.4	17.4
50°-60°	359.1	11.7
60°-70°	181.7	5.9
70°-80°	58.1	1.9
80°-90°	9.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1274.6	41.4
0°-40°	1938.6	62.9
0°-60°	2833.0	91.9
0°-90°	3081.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3081.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1729	1729	1729	1729	1729	
5°	1756	1744	1720	1693	1681	169
15°	1814	1742	1618	1544	1528	512
25°	1698	1564	1355	1272	1265	777
35°	1311	1192	997	941	946	816
45°	827	761	649	628	632	643
55°	499	443	375	358	360	449
65°	282	234	173	114	105	282
75°	126	90	34	12	12	136
85°	20	10	2	2	2	26
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582285

CATALOG NUMBER: HCC6S35D010MW-HM63040827-61WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1729.4	1729.4	1729.4	1729.4	1729.4	1729.4	1729.4	1729.4	1729.4
2.5°	1736.6	1734.2	1731.8	1726.9	1719.6	1712.3	1707.4	1702.7	1700.2
5°	1756.1	1751.2	1744.0	1734.2	1719.6	1702.7	1692.9	1683.2	1680.7
7.5°	1782.8	1773.1	1753.7	1731.8	1707.4	1683.2	1666.1	1656.4	1649.1
10°	1795.1	1778.0	1751.2	1714.8	1678.3	1649.1	1627.1	1612.6	1607.8
12.5°	1804.8	1785.3	1746.4	1697.8	1649.1	1610.2	1585.8	1573.7	1568.8
15°	1814.5	1795.1	1741.5	1678.3	1617.5	1571.2	1544.5	1532.4	1527.5
17.5°	1814.5	1787.7	1724.5	1644.2	1571.2	1515.3	1488.5	1476.4	1473.9
20°	1792.6	1763.5	1685.6	1590.7	1508.0	1444.7	1420.5	1413.1	1408.3
22.5°	1751.2	1717.2	1629.6	1522.6	1432.6	1371.8	1345.1	1340.2	1335.3
25°	1697.8	1663.7	1564.0	1449.6	1354.8	1294.0	1272.0	1267.2	1264.8
27.5°	1629.6	1593.2	1488.5	1371.8	1269.7	1211.2	1191.9	1191.9	1189.4
30°	1542.1	1500.8	1398.5	1281.8	1179.6	1126.2	1111.6	1111.6	1109.1
32.5°	1435.1	1393.7	1301.3	1189.4	1092.1	1036.2	1024.0	1028.8	1026.4
35°	1311.0	1276.9	1191.9	1082.4	997.2	946.2	941.3	946.2	946.2
37.5°	1187.0	1155.3	1082.4	987.5	907.2	861.0	861.0	868.4	865.9
40°	1058.0	1033.7	965.6	883.0	817.3	785.6	780.7	788.1	790.5
42.5°	936.4	916.9	858.6	790.5	732.1	700.6	707.8	712.7	715.1
45°	826.9	807.6	761.4	690.7	649.4	627.5	627.5	634.8	632.4
47.5°	729.7	715.1	668.9	600.8	564.2	554.6	559.5	564.2	564.2
50°	644.5	622.7	578.8	525.4	498.7	486.4	491.3	493.8	493.8
52.5°	564.2	549.7	505.9	457.2	433.0	425.6	425.6	428.1	428.1
55°	498.7	481.6	442.6	394.0	374.6	364.8	357.6	355.1	360.0
57.5°	435.4	420.8	384.3	338.1	316.1	306.5	291.9	287.0	291.9
60°	379.4	367.3	330.8	287.0	265.1	245.7	228.6	218.9	223.7
62.5°	330.8	316.1	279.7	243.2	218.9	197.0	170.3	155.7	162.9
65°	282.2	269.9	233.5	197.0	172.7	146.0	114.4	104.6	104.6
67.5°	238.4	226.2	192.2	160.6	131.3	99.8	70.5	68.2	70.5
70°	197.0	184.9	155.7	124.1	92.4	60.8	41.3	41.3	41.3
72.5°	162.9	148.3	121.6	90.0	58.4	31.6	21.9	24.3	24.3
75°	126.5	114.4	90.0	60.8	34.1	14.6	12.1	12.1	12.1
77.5°	94.9	85.1	63.3	38.9	17.0	4.9	4.9	4.9	4.9
80°	65.7	55.9	41.3	24.3	9.7	4.9	4.9	4.9	4.9
82.5°	38.9	34.1	24.3	12.1	4.9	2.5	2.5	2.5	2.5
85°	19.5	17.0	9.7	4.9	2.5	2.5	2.5	2.5	2.5
87.5°	4.9	4.9	2.5	2.5	0.0	2.5	2.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)