

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582405

Luminaire Tested: **HCC6W35D010BZ-HM63040940-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582405
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010BZ-HM63040940-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3709.3 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582405
CATALOG NUMBER: HCC6W35D010BZ-HM63040940-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582405

CATALOG NUMBER: HCC6W35D010BZ-HM63040940-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	103775	103775	103775
5°	104853	103896	103213
10°	106344	103583	102475
15°	108843	102929	101942
20°	109857	99870	100161
25°	107450	94844	96641
30°	101769	88108	91084
35°	92146	80529	83520
40°	80250	72794	75456
45°	68092	64433	66743
50°	60305	56280	57764
55°	53112	48142	47893
60°	47595	40534	37267
65°	42482	32507	26721
70°	37378	23449	16702
75°	31538	14191	9468
80°	24277	6251	3915
85°	14026	1572	1572



TEST NUMBER: P582405

CATALOG NUMBER: HCC6W35D010BZ-HM63040940-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.7	4.8
10°-20°	516.4	13.9
20°-30°	746.5	20.1
30°-40°	785.5	21.2
40°-50°	660.3	17.8
50°-60°	463.5	12.5
60°-70°	254.9	6.9
70°-80°	90.5	2.4
80°-90°	11.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1442.6	38.9
0°-40°	2228.2	60.1
0°-60°	3352.0	90.4
0°-90°	3709.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3709.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1893	1893	1893	1893	1893	
5°	1905	1900	1888	1881	1876	182
15°	1918	1886	1814	1791	1796	541
25°	1776	1687	1568	1570	1598	813
35°	1377	1298	1203	1228	1248	853
45°	878	853	831	851	861	689
55°	556	526	504	504	501	500
65°	328	293	251	206	206	326
75°	149	119	67	45	45	160
85°	22	12	2	2	2	31
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582405

CATALOG NUMBER: HCC6W35D010BZ-HM63040940-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1893.0	1893.0	1893.0	1893.0	1893.0	1893.0	1893.0	1893.0	1893.0
2.5°	1893.0	1893.0	1890.5	1890.5	1885.5	1885.5	1883.1	1883.1	1883.1
5°	1905.4	1905.4	1900.5	1893.0	1888.0	1880.6	1880.6	1878.1	1875.6
7.5°	1912.8	1910.4	1902.9	1893.0	1880.6	1868.1	1863.2	1865.7	1863.2
10°	1910.4	1905.4	1895.4	1875.6	1860.8	1843.4	1840.9	1838.4	1840.9
12.5°	1915.3	1907.9	1888.0	1863.2	1838.4	1818.5	1816.1	1816.1	1818.5
15°	1917.8	1910.4	1885.5	1848.3	1813.6	1793.8	1791.2	1793.8	1796.2
17.5°	1910.4	1900.5	1863.2	1813.6	1774.0	1754.0	1754.0	1759.0	1763.9
20°	1883.1	1868.1	1816.1	1756.6	1711.9	1696.9	1702.0	1711.9	1716.9
22.5°	1833.5	1816.1	1756.6	1689.6	1642.4	1629.9	1642.4	1654.8	1659.8
25°	1776.4	1756.6	1687.0	1617.6	1568.0	1553.0	1570.4	1590.3	1597.7
27.5°	1699.5	1677.1	1612.7	1533.2	1483.6	1476.1	1496.0	1518.4	1523.3
30°	1607.7	1582.9	1510.9	1436.5	1391.9	1389.3	1411.7	1431.6	1438.9
32.5°	1496.0	1473.7	1411.7	1337.3	1297.6	1297.6	1319.9	1337.3	1344.7
35°	1376.9	1352.1	1297.6	1235.5	1203.3	1205.7	1228.0	1240.5	1248.0
37.5°	1235.5	1228.0	1185.9	1133.9	1111.5	1116.5	1133.9	1143.8	1151.1
40°	1121.4	1101.5	1074.2	1032.1	1017.2	1022.2	1039.6	1049.5	1054.4
42.5°	997.3	984.9	962.7	932.9	923.0	930.3	945.3	952.7	950.2
45°	878.3	875.8	853.4	836.0	831.1	841.1	851.0	858.4	860.9
47.5°	791.5	781.5	761.7	749.2	744.3	754.2	764.2	769.1	769.1
50°	707.1	697.2	677.3	665.0	659.9	669.9	677.3	682.2	677.3
52.5°	622.7	612.8	595.4	580.6	578.0	583.0	585.5	587.9	593.0
55°	555.7	545.8	526.0	508.6	503.7	506.1	503.7	503.7	501.1
57.5°	491.2	481.3	461.4	441.6	434.1	431.7	424.2	421.8	419.3
60°	434.1	421.8	401.9	379.6	369.7	359.8	347.3	339.9	339.9
62.5°	379.6	367.1	344.8	325.0	310.1	292.8	273.0	263.0	263.0
65°	327.5	317.5	292.8	270.4	250.6	228.3	206.0	201.0	206.0
67.5°	277.9	267.9	243.1	220.8	195.9	168.7	148.9	148.9	153.8
70°	233.2	223.2	201.0	173.6	146.3	119.0	104.2	104.2	104.2
72.5°	191.0	181.1	156.3	131.5	104.2	76.9	69.4	72.0	69.4
75°	148.9	141.4	119.0	91.8	67.0	47.1	44.7	42.1	44.7
77.5°	111.7	104.2	84.4	59.5	37.2	27.3	24.9	24.9	24.9
80°	76.9	69.4	54.6	34.8	19.8	12.4	12.4	12.4	12.4
82.5°	47.1	39.7	29.8	17.4	7.5	7.5	7.5	7.5	7.5
85°	22.3	17.4	12.4	5.0	2.5	2.5	2.5	2.5	2.5
87.5°	5.0	5.0	2.5	2.5	0.0	2.5	2.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)