

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582642

Luminaire Tested: **HCC6S45D010MB-HM64560927-61WDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582642  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S45D010MB-HM64560927-61WDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3752.3 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582642  
CATALOG NUMBER: HCC6S45D010MB-HM64560927-61WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P582642  
 CATALOG NUMBER: HCC6S45D010MB-HM64560927-61WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59		
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50		
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46		
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	146956
5°	147936
10°	149647
15°	152719
20°	153570
25°	148787
30°	134983
35°	109747
40°	72844
45°	40539
50°	22728
55°	12616
60°	6962
65°	5266
70°	3670
75°	2690
80°	1578
85°	1635



TEST NUMBER: P582642  
 CATALOG NUMBER: HCC6S45D010MB-HM64560927-61WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	256.6	6.8
10°-20°	758.7	20.2
20°-30°	1118.3	29.8
30°-40°	1000.2	26.7
40°-50°	433.9	11.6
50°-60°	127.5	3.4
60°-70°	40.7	1.1
70°-80°	14.4	0.4
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2133.6	56.9
0°-40°	3133.8	83.5
0°-60°	3695.2	98.5
0°-90°	3752.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3752.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2681	
5°	2688	257
15°	2691	759
25°	2460	1118
35°	1640	1000
45°	523	434
55°	132	127
65°	41	41
75°	13	14
85°	3	2
90°	0	



TEST NUMBER: P582642  
CATALOG NUMBER: HCC6S45D010MB-HM64560927-61WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2680.7
2.5°	2673.0
5°	2688.3
7.5°	2693.3
10°	2688.3
12.5°	2688.3
15°	2690.9
17.5°	2675.6
20°	2632.4
22.5°	2558.8
25°	2459.8
27.5°	2320.2
30°	2132.4
32.5°	1908.9
35°	1639.9
37.5°	1332.8
40°	1017.9
42.5°	743.8
45°	522.9
47.5°	373.1
50°	266.5
52.5°	190.4
55°	132.0
57.5°	88.8
60°	63.5
62.5°	50.8
65°	40.6
67.5°	30.5
70°	22.9
72.5°	17.7
75°	12.7
77.5°	10.2
80°	5.0
82.5°	2.6
85°	2.6
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)