

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582645

Luminaire Tested: **HCC6S45D010MB-HM64560927-61WWBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582645  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S45D010MB-HM64560927-61WWBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3214.4 lumens  
Efficiency: N/A  
Efficacy: 73.1 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582645  
CATALOG NUMBER: HCC6S45D010MB-HM64560927-61WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582645

CATALOG NUMBER: HCC6S45D010MB-HM64560927-61WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	98885	98885	98885
5°	100803	98701	96467
10°	104223	97449	93346
15°	107413	95750	90426
20°	109081	91766	85693
25°	107117	85475	79801
30°	101813	77892	73233
35°	91517	69613	66040
40°	78977	61000	59003
45°	66875	52517	51137
50°	57346	44357	43930
55°	49709	37342	35889
60°	43396	30316	25590
65°	38175	23375	14152
70°	32938	15451	6924
75°	27959	7519	2690
80°	21625	3220	1578
85°	12769	1635	1635



TEST NUMBER: P582645  
 CATALOG NUMBER: HCC6S45D010MB-HM64560927-61WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.2	5.3
10°-20°	481.4	15.0
20°-30°	677.9	21.1
30°-40°	692.6	21.5
40°-50°	558.4	17.4
50°-60°	374.5	11.7
60°-70°	189.5	5.9
70°-80°	60.6	1.9
80°-90°	9.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1329.5	41.4
0°-40°	2022.0	62.9
0°-60°	2955.0	91.9
0°-90°	3214.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3214.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1804	1804	1804	1804	1804	
5°	1832	1819	1794	1766	1753	176
15°	1893	1816	1687	1611	1593	534
25°	1771	1631	1413	1327	1319	811
35°	1368	1243	1040	982	987	851
45°	863	794	677	654	660	671
55°	520	462	391	373	376	468
65°	294	244	180	119	109	294
75°	132	94	36	13	13	142
85°	20	10	3	3	3	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582645

CATALOG NUMBER: HCC6S45D010MB-HM64560927-61WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1803.8	1803.8	1803.8	1803.8	1803.8	1803.8	1803.8	1803.8	1803.8
2.5°	1811.5	1808.9	1806.3	1801.3	1793.6	1786.0	1781.0	1775.9	1773.3
5°	1831.8	1826.6	1819.1	1808.9	1793.6	1775.9	1765.7	1755.6	1753.0
7.5°	1859.7	1849.5	1829.2	1806.3	1781.0	1755.6	1737.8	1727.7	1720.1
10°	1872.3	1854.5	1826.6	1788.6	1750.6	1720.1	1697.2	1682.1	1676.9
12.5°	1882.4	1862.1	1821.6	1770.9	1720.1	1679.5	1654.2	1641.5	1636.3
15°	1892.6	1872.3	1816.5	1750.6	1687.1	1638.9	1611.0	1598.3	1593.3
17.5°	1892.6	1864.7	1798.8	1715.0	1638.9	1580.5	1552.7	1539.9	1537.5
20°	1869.8	1839.4	1758.1	1659.2	1573.0	1507.0	1481.6	1474.0	1468.9
22.5°	1826.6	1791.2	1699.8	1588.1	1494.3	1430.8	1403.0	1397.9	1392.8
25°	1770.9	1735.3	1631.3	1512.1	1413.1	1349.7	1326.9	1321.7	1319.3
27.5°	1699.8	1661.8	1552.7	1430.8	1324.3	1263.4	1243.1	1243.1	1240.6
30°	1608.4	1565.4	1458.7	1337.0	1230.5	1174.6	1159.4	1159.4	1156.9
32.5°	1496.9	1453.7	1357.3	1240.6	1139.1	1080.8	1068.1	1073.2	1070.6
35°	1367.5	1331.9	1243.1	1129.0	1040.2	986.8	981.8	986.8	986.8
37.5°	1238.1	1205.0	1129.0	1030.0	946.3	898.0	898.0	905.7	903.2
40°	1103.6	1078.2	1007.1	920.9	852.4	819.5	814.4	822.0	824.5
42.5°	976.8	956.5	895.6	824.5	763.6	730.7	738.3	743.3	745.9
45°	862.6	842.3	794.1	720.5	677.4	654.5	654.5	662.2	659.6
47.5°	761.2	745.9	697.7	626.6	588.6	578.4	583.6	588.6	588.6
50°	672.4	649.5	603.9	548.0	520.1	507.4	512.5	515.1	515.1
52.5°	588.6	573.4	527.7	476.9	451.6	444.0	444.0	446.6	446.6
55°	520.1	502.3	461.7	411.0	390.7	380.5	372.9	370.4	375.5
57.5°	454.1	438.9	400.8	352.6	329.8	319.6	304.4	299.3	304.4
60°	395.8	383.1	345.0	299.3	276.5	256.2	238.5	228.4	233.4
62.5°	345.0	329.8	291.7	253.7	228.4	205.5	177.6	162.3	170.0
65°	294.3	281.6	243.5	205.5	180.2	152.3	119.3	109.1	109.1
67.5°	248.7	235.9	200.5	167.4	137.0	104.0	73.5	71.1	73.5
70°	205.5	192.8	162.3	129.4	96.4	63.5	43.2	43.2	43.2
72.5°	170.0	154.7	126.8	93.8	60.9	33.0	22.9	25.3	25.3
75°	132.0	119.3	93.8	63.5	35.5	15.2	12.7	12.7	12.7
77.5°	99.0	88.8	65.9	40.6	17.7	5.0	5.0	5.0	5.0
80°	68.5	58.3	43.2	25.3	10.2	5.0	5.0	5.0	5.0
82.5°	40.6	35.5	25.3	12.7	5.0	2.6	2.6	2.6	2.6
85°	20.3	17.7	10.2	5.0	2.6	2.6	2.6	2.6	2.6
87.5°	5.0	5.0	2.6	2.6	0.0	2.6	2.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)