

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582863

Luminaire Tested: **HCC6S05D010MB-HM60525827-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582863
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S05D010MB-HM60525827-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 636.1 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582863
CATALOG NUMBER: HCC6S05D010MB-HM60525827-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582863

CATALOG NUMBER: HCC6S05D010MB-HM60525827-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				76				
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66				66				
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58				58				
5	81	69	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52				52				
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46				46				
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42				42				
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38				38				
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34				34				
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31				31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17806	17806	17806
5°	18187	17802	17488
10°	18743	17641	17039
15°	19342	17401	16623
20°	19643	16749	15944
25°	19326	15757	15031
30°	18395	14604	14040
35°	16778	13184	12976
40°	14670	11844	11779
45°	12621	10427	10660
50°	10976	9074	9270
55°	9577	7971	8057
60°	8508	6918	6315
65°	7588	5824	4838
70°	6684	4760	4055
75°	5740	3749	3855
80°	4641	3220	3788
85°	3082	2768	3334



TEST NUMBER: P582863
 CATALOG NUMBER: HCC6S05D010MB-HM60525827-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.8	4.8
10°-20°	87.5	13.8
20°-30°	125.0	19.6
30°-40°	130.9	20.6
40°-50°	110.2	17.3
50°-60°	78.4	12.3
60°-70°	45.9	7.2
70°-80°	21.7	3.4
80°-90°	5.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	243.3	38.2
0°-40°	374.2	58.8
0°-60°	562.8	88.5
0°-90°	636.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	636.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	325	325	325	325	325	
5°	330	328	324	319	318	32
15°	341	328	307	294	293	96
25°	320	297	260	248	248	146
35°	251	230	197	190	194	156
45°	163	151	134	135	138	126
55°	100	92	83	83	84	90
65°	58	52	45	38	37	58
75°	27	23	18	17	18	29
85°	5	4	4	5	5	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582863

CATALOG NUMBER: HCC6S05D010MB-HM60525827-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	324.8	324.8	324.8	324.8	324.8	324.8	324.8	324.8	324.8
2.5°	325.2	325.2	324.8	324.3	323.5	322.2	321.3	320.4	320.4
5°	330.5	329.7	327.9	325.7	323.5	320.8	319.0	317.8	317.8
7.5°	335.0	333.2	329.7	325.7	321.7	318.1	315.0	313.2	312.8
10°	336.7	334.6	329.3	323.1	316.9	311.9	308.4	306.1	306.1
12.5°	338.5	335.9	328.8	319.9	311.9	305.3	301.7	299.9	299.6
15°	340.8	337.2	328.4	317.3	306.6	299.1	294.1	292.9	292.9
17.5°	340.8	336.3	325.2	311.5	298.2	289.7	285.3	284.0	284.4
20°	336.7	331.9	318.5	301.7	287.1	278.2	273.8	272.9	273.3
22.5°	329.3	323.5	308.4	290.2	274.3	264.9	260.9	260.9	260.5
25°	319.5	313.2	296.9	277.8	260.5	251.2	248.0	248.5	248.5
27.5°	306.6	300.4	284.0	263.5	246.2	237.0	234.7	235.6	236.1
30°	290.6	284.0	266.7	246.7	230.7	221.4	220.1	221.4	221.8
32.5°	271.1	266.2	249.4	228.9	213.9	205.9	205.4	206.8	208.6
35°	250.7	245.3	229.8	211.2	197.0	190.4	190.4	192.6	193.9
37.5°	228.5	223.2	208.9	193.5	181.5	175.3	176.2	178.4	178.8
40°	205.0	201.0	189.0	175.7	165.5	160.6	161.9	164.2	164.6
42.5°	182.8	179.2	169.5	157.5	150.0	146.4	148.3	150.9	151.8
45°	162.8	158.9	150.9	140.7	134.5	132.7	134.9	136.6	137.5
47.5°	144.6	141.1	134.5	125.1	120.7	119.8	122.0	122.9	123.8
50°	128.7	125.1	118.4	110.1	106.4	106.4	108.3	109.2	108.7
52.5°	113.1	110.1	103.8	96.7	94.5	94.5	95.8	96.3	97.2
55°	100.2	97.2	91.9	85.2	83.4	82.5	83.4	83.4	84.3
57.5°	88.3	85.7	80.8	74.6	72.3	71.4	71.0	70.5	71.4
60°	77.6	75.5	70.1	64.7	63.1	60.8	59.0	57.3	57.6
62.5°	67.9	65.7	60.8	55.5	53.7	50.6	48.4	46.1	47.0
65°	58.5	56.4	51.9	47.5	44.9	41.2	37.7	36.4	37.3
67.5°	50.2	48.4	44.0	39.4	37.3	33.3	29.7	29.7	30.2
70°	41.7	39.9	36.4	32.4	29.7	26.2	24.9	25.3	25.3
72.5°	34.1	32.9	29.3	25.8	23.1	20.9	20.9	21.2	21.7
75°	27.1	26.2	22.6	19.5	17.7	16.4	17.3	17.7	18.2
77.5°	20.9	19.5	16.8	14.7	13.3	13.8	14.7	15.1	15.5
80°	14.7	14.2	12.0	10.6	10.2	10.6	11.5	12.0	12.0
82.5°	9.3	8.9	7.6	7.1	7.1	7.6	8.5	8.5	8.5
85°	4.9	4.4	4.0	4.0	4.4	4.9	5.3	5.3	5.3
87.5°	1.8	1.4	1.8	1.8	2.3	2.3	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)