

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582873

Luminaire Tested: **HCC6S05D010SL-HM60525830-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582873
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S05D010SL-HM60525830-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 713.7 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582873
CATALOG NUMBER: HCC6S05D010SL-HM60525830-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582873

CATALOG NUMBER: HCC6S05D010SL-HM60525830-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67																			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59																			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53																			
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47																			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35																			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	19966	19966	19966
5°	20174	19992	19860
10°	20463	19928	19722
15°	20948	19801	19620
20°	21136	19217	19269
25°	20675	18249	18600
30°	19579	16952	17522
35°	17735	15493	16068
40°	15436	14005	14513
45°	13094	12397	12846
50°	11607	10831	11113
55°	10217	9271	9214
60°	9155	7795	7170
65°	8185	6265	5150
70°	7197	4504	3206
75°	6058	2732	1822
80°	4672	1200	758
85°	2705	314	314



TEST NUMBER: P582873
 CATALOG NUMBER: HCC6S05D010SL-HM60525830-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.6	4.8
10°-20°	99.4	13.9
20°-30°	143.6	20.1
30°-40°	151.1	21.2
40°-50°	127.0	17.8
50°-60°	89.2	12.5
60°-70°	49.0	6.9
70°-80°	17.4	2.4
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.6	38.9
0°-40°	428.7	60.1
0°-60°	645.0	90.4
0°-90°	713.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	713.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	364	364	364	364	364	
5°	367	366	363	362	361	35
15°	369	363	349	345	346	104
25°	342	325	302	302	308	156
35°	265	250	232	236	240	164
45°	169	164	160	164	166	133
55°	107	101	97	97	96	96
65°	63	56	48	40	40	63
75°	29	23	13	9	9	31
85°	4	2	0	0	0	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582873

CATALOG NUMBER: HCC6S05D010SL-HM60525830-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	364.2	364.2	364.2	364.2	364.2	364.2	364.2	364.2	364.2
2.5°	364.2	364.2	363.7	363.7	362.8	362.8	362.3	362.3	362.3
5°	366.6	366.6	365.7	364.2	363.3	361.8	361.8	361.4	360.9
7.5°	368.0	367.6	366.1	364.2	361.8	359.5	358.5	359.0	358.5
10°	367.6	366.6	364.7	360.9	358.0	354.7	354.3	353.7	354.3
12.5°	368.5	367.1	363.3	358.5	353.7	350.0	349.4	349.4	350.0
15°	369.1	367.6	362.8	355.6	348.9	345.1	344.6	345.1	345.7
17.5°	367.6	365.7	358.5	348.9	341.3	337.5	337.5	338.4	339.5
20°	362.3	359.5	349.4	338.0	329.4	326.6	327.5	329.4	330.3
22.5°	352.8	349.4	338.0	325.1	316.1	313.6	316.1	318.4	319.3
25°	341.8	338.0	324.6	311.2	301.7	298.9	302.2	306.0	307.5
27.5°	327.0	322.7	310.3	295.0	285.4	284.1	287.8	292.1	293.1
30°	309.3	304.5	290.7	276.4	267.8	267.4	271.7	275.5	276.8
32.5°	287.8	283.5	271.7	257.3	249.6	249.6	253.9	257.3	258.8
35°	265.0	260.1	249.6	237.8	231.5	232.0	236.3	238.7	240.1
37.5°	237.8	236.3	228.1	218.2	213.9	214.8	218.2	220.0	221.5
40°	215.7	212.0	206.7	198.5	195.7	196.6	200.0	201.9	202.8
42.5°	191.9	189.5	185.2	179.4	177.5	179.0	181.9	183.3	182.8
45°	168.9	168.5	164.2	160.9	159.9	161.8	163.7	165.2	165.7
47.5°	152.3	150.4	146.6	144.2	143.2	145.1	147.0	148.0	148.0
50°	136.1	134.1	130.3	127.9	127.0	128.9	130.3	131.3	130.3
52.5°	119.8	117.9	114.6	111.8	111.2	112.2	112.7	113.1	114.1
55°	106.9	105.0	101.2	97.9	97.0	97.4	97.0	97.0	96.4
57.5°	94.5	92.7	88.8	85.0	83.5	83.1	81.6	81.1	80.7
60°	83.5	81.1	77.3	73.0	71.1	69.3	66.8	65.4	65.4
62.5°	73.0	70.6	66.3	62.5	59.7	56.3	52.5	50.6	50.6
65°	63.1	61.1	56.3	52.0	48.3	44.0	39.7	38.6	39.7
67.5°	53.4	51.5	46.8	42.5	37.7	32.4	28.6	28.6	29.6
70°	44.9	42.9	38.6	33.4	28.1	22.9	20.0	20.0	20.0
72.5°	36.7	34.8	30.1	25.3	20.0	14.8	13.3	13.9	13.3
75°	28.6	27.2	22.9	17.6	12.9	9.0	8.6	8.1	8.6
77.5°	21.5	20.0	16.3	11.4	7.1	5.2	4.7	4.7	4.7
80°	14.8	13.3	10.5	6.7	3.8	2.4	2.4	2.4	2.4
82.5°	9.0	7.7	5.8	3.4	1.5	1.5	1.5	1.5	1.5
85°	4.3	3.4	2.4	0.9	0.5	0.5	0.5	0.5	0.5
87.5°	0.9	0.9	0.5	0.5	0.0	0.5	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)