

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582881

Luminaire Tested: **HCC6W05D010MB-HM60525830-61WWWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582881  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W05D010MB-HM60525830-61WWWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 684.1 lumens  
Efficiency: N/A  
Efficacy: 114.0 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582881  
CATALOG NUMBER: HCC6W05D010MB-HM60525830-61WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P582881

CATALOG NUMBER: HCC6W05D010MB-HM60525830-61WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	19149	19149	19149
5°	19563	19145	18804
10°	20162	18965	18331
15°	20800	18712	17872
20°	21130	18009	17146
25°	20783	16943	16162
30°	19788	15705	15110
35°	18042	14181	13960
40°	15780	12738	12674
45°	13575	11210	11466
50°	11803	9774	9978
55°	10303	8573	8659
60°	9155	7434	6798
65°	8159	6265	5202
70°	7197	5129	4360
75°	6185	4046	4130
80°	4956	3473	4072
85°	3271	2956	3648



TEST NUMBER: P582881  
 CATALOG NUMBER: HCC6W05D010MB-HM60525830-61WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.1	4.8
10°-20°	94.2	13.8
20°-30°	134.4	19.6
30°-40°	140.8	20.6
40°-50°	118.5	17.3
50°-60°	84.4	12.3
60°-70°	49.4	7.2
70°-80°	23.4	3.4
80°-90°	6.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.6	38.2
0°-40°	402.4	58.8
0°-60°	605.3	88.5
0°-90°	684.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	684.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	349	349	349	349	349	
5°	356	353	348	343	342	34
15°	366	353	330	316	315	103
25°	344	319	280	267	267	157
35°	270	247	212	205	209	167
45°	175	162	145	145	148	136
55°	108	99	90	90	91	97
65°	63	56	48	41	40	63
75°	29	24	19	19	20	31
85°	5	4	5	6	6	7
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582881

CATALOG NUMBER: HCC6W05D010MB-HM60525830-61WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	349.3	349.3	349.3	349.3	349.3	349.3	349.3	349.3	349.3
2.5°	349.8	349.8	349.3	348.8	347.9	346.5	345.6	344.5	344.5
5°	355.5	354.6	352.7	350.3	347.9	345.0	343.1	341.7	341.7
7.5°	360.2	358.4	354.6	350.3	346.0	342.2	338.8	337.0	336.4
10°	362.2	359.8	354.1	347.4	340.7	335.5	331.7	329.3	329.3
12.5°	364.1	361.3	353.6	344.1	335.5	328.4	324.5	322.6	322.2
15°	366.5	362.7	353.1	341.3	329.7	321.6	316.4	314.9	314.9
17.5°	366.5	361.7	349.8	335.0	320.7	311.7	306.8	305.4	305.9
20°	362.2	357.0	342.6	324.5	308.7	299.2	294.5	293.5	293.9
22.5°	354.1	347.9	331.7	312.1	294.9	284.9	280.6	280.6	280.1
25°	343.6	337.0	319.2	298.8	280.1	270.1	266.8	267.2	267.2
27.5°	329.7	323.1	305.4	283.5	264.9	254.8	252.4	253.3	253.9
30°	312.6	305.4	286.8	265.3	248.1	238.1	236.7	238.1	238.7
32.5°	291.5	286.3	268.1	246.2	230.1	221.5	220.9	222.4	224.3
35°	269.6	263.9	247.2	227.1	211.9	204.8	204.8	207.1	208.6
37.5°	245.8	240.0	224.8	208.0	195.2	188.5	189.5	191.9	192.3
40°	220.5	216.2	203.3	188.9	178.0	172.8	174.1	176.6	177.1
42.5°	196.6	192.8	182.3	169.4	161.3	157.5	159.4	162.3	163.2
45°	175.1	170.9	162.3	151.3	144.6	142.7	145.1	147.0	147.9
47.5°	155.6	151.8	144.6	134.6	129.8	128.8	131.2	132.2	133.1
50°	138.4	134.6	127.5	118.3	114.6	114.6	116.4	117.4	117.0
52.5°	121.7	118.3	111.6	104.1	101.7	101.7	103.1	103.5	104.5
55°	107.8	104.5	98.8	91.6	89.7	88.8	89.7	89.7	90.6
57.5°	94.9	92.1	86.9	80.1	77.7	76.8	76.4	75.8	76.8
60°	83.5	81.1	75.4	69.7	67.8	65.4	63.5	61.6	62.0
62.5°	73.0	70.6	65.4	59.7	57.7	54.4	52.0	49.6	50.6
65°	62.9	60.6	55.8	51.1	48.3	44.4	40.6	39.1	40.1
67.5°	53.9	52.0	47.2	42.5	40.1	35.8	32.0	32.0	32.4
70°	44.9	42.9	39.1	34.8	32.0	28.1	26.7	27.2	27.2
72.5°	36.7	35.4	31.5	27.7	24.9	22.4	22.4	22.9	23.4
75°	29.2	28.1	24.3	21.0	19.1	17.6	18.6	19.1	19.5
77.5°	22.4	21.0	18.1	15.7	14.4	14.8	15.7	16.3	16.7
80°	15.7	15.3	12.9	11.4	11.0	11.4	12.4	12.9	12.9
82.5°	10.1	9.5	8.1	7.7	7.7	8.1	9.0	9.0	9.0
85°	5.2	4.7	4.3	4.3	4.7	5.2	5.8	5.8	5.8
87.5°	1.9	1.5	1.9	1.9	2.4	2.4	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)