

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592993

Luminaire Tested: **HCC6W05D010BZ-HM60525850-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P592993
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W05D010BZ-HM60525850-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 746.0 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592993
CATALOG NUMBER: HCC6W05D010BZ-HM60525850-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P592993

CATALOG NUMBER: HCC6W05D010BZ-HM60525850-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88		
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77		
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68		
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60		
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53		
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47		
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20256	20256	20256
5°	20361	20471	20471
10°	20936	20569	20485
15°	21601	20687	20687
20°	21848	20214	20681
25°	21413	19199	20106
30°	20250	17845	18889
35°	18330	16323	17119
40°	15944	14763	15329
45°	13622	13156	13622
50°	11957	11522	12000
55°	10437	9711	10102
60°	9221	8070	7949
65°	8185	6356	5448
70°	7229	4488	3302
75°	6142	2542	1589
80°	4578	789	474
85°	2516	314	314



TEST NUMBER: P592993
 CATALOG NUMBER: HCC6W05D010BZ-HM60525850-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.4	4.8
10°-20°	103.7	13.9
20°-30°	151.5	20.3
30°-40°	158.8	21.3
40°-50°	133.8	17.9
50°-60°	93.8	12.6
60°-70°	50.3	6.7
70°-80°	16.9	2.3
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.6	39.0
0°-40°	449.5	60.3
0°-60°	677.0	90.8
0°-90°	746.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	746.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	370	370	370	370	370	
5°	370	372	372	372	372	36
15°	381	376	364	362	364	107
25°	354	339	317	323	332	162
35°	274	260	244	251	256	170
45°	176	173	170	174	176	137
55°	109	106	102	104	106	98
65°	63	58	49	41	42	63
75°	29	22	12	8	8	31
85°	4	2	0	0	0	6
90°	0	0	0	0	0	



TEST NUMBER: P592993

CATALOG NUMBER: HCC6W05D010BZ-HM60525850-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	369.5	369.5	369.5	369.5	369.5	369.5	369.5	369.5	369.5
2.5°	367.0	367.0	368.0	369.1	370.0	370.0	370.5	371.0	370.5
5°	370.0	370.0	371.5	372.0	372.0	371.5	372.0	372.0	372.0
7.5°	374.5	373.6	374.0	373.0	372.0	371.5	371.0	371.0	371.0
10°	376.1	375.0	374.0	372.0	369.5	368.0	367.5	368.0	368.0
12.5°	378.0	377.1	374.5	370.5	367.5	365.0	364.5	365.6	365.6
15°	380.6	379.6	375.5	369.1	364.5	362.1	362.5	363.5	364.5
17.5°	380.6	378.5	372.0	363.5	358.0	355.5	357.5	360.0	361.5
20°	374.5	372.6	363.5	353.0	346.5	345.0	348.5	353.0	354.5
22.5°	366.5	362.5	352.0	339.5	332.4	332.4	337.4	343.0	345.0
25°	354.0	351.0	339.0	324.4	317.4	317.0	323.0	330.4	332.4
27.5°	340.0	335.9	323.0	307.9	300.5	300.9	307.5	314.9	317.0
30°	319.9	314.9	303.4	288.9	281.9	283.9	290.4	295.9	298.4
32.5°	297.4	292.9	282.4	268.8	262.8	264.9	270.4	275.4	277.4
35°	273.9	268.8	259.9	247.8	243.9	245.9	250.9	254.8	255.8
37.5°	247.4	243.9	237.3	227.8	224.9	227.4	231.3	233.8	234.8
40°	222.8	219.8	214.2	207.2	206.3	208.3	212.3	213.8	214.2
42.5°	198.8	196.3	192.8	187.8	187.8	189.7	193.2	194.2	194.8
45°	175.7	174.2	172.8	168.7	169.7	172.2	174.2	175.7	175.7
47.5°	155.7	156.2	154.2	151.2	152.2	154.7	156.2	157.7	157.7
50°	140.2	138.7	136.7	133.7	135.1	137.2	139.2	140.2	140.7
52.5°	122.2	121.7	120.1	116.6	117.6	118.6	120.7	122.2	122.7
55°	109.2	107.7	105.7	101.6	101.6	102.6	103.6	104.6	105.7
57.5°	96.6	95.1	92.1	87.6	87.1	87.1	86.7	87.6	89.2
60°	84.1	83.6	79.1	75.1	73.6	72.1	70.1	70.6	72.5
62.5°	73.1	72.1	68.1	63.1	60.1	57.6	55.0	54.6	56.6
65°	63.1	62.0	57.6	52.5	49.0	44.5	40.6	40.6	42.0
67.5°	54.1	52.1	48.0	42.6	38.1	32.5	28.6	29.5	30.1
70°	45.1	43.5	39.1	33.6	28.0	22.5	20.0	20.6	20.6
72.5°	37.1	35.0	30.5	25.1	19.5	14.5	13.6	13.0	13.0
75°	29.0	27.0	22.5	17.1	12.0	8.5	7.5	7.5	7.5
77.5°	21.0	19.5	15.5	10.5	6.6	4.0	3.5	3.1	3.1
80°	14.5	13.0	9.5	5.5	2.5	1.5	1.5	1.5	1.5
82.5°	8.5	7.0	4.5	2.5	1.0	0.5	0.5	0.5	0.5
85°	4.0	3.1	2.0	1.0	0.5	0.5	0.5	0.5	0.5
87.5°	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)