

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582926

Luminaire Tested: **HCC6S05D010SL-HM60525927-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S05D010SL-HM60525927-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 558.5 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582926
CATALOG NUMBER: HCC6S05D010SL-HM60525927-61RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P582926

CATALOG NUMBER: HCC6S05D010SL-HM60525927-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88																			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68																			
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60																			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53																			
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47																			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35																			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	15163	15163	15163
5°	15249	15326	15326
10°	15676	15397	15336
15°	16169	15488	15488
20°	16364	15133	15483
25°	16035	14372	15055
30°	15167	13363	14141
35°	13726	12220	12816
40°	11937	11056	11486
45°	10195	9854	10195
50°	8955	8631	8981
55°	7809	7264	7560
60°	6896	6041	5964
65°	6123	4761	4086
70°	5418	3366	2468
75°	4596	1906	1186
80°	3410	600	347
85°	1950	189	189



TEST NUMBER: P582926
 CATALOG NUMBER: HCC6S05D010SL-HM60525927-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	4.8
10°-20°	77.6	13.9
20°-30°	113.4	20.3
30°-40°	118.9	21.3
40°-50°	100.2	17.9
50°-60°	70.2	12.6
60°-70°	37.6	6.7
70°-80°	12.6	2.3
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.6	39.0
0°-40°	336.5	60.3
0°-60°	506.9	90.8
0°-90°	558.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	558.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	277	277	277	277	277	
5°	277	278	278	278	278	27
15°	285	281	273	271	273	80
25°	265	254	238	242	249	121
35°	205	195	183	188	192	127
45°	132	129	127	130	132	102
55°	82	79	76	78	79	74
65°	47	43	37	30	32	47
75°	22	17	9	6	6	23
85°	3	2	0	0	0	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582926

CATALOG NUMBER: HCC6S05D010SL-HM60525927-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	276.6	276.6	276.6	276.6	276.6	276.6	276.6	276.6	276.6
2.5°	274.8	274.8	275.5	276.3	277.1	277.1	277.4	277.8	277.4
5°	277.1	277.1	278.2	278.5	278.5	278.2	278.5	278.5	278.5
7.5°	280.5	279.7	280.0	279.3	278.5	278.2	277.8	277.8	277.8
10°	281.6	280.8	280.0	278.5	276.6	275.5	275.2	275.5	275.5
12.5°	283.1	282.3	280.5	277.4	275.2	273.3	272.9	273.7	273.7
15°	284.9	284.2	281.1	276.3	272.9	271.1	271.4	272.2	272.9
17.5°	284.9	283.4	278.5	272.2	268.0	266.1	267.7	269.5	270.6
20°	280.5	278.9	272.2	264.3	259.4	258.3	260.9	264.3	265.4
22.5°	274.4	271.4	263.5	254.1	248.9	248.9	252.7	256.8	258.3
25°	265.1	262.8	253.8	243.0	237.6	237.3	241.8	247.5	248.9
27.5°	254.6	251.5	241.8	230.5	225.0	225.3	230.2	235.8	237.3
30°	239.6	235.8	227.1	216.3	211.1	212.6	217.4	221.6	223.4
32.5°	222.7	219.3	211.4	201.4	196.8	198.3	202.4	206.2	207.7
35°	205.1	201.4	194.6	185.5	182.6	184.1	187.8	190.9	191.5
37.5°	185.2	182.6	177.7	170.6	168.4	170.2	173.2	175.0	175.8
40°	166.8	164.5	160.5	155.1	154.5	155.9	159.0	160.1	160.5
42.5°	148.8	146.9	144.3	140.6	140.6	142.0	144.8	145.4	145.9
45°	131.5	130.5	129.4	126.3	127.1	128.9	130.5	131.5	131.5
47.5°	116.6	117.0	115.5	113.2	114.0	115.8	117.0	118.1	118.1
50°	105.0	103.8	102.4	100.1	101.2	102.7	104.2	105.0	105.3
52.5°	91.4	91.1	89.9	87.3	88.1	88.8	90.4	91.4	91.9
55°	81.7	80.6	79.1	76.0	76.0	76.8	77.6	78.3	79.1
57.5°	72.3	71.2	68.9	65.7	65.2	65.2	64.9	65.7	66.8
60°	62.9	62.6	59.2	56.3	55.1	54.0	52.4	52.9	54.4
62.5°	54.7	54.0	51.0	47.2	45.0	43.2	41.2	40.9	42.4
65°	47.2	46.4	43.2	39.3	36.7	33.3	30.4	30.4	31.5
67.5°	40.5	39.0	35.9	31.9	28.5	24.4	21.4	22.1	22.5
70°	33.8	32.7	29.3	25.1	21.0	16.8	15.0	15.4	15.4
72.5°	27.8	26.2	22.8	18.8	14.6	10.8	10.2	9.7	9.7
75°	21.7	20.2	16.8	12.8	9.0	6.3	5.6	5.6	5.6
77.5°	15.7	14.6	11.6	7.9	4.9	3.1	2.6	2.3	2.3
80°	10.8	9.7	7.1	4.1	1.9	1.1	1.1	1.1	1.1
82.5°	6.3	5.2	3.4	1.9	0.8	0.3	0.3	0.3	0.3
85°	3.1	2.3	1.5	0.8	0.3	0.3	0.3	0.3	0.3
87.5°	0.3	0.3	0.3	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)