

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582927

Luminaire Tested: **HCC6W05D010BZ-HM60525927-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582927
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W05D010BZ-HM60525927-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 560.4 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582927
CATALOG NUMBER: HCC6W05D010BZ-HM60525927-61RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P582927

CATALOG NUMBER: HCC6W05D010BZ-HM60525927-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	15679	15679	15679
5°	15843	15694	15595
10°	16065	15648	15481
15°	16442	15551	15403
20°	16597	15092	15133
25°	16235	14323	14602
30°	15382	13312	13762
35°	13920	12167	12622
40°	12123	10999	11400
45°	10288	9730	10086
50°	9108	8503	8733
55°	8028	7264	7235
60°	7203	6118	5625
65°	6421	4916	4034
70°	5658	3542	2516
75°	4766	2160	1440
80°	3662	979	600
85°	2139	189	189



TEST NUMBER: P582927
 CATALOG NUMBER: HCC6W05D010BZ-HM60525927-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.1	4.8
10°-20°	78.0	13.9
20°-30°	112.8	20.1
30°-40°	118.7	21.2
40°-50°	99.8	17.8
50°-60°	70.0	12.5
60°-70°	38.5	6.9
70°-80°	13.7	2.4
80°-90°	1.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	218.0	38.9
0°-40°	336.6	60.1
0°-60°	506.4	90.4
0°-90°	560.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	560.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	286	286	286	286	286	
5°	288	287	285	284	283	28
15°	290	285	274	271	271	82
25°	268	255	237	237	241	123
35°	208	196	182	186	189	129
45°	133	129	126	129	130	104
55°	84	79	76	76	76	76
65°	50	44	38	31	31	49
75°	22	18	10	7	7	24
85°	3	2	0	0	0	5
90°	0	0	0	0	0	



TEST NUMBER: P582927

CATALOG NUMBER: HCC6W05D010BZ-HM60525927-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	286.0	286.0	286.0	286.0	286.0	286.0	286.0	286.0	286.0
2.5°	286.0	286.0	285.7	285.7	284.9	284.9	284.5	284.5	284.5
5°	287.9	287.9	287.1	286.0	285.2	284.1	284.1	283.7	283.4
7.5°	289.1	288.6	287.5	286.0	284.1	282.3	281.5	281.9	281.5
10°	288.6	287.9	286.3	283.4	281.1	278.5	278.1	277.8	278.1
12.5°	289.4	288.3	285.2	281.5	277.8	274.8	274.4	274.4	274.8
15°	289.7	288.6	284.9	279.2	274.0	271.0	270.6	271.0	271.4
17.5°	288.6	287.1	281.5	274.0	268.0	265.0	265.0	265.8	266.6
20°	284.5	282.3	274.4	265.4	258.7	256.4	257.2	258.7	259.4
22.5°	277.0	274.4	265.4	255.3	248.1	246.2	248.1	250.1	250.7
25°	268.4	265.4	254.9	244.4	236.8	234.7	237.3	240.2	241.4
27.5°	256.7	253.3	243.6	231.6	224.2	223.1	226.0	229.4	230.2
30°	243.0	239.1	228.3	217.1	210.3	210.0	213.3	216.3	217.4
32.5°	226.0	222.6	213.3	202.0	196.1	196.1	199.4	202.0	203.2
35°	208.0	204.3	196.1	186.7	181.8	182.2	185.5	187.5	188.6
37.5°	186.7	185.5	179.2	171.3	167.9	168.7	171.3	172.8	173.9
40°	169.4	166.4	162.3	155.9	153.7	154.5	157.1	158.5	159.3
42.5°	150.7	148.8	145.4	140.9	139.4	140.6	142.8	144.0	143.6
45°	132.7	132.3	128.9	126.3	125.5	127.1	128.6	129.7	130.1
47.5°	119.6	118.1	115.0	113.2	112.4	113.9	115.5	116.2	116.2
50°	106.8	105.3	102.4	100.5	99.7	101.2	102.4	103.1	102.4
52.5°	94.1	92.5	89.9	87.7	87.3	88.1	88.5	88.8	89.6
55°	84.0	82.5	79.4	76.8	76.0	76.5	76.0	76.0	75.7
57.5°	74.2	72.8	69.7	66.7	65.7	65.2	64.1	63.7	63.4
60°	65.7	63.7	60.7	57.4	55.8	54.4	52.4	51.3	51.3
62.5°	57.4	55.5	52.1	49.2	46.9	44.2	41.2	39.8	39.8
65°	49.5	48.0	44.2	40.9	37.9	34.5	31.1	30.4	31.1
67.5°	42.0	40.5	36.7	33.3	29.6	25.5	22.5	22.5	23.3
70°	35.3	33.8	30.4	26.2	22.1	18.0	15.7	15.7	15.7
72.5°	28.8	27.3	23.6	19.9	15.7	11.6	10.5	10.8	10.5
75°	22.5	21.4	18.0	13.9	10.2	7.1	6.8	6.3	6.8
77.5°	16.8	15.7	12.8	9.0	5.6	4.1	3.7	3.7	3.7
80°	11.6	10.5	8.2	5.2	3.1	1.9	1.9	1.9	1.9
82.5°	7.1	6.0	4.5	2.6	1.1	1.1	1.1	1.1	1.1
85°	3.4	2.6	1.9	0.8	0.3	0.3	0.3	0.3	0.3
87.5°	0.8	0.8	0.3	0.3	0.0	0.3	0.3	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)