

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582935

Luminaire Tested: **HCC6W05D010MB-HM60525927-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W05D010MB-HM60525927-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 537.2 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582935
CATALOG NUMBER: HCC6W05D010MB-HM60525927-61WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P582935

CATALOG NUMBER: HCC6W05D010MB-HM60525927-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	34	44	38	33	43	37	33	43	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	15037	15037	15037
5°	15364	15034	14764
10°	15831	14896	14390
15°	16334	14699	14041
20°	16591	14147	13470
25°	16319	13307	12690
30°	15534	12331	11863
35°	14174	11129	10955
40°	12387	10004	9947
45°	10660	8807	9009
50°	9270	7667	7829
55°	8086	6729	6805
60°	7181	5833	5339
65°	6421	4916	4086
70°	5658	4023	3430
75°	4829	3177	3262
80°	3883	2715	3220
85°	2579	2327	2830



TEST NUMBER: P582935
 CATALOG NUMBER: HCC6W05D010MB-HM60525927-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.0	4.8
10°-20°	73.9	13.8
20°-30°	105.5	19.6
30°-40°	110.6	20.6
40°-50°	93.1	17.3
50°-60°	66.2	12.3
60°-70°	38.8	7.2
70°-80°	18.3	3.4
80°-90°	4.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	205.5	38.2
0°-40°	316.0	58.8
0°-60°	475.3	88.5
0°-90°	537.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	537.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	274	274	274	274	274	
5°	279	277	273	269	268	27
15°	288	277	259	248	247	81
25°	270	251	220	210	210	124
35°	212	194	166	161	164	132
45°	138	128	114	114	116	107
55°	85	78	70	70	71	76
65°	50	44	38	32	32	49
75°	23	19	15	15	15	25
85°	4	3	4	4	4	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582935

CATALOG NUMBER: HCC6W05D010MB-HM60525927-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	274.3	274.3	274.3	274.3	274.3	274.3	274.3	274.3	274.3
2.5°	274.7	274.7	274.3	273.9	273.2	272.1	271.3	270.5	270.5
5°	279.2	278.4	277.0	275.0	273.2	271.0	269.4	268.3	268.3
7.5°	283.0	281.4	278.4	275.0	271.7	268.7	266.1	264.5	264.2
10°	284.4	282.5	278.1	272.8	267.6	263.4	260.5	258.5	258.5
12.5°	285.9	283.6	277.6	270.2	263.4	257.9	254.8	253.3	252.9
15°	287.8	284.8	277.3	267.9	259.0	252.6	248.5	247.4	247.4
17.5°	287.8	284.1	274.7	263.1	251.9	244.6	240.9	239.8	240.2
20°	284.4	280.4	269.1	254.8	242.5	234.9	231.2	230.4	230.9
22.5°	278.1	273.2	260.5	245.1	231.5	223.7	220.3	220.3	220.0
25°	269.8	264.5	250.7	234.6	220.0	212.1	209.5	209.8	209.8
27.5°	259.0	253.7	239.8	222.6	208.0	200.1	198.2	199.0	199.3
30°	245.4	239.8	225.2	208.4	194.8	187.0	185.9	187.0	187.4
32.5°	228.9	224.9	210.6	193.3	180.6	173.9	173.5	174.6	176.2
35°	211.8	207.2	194.1	178.4	166.3	160.8	160.8	162.6	163.7
37.5°	193.0	188.5	176.5	163.4	153.2	148.0	148.8	150.6	151.0
40°	173.1	169.7	159.7	148.4	139.8	135.6	136.7	138.7	139.0
42.5°	154.4	151.4	143.2	133.0	126.7	123.6	125.2	127.5	128.1
45°	137.5	134.1	127.5	118.8	113.6	112.1	113.9	115.4	116.2
47.5°	122.2	119.2	113.6	105.7	101.9	101.1	103.1	103.8	104.5
50°	108.7	105.7	100.0	92.9	89.9	89.9	91.4	92.2	91.8
52.5°	95.6	92.9	87.7	81.7	79.8	79.8	80.9	81.4	82.0
55°	84.6	82.0	77.5	72.0	70.4	69.7	70.4	70.4	71.2
57.5°	74.6	72.3	68.3	62.9	61.1	60.3	60.0	59.6	60.3
60°	65.5	63.7	59.2	54.7	53.2	51.3	49.8	48.4	48.7
62.5°	57.3	55.5	51.3	46.9	45.3	42.7	40.8	39.0	39.8
65°	49.5	47.6	43.8	40.1	37.9	34.8	31.9	30.7	31.5
67.5°	42.4	40.8	37.1	33.3	31.5	28.1	25.1	25.1	25.5
70°	35.3	33.7	30.7	27.3	25.1	22.1	21.0	21.4	21.4
72.5°	28.8	27.7	24.7	21.7	19.4	17.6	17.6	18.0	18.3
75°	22.8	22.1	19.1	16.5	15.0	13.9	14.6	15.0	15.4
77.5°	17.6	16.5	14.2	12.3	11.2	11.6	12.3	12.8	13.1
80°	12.3	12.0	10.2	9.0	8.6	9.0	9.7	10.2	10.2
82.5°	7.9	7.5	6.3	6.0	6.0	6.3	7.1	7.1	7.1
85°	4.1	3.7	3.4	3.4	3.7	4.1	4.5	4.5	4.5
87.5°	1.5	1.1	1.5	1.5	1.9	1.9	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)