

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582945

Luminaire Tested: **HCC6W05D010MB-HM60525930-61RWWH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W05D010MB-HM60525930-61RWWH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 611.8 lumens  
Efficiency: N/A  
Efficacy: 102.0 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582945  
CATALOG NUMBER: HCC6W05D010MB-HM60525930-61RWWH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582945

CATALOG NUMBER: HCC6W05D010MB-HM60525930-61RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	17115	17115	17115
5°	17296	17136	17026
10°	17535	17084	16900
15°	17951	16975	16816
20°	18120	16475	16521
25°	17723	15648	15938
30°	16787	14534	15021
35°	15198	13278	13779
40°	13239	12008	12445
45°	11234	10629	11009
50°	9944	9279	9535
55°	8755	7942	7904
60°	7850	6688	6140
65°	7005	5370	4410
70°	6155	3879	2757
75°	5189	2351	1546
80°	4009	1042	631
85°	2327	314	314



TEST NUMBER: P582945  
 CATALOG NUMBER: HCC6W05D010MB-HM60525930-61RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	29.6	4.8
10°-20°	85.2	13.9
20°-30°	123.1	20.1
30°-40°	129.6	21.2
40°-50°	108.9	17.8
50°-60°	76.5	12.5
60°-70°	42.0	6.9
70°-80°	14.9	2.4
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	238.0	38.9
0°-40°	367.5	60.1
0°-60°	552.9	90.4
0°-90°	611.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	611.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	312	312	312	312	312	
5°	314	314	311	310	309	30
15°	316	311	299	296	296	89
25°	293	278	259	259	264	134
35°	227	214	198	203	206	141
45°	145	141	137	140	142	114
55°	92	87	83	83	83	82
65°	54	48	41	34	34	54
75°	24	20	11	7	7	26
85°	4	2	0	0	0	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582945

CATALOG NUMBER: HCC6W05D010MB-HM60525930-61RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	312.2	312.2	312.2	312.2	312.2	312.2	312.2	312.2	312.2
2.5°	312.2	312.2	311.8	311.8	311.0	311.0	310.6	310.6	310.6
5°	314.3	314.3	313.5	312.2	311.4	310.2	310.2	309.7	309.4
7.5°	315.5	315.0	313.9	312.2	310.2	308.2	307.4	307.7	307.4
10°	315.0	314.3	312.7	309.4	306.9	304.1	303.6	303.2	303.6
12.5°	315.9	314.7	311.4	307.4	303.2	299.9	299.6	299.6	299.9
15°	316.3	315.0	311.0	304.9	299.1	295.8	295.5	295.8	296.3
17.5°	315.0	313.5	307.4	299.1	292.6	289.3	289.3	290.2	291.0
20°	310.6	308.2	299.6	289.7	282.4	279.9	280.7	282.4	283.2
22.5°	302.4	299.6	289.7	278.7	270.9	268.8	270.9	272.9	273.8
25°	293.0	289.7	278.2	266.8	258.7	256.2	259.0	262.3	263.5
27.5°	280.4	276.6	266.0	252.9	244.8	243.5	246.8	250.4	251.2
30°	265.2	261.0	249.2	237.0	229.6	229.2	232.9	236.2	237.3
32.5°	246.8	243.1	232.9	220.6	214.0	214.0	217.8	220.6	221.8
35°	227.1	223.1	214.0	203.7	198.4	198.9	202.6	204.6	205.9
37.5°	203.7	202.6	195.6	187.0	183.3	184.2	187.0	188.6	189.8
40°	185.0	181.7	177.2	170.2	167.8	168.6	171.4	173.1	173.9
42.5°	164.5	162.5	158.8	153.9	152.2	153.5	155.9	157.2	156.7
45°	144.9	144.4	140.8	137.9	137.1	138.8	140.3	141.6	142.0
47.5°	130.5	128.9	125.7	123.6	122.7	124.4	126.0	126.9	126.9
50°	116.6	115.0	111.8	109.7	108.8	110.5	111.8	112.5	111.8
52.5°	102.7	101.0	98.2	95.7	95.4	96.2	96.6	97.0	97.7
55°	91.6	90.1	86.8	83.8	83.1	83.5	83.1	83.1	82.7
57.5°	81.0	79.4	76.2	72.9	71.6	71.2	69.9	69.6	69.2
60°	71.6	69.6	66.3	62.6	61.0	59.3	57.3	56.0	56.0
62.5°	62.6	60.6	56.8	53.6	51.2	48.3	45.0	43.4	43.4
65°	54.0	52.4	48.3	44.6	41.4	37.6	34.0	33.1	34.0
67.5°	45.9	44.2	40.1	36.4	32.3	27.8	24.5	24.5	25.4
70°	38.4	36.8	33.1	28.6	24.2	19.7	17.2	17.2	17.2
72.5°	31.5	29.8	25.8	21.7	17.2	12.7	11.4	11.9	11.4
75°	24.5	23.3	19.7	15.1	11.1	7.8	7.3	7.0	7.3
77.5°	18.4	17.2	13.9	9.8	6.1	4.5	4.1	4.1	4.1
80°	12.7	11.4	9.0	5.8	3.3	2.0	2.0	2.0	2.0
82.5°	7.8	6.6	4.9	2.8	1.2	1.2	1.2	1.2	1.2
85°	3.7	2.8	2.0	0.8	0.5	0.5	0.5	0.5	0.5
87.5°	0.8	0.8	0.5	0.5	0.0	0.5	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)