

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582963

Luminaire Tested: **HCC6S05D010BZ-HM60525935-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S05D010BZ-HM60525935-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 644.1 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582963
CATALOG NUMBER: HCC6S05D010BZ-HM60525935-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582963

CATALOG NUMBER: HCC6S05D010BZ-HM60525935-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	18019	18019	18019
5°	18209	18039	17923
10°	18464	17986	17796
15°	18899	17872	17702
20°	19077	17338	17391
25°	18660	16465	16779
30°	17667	15300	15813
35°	16001	13980	14502
40°	13933	12638	13103
45°	11823	11187	11590
50°	10473	9774	10030
55°	9223	8363	8315
60°	8267	7039	6469
65°	7368	5643	4631
70°	6491	4071	2901
75°	5486	2457	1652
80°	4199	1073	663
85°	2390	314	314



TEST NUMBER: P582963

CATALOG NUMBER: HCC6S05D010BZ-HM60525935-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.2	4.8
10°-20°	89.7	13.9
20°-30°	129.6	20.1
30°-40°	136.4	21.2
40°-50°	114.7	17.8
50°-60°	80.5	12.5
60°-70°	44.3	6.9
70°-80°	15.7	2.4
80°-90°	2.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	250.5	38.9
0°-40°	386.9	60.1
0°-60°	582.0	90.4
0°-90°	644.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	644.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	329	329	329	329	329	
5°	331	330	328	327	326	32
15°	333	327	315	311	312	94
25°	308	293	272	273	277	141
35°	239	225	209	213	217	148
45°	152	148	144	148	150	120
55°	96	91	88	88	87	87
65°	57	51	44	36	36	57
75°	26	21	12	8	8	28
85°	4	2	0	0	0	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582963

CATALOG NUMBER: HCC6S05D010BZ-HM60525935-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	328.7	328.7	328.7	328.7	328.7	328.7	328.7	328.7	328.7
2.5°	328.7	328.7	328.3	328.3	327.4	327.4	327.0	327.0	327.0
5°	330.9	330.9	330.0	328.7	327.8	326.6	326.6	326.1	325.7
7.5°	332.1	331.7	330.4	328.7	326.6	324.4	323.5	324.0	323.5
10°	331.7	330.9	329.2	325.7	323.1	320.1	319.7	319.2	319.7
12.5°	332.6	331.3	327.8	323.5	319.2	315.7	315.4	315.4	315.7
15°	333.0	331.7	327.4	320.9	314.9	311.4	311.0	311.4	311.9
17.5°	331.7	330.0	323.5	314.9	308.0	304.5	304.5	305.4	306.3
20°	327.0	324.4	315.4	305.0	297.2	294.7	295.5	297.2	298.1
22.5°	318.3	315.4	305.0	293.3	285.2	283.1	285.2	287.4	288.2
25°	308.5	305.0	292.9	280.9	272.2	269.7	272.7	276.2	277.4
27.5°	295.0	291.2	280.0	266.2	257.6	256.3	259.8	263.6	264.5
30°	279.1	274.8	262.4	249.4	241.7	241.3	245.1	248.6	249.8
32.5°	259.8	255.9	245.1	232.2	225.3	225.3	229.2	232.2	233.5
35°	239.1	234.8	225.3	214.6	208.9	209.4	213.2	215.4	216.7
37.5°	214.6	213.2	205.9	196.8	193.0	193.9	196.8	198.5	199.9
40°	194.7	191.3	186.6	179.2	176.6	177.5	180.5	182.3	183.1
42.5°	173.2	171.0	167.1	161.9	160.2	161.6	164.1	165.4	165.0
45°	152.5	152.1	148.1	145.2	144.3	146.0	147.8	149.0	149.5
47.5°	137.4	135.7	132.2	130.1	129.3	131.0	132.7	133.6	133.6
50°	122.8	121.0	117.6	115.5	114.6	116.3	117.6	118.4	117.6
52.5°	108.1	106.4	103.4	100.8	100.3	101.2	101.7	102.2	102.9
55°	96.5	94.8	91.3	88.4	87.5	87.9	87.5	87.5	87.0
57.5°	85.3	83.6	80.1	76.7	75.4	74.9	73.7	73.2	72.8
60°	75.4	73.2	69.8	65.9	64.2	62.5	60.3	59.0	59.0
62.5°	65.9	63.7	59.9	56.4	53.9	50.8	47.3	45.7	45.7
65°	56.8	55.1	50.8	47.0	43.5	39.7	35.7	34.9	35.7
67.5°	48.3	46.6	42.3	38.3	34.0	29.3	25.9	25.9	26.7
70°	40.5	38.8	34.9	30.2	25.4	20.7	18.1	18.1	18.1
72.5°	33.2	31.4	27.1	22.8	18.1	13.3	12.1	12.5	12.1
75°	25.9	24.5	20.7	15.9	11.6	8.1	7.8	7.3	7.8
77.5°	19.4	18.1	14.7	10.3	6.4	4.7	4.3	4.3	4.3
80°	13.3	12.1	9.5	6.0	3.4	2.1	2.1	2.1	2.1
82.5°	8.1	6.9	5.2	3.1	1.2	1.2	1.2	1.2	1.2
85°	3.8	3.1	2.1	0.9	0.5	0.5	0.5	0.5	0.5
87.5°	0.9	0.9	0.5	0.5	0.0	0.5	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)