

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582970

Luminaire Tested: **HCC6W05D010MW-HM60525935-61WWW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582970  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W05D010MW-HM60525935-61WWW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 596.2 lumens  
Efficiency: N/A  
Efficacy: 99.4 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582970  
CATALOG NUMBER: HCC6W05D010MW-HM60525935-61WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582970

CATALOG NUMBER: HCC6W05D010MW-HM60525935-61WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	17548	17548	17548
5°	18325	17499	16690
10°	18826	17190	15681
15°	19291	16822	14694
20°	19374	16061	13494
25°	18969	15037	12376
30°	17996	13825	11344
35°	16349	12428	10179
40°	14241	11071	9153
45°	12327	9691	8047
50°	10763	8332	7053
55°	9519	7331	6050
60°	8552	6414	5241
65°	7653	5591	5085
70°	6828	4760	4760
75°	5931	4024	4469
80°	4735	3378	4072
85°	3271	2956	3522



TEST NUMBER: P582970  
 CATALOG NUMBER: HCC6W05D010MW-HM60525935-61WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	30.1	5.0
10°-20°	83.6	14.0
20°-30°	116.5	19.5
30°-40°	120.1	20.1
40°-50°	99.5	16.7
50°-60°	71.5	12.0
60°-70°	45.5	7.6
70°-80°	23.4	3.9
80°-90°	5.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.3	38.6
0°-40°	350.3	58.8
0°-60°	521.4	87.4
0°-90°	596.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	596.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	320	320	320	320	320	
5°	333	328	318	308	303	32
15°	340	327	296	269	259	96
25°	314	292	249	217	205	144
35°	244	224	186	161	152	152
45°	159	148	125	109	104	123
55°	100	91	77	68	63	90
65°	59	52	43	38	39	59
75°	28	24	19	20	21	30
85°	5	5	5	5	6	7
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582970

CATALOG NUMBER: HCC6W05D010MW-HM60525935-61WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	320.1	320.1	320.1	320.1	320.1	320.1	320.1	320.1	320.1
2.5°	326.1	324.9	323.1	321.4	318.8	315.7	313.2	312.3	311.1
5°	333.0	331.3	327.8	323.5	318.0	312.3	307.6	304.5	303.3
7.5°	337.3	335.2	330.4	323.1	314.9	306.7	299.8	295.5	293.8
10°	338.2	336.1	329.5	319.7	308.8	297.6	289.1	283.9	281.7
12.5°	339.5	336.4	328.3	316.6	302.8	290.0	279.1	272.7	270.5
15°	339.9	336.4	327.0	312.8	296.4	280.9	269.3	261.5	258.9
17.5°	338.2	334.3	323.1	305.9	287.4	271.0	257.2	249.1	245.5
20°	332.1	327.8	314.9	295.5	275.3	258.1	243.9	235.3	231.3
22.5°	324.4	318.8	304.2	283.5	262.4	244.3	230.1	221.5	217.5
25°	313.6	308.5	292.1	270.1	248.6	229.6	216.7	207.7	204.6
27.5°	301.1	295.2	278.3	256.3	234.4	215.4	202.9	194.7	190.9
30°	284.3	278.8	261.9	240.0	218.4	200.8	187.8	180.9	179.2
32.5°	264.5	259.8	243.4	222.7	202.0	185.7	174.9	167.6	165.9
35°	244.3	238.7	224.4	205.1	185.7	171.1	161.1	154.7	152.1
37.5°	222.3	217.1	205.1	187.8	170.6	156.8	148.1	142.6	140.0
40°	199.0	195.2	184.0	170.2	154.7	142.6	135.3	130.5	127.9
42.5°	177.5	173.6	165.9	152.9	140.0	129.3	122.8	118.4	116.3
45°	159.0	155.5	147.8	136.6	125.0	115.9	109.0	106.0	103.8
47.5°	140.5	138.8	131.9	121.5	110.7	102.9	98.2	94.8	93.0
50°	126.2	124.1	117.6	106.8	97.7	91.8	87.5	84.4	82.7
52.5°	111.5	109.4	103.4	94.4	87.0	81.5	77.1	74.6	72.8
55°	99.6	97.7	91.3	83.2	76.7	72.0	68.0	65.1	63.3
57.5°	88.4	86.6	80.6	72.8	67.2	62.9	59.4	56.8	54.7
60°	78.0	76.7	70.6	63.3	58.5	54.2	51.3	49.2	47.8
62.5°	68.9	66.3	61.1	54.7	50.4	47.0	44.0	42.6	43.5
65°	59.0	57.7	52.5	47.0	43.1	39.7	37.5	38.3	39.2
67.5°	50.8	49.2	44.7	39.7	36.2	33.6	32.3	34.0	34.5
70°	42.6	40.9	37.1	32.8	29.7	28.0	28.0	29.3	29.7
72.5°	34.9	33.6	30.2	26.7	24.5	23.3	24.1	25.0	25.4
75°	28.0	26.7	24.1	21.1	19.0	19.0	19.8	20.7	21.1
77.5°	21.6	20.7	18.1	15.9	15.0	15.0	15.9	16.4	16.8
80°	15.0	14.2	12.9	11.6	10.7	11.6	12.5	12.5	12.9
82.5°	9.9	9.5	8.6	7.8	7.8	8.1	8.6	9.0	9.0
85°	5.2	5.2	4.7	4.3	4.7	5.2	5.2	5.6	5.6
87.5°	1.7	1.7	1.7	1.7	2.1	2.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)