

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593015

Luminaire Tested: **HCC6W05D010BZ-HM60525950-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593015
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W05D010BZ-HM60525950-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 625.1 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593015
CATALOG NUMBER: HCC6W05D010BZ-HM60525950-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593015

CATALOG NUMBER: HCC6W05D010BZ-HM60525950-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17499	17499	17499
5°	17879	17494	17180
10°	18425	17329	16750
15°	19007	17100	16334
20°	19310	16463	15670
25°	18987	15479	14771
30°	18085	14357	13800
35°	16483	12956	12749
40°	14420	11636	11579
45°	12404	10241	10474
50°	10780	8921	9108
55°	9414	7828	7914
60°	8366	6787	6217
65°	7459	5720	4748
70°	6572	4696	3991
75°	5634	3685	3791
80°	4546	3189	3725
85°	2956	2768	3271



TEST NUMBER: P593015
 CATALOG NUMBER: HCC6W05D010BZ-HM60525950-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.2	4.8
10°-20°	86.0	13.8
20°-30°	122.8	19.6
30°-40°	128.6	20.6
40°-50°	108.3	17.3
50°-60°	77.1	12.3
60°-70°	45.1	7.2
70°-80°	21.4	3.4
80°-90°	5.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.1	38.2
0°-40°	367.7	58.8
0°-60°	553.1	88.5
0°-90°	625.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	625.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	319	319	319	319	319	
5°	325	322	318	314	312	31
15°	335	323	301	289	288	95
25°	314	292	256	244	244	144
35°	246	226	194	187	190	153
45°	160	148	132	132	135	124
55°	98	90	82	82	83	89
65°	58	51	44	37	37	57
75°	27	22	17	17	18	29
85°	5	4	4	5	5	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593015

CATALOG NUMBER: HCC6W05D010BZ-HM60525950-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	319.2	319.2	319.2	319.2	319.2	319.2	319.2	319.2	319.2
2.5°	319.7	319.7	319.2	318.8	317.9	316.6	315.7	314.8	314.8
5°	324.9	324.0	322.3	320.0	317.9	315.3	313.6	312.2	312.2
7.5°	329.2	327.5	324.0	320.0	316.2	312.7	309.6	307.8	307.5
10°	331.0	328.8	323.5	317.4	311.3	306.6	303.1	300.9	300.9
12.5°	332.7	330.1	323.1	314.4	306.6	300.0	296.5	294.8	294.4
15°	334.9	331.4	322.7	311.8	301.3	293.9	289.1	287.8	287.8
17.5°	334.9	330.5	319.7	306.1	293.0	284.8	280.4	279.1	279.6
20°	331.0	326.1	313.1	296.5	282.2	273.5	269.1	268.1	268.6
22.5°	323.5	317.9	303.1	285.2	269.5	260.4	256.4	256.4	255.9
25°	313.9	307.8	291.8	273.0	255.9	246.8	243.7	244.2	244.2
27.5°	301.3	295.2	279.1	259.0	242.0	232.9	230.6	231.5	232.0
30°	285.7	279.1	262.0	242.5	226.8	217.6	216.3	217.6	218.0
32.5°	266.5	261.6	245.1	225.0	210.2	202.4	201.9	203.2	205.0
35°	246.3	241.1	225.9	207.6	193.6	187.0	187.0	189.3	190.5
37.5°	224.5	219.3	205.4	190.1	178.3	172.2	173.1	175.3	175.7
40°	201.5	197.5	185.8	172.7	162.6	157.9	159.1	161.4	161.8
42.5°	179.7	176.2	166.6	154.8	147.4	143.8	145.7	148.3	149.2
45°	160.0	156.1	148.3	138.2	132.1	130.4	132.5	134.4	135.1
47.5°	142.2	138.7	132.1	122.9	118.6	117.7	119.9	120.8	121.7
50°	126.4	122.9	116.4	108.1	104.6	104.6	106.4	107.2	106.8
52.5°	111.2	108.1	102.0	95.0	92.9	92.9	94.2	94.6	95.5
55°	98.5	95.5	90.3	83.7	81.9	81.1	81.9	81.9	82.8
57.5°	86.8	84.2	79.3	73.2	71.1	70.2	69.7	69.4	70.2
60°	76.3	74.1	68.9	63.6	61.9	59.8	58.0	56.3	56.7
62.5°	66.7	64.5	59.8	54.5	52.8	49.7	47.6	45.3	46.2
65°	57.5	55.4	51.0	46.7	44.1	40.6	37.1	35.7	36.6
67.5°	49.3	47.6	43.2	38.8	36.6	32.7	29.3	29.3	29.6
70°	41.0	39.2	35.7	31.9	29.3	25.8	24.4	24.9	24.9
72.5°	33.6	32.3	28.8	25.3	22.7	20.5	20.5	20.9	21.4
75°	26.6	25.8	22.3	19.2	17.4	16.2	17.0	17.4	17.9
77.5°	20.5	19.2	16.6	14.4	13.1	13.6	14.4	14.8	15.3
80°	14.4	13.9	11.8	10.5	10.1	10.5	11.3	11.8	11.8
82.5°	9.2	8.7	7.5	7.0	7.0	7.5	8.2	8.2	8.2
85°	4.7	4.4	4.0	4.0	4.4	4.7	5.2	5.2	5.2
87.5°	1.7	1.4	1.7	1.7	2.1	2.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)