

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583295

Luminaire Tested: **HCC6S07D010MB-HM60525827-61WWWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583295  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S07D010MB-HM60525827-61WWWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 842.0 lumens  
Efficiency: N/A  
Efficacy: 105.2 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583295  
CATALOG NUMBER: HCC6S07D010MB-HM60525827-61WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P583295

CATALOG NUMBER: HCC6S07D010MB-HM60525827-61WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	23573	23573	23573
5°	24081	23564	23145
10°	24816	23341	22561
15°	25596	23031	21998
20°	26007	22169	21107
25°	25574	20856	19894
30°	24352	19338	18591
35°	22212	17454	17172
40°	19422	15679	15594
45°	16707	13800	14118
50°	14524	12017	12273
55°	12692	10561	10666
60°	11271	9144	8377
65°	10053	7705	6395
70°	8848	6299	5353
75°	7583	4978	5105
80°	6125	4262	5020
85°	4088	3711	4403



TEST NUMBER: P583295  
 CATALOG NUMBER: HCC6S07D010MB-HM60525827-61WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.7	4.8
10°-20°	115.9	13.8
20°-30°	165.4	19.6
30°-40°	173.3	20.6
40°-50°	145.9	17.3
50°-60°	103.8	12.3
60°-70°	60.8	7.2
70°-80°	28.8	3.4
80°-90°	7.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	322.0	38.2
0°-40°	495.3	58.8
0°-60°	745.0	88.5
0°-90°	842.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	842.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	430	430	430	430	430	
5°	438	434	428	422	421	42
15°	451	435	406	389	388	127
25°	423	393	345	328	329	194
35°	332	304	261	252	257	206
45°	216	200	178	179	182	167
55°	133	122	110	110	112	120
65°	78	69	59	50	49	77
75°	36	30	24	23	24	38
85°	6	5	6	7	7	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583295

CATALOG NUMBER: HCC6S07D010MB-HM60525827-61WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	430.0	430.0	430.0	430.0	430.0	430.0	430.0	430.0	430.0
2.5°	430.5	430.5	430.0	429.3	428.2	426.5	425.2	424.1	424.1
5°	437.6	436.4	434.1	431.1	428.2	424.6	422.3	420.6	420.6
7.5°	443.5	441.1	436.4	431.1	425.8	421.1	417.1	414.7	414.1
10°	445.8	442.9	435.8	427.6	419.3	412.9	408.2	405.3	405.3
12.5°	448.1	444.6	435.2	423.5	412.9	404.1	399.4	397.0	396.4
15°	451.0	446.4	434.6	419.9	405.8	395.9	389.4	387.6	387.6
17.5°	451.0	445.2	430.5	412.3	394.7	383.5	377.6	375.9	376.5
20°	445.8	439.4	421.7	399.4	380.0	368.2	362.3	361.2	361.8
22.5°	435.8	428.2	408.2	384.1	363.0	350.7	345.3	345.3	344.8
25°	422.8	414.7	392.9	367.7	344.8	332.4	328.3	328.9	328.9
27.5°	405.8	397.7	375.9	348.9	326.0	313.6	310.7	311.9	312.5
30°	384.7	375.9	353.0	326.5	305.5	293.1	291.3	293.1	293.7
32.5°	358.8	352.4	330.0	303.1	283.1	272.5	271.9	273.7	276.0
35°	331.9	324.8	304.2	279.6	260.8	252.0	252.0	254.9	256.6
37.5°	302.5	295.5	276.7	256.1	240.2	232.0	233.2	236.1	236.7
40°	271.4	266.0	250.2	232.6	219.1	212.7	214.4	217.3	217.9
42.5°	242.0	237.3	224.3	208.5	198.5	193.9	196.1	199.7	200.9
45°	215.5	210.3	199.7	186.2	178.0	175.6	178.6	180.9	182.1
47.5°	191.5	186.7	178.0	165.6	159.8	158.6	161.6	162.7	163.8
50°	170.3	165.6	156.8	145.7	140.9	140.9	143.3	144.5	143.9
52.5°	149.8	145.7	137.4	128.0	125.1	125.1	126.9	127.5	128.6
55°	132.8	128.6	121.6	112.7	110.5	109.2	110.5	110.5	111.6
57.5°	116.9	113.3	106.8	98.7	95.7	94.6	93.9	93.4	94.6
60°	102.8	99.8	92.8	85.8	83.4	80.4	78.1	75.8	76.4
62.5°	89.8	86.9	80.4	73.4	71.0	67.0	64.0	61.1	62.2
65°	77.5	74.6	68.8	62.9	59.4	54.6	50.0	48.2	49.3
67.5°	66.4	64.0	58.1	52.2	49.3	44.1	39.3	39.3	40.0
70°	55.2	52.9	48.2	42.8	39.3	34.7	32.9	33.4	33.4
72.5°	45.2	43.5	38.7	34.1	30.6	27.6	27.6	28.2	28.8
75°	35.8	34.7	29.9	25.8	23.5	21.8	22.9	23.5	24.1
77.5°	27.6	25.8	22.3	19.4	17.7	18.2	19.4	19.9	20.5
80°	19.4	18.8	15.9	14.0	13.5	14.0	15.3	15.9	15.9
82.5°	12.3	11.8	10.0	9.4	9.4	10.0	11.1	11.1	11.1
85°	6.5	5.9	5.3	5.3	5.9	6.5	7.0	7.0	7.0
87.5°	2.4	1.8	2.4	2.4	2.9	2.9	2.9	2.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)