

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583286

Luminaire Tested: **HCC6W07D010SL-HM60525827-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583286
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W07D010SL-HM60525827-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 875.4 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583286
CATALOG NUMBER: HCC6W07D010SL-HM60525827-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583286

CATALOG NUMBER: HCC6W07D010SL-HM60525827-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	23770	23770	23770
5°	23894	24020	24020
10°	24565	24137	24042
15°	25341	24274	24274
20°	25640	23720	24269
25°	25132	22532	23602
30°	23769	20940	22168
35°	21509	19153	20090
40°	18714	17325	17998
45°	15986	15443	15986
50°	14029	13526	14081
55°	12243	11402	11851
60°	10822	9462	9341
65°	9599	7472	6408
70°	8479	5273	3863
75°	7223	2965	1864
80°	5367	916	568
85°	2893	377	377



TEST NUMBER: P583286
 CATALOG NUMBER: HCC6W07D010SL-HM60525827-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	4.8
10°-20°	121.7	13.9
20°-30°	177.7	20.3
30°-40°	186.4	21.3
40°-50°	157.0	17.9
50°-60°	110.0	12.6
60°-70°	59.0	6.7
70°-80°	19.8	2.3
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.0	39.0
0°-40°	527.4	60.3
0°-60°	794.5	90.8
0°-90°	875.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	434	434	434	434	434	
5°	434	436	436	436	436	42
15°	446	441	428	425	428	126
25°	416	398	372	379	390	190
35°	321	305	286	294	300	200
45°	206	203	199	204	206	161
55°	128	124	119	122	124	115
65°	74	68	58	48	49	74
75°	34	26	14	9	9	36
85°	5	2	1	1	1	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583286

CATALOG NUMBER: HCC6W07D010SL-HM60525827-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	433.6	433.6	433.6	433.6	433.6	433.6	433.6	433.6	433.6
2.5°	430.7	430.7	431.9	433.0	434.2	434.2	434.8	435.4	434.8
5°	434.2	434.2	436.0	436.5	436.5	436.0	436.5	436.5	436.5
7.5°	439.5	438.4	438.9	437.8	436.5	436.0	435.4	435.4	435.4
10°	441.3	440.1	438.9	436.5	433.6	431.9	431.3	431.9	431.9
12.5°	443.6	442.4	439.5	434.8	431.3	428.4	427.7	429.0	429.0
15°	446.5	445.4	440.7	433.0	427.7	424.9	425.4	426.6	427.7
17.5°	446.5	444.2	436.5	426.6	420.1	417.2	419.5	422.5	424.2
20°	439.5	437.1	426.6	414.2	406.6	404.8	408.9	414.2	416.0
22.5°	430.1	425.4	413.1	398.4	390.2	390.2	396.0	402.4	404.8
25°	415.5	411.8	397.8	380.8	372.5	372.0	379.0	387.8	390.2
27.5°	398.9	394.3	379.0	361.3	352.6	353.2	360.7	369.6	372.0
30°	375.5	369.6	356.1	339.0	330.8	333.1	340.8	347.3	350.2
32.5°	349.1	343.8	331.4	315.5	308.5	310.8	317.2	323.1	325.5
35°	321.4	315.5	305.0	290.8	286.2	288.5	294.4	299.1	300.2
37.5°	290.3	286.2	278.5	267.4	263.9	266.7	271.5	274.4	275.5
40°	261.5	258.0	251.5	243.3	242.1	244.4	249.1	250.8	251.5
42.5°	233.3	230.3	226.3	220.4	220.4	222.7	226.8	228.0	228.5
45°	206.2	204.5	202.7	198.0	199.2	202.1	204.5	206.2	206.2
47.5°	182.8	183.3	180.9	177.4	178.7	181.5	183.3	185.1	185.1
50°	164.5	162.8	160.4	156.9	158.6	161.0	163.4	164.5	165.1
52.5°	143.3	142.8	141.1	136.9	138.1	139.2	141.6	143.3	144.0
55°	128.1	126.3	124.0	119.3	119.3	120.4	121.7	122.8	124.0
57.5°	113.4	111.6	108.1	102.9	102.2	102.2	101.6	102.9	104.6
60°	98.7	98.1	92.8	88.1	86.3	84.6	82.3	82.8	85.2
62.5°	85.8	84.6	79.9	74.0	70.5	67.5	64.6	64.0	66.4
65°	74.0	72.9	67.5	61.7	57.6	52.3	47.6	47.6	49.4
67.5°	63.4	61.1	56.4	50.0	44.6	38.2	33.5	34.7	35.2
70°	52.9	51.1	45.9	39.3	32.9	26.4	23.5	24.1	24.1
72.5°	43.5	41.1	35.8	29.3	22.9	17.0	15.9	15.3	15.3
75°	34.1	31.7	26.4	19.9	14.0	10.0	8.8	8.8	8.8
77.5°	24.7	22.9	18.2	12.3	7.6	4.6	4.1	3.5	3.5
80°	17.0	15.3	11.2	6.5	2.9	1.8	1.8	1.8	1.8
82.5°	10.0	8.3	5.3	2.9	1.1	0.6	0.6	0.6	0.6
85°	4.6	3.5	2.4	1.1	0.6	0.6	0.6	0.6	0.6
87.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)