

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583322

Luminaire Tested: **HCC6S07D010MB-HM60525835-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583322
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010MB-HM60525835-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 956.7 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583322
CATALOG NUMBER: HCC6S07D010MB-HM60525835-61RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P583322

CATALOG NUMBER: HCC6S07D010MB-HM60525835-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68			68
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60			60
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			53
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47			47
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42			42
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	25974	25974	25974
5°	26112	26255	26255
10°	26842	26374	26269
15°	27696	26533	26533
20°	28020	25926	26521
25°	27461	24624	25786
30°	25972	22883	24225
35°	23503	20927	21957
40°	20445	18935	19673
45°	17475	16870	17475
50°	15334	14780	15385
55°	13371	12454	12951
60°	11830	10350	10208
65°	10494	8159	6992
70°	9264	5754	4215
75°	7900	3262	2033
80°	5872	1010	600
85°	3208	440	440



TEST NUMBER: P583322
 CATALOG NUMBER: HCC6S07D010MB-HM60525835-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	4.8
10°-20°	133.0	13.9
20°-30°	194.2	20.3
30°-40°	203.7	21.3
40°-50°	171.6	17.9
50°-60°	120.2	12.6
60°-70°	64.5	6.7
70°-80°	21.6	2.3
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.7	39.0
0°-40°	576.4	60.2
0°-60°	868.2	90.8
0°-90°	956.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	956.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	474	474	474	474	474	
5°	474	476	477	477	477	46
15°	488	482	468	465	468	138
25°	454	435	407	414	426	208
35°	351	333	313	322	328	218
45°	225	222	218	223	225	176
55°	140	136	130	133	136	126
65°	81	74	63	52	54	81
75°	37	29	15	10	10	40
85°	5	3	1	1	1	7
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583322

CATALOG NUMBER: HCC6S07D010MB-HM60525835-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	473.8	473.8	473.8	473.8	473.8	473.8	473.8	473.8	473.8
2.5°	470.6	470.6	471.9	473.3	474.5	474.5	475.2	475.7	475.2
5°	474.5	474.5	476.4	477.1	477.1	476.4	477.1	477.1	477.1
7.5°	480.3	479.0	479.6	478.4	477.1	476.4	475.7	475.7	475.7
10°	482.2	481.0	479.6	477.1	473.8	471.9	471.3	471.9	471.9
12.5°	484.8	483.5	480.3	475.2	471.3	468.0	467.5	468.7	468.7
15°	488.0	486.7	481.5	473.3	467.5	464.2	464.9	466.1	467.5
17.5°	488.0	485.4	477.1	466.1	459.1	455.9	458.4	461.7	463.6
20°	480.3	477.7	466.1	452.6	444.4	442.4	446.9	452.6	454.6
22.5°	470.0	464.9	451.4	435.3	426.3	426.3	432.8	439.8	442.4
25°	454.0	450.1	434.7	416.0	407.1	406.4	414.1	423.7	426.3
27.5°	436.0	430.9	414.1	394.9	385.2	385.9	394.3	403.9	406.4
30°	410.3	403.9	389.1	370.5	361.5	364.0	372.4	379.4	382.7
32.5°	381.4	375.6	362.1	344.8	337.1	339.7	346.7	353.2	355.8
35°	351.2	344.8	333.2	317.8	312.7	315.3	321.7	326.9	328.1
37.5°	317.2	312.7	304.3	292.2	288.3	291.5	296.6	299.9	301.2
40°	285.7	281.9	274.9	265.8	264.6	267.2	272.3	274.2	274.9
42.5°	254.9	251.8	247.2	240.8	240.8	243.4	247.9	249.1	249.8
45°	225.4	223.4	221.5	216.4	217.6	220.8	223.4	225.4	225.4
47.5°	199.6	200.3	197.7	193.9	195.2	198.4	200.3	202.2	202.2
50°	179.8	177.9	175.3	171.4	173.3	176.0	178.4	179.8	180.4
52.5°	156.7	156.0	154.1	149.6	150.9	152.2	154.8	156.7	157.3
55°	139.9	138.0	135.5	130.3	130.3	131.7	132.9	134.1	135.5
57.5°	124.0	122.0	118.2	112.4	111.7	111.7	111.0	112.4	114.3
60°	107.9	107.2	101.4	96.3	94.4	92.5	89.8	90.5	93.1
62.5°	93.7	92.5	87.4	80.9	77.0	73.9	70.6	70.0	72.5
65°	80.9	79.6	73.9	67.4	62.9	57.1	52.0	52.0	53.9
67.5°	69.3	66.7	61.6	54.6	48.8	41.7	36.6	37.8	38.5
70°	57.8	55.9	50.1	43.1	35.9	28.9	25.7	26.3	26.3
72.5°	47.5	45.0	39.2	32.1	25.0	18.6	17.3	16.7	16.7
75°	37.3	34.7	28.9	21.9	15.4	10.9	9.6	9.6	9.6
77.5°	27.0	25.0	19.9	13.5	8.4	5.1	4.5	3.9	3.9
80°	18.6	16.7	12.2	7.0	3.2	1.9	1.9	1.9	1.9
82.5°	10.9	9.0	5.8	3.2	1.2	0.7	0.7	0.7	0.7
85°	5.1	3.9	2.6	1.2	0.7	0.7	0.7	0.7	0.7
87.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)