

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583323

Luminaire Tested: **HCC6S07D010SL-HM60525835-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583323
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010SL-HM60525835-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 959.9 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583323
CATALOG NUMBER: HCC6S07D010SL-HM60525835-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583323

CATALOG NUMBER: HCC6S07D010SL-HM60525835-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77					77			
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	26856	26856	26856
5°	27135	26882	26711
10°	27516	26803	26519
15°	28167	26635	26385
20°	28428	25844	25914
25°	27806	24540	25005
30°	26333	22801	23573
35°	23845	20833	21609
40°	20767	18835	19522
45°	17622	16668	17265
50°	15607	14558	14950
55°	13744	12454	12396
60°	12324	10482	9637
65°	10987	8406	6914
70°	9681	6059	4328
75°	8155	3664	2457
80°	6282	1610	1010
85°	3648	440	440



TEST NUMBER: P583323
 CATALOG NUMBER: HCC6S07D010SL-HM60525835-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	4.8
10°-20°	133.6	13.9
20°-30°	193.2	20.1
30°-40°	203.3	21.2
40°-50°	170.9	17.8
50°-60°	119.9	12.5
60°-70°	66.0	6.9
70°-80°	23.4	2.4
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	373.3	38.9
0°-40°	576.6	60.1
0°-60°	867.4	90.4
0°-90°	959.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	959.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	490	490	490	490	490	
5°	493	492	488	487	485	47
15°	496	488	469	464	465	140
25°	460	436	406	406	413	210
35°	356	336	311	318	323	221
45°	227	221	215	220	223	178
55°	144	136	130	130	130	129
65°	85	76	65	53	53	84
75°	38	31	17	12	12	41
85°	6	3	1	1	1	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583323

CATALOG NUMBER: HCC6S07D010SL-HM60525835-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	489.9	489.9	489.9	489.9	489.9	489.9	489.9	489.9	489.9
2.5°	489.9	489.9	489.2	489.2	488.0	488.0	487.3	487.3	487.3
5°	493.1	493.1	491.8	489.9	488.5	486.6	486.6	486.1	485.4
7.5°	495.0	494.3	492.4	489.9	486.6	483.5	482.2	482.8	482.2
10°	494.3	493.1	490.5	485.4	481.5	477.0	476.4	475.7	476.4
12.5°	495.7	493.8	488.5	482.2	475.7	470.6	470.0	470.0	470.6
15°	496.3	494.3	488.0	478.4	469.3	464.2	463.5	464.2	464.9
17.5°	494.3	491.8	482.2	469.3	459.1	453.9	453.9	455.2	456.5
20°	487.3	483.5	470.0	454.6	443.0	439.2	440.4	443.0	444.2
22.5°	474.5	470.0	454.6	437.2	425.0	421.8	425.0	428.3	429.5
25°	459.7	454.6	436.5	418.6	405.7	401.9	406.4	411.5	413.4
27.5°	439.8	434.1	417.3	396.8	384.0	382.0	387.1	392.9	394.2
30°	416.0	409.6	391.0	371.7	360.2	359.5	365.3	370.5	372.4
32.5°	387.1	381.4	365.3	346.0	335.8	335.8	341.6	346.0	347.9
35°	356.3	349.9	335.8	319.7	311.3	312.0	317.8	321.0	322.9
37.5°	319.7	317.8	306.9	293.4	287.7	288.9	293.4	295.9	297.9
40°	290.2	285.1	278.0	267.0	263.2	264.6	269.0	271.6	272.8
42.5°	258.1	254.9	249.1	241.4	238.8	240.8	244.6	246.5	245.9
45°	227.3	226.6	220.8	216.4	215.0	217.6	220.3	222.2	222.7
47.5°	204.8	202.2	197.1	193.9	192.6	195.2	197.7	199.1	199.1
50°	183.0	180.4	175.3	172.1	170.7	173.3	175.3	176.5	175.3
52.5°	161.1	158.6	154.1	150.2	149.6	150.9	151.5	152.2	153.4
55°	143.8	141.3	136.1	131.7	130.3	131.0	130.3	130.3	129.7
57.5°	127.1	124.5	119.4	114.3	112.4	111.7	109.8	109.1	108.5
60°	112.4	109.1	104.0	98.2	95.6	93.1	89.8	87.9	87.9
62.5°	98.2	95.1	89.3	84.1	80.2	75.8	70.6	68.1	68.1
65°	84.7	82.1	75.8	70.0	64.8	59.0	53.3	52.0	53.3
67.5°	71.9	69.3	62.9	57.1	50.8	43.6	38.5	38.5	39.8
70°	60.4	57.8	52.0	45.0	37.8	30.8	27.0	27.0	27.0
72.5°	49.4	46.9	40.4	34.0	27.0	19.9	18.0	18.6	18.0
75°	38.5	36.6	30.8	23.8	17.3	12.2	11.6	10.9	11.6
77.5°	28.9	27.0	21.9	15.4	9.6	7.0	6.5	6.5	6.5
80°	19.9	18.0	14.2	9.0	5.1	3.2	3.2	3.2	3.2
82.5°	12.2	10.3	7.7	4.5	1.9	1.9	1.9	1.9	1.9
85°	5.8	4.5	3.2	1.2	0.7	0.7	0.7	0.7	0.7
87.5°	1.2	1.2	0.7	0.7	0.0	0.7	0.7	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)