

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583331

Luminaire Tested: **HCC6S07D010SL-HM60525835-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010SL-HM60525835-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 920.1 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583331
CATALOG NUMBER: HCC6S07D010SL-HM60525835-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583331

CATALOG NUMBER: HCC6S07D010SL-HM60525835-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	25760	25760	25760
5°	26310	25748	25286
10°	27120	25512	24654
15°	27980	25170	24041
20°	28422	24222	23067
25°	27957	22786	21739
30°	26605	21130	20313
35°	24273	19066	18772
40°	21218	17132	17046
45°	18265	15071	15428
50°	15880	13142	13415
55°	13859	11536	11651
60°	12313	9988	9144
65°	10987	8406	6992
70°	9665	6908	5866
75°	8303	5443	5571
80°	6693	4641	5462
85°	4403	4088	4843



TEST NUMBER: P583331

CATALOG NUMBER: HCC6S07D010SL-HM60525835-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.5	4.8
10°-20°	126.6	13.8
20°-30°	180.8	19.6
30°-40°	189.4	20.6
40°-50°	159.4	17.3
50°-60°	113.5	12.3
60°-70°	66.4	7.2
70°-80°	31.4	3.4
80°-90°	8.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	351.9	38.2
0°-40°	541.2	58.8
0°-60°	814.1	88.5
0°-90°	920.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	920.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	470	470	470	470	470	
5°	478	474	468	462	460	46
15°	493	475	444	426	424	139
25°	462	429	377	359	359	212
35°	363	332	285	275	280	225
45°	236	218	194	195	199	183
55°	145	133	121	121	122	131
65°	85	75	65	55	54	84
75°	39	33	26	25	26	42
85°	7	6	6	8	8	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583331

CATALOG NUMBER: HCC6S07D010SL-HM60525835-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9
2.5°	470.4	470.4	469.9	469.2	467.9	466.0	464.6	463.4	463.4
5°	478.1	476.9	474.3	471.1	467.9	464.1	461.5	459.5	459.5
7.5°	484.6	482.0	476.9	471.1	465.3	460.2	455.7	453.1	452.5
10°	487.2	483.9	476.2	467.2	458.3	451.2	446.1	442.9	442.9
12.5°	489.7	485.8	475.6	462.7	451.2	441.5	436.4	433.8	433.3
15°	493.0	487.8	475.0	458.9	443.5	432.6	425.6	423.6	423.6
17.5°	493.0	486.5	470.4	450.6	431.3	419.1	412.6	410.7	411.4
20°	487.2	480.1	460.8	436.4	415.2	402.4	396.0	394.7	395.4
22.5°	476.2	467.9	446.1	419.8	396.7	383.2	377.4	377.4	376.7
25°	462.2	453.1	429.4	401.8	376.7	363.2	358.8	359.4	359.4
27.5°	443.5	434.5	410.7	381.3	356.2	342.7	339.6	340.8	341.5
30°	420.3	410.7	385.8	356.9	333.8	320.3	318.4	320.3	320.9
32.5°	392.1	385.1	360.7	331.2	309.3	297.8	297.2	299.1	301.6
35°	362.7	355.0	332.4	305.5	284.9	275.3	275.3	278.6	280.5
37.5°	330.5	322.8	302.3	279.9	262.5	253.6	254.8	258.0	258.7
40°	296.5	290.7	273.4	254.1	239.4	232.4	234.3	237.5	238.2
42.5°	264.4	259.3	245.2	227.8	217.0	211.8	214.4	218.2	219.5
45°	235.6	229.8	218.2	203.5	194.4	191.9	195.1	197.7	199.0
47.5°	209.3	204.1	194.4	180.9	174.6	173.3	176.5	177.8	179.0
50°	186.2	180.9	171.4	159.2	154.1	154.1	156.6	157.9	157.3
52.5°	163.7	159.2	150.2	139.9	136.8	136.8	138.7	139.2	140.6
55°	145.0	140.6	132.9	123.3	120.7	119.4	120.7	120.7	121.9
57.5°	127.7	123.8	116.8	107.9	104.6	103.3	102.6	102.1	103.3
60°	112.3	109.1	101.4	93.7	91.1	87.9	85.3	82.8	83.4
62.5°	98.2	94.9	87.9	80.2	77.6	73.2	69.9	66.7	68.0
65°	84.7	81.5	75.1	68.7	64.8	59.7	54.6	52.7	53.9
67.5°	72.5	69.9	63.6	57.1	53.9	48.2	43.1	43.1	43.6
70°	60.3	57.8	52.7	46.9	43.1	37.8	35.9	36.6	36.6
72.5°	49.4	47.5	42.4	37.3	33.4	30.1	30.1	30.8	31.5
75°	39.2	37.8	32.7	28.2	25.7	23.8	25.0	25.7	26.3
77.5°	30.1	28.2	24.4	21.2	19.3	19.9	21.2	21.9	22.4
80°	21.2	20.5	17.3	15.4	14.7	15.4	16.7	17.3	17.3
82.5°	13.5	12.8	10.9	10.3	10.3	10.9	12.2	12.2	12.2
85°	7.0	6.5	5.8	5.8	6.5	7.0	7.7	7.7	7.7
87.5°	2.6	1.9	2.6	2.6	3.2	3.2	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)