

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583358

Luminaire Tested: **HCC6S07D010MB-HM60525927-61RWWC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583358  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S07D010MB-HM60525927-61RWWC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 739.3 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583358  
CATALOG NUMBER: HCC6S07D010MB-HM60525927-61RWWC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583358

CATALOG NUMBER: HCC6S07D010MB-HM60525927-61RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88																			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68																			
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60																			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53																			
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47																			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35																			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	20075	20075	20075
5°	20185	20289	20289
10°	20741	20385	20301
15°	21408	20500	20500
20°	21655	20033	20494
25°	21219	19029	19931
30°	20073	17686	18718
35°	18170	16175	16972
40°	15801	14627	15200
45°	13498	13048	13498
50°	11846	11428	11897
55°	10341	9625	10007
60°	9144	8004	7883
65°	8107	6304	5409
70°	7149	4456	3270
75°	6100	2521	1589
80°	4546	789	474
85°	2516	314	314



TEST NUMBER: P583358  
 CATALOG NUMBER: HCC6S07D010MB-HM60525927-61RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.1	4.8
10°-20°	102.8	13.9
20°-30°	150.1	20.3
30°-40°	157.4	21.3
40°-50°	132.6	17.9
50°-60°	92.9	12.6
60°-70°	49.8	6.7
70°-80°	16.7	2.3
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	288.0	39.0
0°-40°	445.4	60.2
0°-60°	671.0	90.8
0°-90°	739.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	739.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	366	366	366	366	366	
5°	367	368	369	369	369	35
15°	377	372	361	359	361	106
25°	351	336	315	320	330	161
35°	272	258	242	249	254	168
45°	174	171	168	173	174	136
55°	108	105	101	103	105	97
65°	62	57	49	40	42	62
75°	29	22	12	8	8	31
85°	4	2	0	0	0	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583358

CATALOG NUMBER: HCC6S07D010MB-HM60525927-61RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	366.2	366.2	366.2	366.2	366.2	366.2	366.2	366.2	366.2
2.5°	363.7	363.7	364.7	365.7	366.8	366.8	367.2	367.7	367.2
5°	366.8	366.8	368.2	368.7	368.7	368.2	368.7	368.7	368.7
7.5°	371.2	370.2	370.7	369.7	368.7	368.2	367.7	367.7	367.7
10°	372.6	371.6	370.7	368.7	366.2	364.7	364.3	364.7	364.7
12.5°	374.7	373.7	371.2	367.2	364.3	361.8	361.2	362.2	362.2
15°	377.2	376.2	372.2	365.7	361.2	358.8	359.3	360.3	361.2
17.5°	377.2	375.1	368.7	360.3	354.9	352.4	354.3	356.8	358.3
20°	371.2	369.2	360.3	349.9	343.4	341.9	345.3	349.9	351.3
22.5°	363.2	359.3	348.9	336.4	329.5	329.5	334.5	339.9	341.9
25°	350.8	347.8	335.9	321.5	314.6	314.1	320.1	327.6	329.5
27.5°	337.0	333.0	320.1	305.2	297.8	298.2	304.7	312.1	314.1
30°	317.1	312.1	300.7	286.3	279.4	281.3	287.8	293.2	295.7
32.5°	294.8	290.3	279.9	266.5	260.5	262.5	268.0	272.9	274.9
35°	271.5	266.5	257.5	245.6	241.7	243.6	248.6	252.5	253.6
37.5°	245.2	241.7	235.2	225.8	222.9	225.2	229.2	231.7	232.7
40°	220.8	217.9	212.4	205.4	204.4	206.4	210.4	211.9	212.4
42.5°	197.0	194.5	191.0	186.0	186.0	188.1	191.6	192.5	193.1
45°	174.1	172.7	171.2	167.2	168.3	170.7	172.7	174.1	174.1
47.5°	154.3	154.8	152.8	149.9	150.8	153.3	154.8	156.4	156.4
50°	138.9	137.4	135.5	132.4	134.0	136.0	138.0	138.9	139.5
52.5°	121.1	120.6	119.1	115.6	116.6	117.6	119.6	121.1	121.6
55°	108.2	106.7	104.7	100.7	100.7	101.7	102.8	103.7	104.7
57.5°	95.7	94.3	91.3	86.8	86.3	86.3	85.9	86.8	88.4
60°	83.4	82.8	78.4	74.4	73.0	71.5	69.5	70.0	71.9
62.5°	72.4	71.5	67.5	62.5	59.6	57.1	54.6	54.0	56.1
65°	62.5	61.5	57.1	52.1	48.6	44.2	40.2	40.2	41.7
67.5°	53.6	51.6	47.6	42.1	37.7	32.3	28.3	29.2	29.8
70°	44.6	43.2	38.7	33.2	27.8	22.3	19.8	20.4	20.4
72.5°	36.7	34.8	30.3	24.8	19.4	14.4	13.4	12.9	12.9
75°	28.8	26.9	22.3	16.9	11.9	8.4	7.5	7.5	7.5
77.5°	20.8	19.4	15.4	10.4	6.5	4.0	3.5	2.9	2.9
80°	14.4	12.9	9.4	5.4	2.5	1.5	1.5	1.5	1.5
82.5°	8.4	6.9	4.4	2.5	1.0	0.5	0.5	0.5	0.5
85°	4.0	2.9	2.0	1.0	0.5	0.5	0.5	0.5	0.5
87.5°	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)