

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583366

Luminaire Tested: **HCC6S07D010MB-HM60525927-61WWW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583366  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S07D010MB-HM60525927-61WWW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 686.8 lumens  
Efficiency: N/A  
Efficacy: 85.8 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583366  
CATALOG NUMBER: HCC6S07D010MB-HM60525927-61WWW

### Luminous Intensity Polar Plot





TEST NUMBER: P583366

CATALOG NUMBER: HCC6S07D010MB-HM60525927-61WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87	87	87	87	87	87		
	2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76	76	76		
	3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66	66	66	66	66	66		
	4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58	58	58		
	5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51	51	51	51	51	51		
	6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46	46	46	46	46	46		
	7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42	42	42	42	42	42		
	8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38	38	38	38	38	38		
	9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34	34	34	34	34	34		
	10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32	32	32	32	32	32		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	20212	20212	20212
5°	21104	20152	19222
10°	21682	19806	18064
15°	22219	19376	16924
20°	22320	18493	15547
25°	21848	17318	14257
30°	20725	15920	13065
35°	18825	14315	11725
40°	16402	12745	10548
45°	14195	11156	9265
50°	12400	9603	8128
55°	10963	8449	6977
60°	9846	7401	6041
65°	8821	6434	5863
70°	7886	5482	5482
75°	6841	4639	5168
80°	5462	3883	4672
85°	3774	3397	4088



TEST NUMBER: P583366

CATALOG NUMBER: HCC6S07D010MB-HM60525927-61WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	34.6	5.0
10°-20°	96.3	14.0
20°-30°	134.2	19.5
30°-40°	138.3	20.1
40°-50°	114.6	16.7
50°-60°	82.4	12.0
60°-70°	52.5	7.6
70°-80°	26.9	3.9
80°-90°	6.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	265.2	38.6
0°-40°	403.5	58.8
0°-60°	600.5	87.4
0°-90°	686.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	686.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	369	369	369	369	369	
5°	384	378	366	354	349	37
15°	392	377	341	310	298	110
25°	361	336	286	250	236	166
35°	281	259	214	186	175	175
45°	183	170	144	126	120	142
55°	115	105	88	78	73	103
65°	68	60	50	43	45	68
75°	32	28	22	23	24	34
85°	6	5	5	6	6	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583366

CATALOG NUMBER: HCC6S07D010MB-HM60525927-61WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	368.7	368.7	368.7	368.7	368.7	368.7	368.7	368.7	368.7
2.5°	375.6	374.1	372.2	370.2	367.2	363.7	360.7	359.7	358.3
5°	383.5	381.6	377.6	372.6	366.2	359.7	354.3	350.8	349.3
7.5°	388.5	386.0	380.6	372.2	362.7	353.3	345.3	340.4	338.4
10°	389.5	387.0	379.6	368.2	355.8	342.8	333.0	327.0	324.5
12.5°	391.0	387.5	378.1	364.7	348.9	333.9	321.5	314.1	311.6
15°	391.5	387.5	376.6	360.2	341.4	323.5	310.1	301.2	298.2
17.5°	389.5	385.0	372.2	352.2	330.9	312.1	296.3	286.8	282.8
20°	382.6	377.6	362.7	340.4	317.0	297.2	280.9	270.9	266.5
22.5°	373.7	367.2	350.3	326.5	302.2	281.3	265.0	255.0	250.6
25°	361.2	355.3	336.4	311.1	286.3	264.4	249.6	239.2	235.7
27.5°	346.8	339.9	320.5	295.3	269.9	248.1	233.7	224.2	219.8
30°	327.4	321.0	301.7	276.3	251.5	231.2	216.3	208.4	206.4
32.5°	304.7	299.2	280.3	256.5	232.7	213.9	201.4	193.1	191.0
35°	281.3	274.9	258.6	236.2	213.9	197.0	185.6	178.1	175.2
37.5°	256.1	250.1	236.2	216.3	196.5	180.6	170.7	164.3	161.2
40°	229.2	224.8	211.9	196.0	178.1	164.3	155.8	150.3	147.4
42.5°	204.4	200.0	191.0	176.2	161.2	148.9	141.4	136.4	133.9
45°	183.1	179.1	170.2	157.3	143.9	133.5	125.5	122.0	119.5
47.5°	161.8	159.8	151.8	139.9	127.6	118.6	113.2	109.1	107.2
50°	145.4	142.9	135.5	123.0	112.6	105.7	100.7	97.2	95.3
52.5°	128.5	126.0	119.1	108.7	100.3	93.8	88.8	85.9	83.8
55°	114.7	112.6	105.1	95.7	88.4	82.8	78.4	74.9	73.0
57.5°	101.7	99.7	92.8	83.8	77.4	72.4	68.4	65.5	63.0
60°	89.8	88.4	81.3	73.0	67.5	62.5	59.0	56.5	55.1
62.5°	79.4	76.4	70.5	63.0	58.0	54.0	50.6	49.2	50.1
65°	68.0	66.5	60.5	54.0	49.6	45.7	43.2	44.2	45.2
67.5°	58.6	56.5	51.6	45.7	41.7	38.7	37.2	39.2	39.7
70°	49.2	47.1	42.7	37.7	34.2	32.3	32.3	33.8	34.2
72.5°	40.2	38.7	34.8	30.8	28.3	26.7	27.8	28.8	29.2
75°	32.3	30.8	27.8	24.4	21.9	21.9	22.8	23.8	24.4
77.5°	24.8	23.8	20.8	18.4	17.3	17.3	18.4	18.8	19.4
80°	17.3	16.4	14.8	13.4	12.3	13.4	14.4	14.4	14.8
82.5°	11.4	10.9	10.0	9.0	9.0	9.4	10.0	10.4	10.4
85°	6.0	6.0	5.4	5.0	5.4	6.0	6.0	6.5	6.5
87.5°	2.0	2.0	2.0	2.0	2.5	2.5	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)