

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583385

Luminaire Tested: **HCC6W07D010BZ-HM60525930-61WWWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583385  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W07D010BZ-HM60525930-61WWWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 776.2 lumens  
Efficiency: N/A  
Efficacy: 97.0 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583385  
CATALOG NUMBER: HCC6W07D010BZ-HM60525930-61WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583385

CATALOG NUMBER: HCC6W07D010BZ-HM60525930-61WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31					31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	21725	21725	21725
5°	22204	21720	21335
10°	22873	21520	20802
15°	23598	21232	20278
20°	23971	20436	19462
25°	23584	19223	18340
30°	22446	17826	17142
35°	20472	16088	15841
40°	17905	14456	14377
45°	15405	12722	13017
50°	13390	11087	11317
55°	11699	9739	9835
60°	10383	8431	7719
65°	9275	7095	5889
70°	8158	5818	4937
75°	7011	4575	4702
80°	5651	3946	4609
85°	3774	3397	4088



TEST NUMBER: P583385  
 CATALOG NUMBER: HCC6W07D010BZ-HM60525930-61WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.5	4.8
10°-20°	106.8	13.8
20°-30°	152.5	19.6
30°-40°	159.8	20.6
40°-50°	134.5	17.3
50°-60°	95.7	12.3
60°-70°	56.0	7.2
70°-80°	26.5	3.4
80°-90°	6.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	296.9	38.2
0°-40°	456.6	58.8
0°-60°	686.9	88.5
0°-90°	776.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	776.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	396	396	396	396	396	
5°	404	400	395	389	388	39
15°	416	401	374	359	357	117
25°	390	362	318	303	303	178
35°	306	280	240	232	237	190
45°	199	184	164	165	168	154
55°	122	112	102	102	103	110
65°	72	63	55	46	45	71
75°	33	28	22	21	22	35
85°	6	5	5	6	6	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583385

CATALOG NUMBER: HCC6W07D010BZ-HM60525930-61WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	396.3	396.3	396.3	396.3	396.3	396.3	396.3	396.3	396.3
2.5°	396.9	396.9	396.3	395.9	394.7	393.2	392.0	391.0	391.0
5°	403.5	402.3	400.2	397.5	394.7	391.5	389.3	387.7	387.7
7.5°	408.8	406.6	402.3	397.5	392.6	388.3	384.4	382.3	381.7
10°	410.9	408.3	401.8	394.2	386.6	380.7	376.4	373.7	373.7
12.5°	413.2	409.9	401.2	390.4	380.7	372.5	368.2	366.1	365.5
15°	415.8	411.5	400.7	387.1	374.1	364.9	359.0	357.3	357.3
17.5°	415.8	410.5	396.9	380.1	363.9	353.6	348.2	346.6	347.2
20°	410.9	405.0	388.8	368.2	350.3	339.6	334.1	333.0	333.6
22.5°	401.8	394.7	376.4	354.2	334.7	323.2	318.4	318.4	317.8
25°	389.9	382.3	362.2	339.0	317.8	306.5	302.7	303.2	303.2
27.5°	374.1	366.6	346.6	321.7	300.5	289.1	286.4	287.6	288.1
30°	354.6	346.6	325.4	301.0	281.6	270.2	268.6	270.2	270.8
32.5°	330.8	324.9	304.3	279.4	261.0	251.3	250.7	252.3	254.5
35°	305.9	299.5	280.5	257.8	240.4	232.3	232.3	235.0	236.7
37.5°	278.8	272.4	255.0	236.1	221.5	213.9	214.9	217.6	218.2
40°	250.2	245.3	230.7	214.5	202.0	196.0	197.6	200.3	200.9
42.5°	223.1	218.8	206.9	192.3	183.0	178.7	180.8	184.1	185.2
45°	198.7	193.9	184.1	171.6	164.1	161.9	164.6	166.8	167.9
47.5°	176.5	172.2	164.1	152.7	147.3	146.2	148.9	150.0	151.0
50°	157.0	152.7	144.6	134.3	130.0	130.0	132.1	133.2	132.7
52.5°	138.1	134.3	126.7	118.1	115.3	115.3	116.9	117.5	118.6
55°	122.4	118.6	112.1	104.0	101.9	100.7	101.9	101.9	102.9
57.5°	107.7	104.5	98.6	91.0	88.3	87.1	86.7	86.1	87.1
60°	94.7	92.0	85.5	79.1	76.9	74.2	72.1	69.9	70.4
62.5°	82.8	80.1	74.2	67.6	65.5	61.7	59.0	56.3	57.4
65°	71.5	68.8	63.3	57.9	54.7	50.3	46.0	44.4	45.4
67.5°	61.2	59.0	53.6	48.2	45.4	40.6	36.3	36.3	36.8
70°	50.9	48.7	44.4	39.5	36.3	32.0	30.4	30.8	30.8
72.5°	41.7	40.1	35.7	31.4	28.2	25.5	25.5	25.9	26.5
75°	33.1	32.0	27.6	23.8	21.6	20.1	21.1	21.6	22.2
77.5°	25.5	23.8	20.6	17.9	16.2	16.8	17.9	18.4	18.9
80°	17.9	17.3	14.6	13.0	12.5	13.0	14.0	14.6	14.6
82.5°	11.3	10.9	9.2	8.6	8.6	9.2	10.3	10.3	10.3
85°	6.0	5.4	4.9	4.9	5.4	6.0	6.5	6.5	6.5
87.5°	2.2	1.6	2.2	2.2	2.7	2.7	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)