

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583376

Luminaire Tested: **HCC6W07D010MB-HM60525930-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W07D010MB-HM60525930-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 807.1 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583376
CATALOG NUMBER: HCC6W07D010MB-HM60525930-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583376

CATALOG NUMBER: HCC6W07D010MB-HM60525930-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	21917	21917	21917
5°	22028	22144	22144
10°	22650	22255	22161
15°	23366	22384	22384
20°	23639	21871	22373
25°	23167	20771	21757
30°	21908	19307	20440
35°	19829	17654	18524
40°	17254	15973	16588
45°	14738	14242	14738
50°	12938	12477	12989
55°	11288	10513	10924
60°	9977	8727	8607
65°	8847	6888	5902
70°	7806	4873	3558
75°	6651	2754	1737
80°	4956	852	505
85°	2705	377	377



TEST NUMBER: P583376
 CATALOG NUMBER: HCC6W07D010MB-HM60525930-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	4.8
10°-20°	112.2	13.9
20°-30°	163.9	20.3
30°-40°	171.9	21.3
40°-50°	144.8	17.9
50°-60°	101.4	12.6
60°-70°	54.4	6.7
70°-80°	18.2	2.3
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.4	39.0
0°-40°	486.3	60.2
0°-60°	732.5	90.8
0°-90°	807.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	400	400	400	400	400	
5°	400	402	402	402	402	38
15°	412	406	394	392	394	116
25°	383	367	343	349	360	175
35°	296	281	264	271	277	184
45°	190	187	184	188	190	148
55°	118	114	110	112	114	106
65°	68	62	53	44	46	68
75°	31	24	13	8	8	33
85°	4	2	1	1	1	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583376

CATALOG NUMBER: HCC6W07D010MB-HM60525930-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	399.8	399.8	399.8	399.8	399.8	399.8	399.8	399.8	399.8
2.5°	397.1	397.1	398.1	399.3	400.3	400.3	400.9	401.4	400.9
5°	400.3	400.3	402.0	402.4	402.4	402.0	402.4	402.4	402.4
7.5°	405.2	404.1	404.7	403.6	402.4	402.0	401.4	401.4	401.4
10°	406.9	405.7	404.7	402.4	399.8	398.1	397.6	398.1	398.1
12.5°	409.0	407.9	405.2	400.9	397.6	395.0	394.4	395.4	395.4
15°	411.7	410.6	406.3	399.3	394.4	391.7	392.2	393.3	394.4
17.5°	411.7	409.6	402.4	393.3	387.4	384.7	386.8	389.5	391.1
20°	405.2	403.0	393.3	381.9	374.9	373.2	377.1	381.9	383.5
22.5°	396.6	392.2	380.8	367.3	359.7	359.7	365.2	371.1	373.2
25°	383.0	379.8	366.8	351.0	343.4	343.0	349.4	357.6	359.7
27.5°	367.8	363.5	349.4	333.1	325.1	325.6	332.6	340.7	343.0
30°	346.1	340.7	328.2	312.6	305.0	307.2	314.2	320.2	322.9
32.5°	321.8	316.9	305.6	291.0	284.4	286.5	292.5	298.0	300.1
35°	296.3	291.0	281.1	268.2	263.8	266.0	271.4	275.8	276.8
37.5°	267.6	263.8	256.7	246.4	243.3	246.0	250.3	253.0	254.0
40°	241.1	237.8	231.8	224.2	223.2	225.4	229.7	231.4	231.8
42.5°	215.0	212.3	208.6	203.1	203.1	205.3	209.2	210.2	210.7
45°	190.1	188.5	186.9	182.5	183.7	186.4	188.5	190.1	190.1
47.5°	168.5	169.0	166.9	163.6	164.6	167.3	169.0	170.6	170.6
50°	151.7	150.0	147.9	144.7	146.3	148.4	150.6	151.7	152.3
52.5°	132.2	131.7	130.0	126.2	127.3	128.4	130.5	132.2	132.7
55°	118.1	116.5	114.3	110.0	110.0	111.0	112.2	113.2	114.3
57.5°	104.6	102.9	99.7	94.8	94.3	94.3	93.7	94.8	96.4
60°	91.0	90.4	85.5	81.2	79.6	78.0	75.8	76.4	78.5
62.5°	79.1	78.0	73.6	68.2	65.0	62.3	59.6	59.0	61.2
65°	68.2	67.2	62.3	56.9	53.1	48.3	43.8	43.8	45.5
67.5°	58.5	56.3	52.0	46.0	41.1	35.2	30.9	32.0	32.5
70°	48.7	47.1	42.3	36.3	30.4	24.4	21.6	22.2	22.2
72.5°	40.1	38.0	33.1	27.1	21.1	15.7	14.6	14.0	14.0
75°	31.4	29.2	24.4	18.5	13.0	9.2	8.2	8.2	8.2
77.5°	22.8	21.1	16.8	11.3	7.0	4.3	3.7	3.3	3.3
80°	15.7	14.0	10.3	6.0	2.7	1.6	1.6	1.6	1.6
82.5°	9.2	7.6	4.9	2.7	1.1	0.6	0.6	0.6	0.6
85°	4.3	3.3	2.2	1.1	0.6	0.6	0.6	0.6	0.6
87.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)