

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583401

Luminaire Tested: **HCC6W07D010MW-HM60525935-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583401
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W07D010MW-HM60525935-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 722.5 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583401
CATALOG NUMBER: HCC6W07D010MW-HM60525935-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583401

CATALOG NUMBER: HCC6W07D010MW-HM60525935-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89					89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78					78			
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69					69			
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	67	63	61					61			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54					54			
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49					49			
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44					44			
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40					40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37					37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	22230	22230	22230
5°	22656	22182	21687
10°	23424	21905	20980
15°	24143	21521	20324
20°	24514	20628	19263
25°	24074	19211	17935
30°	22883	17509	16458
35°	20572	15653	14844
40°	17748	13711	13268
45°	15033	11807	11497
50°	12887	9970	9876
55°	11173	8392	8067
60°	9747	6820	5756
65°	8587	5241	3178
70°	7405	3462	1555
75°	6291	1673	593
80°	4862	726	347
85°	2830	377	377



TEST NUMBER: P583401
 CATALOG NUMBER: HCC6W07D010MW-HM60525935-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	5.3
10°-20°	108.2	15.0
20°-30°	152.4	21.1
30°-40°	155.7	21.5
40°-50°	125.5	17.4
50°-60°	84.2	11.7
60°-70°	42.6	5.9
70°-80°	13.6	1.9
80°-90°	2.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.8	41.4
0°-40°	454.5	62.9
0°-60°	664.2	91.9
0°-90°	722.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	722.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	406	406	406	406	406	
5°	412	409	403	397	394	40
15°	425	408	379	362	358	120
25°	398	367	318	298	296	182
35°	307	279	234	221	222	191
45°	194	178	152	147	148	151
55°	117	104	88	84	84	105
65°	66	55	40	27	24	66
75°	30	21	8	3	3	32
85°	4	2	1	1	1	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583401

CATALOG NUMBER: HCC6W07D010MW-HM60525935-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	405.5	405.5	405.5	405.5	405.5	405.5	405.5	405.5	405.5
2.5°	407.2	406.6	406.1	404.8	403.1	401.4	400.3	399.2	398.6
5°	411.7	410.6	408.9	406.6	403.1	399.2	396.9	394.6	394.1
7.5°	418.0	415.7	411.2	406.1	400.3	394.6	390.7	388.4	386.6
10°	420.8	416.8	410.6	402.0	393.5	386.6	381.5	378.1	376.9
12.5°	423.2	418.5	409.5	398.0	386.6	377.5	371.9	368.9	367.8
15°	425.4	420.8	408.3	393.5	379.2	368.3	362.1	359.3	358.1
17.5°	425.4	419.1	404.3	385.4	368.3	355.3	349.0	346.1	345.6
20°	420.2	413.4	395.2	373.0	353.6	338.8	333.0	331.3	330.2
22.5°	410.6	402.6	382.0	357.0	335.8	321.7	315.3	314.2	313.0
25°	398.0	390.1	366.6	339.9	317.6	303.4	298.2	297.1	296.5
27.5°	382.0	373.6	349.0	321.7	297.6	283.9	279.4	279.4	278.8
30°	361.5	351.8	327.9	300.5	276.6	264.0	260.6	260.6	260.0
32.5°	336.5	326.8	305.1	278.8	256.1	242.9	240.1	241.2	240.6
35°	307.4	299.3	279.4	253.8	233.9	221.8	220.7	221.8	221.8
37.5°	278.3	270.9	253.8	231.5	212.7	201.9	201.9	203.6	203.0
40°	248.0	242.3	226.4	207.0	191.6	184.2	183.1	184.8	185.4
42.5°	219.6	214.9	201.3	185.4	171.6	164.3	166.0	167.1	167.7
45°	193.9	189.3	178.4	161.9	152.3	147.2	147.2	148.9	148.3
47.5°	171.1	167.7	156.8	140.8	132.3	130.1	131.2	132.3	132.3
50°	151.1	145.9	135.7	123.2	116.9	114.1	115.2	115.8	115.8
52.5°	132.3	128.8	118.6	107.2	101.5	99.8	99.8	100.4	100.4
55°	116.9	113.0	103.8	92.3	87.8	85.5	83.8	83.3	84.4
57.5°	102.1	98.7	90.1	79.3	74.1	71.8	68.4	67.3	68.4
60°	88.9	86.1	77.5	67.3	62.2	57.6	53.6	51.3	52.5
62.5°	77.5	74.1	65.6	57.0	51.3	46.2	39.9	36.5	38.2
65°	66.2	63.3	54.7	46.2	40.4	34.2	26.9	24.5	24.5
67.5°	55.9	53.0	45.1	37.6	30.8	23.3	16.5	16.0	16.5
70°	46.2	43.4	36.5	29.1	21.6	14.3	9.7	9.7	9.7
72.5°	38.2	34.8	28.6	21.1	13.7	7.4	5.1	5.7	5.7
75°	29.7	26.9	21.1	14.3	7.9	3.4	2.8	2.8	2.8
77.5°	22.2	19.9	14.8	9.2	4.0	1.1	1.1	1.1	1.1
80°	15.4	13.1	9.7	5.7	2.3	1.1	1.1	1.1	1.1
82.5°	9.2	7.9	5.7	2.8	1.1	0.6	0.6	0.6	0.6
85°	4.5	4.0	2.3	1.1	0.6	0.6	0.6	0.6	0.6
87.5°	1.1	1.1	0.6	0.6	0.0	0.6	0.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)