

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583709

Luminaire Tested: **HCC8W10D010MB-HM80520827-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583709  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W10D010MB-HM80520827-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 970.3 lumens  
Efficiency: N/A  
Efficacy: 98.0 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583709  
CATALOG NUMBER: HCC8W10D010MB-HM80520827-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583709

CATALOG NUMBER: HCC8W10D010MB-HM80520827-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59				59
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53				53
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47				47
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43				43
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39				39
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35				35
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32				32

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	16063	16063	16063
5°	16728	16028	15356
10°	17287	15822	14604
15°	17724	15461	13845
20°	17756	14819	13159
25°	17458	13885	12477
30°	16525	12811	11893
35°	15069	11519	11169
40°	13103	10156	10309
45°	11238	8796	9441
50°	9599	7584	8482
55°	8414	6532	7365
60°	7493	5569	6198
65°	6647	4546	4947
70°	5896	3372	2804
75°	4909	1763	834
80°	3871	550	124
85°	2760	248	0



TEST NUMBER: P583709  
 CATALOG NUMBER: HCC8W10D010MB-HM80520827-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.1	5.1
10°-20°	137.6	14.2
20°-30°	194.7	20.1
30°-40°	203.7	21.0
40°-50°	169.9	17.5
50°-60°	120.5	12.4
60°-70°	69.4	7.2
70°-80°	22.3	2.3
80°-90°	3.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.4	39.3
0°-40°	585.1	60.3
0°-60°	875.5	90.2
0°-90°	970.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	970.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	521	521	521	521	521	
5°	540	533	518	502	496	52
15°	555	533	484	446	434	156
25°	513	475	408	375	367	234
35°	400	365	306	290	297	248
45°	258	237	202	204	216	200
55°	156	140	122	128	137	141
65°	91	76	62	62	68	91
75°	41	30	15	7	7	45
85°	8	4	1	0	0	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583709

CATALOG NUMBER: HCC8W10D010MB-HM80520827-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	531.9	531.0	530.3	531.0	530.3	531.0	530.3	530.3	529.5	528.8	528.8
5°	540.4	539.6	539.6	539.6	538.9	538.0	538.0	537.3	535.7	534.9	533.4
7.5°	545.8	546.7	546.7	546.7	545.1	545.1	543.5	542.0	540.4	538.9	536.5
10°	552.1	552.1	551.4	550.5	549.0	548.2	547.4	545.8	543.5	540.4	538.0
12.5°	554.4	554.4	553.6	552.1	551.4	550.5	549.8	547.4	544.3	540.4	537.3
15°	555.2	553.6	552.8	552.1	550.5	548.2	548.2	545.1	541.1	536.5	532.6
17.5°	549.0	549.8	548.2	546.7	544.3	542.7	540.4	538.0	533.4	527.9	524.1
20°	541.1	540.4	539.6	537.3	534.2	533.4	531.0	527.2	523.2	517.0	511.6
22.5°	528.8	527.9	526.4	524.8	521.7	520.1	517.8	513.1	507.7	501.5	495.2
25°	513.1	511.6	509.3	506.2	503.8	502.2	499.1	494.5	488.3	481.2	475.0
27.5°	488.3	490.5	489.0	484.3	482.0	478.9	478.2	471.9	466.4	459.4	452.4
30°	464.1	464.1	461.8	459.4	455.6	453.2	450.0	445.3	439.9	431.4	426.0
32.5°	433.7	433.0	429.8	429.0	426.0	421.3	420.5	414.2	408.8	402.5	395.6
35°	400.3	398.7	395.6	393.2	391.7	389.3	387.0	381.5	376.1	369.9	365.2
37.5°	362.0	362.0	361.3	357.4	355.9	354.3	351.9	346.5	343.4	337.2	332.5
40°	325.5	324.7	322.4	321.5	320.1	317.7	316.1	313.0	308.3	303.6	299.1
42.5°	289.7	290.4	287.3	288.1	285.0	283.4	282.7	278.0	275.6	270.9	267.1
45°	257.7	257.0	255.4	254.6	253.0	251.5	249.9	247.6	243.8	239.1	236.7
47.5°	228.1	225.9	225.9	225.0	224.3	221.2	220.3	218.0	215.6	211.1	207.9
50°	200.1	200.1	200.1	199.3	197.0	196.2	194.7	192.3	190.0	186.9	182.2
52.5°	177.5	177.5	177.5	176.8	173.7	172.8	172.1	169.0	165.9	163.5	160.3
55°	156.5	157.3	156.5	154.9	152.7	152.7	150.2	148.7	145.6	143.3	140.2
57.5°	138.6	138.6	137.0	136.3	134.7	133.9	132.3	130.8	126.9	124.6	120.7
60°	121.5	120.7	120.7	119.1	117.6	116.0	115.3	112.9	111.3	107.5	104.3
62.5°	105.9	105.9	104.3	104.3	101.2	101.2	100.5	98.1	95.8	91.8	90.3
65°	91.1	91.1	90.3	89.5	87.3	86.4	85.7	83.3	81.0	78.6	76.3
67.5°	77.9	77.9	76.3	75.5	73.9	73.2	71.6	70.1	67.8	65.4	63.1
70°	65.4	64.7	63.8	63.1	61.5	60.7	59.1	57.6	55.3	53.7	51.4
72.5°	53.0	53.0	52.2	50.6	49.9	49.0	48.3	46.8	44.4	42.1	40.5
75°	41.2	41.2	41.2	39.7	38.1	37.4	37.4	35.8	34.3	32.0	30.4
77.5°	32.0	31.1	30.4	30.4	28.8	28.0	27.3	26.4	24.2	23.3	21.8
80°	21.8	22.6	21.8	21.0	20.2	19.5	19.5	17.9	17.2	15.6	14.1
82.5°	14.8	14.1	14.1	13.2	13.2	12.5	12.5	10.9	10.1	9.4	8.5
85°	7.8	7.8	7.0	7.0	7.0	6.3	6.3	5.4	5.4	4.7	3.8
87.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583709

CATALOG NUMBER: HCC8W10D010MB-HM80520827-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	527.9	526.4	525.6	525.6	524.8	524.1	523.2	522.5	520.9	520.9	519.4
5°	531.9	530.3	529.5	527.2	525.6	525.6	522.5	521.7	519.4	517.8	516.3
7.5°	534.9	531.9	529.5	527.2	525.6	524.1	520.9	517.8	514.7	511.6	510.0
10°	534.9	531.9	527.9	524.1	522.5	520.9	517.0	512.4	508.4	505.3	501.5
12.5°	533.4	528.8	524.1	520.9	517.8	515.5	510.8	506.2	501.5	495.2	492.1
15°	528.8	522.5	517.8	512.4	510.0	506.2	502.2	495.2	489.8	484.3	480.4
17.5°	519.4	511.6	506.2	500.6	496.8	494.5	488.3	482.0	475.8	469.5	464.8
20°	505.3	498.3	492.1	485.1	482.0	478.9	471.1	464.8	458.7	451.6	446.9
22.5°	488.3	481.2	472.6	467.2	462.5	458.7	451.6	444.6	438.4	432.1	426.0
25°	467.2	460.2	452.4	443.9	440.8	436.8	429.0	422.0	415.1	408.1	402.5
27.5°	444.6	435.2	429.0	419.7	416.6	412.6	404.1	396.3	390.2	384.6	378.4
30°	417.3	410.4	401.8	393.2	390.2	386.2	379.2	372.3	366.0	359.8	353.5
32.5°	387.8	380.8	372.3	366.0	361.3	358.2	351.2	345.0	338.7	332.5	327.1
35°	356.6	348.8	342.6	336.4	332.5	328.6	321.5	316.1	311.4	306.0	300.6
37.5°	324.7	319.3	313.0	306.0	302.2	299.1	293.5	287.3	283.4	278.7	274.9
40°	293.5	287.3	281.9	275.6	272.5	270.2	264.8	260.1	256.1	252.3	249.9
42.5°	261.7	256.1	250.7	246.9	244.5	242.2	238.2	232.8	230.5	226.6	224.3
45°	232.0	227.4	223.5	218.0	216.5	214.9	210.2	206.4	204.0	201.7	200.1
47.5°	204.0	200.9	196.2	193.2	190.8	189.2	186.1	182.9	180.7	179.1	177.5
50°	179.8	176.0	172.8	169.7	168.2	165.9	162.8	161.2	159.6	158.1	158.1
52.5°	157.3	153.4	150.2	148.0	146.4	144.8	142.4	141.7	140.2	140.2	139.4
55°	136.3	133.9	130.8	127.7	126.9	126.1	124.6	123.1	122.2	121.5	122.2
57.5°	118.4	116.0	112.9	110.6	109.7	109.0	108.2	106.7	105.9	105.9	105.9
60°	102.0	99.6	97.4	95.0	95.0	93.4	92.7	91.8	91.1	90.3	90.3
62.5°	87.3	84.9	82.6	81.0	80.2	79.5	77.9	77.0	76.3	76.3	75.5
65°	73.9	70.9	70.1	67.8	67.0	66.2	65.4	63.8	63.1	62.3	61.5
67.5°	60.7	59.1	56.9	55.3	54.5	53.7	53.0	51.4	50.6	49.9	48.3
70°	49.0	47.5	45.9	44.4	43.6	42.8	41.2	39.7	38.9	37.4	35.1
72.5°	38.1	36.5	35.1	33.5	32.7	32.0	30.4	28.8	27.3	25.7	24.2
75°	28.8	27.3	24.9	23.3	22.6	22.6	20.2	18.6	17.2	14.8	13.2
77.5°	20.2	17.9	17.2	15.6	14.8	13.2	11.7	10.1	8.5	7.8	6.3
80°	13.2	11.7	10.1	9.4	8.5	7.8	7.0	5.4	3.8	3.1	2.3
82.5°	7.8	7.0	6.3	5.4	4.7	3.8	3.1	3.1	2.3	1.6	0.7
85°	3.8	3.1	2.3	2.3	1.6	1.6	1.6	0.7	0.7	0.7	0.7
87.5°	1.6	0.7	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583709

CATALOG NUMBER: HCC8W10D010MB-HM80520827-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	518.5	517.8	517.0	516.3	516.3	514.7	514.7	514.0	512.4	511.6	511.6
5°	514.0	511.6	510.0	509.3	508.4	506.2	505.3	503.8	502.2	500.6	499.9
7.5°	506.9	503.0	501.5	500.6	498.3	496.1	494.5	492.1	489.8	487.4	486.7
10°	498.3	494.5	490.5	489.0	486.7	485.1	482.0	478.9	476.6	474.2	471.9
12.5°	487.4	482.7	478.9	477.3	475.0	471.9	467.2	465.7	461.8	460.2	457.1
15°	475.0	469.5	465.7	463.3	461.0	456.3	453.2	450.0	446.2	444.6	441.5
17.5°	459.4	453.2	449.3	446.9	445.3	441.5	436.8	433.0	429.0	427.4	425.1
20°	440.8	436.8	431.4	429.0	427.4	422.9	418.2	416.6	413.5	410.4	408.1
22.5°	419.7	415.8	410.4	408.1	407.2	403.4	399.4	397.1	394.7	392.5	390.2
25°	397.9	393.2	388.6	387.0	385.5	382.4	379.2	377.7	375.3	373.8	372.3
27.5°	374.5	369.9	366.0	363.6	362.0	359.8	358.2	356.6	355.1	353.5	352.8
30°	349.7	345.0	341.8	340.3	338.7	338.0	335.6	334.9	334.0	332.5	333.3
32.5°	324.7	320.8	317.7	315.4	315.4	313.8	313.0	313.0	312.3	312.3	312.3
35°	297.5	295.1	292.8	292.0	291.2	290.4	289.7	290.4	289.7	290.4	291.2
37.5°	272.5	270.2	268.6	267.8	267.1	267.8	267.1	267.1	267.8	269.4	270.2
40°	246.9	245.3	243.8	244.5	243.8	243.8	243.8	246.0	246.9	247.6	248.5
42.5°	222.7	221.2	220.3	220.3	221.2	220.3	221.9	222.7	224.3	226.6	228.1
45°	199.3	198.6	198.6	199.3	198.6	200.1	200.1	201.7	204.0	205.5	207.1
47.5°	177.5	177.5	177.5	178.3	178.3	179.1	180.7	181.4	182.9	184.5	186.1
50°	157.3	158.1	158.9	158.9	158.9	160.3	161.9	162.8	163.5	164.3	166.6
52.5°	139.4	140.2	140.2	141.0	141.7	142.4	143.3	144.8	145.6	147.1	148.0
55°	122.2	122.2	123.8	124.6	124.6	124.6	126.1	126.1	127.7	128.5	130.1
57.5°	105.9	106.7	106.7	107.5	107.5	108.2	109.0	109.7	110.6	111.3	112.1
60°	90.3	90.3	90.3	91.1	91.8	92.7	91.8	93.4	93.4	95.0	95.8
62.5°	75.5	76.3	76.3	76.3	76.3	76.3	76.3	77.0	77.9	78.6	79.5
65°	61.5	61.5	61.5	60.7	61.5	60.7	61.5	62.3	62.3	63.1	63.8
67.5°	47.5	47.5	45.9	45.9	46.8	46.8	46.8	46.8	45.9	47.5	47.5
70°	34.3	33.5	32.7	32.0	32.0	31.1	31.1	30.4	30.4	30.4	30.4
72.5°	22.6	21.0	19.5	18.6	17.9	17.9	16.3	15.6	16.3	16.3	16.3
75°	11.7	10.1	9.4	8.5	7.8	7.8	7.0	7.0	7.0	7.0	7.0
77.5°	4.7	3.8	3.1	3.1	2.3	2.3	2.3	2.3	2.3	2.3	2.3
80°	1.6	1.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
85°	0.7	0.0	0.0	0.7	0.0	0.7	0.7	0.7	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583709

CATALOG NUMBER: HCC8W10D010MB-HM80520827-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	510.8	510.8	510.0	510.8	509.3	510.0	509.3	509.3
5°	499.1	497.6	497.6	497.6	496.8	496.8	496.1	496.1
7.5°	485.1	484.3	483.6	482.7	482.0	481.2	481.2	481.2
10°	471.1	469.5	469.5	468.8	467.2	466.4	466.4	466.4
12.5°	454.7	454.0	453.2	453.2	450.0	450.9	450.0	450.0
15°	439.2	438.4	438.4	436.1	434.5	434.5	434.5	433.7
17.5°	422.9	422.0	421.3	419.7	418.2	418.2	417.3	418.2
20°	405.7	405.0	403.4	403.4	402.5	401.8	400.3	401.0
22.5°	388.6	387.0	386.2	386.2	385.5	385.5	383.9	383.9
25°	370.7	369.9	369.1	369.9	368.3	368.3	366.7	366.7
27.5°	351.9	351.2	351.2	351.2	350.4	351.2	350.4	350.4
30°	333.3	333.3	332.5	332.5	333.3	332.5	333.3	334.0
32.5°	313.0	313.0	313.8	313.8	314.6	314.6	314.6	314.6
35°	292.0	293.5	293.5	294.4	295.1	295.9	295.9	296.7
37.5°	272.5	273.3	274.1	274.9	276.5	276.5	276.5	276.5
40°	251.5	252.3	253.9	253.0	256.1	257.0	256.1	256.1
42.5°	229.7	231.3	232.0	233.5	234.4	236.0	236.7	236.7
45°	209.5	210.2	211.8	213.4	214.1	216.5	216.5	216.5
47.5°	188.5	190.0	190.8	192.3	193.2	195.4	196.2	195.4
50°	168.2	169.7	171.3	171.3	173.7	174.4	176.0	176.8
52.5°	148.7	149.5	151.1	151.8	153.4	154.9	155.8	156.5
55°	130.1	130.8	132.3	132.3	134.7	135.5	137.0	137.0
57.5°	112.9	113.7	115.3	114.4	116.0	117.6	117.6	116.8
60°	96.5	96.5	96.5	98.1	98.9	99.6	100.5	100.5
62.5°	79.5	81.0	81.7	81.7	82.6	83.3	83.3	82.6
65°	63.8	65.4	66.2	66.2	67.0	67.0	67.0	67.8
67.5°	48.3	48.3	48.3	49.0	48.3	48.3	48.3	48.3
70°	30.4	30.4	30.4	30.4	29.6	30.4	30.4	31.1
72.5°	16.3	16.3	16.3	16.3	16.3	16.3	16.3	16.3
75°	7.0	7.0	7.0	7.8	7.0	7.0	7.0	7.0
77.5°	3.1	2.3	3.1	3.1	2.3	2.3	2.3	2.3
80°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
85°	0.0	0.7	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)