

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583727

Luminaire Tested: **HCC8S10D010BZ-HM80520830-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S10D010BZ-HM80520830-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1053.4 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583727
CATALOG NUMBER: HCC8S10D010BZ-HM80520830-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583727

CATALOG NUMBER: HCC8S10D010BZ-HM80520830-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17598	17598	17598
5°	18220	17498	16805
10°	18621	17193	15860
15°	18886	16616	14810
20°	18829	15810	13750
25°	18366	14783	12620
30°	17401	13595	11583
35°	15833	12302	10525
40°	13908	10941	9508
45°	12123	9625	8478
50°	10554	8438	7469
55°	9408	7414	6494
60°	8548	6494	5538
65°	7683	5647	5027
70°	6834	4824	4544
75°	6005	4051	3884
80°	5079	3303	3445
85°	3821	2477	2724



TEST NUMBER: P583727
 CATALOG NUMBER: HCC8S10D010BZ-HM80520830-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	5.1
10°-20°	147.3	14.0
20°-30°	204.5	19.4
30°-40°	211.4	20.1
40°-50°	177.0	16.8
50°-60°	128.5	12.2
60°-70°	81.1	7.7
70°-80°	40.2	3.8
80°-90°	10.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.2	38.5
0°-40°	616.6	58.5
0°-60°	922.1	87.5
0°-90°	1053.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1053.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	571	571	571	571	571	
5°	589	582	565	550	543	56
15°	592	569	520	479	464	167
25°	540	505	434	387	371	247
35°	421	390	327	290	280	262
45°	278	258	221	199	194	215
55°	175	160	138	126	121	158
65°	105	92	77	68	69	105
75°	50	42	34	33	33	54
85°	11	8	7	8	8	13
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583727

CATALOG NUMBER: HCC8S10D010BZ-HM80520830-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7
2.5°	580.1	580.1	580.8	580.1	580.1	580.1	579.2	579.2	578.5	578.5	577.0
5°	588.6	587.1	588.6	587.1	587.1	587.1	586.2	584.7	583.9	582.4	581.6
7.5°	592.5	591.6	591.6	590.9	590.9	590.2	589.3	588.6	585.5	584.7	582.4
10°	594.7	594.0	594.0	593.2	591.6	591.6	590.2	589.3	585.5	583.9	580.8
12.5°	594.0	594.0	594.0	593.2	590.9	590.2	588.6	586.2	583.2	580.1	577.0
15°	591.6	591.6	590.2	589.3	587.1	585.5	584.7	580.8	577.7	573.8	569.3
17.5°	583.9	583.9	583.2	581.6	579.2	577.7	576.2	572.3	569.3	563.0	558.3
20°	573.8	573.1	572.3	570.0	567.7	566.9	564.6	559.2	555.3	550.6	544.4
22.5°	559.2	558.3	557.6	556.0	552.2	550.6	549.1	545.2	538.3	533.6	525.9
25°	539.8	539.8	538.3	536.0	532.0	530.4	528.2	524.3	518.1	511.1	505.0
27.5°	517.3	516.5	514.2	512.7	509.5	507.2	503.4	498.7	492.6	487.2	479.4
30°	488.7	488.7	487.2	484.8	480.9	479.4	476.2	470.8	464.7	457.7	452.3
32.5°	456.2	456.2	453.9	452.3	449.9	446.1	445.3	439.1	433.7	428.3	422.0
35°	420.6	421.3	419.7	416.6	412.8	412.8	411.2	405.8	399.7	394.1	389.6
37.5°	384.9	382.6	381.8	380.3	377.9	374.8	373.3	370.9	365.5	361.7	354.7
40°	345.5	346.2	344.6	343.1	342.3	339.9	339.2	335.4	331.5	326.8	323.7
42.5°	309.8	309.8	309.8	308.2	306.6	304.3	303.6	301.2	296.7	293.5	288.8
45°	278.0	275.7	275.7	274.9	274.2	272.6	270.3	268.8	265.6	263.4	257.9
47.5°	247.0	247.9	247.0	246.3	244.0	243.2	242.4	239.3	236.2	233.9	230.1
50°	220.0	221.5	220.0	220.0	218.4	217.6	216.1	213.7	211.4	207.6	203.7
52.5°	197.5	197.5	196.8	195.9	193.6	192.1	191.2	190.5	186.7	183.5	180.4
55°	175.0	175.9	175.9	173.4	172.7	171.2	170.3	168.0	166.5	161.9	159.5
57.5°	155.7	154.9	155.7	154.1	152.5	151.0	150.2	148.7	146.4	143.3	140.2
60°	138.6	137.0	137.0	136.3	134.7	134.0	132.5	130.1	127.8	124.6	122.4
62.5°	121.6	120.8	120.1	119.2	117.7	117.0	116.1	113.8	111.5	109.1	106.9
65°	105.3	105.3	104.6	103.0	102.2	101.4	100.7	99.2	96.0	94.5	92.2
67.5°	90.6	89.8	89.8	88.2	86.8	85.9	85.9	84.4	82.1	79.8	78.3
70°	75.8	76.7	75.8	75.1	73.6	73.6	72.0	71.3	68.2	67.4	65.0
72.5°	62.7	62.7	61.9	61.9	60.5	59.6	59.6	58.1	56.5	54.9	53.5
75°	50.4	50.4	50.4	49.5	48.8	47.2	47.2	46.5	45.0	43.4	41.8
77.5°	39.5	38.7	38.7	38.0	37.1	36.4	36.4	35.6	34.0	33.3	31.7
80°	28.6	27.9	27.9	27.9	26.3	27.2	26.3	25.6	24.8	24.0	23.2
82.5°	18.6	19.4	19.4	18.6	17.8	17.8	17.8	17.1	17.1	16.2	15.5
85°	10.8	10.8	10.8	10.8	10.1	10.1	10.1	9.3	9.3	9.3	8.5
87.5°	4.7	4.7	4.7	4.7	4.7	4.7	3.8	3.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583727

CATALOG NUMBER: HCC8S10D010BZ-HM80520830-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7
2.5°	577.0	575.4	574.7	573.8	573.8	573.1	572.3	570.7	570.7	569.3	568.4
5°	580.1	577.7	576.2	574.7	573.8	572.3	570.7	568.4	567.7	565.3	563.0
7.5°	580.8	577.0	575.4	572.3	570.7	569.3	566.1	563.7	560.7	558.3	555.3
10°	577.7	574.7	570.7	566.9	566.1	563.7	559.2	556.0	552.2	549.1	544.4
12.5°	573.1	568.4	564.6	559.9	557.6	555.3	550.6	545.9	540.5	535.1	530.4
15°	565.3	559.9	554.5	549.1	545.9	543.7	538.3	532.8	527.4	520.5	515.8
17.5°	553.8	547.5	542.1	535.1	532.0	529.7	522.7	516.5	509.5	502.6	498.0
20°	539.0	531.3	525.0	517.3	515.1	511.1	504.1	497.1	489.5	481.8	476.2
22.5°	519.6	511.9	505.0	497.1	493.3	489.5	482.5	473.9	466.3	460.0	454.6
25°	497.1	490.2	481.8	474.8	470.1	465.4	457.7	450.8	443.8	434.5	429.0
27.5°	472.4	463.9	457.7	448.3	443.8	440.7	432.1	422.9	416.6	408.1	401.9
30°	444.5	436.8	429.8	420.6	415.9	412.8	405.1	396.5	390.3	381.8	375.6
32.5°	415.1	406.6	398.1	391.9	386.4	383.3	374.8	369.4	361.7	354.7	347.7
35°	383.3	374.8	368.7	360.1	357.0	353.9	346.9	339.9	333.0	326.8	321.4
37.5°	349.3	343.1	336.1	329.9	327.5	324.5	316.0	309.8	304.3	298.2	293.5
40°	316.0	310.6	305.9	299.7	295.8	293.5	287.3	281.9	275.7	271.8	267.2
42.5°	285.7	279.6	274.9	270.3	266.4	264.1	258.7	254.8	250.1	246.3	240.9
45°	254.0	251.0	245.4	241.6	239.3	236.2	232.3	227.7	223.8	220.7	216.8
47.5°	226.1	223.1	219.1	214.6	213.0	210.6	206.7	203.7	200.6	197.5	193.6
50°	200.6	196.8	193.6	190.5	189.0	186.7	182.8	181.3	178.9	175.9	173.4
52.5°	177.3	174.3	171.2	167.3	166.5	164.9	162.6	159.5	157.2	155.7	154.1
55°	156.4	153.4	151.0	148.0	147.1	145.6	142.6	141.0	139.4	137.9	136.3
57.5°	137.9	134.7	131.6	130.1	128.6	127.1	126.2	123.9	122.4	121.6	120.1
60°	120.8	117.7	115.4	113.1	112.3	111.5	110.0	108.4	106.9	105.3	104.6
62.5°	104.6	101.4	99.9	98.3	96.8	96.8	95.2	93.8	92.2	91.4	89.8
65°	89.8	88.2	85.9	83.7	82.8	82.8	80.5	79.8	79.0	77.4	75.8
67.5°	75.8	74.4	72.0	71.3	70.4	69.7	68.9	67.4	65.9	65.0	63.5
70°	63.5	61.9	60.5	59.6	58.9	58.1	56.5	55.8	54.2	53.5	52.6
72.5°	51.1	50.4	48.8	48.0	47.2	46.5	45.7	45.0	43.4	42.6	41.8
75°	41.0	40.3	38.7	38.0	37.1	37.1	36.4	34.9	34.0	34.0	33.3
77.5°	31.0	30.2	29.4	28.6	27.9	27.9	27.2	26.3	25.6	25.6	24.8
80°	22.5	21.6	20.9	20.9	20.9	20.2	19.4	19.4	18.6	18.6	17.8
82.5°	14.7	14.7	13.9	13.9	13.9	13.2	13.2	12.4	12.4	12.4	12.4
85°	8.5	8.5	8.5	7.7	7.7	7.7	7.7	7.7	7.7	7.0	7.7
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583727

CATALOG NUMBER: HCC8S10D010BZ-HM80520830-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7
2.5°	567.7	566.9	565.3	565.3	563.7	563.7	563.0	562.3	561.5	560.7	559.9
5°	562.3	559.2	557.6	556.9	555.3	554.5	552.2	550.6	549.9	548.4	546.8
7.5°	552.2	549.1	545.9	545.2	544.4	541.4	539.0	536.7	535.1	533.6	532.0
10°	540.5	537.4	533.6	532.0	530.4	526.6	523.5	521.2	518.1	515.1	514.2
12.5°	526.6	522.0	517.3	515.8	513.5	509.5	506.5	502.6	500.3	496.4	495.7
15°	510.4	505.0	501.1	497.1	495.7	491.7	486.3	483.2	478.6	477.1	473.2
17.5°	491.0	485.6	480.2	478.6	476.2	470.8	465.4	461.6	456.9	454.6	452.3
20°	470.8	463.9	458.4	456.9	453.9	449.2	443.8	439.9	436.0	431.4	429.0
22.5°	447.6	439.9	435.2	431.4	430.6	425.1	419.0	415.9	412.8	408.9	405.8
25°	422.0	415.1	409.6	406.6	405.1	400.4	395.7	391.9	387.2	384.9	381.0
27.5°	395.7	391.1	384.2	381.0	378.8	374.8	369.4	367.1	362.4	359.4	357.0
30°	370.2	363.2	359.4	355.4	353.1	349.3	344.6	342.3	338.5	335.4	333.0
32.5°	342.3	337.6	332.2	330.7	327.5	323.7	320.6	316.7	313.6	310.6	309.8
35°	316.7	310.6	305.2	303.6	301.2	297.4	295.8	293.5	289.7	288.8	285.7
37.5°	288.8	285.7	279.6	277.3	276.5	273.3	270.3	268.8	266.4	264.1	263.4
40°	262.5	258.7	255.5	253.3	251.7	249.4	246.3	245.4	244.0	240.9	240.0
42.5°	237.8	233.9	230.8	230.1	227.7	225.4	223.8	221.5	220.7	220.0	218.4
45°	213.7	211.4	208.3	207.6	206.7	203.7	202.2	200.6	199.1	198.2	196.8
47.5°	192.1	189.8	187.4	186.7	185.1	184.3	182.0	181.3	178.9	178.1	177.3
50°	171.2	169.6	168.0	167.3	165.8	164.9	163.4	161.9	160.3	159.5	158.8
52.5°	152.5	151.0	149.4	148.7	148.0	146.4	144.8	143.3	142.6	141.7	141.0
55°	134.7	133.2	132.5	131.6	130.9	130.1	127.8	127.1	126.2	125.5	123.9
57.5°	118.5	117.0	115.4	115.4	114.7	113.8	112.3	110.7	110.7	109.1	107.7
60°	103.7	102.2	100.7	99.9	99.2	97.6	96.8	96.0	95.2	94.5	92.9
62.5°	88.2	87.5	85.9	85.9	84.4	83.7	82.8	82.1	81.4	79.8	79.0
65°	75.1	74.4	72.8	72.0	72.0	71.3	69.7	68.9	68.2	68.2	67.4
67.5°	62.7	61.9	60.5	59.6	59.6	58.9	58.1	58.1	57.3	56.5	57.3
70°	51.9	50.4	50.4	49.5	49.5	48.8	48.0	48.0	48.0	48.8	48.8
72.5°	41.0	40.3	39.5	39.5	39.5	39.5	38.7	38.7	39.5	40.3	40.3
75°	32.6	31.7	31.7	31.7	31.0	31.0	31.7	31.7	32.6	32.6	32.6
77.5°	24.0	24.0	24.0	24.0	24.0	24.0	24.8	24.8	25.6	25.6	25.6
80°	17.8	17.8	17.8	17.8	17.8	18.6	18.6	18.6	18.6	18.6	19.4
82.5°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	13.2	13.2	13.2	13.2
85°	7.0	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583727

CATALOG NUMBER: HCC8S10D010BZ-HM80520830-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	570.7	570.7	570.7	570.7	570.7	570.7	570.7	570.7
2.5°	559.2	559.2	559.2	559.9	558.3	558.3	558.3	558.3
5°	545.9	545.2	544.4	545.2	543.7	543.7	542.9	542.9
7.5°	529.7	529.0	528.2	528.2	526.6	526.6	525.9	525.0
10°	511.9	510.4	511.1	509.5	508.8	508.1	507.2	506.5
12.5°	492.6	491.0	490.2	488.7	487.2	486.3	487.2	485.6
15°	471.7	469.3	468.5	467.0	465.4	464.7	464.7	463.9
17.5°	448.3	446.9	446.1	444.5	443.8	442.2	441.4	440.7
20°	426.7	422.9	423.6	422.0	421.3	418.2	418.2	419.0
22.5°	402.7	400.4	398.8	397.3	396.5	395.0	395.0	394.1
25°	378.8	376.3	375.6	374.1	373.3	371.8	370.9	370.9
27.5°	355.4	352.4	352.4	350.9	349.3	348.5	347.7	346.9
30°	330.7	328.4	327.5	327.5	326.8	326.8	324.5	325.3
32.5°	307.5	305.9	305.2	303.6	303.6	302.8	302.8	300.5
35°	284.3	281.9	282.7	281.1	280.3	279.6	280.3	279.6
37.5°	261.8	260.2	260.2	258.7	258.7	257.9	257.1	258.7
40°	239.3	238.5	237.8	237.0	237.8	237.0	235.5	236.2
42.5°	216.8	216.8	216.1	216.1	215.3	215.3	215.3	215.3
45°	196.8	195.9	195.9	195.2	195.2	195.2	195.2	194.4
47.5°	176.6	175.9	175.9	175.9	175.0	175.0	174.3	175.0
50°	157.2	157.2	156.4	156.4	157.2	156.4	155.7	155.7
52.5°	139.4	139.4	138.6	138.6	137.9	137.0	137.9	137.9
55°	123.1	122.4	121.6	121.6	120.8	120.1	120.1	120.8
57.5°	107.7	106.9	106.1	106.1	104.6	103.7	103.7	103.7
60°	92.9	91.4	91.4	90.6	90.6	89.8	89.8	89.8
62.5°	79.0	78.3	78.3	78.3	78.3	77.4	77.4	77.4
65°	67.4	67.4	67.4	68.2	68.2	68.9	68.9	68.9
67.5°	58.1	58.9	58.9	58.9	59.6	59.6	59.6	58.9
70°	49.5	49.5	49.5	50.4	50.4	50.4	50.4	50.4
72.5°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0
75°	32.6	33.3	33.3	33.3	32.6	33.3	33.3	32.6
77.5°	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6
80°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
82.5°	13.2	13.2	13.2	13.2	13.2	13.2	13.2	13.2
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)