

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583726

Luminaire Tested: **HCC8S10D010MB-HM80520830-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583726  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S10D010MB-HM80520830-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 965.0 lumens  
Efficiency: N/A  
Efficacy: 97.5 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583726  
CATALOG NUMBER: HCC8S10D010MB-HM80520830-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583726

CATALOG NUMBER: HCC8S10D010MB-HM80520830-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	15976	15976	15976
5°	16635	15944	15270
10°	17193	15741	14526
15°	17628	15381	13772
20°	17664	14741	13087
25°	17366	13807	12412
30°	16436	12740	11829
35°	14986	11455	11109
40°	13030	10104	10257
45°	11181	8748	9389
50°	9551	7541	8438
55°	8371	6494	7328
60°	7450	5538	6161
65°	6611	4517	4918
70°	5860	3345	2795
75°	4885	1751	834
80°	3836	550	124
85°	2724	248	0



TEST NUMBER: P583726  
 CATALOG NUMBER: HCC8S10D010MB-HM80520830-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.8	5.1
10°-20°	136.8	14.2
20°-30°	193.7	20.1
30°-40°	202.6	21.0
40°-50°	169.0	17.5
50°-60°	119.8	12.4
60°-70°	69.0	7.2
70°-80°	22.2	2.3
80°-90°	3.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.3	39.3
0°-40°	581.9	60.3
0°-60°	870.8	90.2
0°-90°	965.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	965.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	518	518	518	518	518	
5°	537	530	515	500	493	52
15°	552	530	482	444	431	155
25°	510	472	406	373	365	233
35°	398	363	304	288	295	247
45°	256	236	201	203	215	199
55°	156	139	121	127	136	141
65°	91	76	62	62	67	91
75°	41	30	15	7	7	44
85°	8	4	1	0	0	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583726

CATALOG NUMBER: HCC8S10D010MB-HM80520830-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1
2.5°	529.0	528.2	527.4	528.2	527.4	528.2	527.4	527.4	526.6	525.9	525.9
5°	537.4	536.7	536.7	536.7	536.0	535.1	535.1	534.4	532.8	532.0	530.4
7.5°	542.9	543.7	543.7	543.7	542.1	542.1	540.5	539.0	537.4	536.0	533.6
10°	549.1	549.1	548.4	547.5	545.9	545.2	544.4	542.9	540.5	537.4	535.1
12.5°	551.4	551.4	550.6	549.1	548.4	547.5	546.8	544.4	541.4	537.4	534.4
15°	552.2	550.6	549.9	549.1	547.5	545.2	545.2	542.1	538.3	533.6	529.7
17.5°	545.9	546.8	545.2	543.7	541.4	539.8	537.4	535.1	530.4	525.0	521.2
20°	538.3	537.4	536.7	534.4	531.3	530.4	528.2	524.3	520.5	514.2	508.8
22.5°	525.9	525.0	523.5	522.0	518.9	517.3	515.1	510.4	505.0	498.7	492.6
25°	510.4	508.8	506.5	503.4	501.1	499.6	496.4	491.7	485.6	478.6	472.4
27.5°	485.6	487.9	486.3	481.8	479.4	476.2	475.5	469.3	463.9	456.9	449.9
30°	461.6	461.6	459.3	456.9	453.0	450.8	447.6	442.9	437.5	429.0	423.6
32.5°	431.4	430.6	427.6	426.7	423.6	419.0	418.2	412.0	406.6	400.4	393.4
35°	398.1	396.5	393.4	391.1	389.6	387.3	384.9	379.5	374.1	367.8	363.2
37.5°	360.1	360.1	359.4	355.4	353.9	352.4	350.0	344.6	341.5	335.4	330.7
40°	323.7	323.0	320.6	319.9	318.3	316.0	314.4	311.3	306.6	302.1	297.4
42.5°	288.1	288.8	285.7	286.6	283.4	281.9	281.1	276.5	274.2	269.5	265.6
45°	256.4	255.5	254.0	253.3	251.7	250.1	248.6	246.3	242.4	237.8	235.5
47.5°	226.9	224.5	224.5	223.8	223.1	220.0	219.1	216.8	214.6	209.9	206.7
50°	199.1	199.1	199.1	198.2	195.9	195.2	193.6	191.2	189.0	185.8	181.3
52.5°	176.6	176.6	176.6	175.9	172.7	171.9	171.2	168.0	164.9	162.6	159.5
55°	155.7	156.4	155.7	154.1	151.8	151.8	149.5	148.0	144.8	142.6	139.4
57.5°	137.9	137.9	136.3	135.6	134.0	133.2	131.6	130.1	126.2	123.9	120.1
60°	120.8	120.1	120.1	118.5	117.0	115.4	114.7	112.3	110.7	106.9	103.7
62.5°	105.3	105.3	103.7	103.7	100.7	100.7	99.9	97.6	95.2	91.4	89.8
65°	90.6	90.6	89.8	89.1	86.8	85.9	85.2	82.8	80.5	78.3	75.8
67.5°	77.4	77.4	75.8	75.1	73.6	72.8	71.3	69.7	67.4	65.0	62.7
70°	65.0	64.3	63.5	62.7	61.2	60.5	58.9	57.3	54.9	53.5	51.1
72.5°	52.6	52.6	51.9	50.4	49.5	48.8	48.0	46.5	44.1	41.8	40.3
75°	41.0	41.0	41.0	39.5	38.0	37.1	37.1	35.6	34.0	31.7	30.2
77.5°	31.7	31.0	30.2	30.2	28.6	27.9	27.2	26.3	24.0	23.2	21.6
80°	21.6	22.5	21.6	20.9	20.2	19.4	19.4	17.8	17.1	15.5	13.9
82.5°	14.7	13.9	13.9	13.2	13.2	12.4	12.4	10.8	10.1	9.3	8.5
85°	7.7	7.7	7.0	7.0	7.0	6.3	6.3	5.4	5.4	4.7	3.8
87.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583726

CATALOG NUMBER: HCC8S10D010MB-HM80520830-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1
2.5°	525.0	523.5	522.7	522.7	522.0	521.2	520.5	519.6	518.1	518.1	516.5
5°	529.0	527.4	526.6	524.3	522.7	522.7	519.6	518.9	516.5	515.1	513.5
7.5°	532.0	529.0	526.6	524.3	522.7	521.2	518.1	515.1	511.9	508.8	507.2
10°	532.0	529.0	525.0	521.2	519.6	518.1	514.2	509.6	505.7	502.7	498.7
12.5°	530.4	525.9	521.2	518.1	515.1	512.7	508.1	503.4	498.7	492.6	489.5
15°	525.9	519.6	515.1	509.6	507.2	503.4	499.6	492.6	487.2	481.8	477.8
17.5°	516.5	508.8	503.4	498.0	494.1	491.7	485.6	479.4	473.2	467.0	462.3
20°	502.7	495.7	489.5	482.5	479.4	476.2	468.5	462.3	456.2	449.2	444.5
22.5°	485.6	478.6	470.1	464.7	460.0	456.2	449.2	442.2	436.0	429.8	423.6
25°	464.7	457.7	449.9	441.5	438.4	434.5	426.7	419.7	412.8	405.8	400.4
27.5°	442.2	433.0	426.7	417.5	414.3	410.5	401.9	394.3	388.0	382.6	376.3
30°	415.1	408.1	399.7	391.1	388.0	384.2	377.2	370.2	364.0	357.8	351.6
32.5°	385.7	378.8	370.2	364.0	359.4	356.3	349.3	343.1	336.9	330.7	325.3
35°	354.7	346.9	340.8	334.5	330.7	326.8	319.9	314.4	309.8	304.3	298.9
37.5°	323.0	317.6	311.3	304.3	300.5	297.4	292.0	285.7	281.9	277.3	273.3
40°	292.0	285.7	280.3	274.2	271.1	268.8	263.4	258.7	254.8	251.0	248.6
42.5°	260.2	254.8	249.4	245.4	243.2	240.9	237.0	231.5	229.2	225.4	223.1
45°	230.8	226.1	222.2	216.8	215.3	213.7	209.1	205.2	202.9	200.6	199.1
47.5°	202.9	199.8	195.2	192.1	189.8	188.2	185.1	182.0	179.7	178.1	176.6
50°	178.9	175.0	171.9	168.9	167.3	164.9	161.9	160.3	158.8	157.2	157.2
52.5°	156.4	152.5	149.5	147.1	145.6	144.0	141.7	141.0	139.4	139.4	138.6
55°	135.6	133.2	130.1	127.1	126.2	125.5	123.9	122.4	121.6	120.8	121.6
57.5°	117.7	115.4	112.3	110.0	109.1	108.4	107.7	106.1	105.3	105.3	105.3
60°	101.4	99.2	96.8	94.5	94.5	92.9	92.2	91.4	90.6	89.8	89.8
62.5°	86.8	84.4	82.1	80.5	79.8	79.0	77.4	76.7	75.8	75.8	75.1
65°	73.6	70.4	69.7	67.4	66.6	65.9	65.0	63.5	62.7	61.9	61.2
67.5°	60.5	58.9	56.5	54.9	54.2	53.5	52.6	51.1	50.4	49.5	48.0
70°	48.8	47.2	45.7	44.1	43.4	42.6	41.0	39.5	38.7	37.1	34.9
72.5°	38.0	36.4	34.9	33.3	32.6	31.7	30.2	28.6	27.2	25.6	24.0
75°	28.6	27.2	24.8	23.2	22.5	22.5	20.2	18.6	17.1	14.7	13.2
77.5°	20.2	17.8	17.1	15.5	14.7	13.2	11.7	10.1	8.5	7.7	6.3
80°	13.2	11.7	10.1	9.3	8.5	7.7	7.0	5.4	3.8	3.1	2.3
82.5°	7.7	7.0	6.3	5.4	4.7	3.8	3.1	3.1	2.3	1.6	0.7
85°	3.8	3.1	2.3	2.3	1.6	1.6	1.6	0.7	0.7	0.7	0.7
87.5°	1.6	0.7	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583726

CATALOG NUMBER: HCC8S10D010MB-HM80520830-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1
2.5°	515.8	515.1	514.2	513.5	513.5	511.9	511.9	511.1	509.6	508.8	508.8
5°	511.1	508.8	507.2	506.5	505.7	503.4	502.7	501.1	499.6	498.0	497.1
7.5°	504.1	500.3	498.7	498.0	495.7	493.3	491.7	489.5	487.2	484.8	484.0
10°	495.7	491.7	487.9	486.3	484.0	482.5	479.4	476.2	473.9	471.7	469.3
12.5°	484.8	480.2	476.2	474.8	472.4	469.3	464.7	463.1	459.3	457.7	454.6
15°	472.4	467.0	463.1	460.8	458.4	453.9	450.8	447.6	443.8	442.2	439.1
17.5°	456.9	450.8	446.9	444.5	442.9	439.1	434.5	430.6	426.7	425.1	422.9
20°	438.4	434.5	429.0	426.7	425.1	420.6	415.9	414.3	411.2	408.1	405.8
22.5°	417.5	413.6	408.1	405.8	405.1	401.1	397.3	395.0	392.7	390.3	388.0
25°	395.7	391.1	386.4	384.9	383.3	380.3	377.2	375.6	373.3	371.8	370.2
27.5°	372.5	367.8	364.0	361.7	360.1	357.8	356.3	354.7	353.1	351.6	350.9
30°	347.7	343.1	339.9	338.5	336.9	336.1	333.8	333.1	332.2	330.7	331.5
32.5°	323.0	319.1	316.0	313.6	313.6	312.2	311.3	311.3	310.6	310.6	310.6
35°	295.8	293.5	291.2	290.4	289.7	288.8	288.1	288.8	288.1	288.8	289.7
37.5°	271.1	268.8	267.2	266.4	265.6	266.4	265.6	265.6	266.4	267.9	268.8
40°	245.4	244.0	242.4	243.2	242.4	242.4	242.4	244.7	245.4	246.3	247.0
42.5°	221.5	220.0	219.1	219.1	220.0	219.1	220.7	221.5	223.1	225.4	226.9
45°	198.2	197.5	197.5	198.2	197.5	199.1	199.1	200.6	202.9	204.5	206.0
47.5°	176.6	176.6	176.6	177.3	177.3	178.1	179.7	180.4	182.0	183.5	185.1
50°	156.4	157.2	157.9	157.9	157.9	159.5	161.1	161.9	162.6	163.4	165.8
52.5°	138.6	139.4	139.4	140.2	141.0	141.7	142.6	144.0	144.8	146.4	147.1
55°	121.6	121.6	123.1	123.9	123.9	123.9	125.5	125.5	127.1	127.8	129.3
57.5°	105.3	106.1	106.1	106.9	106.9	107.7	108.4	109.1	110.0	110.7	111.5
60°	89.8	89.8	89.8	90.6	91.4	92.2	91.4	92.9	92.9	94.5	95.2
62.5°	75.1	75.8	75.8	75.8	75.8	75.8	75.8	76.7	77.4	78.3	79.0
65°	61.2	61.2	61.2	60.5	61.2	60.5	61.2	61.9	61.9	62.7	63.5
67.5°	47.2	47.2	45.7	45.7	46.5	46.5	46.5	46.5	45.7	47.2	47.2
70°	34.0	33.3	32.6	31.7	31.7	31.0	31.0	30.2	30.2	30.2	30.2
72.5°	22.5	20.9	19.4	18.6	17.8	17.8	16.2	15.5	16.2	16.2	16.2
75°	11.7	10.1	9.3	8.5	7.7	7.7	7.0	7.0	7.0	7.0	7.0
77.5°	4.7	3.8	3.1	3.1	2.3	2.3	2.3	2.3	2.3	2.3	2.3
80°	1.6	1.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
85°	0.7	0.0	0.0	0.7	0.0	0.7	0.7	0.7	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583726

CATALOG NUMBER: HCC8S10D010MB-HM80520830-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	518.1	518.1	518.1	518.1	518.1	518.1	518.1	518.1
2.5°	508.1	508.1	507.2	508.1	506.5	507.2	506.5	506.5
5°	496.4	494.9	494.9	494.9	494.1	494.1	493.3	493.3
7.5°	482.5	481.8	480.9	480.2	479.4	478.6	478.6	478.6
10°	468.5	467.0	467.0	466.3	464.7	463.9	463.9	463.9
12.5°	452.3	451.5	450.8	450.8	447.6	448.5	447.6	447.6
15°	436.8	436.0	436.0	433.7	432.1	432.1	432.1	431.4
17.5°	420.6	419.7	419.0	417.5	415.9	415.9	415.1	415.9
20°	403.5	402.7	401.1	401.1	400.4	399.7	398.1	398.8
22.5°	386.4	384.9	384.2	384.2	383.3	383.3	381.8	381.8
25°	368.7	367.8	367.1	367.8	366.4	366.4	364.8	364.8
27.5°	350.0	349.3	349.3	349.3	348.5	349.3	348.5	348.5
30°	331.5	331.5	330.7	330.7	331.5	330.7	331.5	332.2
32.5°	311.3	311.3	312.2	312.2	312.9	312.9	312.9	312.9
35°	290.4	292.0	292.0	292.7	293.5	294.2	294.2	295.1
37.5°	271.1	271.9	272.6	273.3	274.9	274.9	274.9	274.9
40°	250.1	251.0	252.4	251.7	254.8	255.5	254.8	254.8
42.5°	228.5	230.1	230.8	232.3	233.1	234.6	235.5	235.5
45°	208.3	209.1	210.7	212.2	213.0	215.3	215.3	215.3
47.5°	187.4	189.0	189.8	191.2	192.1	194.4	195.2	194.4
50°	167.3	168.9	170.3	170.3	172.7	173.4	175.0	175.9
52.5°	148.0	148.7	150.2	151.0	152.5	154.1	154.9	155.7
55°	129.3	130.1	131.6	131.6	134.0	134.7	136.3	136.3
57.5°	112.3	113.1	114.7	113.8	115.4	117.0	117.0	116.1
60°	96.0	96.0	96.0	97.6	98.3	99.2	99.9	99.9
62.5°	79.0	80.5	81.4	81.4	82.1	82.8	82.8	82.1
65°	63.5	65.0	65.9	65.9	66.6	66.6	66.6	67.4
67.5°	48.0	48.0	48.0	48.8	48.0	48.0	48.0	48.0
70°	30.2	30.2	30.2	30.2	29.4	30.2	30.2	31.0
72.5°	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2
75°	7.0	7.0	7.0	7.7	7.0	7.0	7.0	7.0
77.5°	3.1	2.3	3.1	3.1	2.3	2.3	2.3	2.3
80°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
85°	0.0	0.7	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)