

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583736

Luminaire Tested: **HCC8W10D010MW-HM80520835-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583736  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W10D010MW-HM80520835-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1147.4 lumens  
Efficiency: N/A  
Efficacy: 115.9 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583736  
CATALOG NUMBER: HCC8W10D010MW-HM80520835-81RWWC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583736

CATALOG NUMBER: HCC8W10D010MW-HM80520835-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	18619	18619	18619
5°	18863	18535	18365
10°	19056	18349	18070
15°	19247	17964	17603
20°	19151	17300	16903
25°	18703	16264	16042
30°	17768	15094	15040
35°	16172	13774	13894
40°	14177	12330	12785
45°	12232	10968	11740
50°	10712	9628	10631
55°	9494	8279	9354
60°	8548	6963	7752
65°	7698	5589	5939
70°	6762	4075	3273
75°	5755	2121	858
80°	4439	568	142
85°	2866	0	0



TEST NUMBER: P583736  
 CATALOG NUMBER: HCC8W10D010MW-HM80520835-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.0	5.0
10°-20°	160.1	14.0
20°-30°	227.3	19.8
30°-40°	239.2	20.9
40°-50°	203.5	17.7
50°-60°	147.1	12.8
60°-70°	83.7	7.3
70°-80°	26.4	2.3
80°-90°	3.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	444.4	38.7
0°-40°	683.6	59.6
0°-60°	1034.2	90.1
0°-90°	1147.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1147.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	604	604	604	604	604	
5°	609	606	599	595	593	58
15°	603	588	563	552	551	170
25°	550	522	478	470	472	252
35°	430	405	366	364	369	267
45°	280	270	252	258	269	218
55°	177	164	154	163	174	159
65°	106	91	77	76	81	105
75°	48	37	18	8	7	52
85°	8	5	0	0	0	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583736

CATALOG NUMBER: HCC8W10D010MW-HM80520835-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8
2.5°	607.0	607.7	606.2	606.2	607.7	606.2	607.0	607.0	606.2	606.2	605.3
5°	609.4	608.6	608.6	608.6	609.4	607.7	607.0	607.7	606.2	606.2	606.2
7.5°	610.1	610.1	609.4	608.6	608.6	608.6	607.7	607.0	606.2	604.5	603.8
10°	608.6	608.6	609.4	607.7	607.7	606.2	606.2	604.5	604.5	602.9	600.5
12.5°	607.0	606.2	606.2	604.5	604.5	602.9	602.9	600.5	599.7	597.3	594.9
15°	602.9	602.1	600.5	599.7	598.8	598.1	596.4	595.7	593.3	590.1	587.7
17.5°	594.9	594.0	593.3	591.6	590.1	589.2	588.4	586.0	582.7	580.3	576.4
20°	583.6	582.7	582.7	580.3	579.6	577.1	576.4	573.1	570.7	565.9	562.7
22.5°	568.3	569.0	567.5	565.9	564.2	561.8	560.3	557.0	552.9	548.1	544.0
25°	549.7	550.5	549.0	547.3	544.9	543.3	541.6	536.8	532.8	527.2	522.3
27.5°	526.4	526.4	526.4	524.8	520.7	519.9	518.3	513.5	507.8	502.9	498.1
30°	499.0	498.1	498.1	495.7	494.1	490.9	488.5	484.4	480.4	474.8	469.1
32.5°	465.9	466.7	464.3	462.6	460.2	460.2	457.0	453.8	448.9	443.3	437.6
35°	429.6	430.4	428.9	428.0	423.9	423.2	422.4	418.3	415.2	411.1	404.6
37.5°	392.6	391.7	390.9	390.9	388.5	386.9	385.2	382.8	378.0	374.8	371.5
40°	352.2	352.2	352.2	351.5	350.6	349.1	348.2	346.7	343.4	340.2	337.8
42.5°	316.0	316.0	315.2	314.3	312.8	313.6	311.9	310.4	307.1	304.7	303.0
45°	280.5	280.5	280.5	281.3	279.7	277.3	277.3	275.6	274.1	272.5	270.0
47.5°	249.1	251.5	249.9	249.1	249.9	246.7	246.7	245.1	243.4	241.8	238.6
50°	223.3	223.3	223.3	221.6	220.8	220.8	218.4	216.8	216.0	214.4	211.2
52.5°	199.9	198.3	198.3	197.5	196.6	195.1	195.1	193.4	190.3	188.6	186.2
55°	176.6	176.6	175.7	174.9	174.0	173.3	172.5	170.1	168.5	166.0	163.6
57.5°	155.5	157.2	156.4	154.8	153.1	153.1	151.6	149.9	147.5	145.1	142.7
60°	138.6	137.9	137.9	137.0	135.5	134.6	133.8	131.4	129.0	126.6	124.2
62.5°	120.9	120.9	120.9	119.2	117.7	116.8	116.1	114.4	111.2	108.8	107.2
65°	105.5	104.8	104.0	103.1	102.4	100.7	100.0	98.3	95.9	93.5	91.1
67.5°	90.3	89.4	89.4	88.7	86.3	85.5	85.5	83.1	80.7	78.1	75.7
70°	75.0	75.0	75.0	73.3	72.6	71.8	70.9	69.4	67.0	64.4	62.0
72.5°	62.0	61.3	61.3	60.5	58.1	57.2	56.4	54.8	52.4	50.7	49.2
75°	48.3	48.3	47.6	46.8	45.9	45.2	44.4	42.7	40.3	37.9	37.0
77.5°	37.0	36.3	36.3	35.5	33.9	33.1	33.1	31.5	29.0	27.4	25.8
80°	25.0	25.8	25.0	24.2	23.3	22.6	21.8	20.9	19.4	17.8	16.1
82.5°	15.3	16.1	15.3	15.3	14.5	13.7	13.7	12.1	11.3	10.5	9.6
85°	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.5	5.6	4.8	4.8
87.5°	2.4	3.2	2.4	2.4	2.4	2.4	2.4	2.4	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583736

CATALOG NUMBER: HCC8W10D010MW-HM80520835-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8
2.5°	606.2	605.3	604.5	604.5	604.5	604.5	604.5	603.8	602.9	602.9	602.9
5°	604.5	604.5	604.5	603.8	602.9	602.9	601.4	600.5	599.7	598.8	598.1
7.5°	602.9	601.4	600.5	599.7	598.8	598.8	597.3	595.7	595.7	594.0	592.5
10°	598.1	597.3	595.7	594.0	593.3	592.5	590.8	588.4	587.7	586.0	584.4
12.5°	592.5	590.8	589.2	586.0	585.1	584.4	581.2	578.8	577.1	576.4	572.3
15°	585.1	582.0	579.6	575.5	574.7	573.1	570.7	568.3	565.1	562.7	561.0
17.5°	572.3	569.0	565.1	561.0	559.4	559.4	555.3	552.2	548.1	546.5	543.3
20°	557.0	552.9	549.7	544.9	542.5	540.1	537.7	532.8	529.6	527.2	523.1
22.5°	539.2	533.6	529.6	524.8	520.7	518.3	514.2	510.2	506.2	503.8	500.5
25°	516.6	511.8	505.4	500.5	498.1	494.9	490.1	486.1	482.0	478.0	476.4
27.5°	491.7	485.2	479.6	473.9	471.5	469.1	463.5	458.7	455.4	451.4	449.8
30°	464.3	457.8	451.4	446.5	444.1	440.1	436.9	431.3	427.2	423.9	420.0
32.5°	432.8	428.0	422.4	415.2	413.5	410.2	405.4	403.0	398.2	395.8	392.6
35°	398.9	395.8	390.2	384.5	382.1	380.4	376.5	371.5	368.4	365.9	364.3
37.5°	366.7	362.8	357.1	353.0	351.5	349.1	344.1	341.7	338.5	336.9	333.7
40°	332.1	328.0	324.1	321.7	319.3	317.6	314.3	311.9	308.7	306.3	305.5
42.5°	298.2	295.8	292.6	289.3	288.6	286.2	284.5	282.1	279.7	278.9	276.5
45°	267.6	265.2	261.9	258.8	257.9	256.3	255.5	253.1	251.5	251.5	251.5
47.5°	237.0	234.5	231.4	229.7	230.5	227.3	227.3	226.5	224.9	224.9	225.7
50°	209.6	206.4	205.5	204.0	202.3	200.7	201.5	199.1	199.1	200.7	199.9
52.5°	183.8	180.5	179.7	178.1	177.3	177.3	176.6	176.6	175.7	176.6	176.6
55°	160.3	157.9	156.4	154.8	154.0	154.0	154.0	153.1	152.3	154.0	154.8
57.5°	139.4	138.6	137.0	134.6	133.8	132.9	132.2	132.2	132.2	132.2	132.9
60°	120.9	119.2	117.7	115.3	115.3	114.4	113.7	112.9	112.9	112.9	112.9
62.5°	104.8	102.4	100.0	98.3	97.5	96.8	95.9	94.4	94.4	94.4	94.4
65°	88.7	86.3	84.6	83.1	81.4	81.4	79.8	79.0	77.4	76.6	75.0
67.5°	73.3	71.8	70.1	67.7	67.0	66.1	64.4	63.7	61.3	60.5	59.6
70°	59.6	57.2	55.7	54.0	53.2	51.6	50.0	48.3	46.8	45.2	43.5
72.5°	46.8	44.4	42.7	41.1	39.5	39.5	37.0	35.5	33.1	31.5	29.0
75°	34.6	32.2	30.7	28.2	27.4	26.6	24.2	22.6	20.2	17.8	16.1
77.5°	23.3	21.8	20.2	17.8	16.1	16.1	13.7	12.1	10.5	8.1	7.2
80°	14.5	12.9	11.3	9.6	9.6	8.1	7.2	5.6	4.1	3.2	2.4
82.5°	8.1	7.2	6.5	4.8	4.8	4.1	3.2	2.4	1.6	0.8	0.8
85°	4.1	3.2	2.4	2.4	1.6	1.6	1.6	0.8	0.8	0.0	0.0
87.5°	1.6	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583736

CATALOG NUMBER: HCC8W10D010MW-HM80520835-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8
2.5°	602.1	602.1	601.4	601.4	601.4	600.5	601.4	600.5	600.5	600.5	601.4
5°	598.8	597.3	597.3	596.4	596.4	595.7	596.4	595.7	594.9	594.0	594.9
7.5°	592.5	590.8	590.1	589.2	589.2	589.2	588.4	587.7	588.4	586.0	587.7
10°	583.6	582.7	581.2	580.3	579.6	580.3	579.6	577.9	577.9	577.9	577.1
12.5°	572.3	570.7	569.9	569.0	567.5	567.5	568.3	566.6	566.6	565.1	565.1
15°	558.6	557.0	555.3	555.3	553.8	553.8	552.9	552.9	552.2	551.4	551.4
17.5°	541.6	539.2	537.7	538.5	537.7	536.8	536.8	535.3	534.4	535.3	535.3
20°	521.5	519.9	518.3	519.1	517.5	516.6	517.5	515.1	515.9	515.9	515.9
22.5°	499.0	498.1	495.7	495.7	494.1	493.3	494.1	494.1	494.9	494.1	494.1
25°	473.9	472.4	470.7	470.7	470.0	469.1	470.0	470.7	470.0	470.7	470.7
27.5°	447.4	445.0	445.0	443.3	443.3	444.1	443.3	444.1	445.0	445.0	446.5
30°	418.3	417.6	416.7	415.9	415.9	416.7	416.7	416.7	417.6	419.1	419.1
32.5°	390.9	389.3	387.8	387.8	389.3	388.5	389.3	389.3	390.9	390.9	392.6
35°	361.1	361.1	359.5	360.4	360.4	360.4	360.4	361.9	363.5	364.3	365.9
37.5°	333.7	331.3	332.1	332.1	333.0	332.1	334.5	334.5	336.1	336.1	337.8
40°	303.9	303.9	304.7	303.9	304.7	304.7	306.3	308.0	308.7	310.4	311.1
42.5°	275.6	277.3	275.6	276.5	277.3	278.1	278.9	279.7	283.0	284.5	286.9
45°	249.9	250.7	251.5	252.3	251.5	253.1	253.9	255.5	257.9	258.8	259.5
47.5°	224.9	225.7	226.5	227.3	227.3	228.9	229.7	231.4	232.9	233.8	234.5
50°	200.7	202.3	203.1	203.1	204.0	205.5	207.1	207.1	208.8	211.2	212.0
52.5°	179.0	179.0	180.5	181.4	182.2	182.2	184.6	185.3	186.2	187.8	189.4
55°	154.8	157.2	157.9	157.9	159.6	161.2	162.0	162.9	162.9	166.0	166.0
57.5°	133.8	134.6	136.2	136.2	136.2	138.6	138.6	140.3	141.1	141.8	143.5
60°	112.9	114.4	114.4	115.3	114.4	116.1	116.8	118.5	119.2	120.1	120.9
62.5°	93.5	93.5	94.4	94.4	94.4	94.4	95.9	95.9	97.5	98.3	99.2
65°	75.0	75.0	75.0	75.0	75.0	75.0	75.0	75.0	75.7	75.7	77.4
67.5°	58.1	57.2	55.7	56.4	55.7	55.7	54.8	54.8	55.7	55.7	57.2
70°	41.9	41.1	39.5	39.5	38.7	37.9	37.0	36.3	35.5	35.5	35.5
72.5°	27.4	25.8	23.3	22.6	22.6	20.9	19.4	18.5	18.5	18.5	18.5
75°	13.7	12.1	10.5	9.6	9.6	8.1	8.9	8.1	8.1	8.1	8.1
77.5°	5.6	4.1	3.2	3.2	3.2	2.4	2.4	2.4	2.4	2.4	2.4
80°	1.6	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
82.5°	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583736

CATALOG NUMBER: HCC8W10D010MW-HM80520835-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	603.8	603.8	603.8	603.8	603.8	603.8	603.8	603.8
2.5°	600.5	600.5	598.8	599.7	599.7	599.7	599.7	599.7
5°	593.3	594.0	593.3	594.0	594.0	593.3	593.3	593.3
7.5°	586.0	586.8	586.0	586.8	586.8	586.8	586.0	586.0
10°	577.1	577.1	577.1	577.1	577.1	576.4	577.1	577.1
12.5°	565.1	565.1	565.1	565.9	565.9	565.1	565.1	564.2
15°	552.2	550.5	551.4	552.2	551.4	551.4	551.4	551.4
17.5°	534.4	535.3	534.4	534.4	534.4	534.4	535.3	534.4
20°	515.9	515.9	516.6	515.9	515.9	515.9	515.9	515.1
22.5°	494.9	494.1	494.1	494.9	494.9	494.1	494.9	494.9
25°	471.5	472.4	471.5	471.5	472.4	472.4	472.4	471.5
27.5°	446.5	447.4	448.1	447.4	447.4	447.4	448.1	448.9
30°	420.7	422.4	420.7	420.7	422.4	421.5	422.4	422.4
32.5°	393.3	395.8	394.1	395.8	395.8	396.5	395.8	396.5
35°	365.9	368.4	368.4	368.4	369.1	370.0	370.0	369.1
37.5°	340.2	341.0	341.0	342.6	343.4	344.1	344.1	343.4
40°	313.6	315.2	316.0	316.0	316.0	317.6	319.3	317.6
42.5°	287.8	288.6	289.3	289.3	291.0	291.8	292.6	292.6
45°	262.8	264.4	265.2	266.0	266.8	268.4	267.6	269.2
47.5°	237.0	239.4	240.2	241.0	242.6	243.4	244.2	245.1
50°	213.6	215.2	215.2	216.8	219.2	219.2	220.8	221.6
52.5°	190.3	191.0	191.8	192.7	194.2	195.9	195.9	197.5
55°	167.7	168.5	168.5	169.2	170.1	173.3	174.0	174.0
57.5°	144.2	144.2	145.9	146.6	147.5	149.2	149.2	149.2
60°	121.8	122.5	122.5	123.3	124.2	125.7	126.6	125.7
62.5°	99.2	100.0	100.0	100.7	102.4	103.1	102.4	102.4
65°	78.1	79.0	79.0	79.8	81.4	81.4	80.7	81.4
67.5°	57.2	57.2	57.2	57.2	57.2	57.2	57.2	57.2
70°	36.3	35.5	34.6	35.5	35.5	35.5	34.6	36.3
72.5°	17.8	18.5	18.5	18.5	18.5	18.5	18.5	17.8
75°	8.1	8.1	7.2	7.2	7.2	8.1	8.1	7.2
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
80°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)