

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583761

Luminaire Tested: **HCC8W10D010BZ-HM80520840-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583761
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W10D010BZ-HM80520840-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1177.4 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583761
CATALOG NUMBER: HCC8W10D010BZ-HM80520840-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P583761

CATALOG NUMBER: HCC8W10D010BZ-HM80520840-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	19670	19670	19670
5°	20365	19560	18783
10°	20816	19216	17726
15°	21111	18567	16553
20°	21048	17668	15367
25°	20527	16522	14106
30°	19448	15193	12947
35°	17693	13751	11764
40°	15542	12233	10627
45°	13549	10758	9476
50°	11792	9427	8342
55°	10521	8285	7258
60°	9553	7259	6192
65°	8588	6311	5618
70°	7655	5383	5076
75°	6708	4539	4325
80°	5683	3694	3836
85°	4281	2760	3078



TEST NUMBER: P583761
 CATALOG NUMBER: HCC8W10D010BZ-HM80520840-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	5.1
10°-20°	164.6	14.0
20°-30°	228.5	19.4
30°-40°	236.3	20.1
40°-50°	197.8	16.8
50°-60°	143.6	12.2
60°-70°	90.6	7.7
70°-80°	44.9	3.8
80°-90°	11.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	452.9	38.5
0°-40°	689.2	58.5
0°-60°	1030.7	87.5
0°-90°	1177.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1177.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	638	638	638	638	638	
5°	658	650	632	615	607	63
15°	661	636	582	535	518	186
25°	603	564	486	433	415	276
35°	470	435	365	324	312	293
45°	311	288	247	222	217	240
55°	196	178	154	141	135	177
65°	118	103	86	76	77	117
75°	56	47	38	36	36	60
85°	12	10	8	9	9	15
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583761

CATALOG NUMBER: HCC8W10D010BZ-HM80520840-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9
2.5°	648.4	648.4	649.2	648.4	648.4	648.4	647.5	647.5	646.6	646.6	644.9
5°	657.9	656.2	657.9	656.2	656.2	656.2	655.2	653.5	652.7	650.9	650.0
7.5°	662.2	661.3	661.3	660.5	660.5	659.5	658.7	657.9	654.4	653.5	650.9
10°	664.8	663.9	663.9	663.0	661.3	661.3	659.5	658.7	654.4	652.7	649.2
12.5°	663.9	663.9	663.9	663.0	660.5	659.5	657.9	655.2	651.8	648.4	644.9
15°	661.3	661.3	659.5	658.7	656.2	654.4	653.5	649.2	645.7	641.4	636.2
17.5°	652.7	652.7	651.8	650.0	647.5	645.7	644.0	639.7	636.2	629.2	624.1
20°	641.4	640.5	639.7	637.1	634.5	633.6	631.0	624.9	620.6	615.4	608.6
22.5°	624.9	624.1	623.2	621.6	617.2	615.4	613.7	609.4	601.6	596.4	587.8
25°	603.3	603.3	601.6	599.0	594.6	592.9	590.3	586.0	579.1	571.3	564.3
27.5°	578.3	577.3	574.8	573.0	569.6	567.0	562.7	557.5	550.5	544.5	535.9
30°	546.2	546.2	544.5	541.9	537.5	535.9	532.4	526.2	519.4	511.6	505.6
32.5°	509.9	509.9	507.2	505.6	502.9	498.6	497.7	490.8	484.8	478.6	471.8
35°	470.0	470.9	469.1	465.7	461.3	461.3	459.6	453.6	446.7	440.7	435.4
37.5°	430.2	427.6	426.7	425.0	422.4	418.9	417.2	414.6	408.6	404.2	396.4
40°	386.1	386.9	385.2	383.4	382.6	380.0	379.1	374.8	370.5	365.3	361.8
42.5°	346.3	346.3	346.3	344.5	342.8	340.2	339.3	336.7	331.5	328.0	322.9
45°	310.7	308.2	308.2	307.2	306.4	304.7	302.1	300.4	296.9	294.2	288.2
47.5°	276.1	276.9	276.1	275.3	272.6	271.8	270.9	267.4	264.0	261.4	257.1
50°	245.8	247.6	245.8	245.8	244.1	243.3	241.5	239.0	236.3	232.0	227.7
52.5°	220.7	220.7	219.8	219.0	216.4	214.7	213.8	213.0	208.7	205.2	201.7
55°	195.7	196.5	196.5	193.9	193.0	191.4	190.4	187.9	186.1	180.9	178.3
57.5°	173.9	173.1	173.9	172.2	170.6	168.8	167.9	166.2	163.6	160.1	156.6
60°	154.9	153.3	153.3	152.3	150.6	149.8	148.0	145.4	142.8	139.3	136.8
62.5°	135.9	135.0	134.1	133.3	131.6	130.7	129.8	127.3	124.6	122.0	119.5
65°	117.7	117.7	116.8	115.2	114.3	113.3	112.5	110.8	107.3	105.7	103.0
67.5°	101.3	100.4	100.4	98.7	97.0	96.0	96.0	94.4	91.7	89.2	87.4
70°	84.9	85.7	84.9	84.0	82.2	82.2	80.5	79.7	76.2	75.4	72.7
72.5°	70.1	70.1	69.2	69.2	67.6	66.7	66.7	64.9	63.2	61.4	59.7
75°	56.3	56.3	56.3	55.4	54.6	52.8	52.8	51.9	50.2	48.4	46.8
77.5°	44.1	43.3	43.3	42.4	41.6	40.6	40.6	39.8	38.1	37.3	35.5
80°	32.0	31.1	31.1	31.1	29.4	30.3	29.4	28.6	27.6	26.8	26.0
82.5°	20.8	21.6	21.6	20.8	20.0	20.0	20.0	19.0	19.0	18.2	17.3
85°	12.1	12.1	12.1	12.1	11.3	11.3	11.3	10.3	10.3	10.3	9.5
87.5°	5.2	5.2	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583761

CATALOG NUMBER: HCC8W10D010BZ-HM80520840-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9
2.5°	644.9	643.2	642.2	641.4	641.4	640.5	639.7	637.9	637.9	636.2	635.4
5°	648.4	645.7	644.0	642.2	641.4	639.7	637.9	635.4	634.5	631.9	629.2
7.5°	649.2	644.9	643.2	639.7	637.9	636.2	632.7	630.2	626.7	624.1	620.6
10°	645.7	642.2	637.9	633.6	632.7	630.2	624.9	621.6	617.2	613.7	608.6
12.5°	640.5	635.4	631.0	625.9	623.2	620.6	615.4	610.3	604.2	598.1	592.9
15°	631.9	625.9	619.8	613.7	610.3	607.6	601.6	595.6	589.5	581.6	576.5
17.5°	618.9	611.9	605.9	598.1	594.6	592.1	584.3	577.3	569.6	561.8	556.5
20°	602.4	593.8	586.9	578.3	575.6	571.3	563.5	555.7	547.0	538.4	532.4
22.5°	580.8	572.2	564.3	555.7	551.4	547.0	539.2	529.7	521.1	514.2	508.1
25°	555.7	547.9	538.4	530.6	525.4	520.2	511.6	503.8	495.9	485.6	479.6
27.5°	528.0	518.5	511.6	501.2	495.9	492.6	483.0	472.6	465.7	456.2	449.3
30°	496.9	488.3	480.4	470.0	464.8	461.3	452.7	443.2	436.2	426.7	419.9
32.5°	464.0	454.5	445.0	438.0	431.9	428.5	418.9	412.9	404.2	396.4	388.6
35°	428.5	418.9	412.0	402.5	399.1	395.6	387.8	380.0	372.3	365.3	359.3
37.5°	390.4	383.4	375.6	368.8	366.1	362.6	353.1	346.3	340.2	333.3	328.0
40°	353.1	347.1	342.0	335.0	330.7	328.0	321.2	315.0	308.2	303.9	298.6
42.5°	319.4	312.5	307.2	302.1	297.7	295.2	289.1	284.8	279.6	275.3	269.2
45°	283.9	280.4	274.4	270.1	267.4	264.0	259.6	254.5	250.1	246.7	242.3
47.5°	252.8	249.3	245.0	239.8	238.0	235.5	231.1	227.7	224.2	220.7	216.4
50°	224.2	219.8	216.4	213.0	211.2	208.7	204.3	202.5	200.0	196.5	193.9
52.5°	198.2	194.7	191.4	186.9	186.1	184.4	181.7	178.3	175.7	173.9	172.2
55°	174.9	171.4	168.8	165.3	164.4	162.8	159.3	157.6	155.8	154.1	152.3
57.5°	154.1	150.6	147.1	145.4	143.6	142.0	141.1	138.5	136.8	135.9	134.1
60°	135.0	131.6	129.0	126.3	125.5	124.6	123.0	121.2	119.5	117.7	116.8
62.5°	116.8	113.3	111.7	110.0	108.2	108.2	106.5	104.7	103.0	102.2	100.4
65°	100.4	98.7	96.0	93.5	92.7	92.7	90.0	89.2	88.3	86.5	84.9
67.5°	84.9	83.1	80.5	79.7	78.7	77.9	77.0	75.4	73.6	72.7	71.0
70°	71.0	69.2	67.6	66.7	65.7	64.9	63.2	62.3	60.6	59.7	58.9
72.5°	57.1	56.3	54.6	53.6	52.8	51.9	51.1	50.2	48.4	47.6	46.8
75°	45.9	45.0	43.3	42.4	41.6	41.6	40.6	38.9	38.1	38.1	37.3
77.5°	34.6	33.8	32.9	32.0	31.1	31.1	30.3	29.4	28.6	28.6	27.6
80°	25.1	24.3	23.3	23.3	23.3	22.5	21.6	21.6	20.8	20.8	20.0
82.5°	16.5	16.5	15.6	15.6	15.6	14.7	14.7	13.8	13.8	13.8	13.8
85°	9.5	9.5	9.5	8.7	8.7	8.7	8.7	8.7	8.7	7.8	8.7
87.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583761

CATALOG NUMBER: HCC8W10D010BZ-HM80520840-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9
2.5°	634.5	633.6	631.9	631.9	630.2	630.2	629.2	628.4	627.6	626.7	625.9
5°	628.4	624.9	623.2	622.4	620.6	619.8	617.2	615.4	614.6	612.9	611.1
7.5°	617.2	613.7	610.3	609.4	608.6	605.1	602.4	599.9	598.1	596.4	594.6
10°	604.2	600.8	596.4	594.6	592.9	588.6	585.1	582.6	579.1	575.6	574.8
12.5°	588.6	583.5	578.3	576.5	574.0	569.6	566.1	561.8	559.2	554.8	554.0
15°	570.5	564.3	560.0	555.7	554.0	549.7	543.5	540.2	534.9	533.2	528.9
17.5°	548.8	542.7	536.7	534.9	532.4	526.2	520.2	515.9	510.7	508.1	505.6
20°	526.2	518.5	512.4	510.7	507.2	502.1	495.9	491.6	487.3	482.1	479.6
22.5°	500.3	491.6	486.4	482.1	481.3	475.3	468.3	464.8	461.3	457.0	453.6
25°	471.8	464.0	458.0	454.5	452.7	447.5	442.3	438.0	432.8	430.2	425.9
27.5°	442.3	437.2	429.4	425.9	423.2	418.9	412.9	410.2	405.1	401.6	399.1
30°	413.7	405.9	401.6	397.3	394.7	390.4	385.2	382.6	378.3	374.8	372.3
32.5°	382.6	377.4	371.3	369.6	366.1	361.8	358.3	354.0	350.6	347.1	346.3
35°	354.0	347.1	341.0	339.3	336.7	332.4	330.7	328.0	323.7	322.9	319.4
37.5°	322.9	319.4	312.5	309.9	309.0	305.5	302.1	300.4	297.7	295.2	294.2
40°	293.4	289.1	285.6	283.1	281.3	278.7	275.3	274.4	272.6	269.2	268.3
42.5°	265.8	261.4	257.9	257.1	254.5	251.9	250.1	247.6	246.7	245.8	244.1
45°	239.0	236.3	232.8	232.0	231.1	227.7	226.0	224.2	222.5	221.6	219.8
47.5°	214.7	212.0	209.5	208.7	206.9	206.0	203.4	202.5	200.0	199.1	198.2
50°	191.4	189.6	187.9	186.9	185.2	184.4	182.6	180.9	179.2	178.3	177.4
52.5°	170.6	168.8	167.1	166.2	165.3	163.6	161.9	160.1	159.3	158.4	157.6
55°	150.6	148.9	148.0	147.1	146.3	145.4	142.8	142.0	141.1	140.3	138.5
57.5°	132.5	130.7	129.0	129.0	128.1	127.3	125.5	123.8	123.8	122.0	120.3
60°	116.0	114.3	112.5	111.7	110.8	109.0	108.2	107.3	106.5	105.7	103.9
62.5°	98.7	97.8	96.0	96.0	94.4	93.5	92.7	91.7	90.9	89.2	88.3
65°	84.0	83.1	81.4	80.5	80.5	79.7	77.9	77.0	76.2	76.2	75.4
67.5°	70.1	69.2	67.6	66.7	66.7	65.7	64.9	64.9	64.1	63.2	64.1
70°	57.9	56.3	56.3	55.4	55.4	54.6	53.6	53.6	53.6	54.6	54.6
72.5°	45.9	45.0	44.1	44.1	44.1	44.1	43.3	43.3	44.1	45.0	45.0
75°	36.3	35.5	35.5	35.5	34.6	34.6	35.5	35.5	36.3	36.3	36.3
77.5°	26.8	26.8	26.8	26.8	26.8	26.8	27.6	27.6	28.6	28.6	28.6
80°	20.0	20.0	20.0	20.0	20.0	20.8	20.8	20.8	20.8	20.8	21.6
82.5°	13.8	13.8	13.8	13.8	13.8	13.8	13.8	14.7	14.7	14.7	14.7
85°	7.8	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583761

CATALOG NUMBER: HCC8W10D010BZ-HM80520840-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	637.9	637.9	637.9	637.9	637.9	637.9	637.9	637.9
2.5°	624.9	624.9	624.9	625.9	624.1	624.1	624.1	624.1
5°	610.3	609.4	608.6	609.4	607.6	607.6	606.8	606.8
7.5°	592.1	591.3	590.3	590.3	588.6	588.6	587.8	586.9
10°	572.2	570.5	571.3	569.6	568.7	567.8	567.0	566.1
12.5°	550.5	548.8	547.9	546.2	544.5	543.5	544.5	542.7
15°	527.2	524.6	523.7	521.9	520.2	519.4	519.4	518.5
17.5°	501.2	499.4	498.6	496.9	495.9	494.3	493.4	492.6
20°	477.0	472.6	473.5	471.8	470.9	467.5	467.5	468.3
22.5°	450.1	447.5	445.8	444.0	443.2	441.5	441.5	440.7
25°	423.2	420.7	419.9	418.1	417.2	415.5	414.6	414.6
27.5°	397.3	393.9	393.9	392.1	390.4	389.6	388.6	387.8
30°	369.6	367.0	366.1	366.1	365.3	365.3	362.6	363.6
32.5°	343.7	342.0	341.0	339.3	339.3	338.5	338.5	335.8
35°	317.7	315.0	316.0	314.2	313.4	312.5	313.4	312.5
37.5°	292.6	290.9	290.9	289.1	289.1	288.2	287.4	289.1
40°	267.4	266.6	265.8	264.9	265.8	264.9	263.1	264.0
42.5°	242.3	242.3	241.5	241.5	240.6	240.6	240.6	240.6
45°	219.8	219.0	219.0	218.2	218.2	218.2	218.2	217.3
47.5°	197.4	196.5	196.5	196.5	195.7	195.7	194.7	195.7
50°	175.7	175.7	174.9	174.9	175.7	174.9	173.9	173.9
52.5°	155.8	155.8	154.9	154.9	154.1	153.3	154.1	154.1
55°	137.6	136.8	135.9	135.9	135.0	134.1	134.1	135.0
57.5°	120.3	119.5	118.6	118.6	116.8	116.0	116.0	116.0
60°	103.9	102.2	102.2	101.3	101.3	100.4	100.4	100.4
62.5°	88.3	87.4	87.4	87.4	87.4	86.5	86.5	86.5
65°	75.4	75.4	75.4	76.2	76.2	77.0	77.0	77.0
67.5°	64.9	65.7	65.7	65.7	66.7	66.7	66.7	65.7
70°	55.4	55.4	55.4	56.3	56.3	56.3	56.3	56.3
72.5°	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9
75°	36.3	37.3	37.3	37.3	36.3	37.3	37.3	36.3
77.5°	28.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6
80°	21.6	21.6	21.6	21.6	21.6	21.6	21.6	21.6
82.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7
85°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)