

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583777

Luminaire Tested: **HCC8S10D010BZ-HM80520927-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583777  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S10D010BZ-HM80520927-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 787.8 lumens  
Efficiency: N/A  
Efficacy: 79.6 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583777  
CATALOG NUMBER: HCC8S10D010BZ-HM80520927-81WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P583777

CATALOG NUMBER: HCC8S10D010BZ-HM80520927-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	13044	13044	13044
5°	13580	13016	12465
10°	14034	12850	11861
15°	14391	12556	11244
20°	14422	12033	10685
25°	14174	11272	10129
30°	13417	10401	9657
35°	12234	9355	9068
40°	10639	8244	8369
45°	9127	7139	7662
50°	7796	6160	6884
55°	6833	5306	5984
60°	6087	4521	5032
65°	5392	3692	4020
70°	4787	2732	2272
75°	3991	1430	667
80°	3143	444	107
85°	2264	212	0



TEST NUMBER: P583777  
 CATALOG NUMBER: HCC8S10D010BZ-HM80520927-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.9	5.1
10°-20°	111.7	14.2
20°-30°	158.1	20.1
30°-40°	165.4	21.0
40°-50°	138.0	17.5
50°-60°	97.8	12.4
60°-70°	56.3	7.2
70°-80°	18.1	2.3
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.7	39.3
0°-40°	475.1	60.3
0°-60°	710.9	90.2
0°-90°	787.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	787.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	423	423	423	423	423	
5°	439	433	420	408	403	42
15°	451	432	393	362	352	127
25°	417	386	331	305	298	190
35°	325	296	248	235	241	201
45°	209	192	164	166	176	162
55°	127	114	99	104	111	115
65°	74	62	51	51	55	74
75°	34	25	12	6	6	36
85°	6	3	1	0	0	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583777

CATALOG NUMBER: HCC8S10D010BZ-HM80520927-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0
2.5°	431.8	431.2	430.6	431.2	430.6	431.2	430.6	430.6	430.0	429.2	429.2
5°	438.7	438.1	438.1	438.1	437.5	436.8	436.8	436.2	435.0	434.3	433.1
7.5°	443.2	443.8	443.8	443.8	442.6	442.6	441.3	440.1	438.7	437.5	435.6
10°	448.2	448.2	447.6	447.0	445.7	445.1	444.5	443.2	441.3	438.7	436.8
12.5°	450.1	450.1	449.5	448.2	447.6	447.0	446.3	444.5	442.0	438.7	436.2
15°	450.8	449.5	448.8	448.2	447.0	445.1	445.1	442.6	439.5	435.6	432.5
17.5°	445.7	446.3	445.1	443.8	442.0	440.7	438.7	436.8	433.1	428.6	425.5
20°	439.5	438.7	438.1	436.2	433.7	433.1	431.2	428.0	424.9	419.7	415.4
22.5°	429.2	428.6	427.4	426.1	423.6	422.4	420.5	416.6	412.2	407.1	402.1
25°	416.6	415.4	413.5	411.0	409.0	407.8	405.3	401.5	396.4	390.8	385.6
27.5°	396.4	398.3	397.0	393.3	391.4	388.8	388.1	383.1	378.8	373.0	367.3
30°	376.8	376.8	374.9	373.0	369.9	367.9	365.4	361.7	357.2	350.3	345.8
32.5°	352.2	351.5	348.9	348.3	345.8	342.1	341.4	336.3	331.9	326.8	321.2
35°	325.0	323.7	321.2	319.3	318.0	316.1	314.2	309.8	305.3	300.3	296.5
37.5°	294.0	294.0	293.4	290.2	289.0	287.6	285.7	281.4	278.9	273.7	270.0
40°	264.3	263.6	261.8	261.1	259.9	257.9	256.6	254.1	250.4	246.5	242.8
42.5°	235.2	235.8	233.3	233.9	231.4	230.2	229.5	225.7	223.8	220.0	216.8
45°	209.3	208.7	207.3	206.7	205.4	204.2	202.9	201.1	197.8	194.1	192.2
47.5°	185.2	183.3	183.3	182.7	182.1	179.6	179.0	177.1	175.1	171.3	168.8
50°	162.5	162.5	162.5	161.8	160.0	159.3	158.1	156.1	154.2	151.7	148.0
52.5°	144.1	144.1	144.1	143.5	141.0	140.4	139.7	137.1	134.6	132.8	130.3
55°	127.1	127.7	127.1	125.8	123.9	123.9	122.0	120.8	118.3	116.4	113.8
57.5°	112.5	112.5	111.3	110.6	109.4	108.8	107.5	106.3	103.0	101.2	98.0
60°	98.7	98.0	98.0	96.8	95.4	94.2	93.5	91.7	90.4	87.3	84.7
62.5°	85.9	85.9	84.7	84.7	82.2	82.2	81.6	79.7	77.8	74.6	73.3
65°	73.9	73.9	73.3	72.7	70.8	70.2	69.6	67.7	65.7	63.8	61.9
67.5°	63.2	63.2	61.9	61.3	60.1	59.4	58.2	56.9	55.1	53.1	51.2
70°	53.1	52.5	51.8	51.2	50.0	49.3	48.1	46.8	44.8	43.6	41.7
72.5°	43.0	43.0	42.3	41.1	40.5	39.8	39.2	38.0	36.1	34.1	32.9
75°	33.5	33.5	33.5	32.2	31.0	30.3	30.3	29.1	27.8	26.0	24.6
77.5°	26.0	25.2	24.6	24.6	23.4	22.7	22.1	21.5	19.6	19.0	17.7
80°	17.7	18.4	17.7	17.1	16.5	15.7	15.7	14.5	13.9	12.6	11.4
82.5°	12.0	11.4	11.4	10.7	10.7	10.1	10.1	8.9	8.2	7.6	7.0
85°	6.4	6.4	5.6	5.6	5.6	5.0	5.0	4.4	4.4	3.8	3.1
87.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583777

CATALOG NUMBER: HCC8S10D010BZ-HM80520927-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0
2.5°	428.6	427.4	426.7	426.7	426.1	425.5	424.9	424.2	423.0	423.0	421.7
5°	431.8	430.6	430.0	428.0	426.7	426.7	424.2	423.6	421.7	420.5	419.1
7.5°	434.3	431.8	430.0	428.0	426.7	425.5	423.0	420.5	417.9	415.4	414.1
10°	434.3	431.8	428.6	425.5	424.2	423.0	419.7	416.0	412.9	410.4	407.1
12.5°	433.1	429.2	425.5	423.0	420.5	418.5	414.7	411.0	407.1	402.1	399.5
15°	429.2	424.2	420.5	416.0	414.1	411.0	407.8	402.1	397.6	393.3	390.0
17.5°	421.7	415.4	411.0	406.5	403.4	401.5	396.4	391.4	386.3	381.3	377.4
20°	410.4	404.6	399.5	393.9	391.4	388.8	382.5	377.4	372.4	366.7	362.9
22.5°	396.4	390.8	383.8	379.4	375.5	372.4	366.7	361.0	355.9	350.9	345.8
25°	379.4	373.7	367.3	360.4	357.8	354.7	348.3	342.7	336.9	331.3	326.8
27.5°	361.0	353.4	348.3	340.8	338.2	335.1	328.1	321.8	316.7	312.3	307.2
30°	338.8	333.2	326.2	319.3	316.7	313.6	308.0	302.2	297.1	292.1	287.0
32.5°	314.8	309.2	302.2	297.1	293.4	290.8	285.1	280.1	275.0	270.0	265.5
35°	289.6	283.2	278.1	273.1	270.0	266.8	261.1	256.6	252.9	248.5	244.0
37.5°	263.6	259.3	254.1	248.5	245.3	242.8	238.4	233.3	230.2	226.3	223.2
40°	238.4	233.3	228.9	223.8	221.3	219.4	214.9	211.2	207.9	204.8	202.9
42.5°	212.4	207.9	203.6	200.4	198.6	196.6	193.4	189.1	187.2	184.0	182.1
45°	188.4	184.6	181.5	177.1	175.7	174.5	170.7	167.6	165.6	163.7	162.5
47.5°	165.6	163.1	159.3	156.7	154.9	153.6	151.1	148.6	146.6	145.4	144.1
50°	146.0	142.9	140.4	137.9	136.5	134.6	132.1	130.9	129.6	128.4	128.4
52.5°	127.7	124.5	122.0	120.1	118.9	117.6	115.8	115.0	113.8	113.8	113.1
55°	110.6	108.8	106.3	103.7	103.0	102.4	101.2	99.9	99.3	98.7	99.3
57.5°	96.0	94.2	91.7	89.8	89.2	88.5	87.9	86.7	85.9	85.9	85.9
60°	82.8	80.9	79.0	77.2	77.2	75.8	75.2	74.6	73.9	73.3	73.3
62.5°	70.8	68.9	67.1	65.7	65.1	64.4	63.2	62.6	61.9	61.9	61.3
65°	60.1	57.6	56.9	55.1	54.3	53.7	53.1	51.8	51.2	50.6	50.0
67.5°	49.3	48.1	46.2	44.8	44.2	43.6	43.0	41.7	41.1	40.5	39.2
70°	39.8	38.6	37.3	36.1	35.5	34.7	33.5	32.2	31.6	30.3	28.5
72.5°	31.0	29.7	28.5	27.2	26.6	26.0	24.6	23.4	22.1	20.9	19.6
75°	23.4	22.1	20.2	19.0	18.4	18.4	16.5	15.1	13.9	12.0	10.7
77.5°	16.5	14.5	13.9	12.6	12.0	10.7	9.5	8.2	7.0	6.4	5.0
80°	10.7	9.5	8.2	7.6	7.0	6.4	5.6	4.4	3.1	2.5	1.9
82.5°	6.4	5.6	5.0	4.4	3.8	3.1	2.5	2.5	1.9	1.3	0.6
85°	3.1	2.5	1.9	1.9	1.3	1.3	1.3	0.6	0.6	0.6	0.6
87.5°	1.3	0.6	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583777

CATALOG NUMBER: HCC8S10D010BZ-HM80520927-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0
2.5°	421.1	420.5	419.7	419.1	419.1	417.9	417.9	417.2	416.0	415.4	415.4
5°	417.2	415.4	414.1	413.5	412.9	411.0	410.4	409.0	407.8	406.5	405.9
7.5°	411.6	408.4	407.1	406.5	404.6	402.7	401.5	399.5	397.6	395.8	395.1
10°	404.6	401.5	398.3	397.0	395.1	393.9	391.4	388.8	386.9	385.0	383.1
12.5°	395.8	392.0	388.8	387.5	385.6	383.1	379.4	378.0	374.9	373.7	371.1
15°	385.6	381.3	378.0	376.2	374.3	370.5	367.9	365.4	362.3	361.0	358.4
17.5°	373.0	367.9	364.8	362.9	361.7	358.4	354.7	351.5	348.3	347.1	345.2
20°	357.8	354.7	350.3	348.3	347.1	343.3	339.4	338.2	335.7	333.2	331.3
22.5°	340.8	337.6	333.2	331.3	330.7	327.5	324.3	322.4	320.6	318.7	316.7
25°	323.1	319.3	315.5	314.2	313.0	310.5	308.0	306.6	304.7	303.5	302.2
27.5°	304.1	300.3	297.1	295.2	294.0	292.1	290.8	289.6	288.2	287.0	286.4
30°	283.9	280.1	277.5	276.3	275.0	274.4	272.5	271.9	271.2	270.0	270.6
32.5°	263.6	260.5	257.9	256.0	256.0	254.8	254.1	254.1	253.5	253.5	253.5
35°	241.5	239.6	237.8	237.0	236.4	235.8	235.2	235.8	235.2	235.8	236.4
37.5°	221.3	219.4	218.2	217.4	216.8	217.4	216.8	216.8	217.4	218.8	219.4
40°	200.4	199.2	197.8	198.6	197.8	197.8	197.8	199.8	200.4	201.1	201.7
42.5°	180.8	179.6	179.0	179.0	179.6	179.0	180.2	180.8	182.1	184.0	185.2
45°	161.8	161.2	161.2	161.8	161.2	162.5	162.5	163.7	165.6	167.0	168.2
47.5°	144.1	144.1	144.1	144.7	144.7	145.4	146.6	147.4	148.6	149.9	151.1
50°	127.7	128.4	129.0	129.0	129.0	130.3	131.5	132.1	132.8	133.4	135.3
52.5°	113.1	113.8	113.8	114.4	115.0	115.8	116.4	117.6	118.3	119.5	120.1
55°	99.3	99.3	100.5	101.2	101.2	101.2	102.4	102.4	103.7	104.3	105.5
57.5°	85.9	86.7	86.7	87.3	87.3	87.9	88.5	89.2	89.8	90.4	91.0
60°	73.3	73.3	73.3	73.9	74.6	75.2	74.6	75.8	75.8	77.2	77.8
62.5°	61.3	61.9	61.9	61.9	61.9	61.9	61.9	62.6	63.2	63.8	64.4
65°	50.0	50.0	50.0	49.3	50.0	49.3	50.0	50.6	50.6	51.2	51.8
67.5°	38.6	38.6	37.3	37.3	38.0	38.0	38.0	38.0	37.3	38.6	38.6
70°	27.8	27.2	26.6	26.0	26.0	25.2	25.2	24.6	24.6	24.6	24.6
72.5°	18.4	17.1	15.7	15.1	14.5	14.5	13.2	12.6	13.2	13.2	13.2
75°	9.5	8.2	7.6	7.0	6.4	6.4	5.6	5.6	5.6	5.6	5.6
77.5°	3.8	3.1	2.5	2.5	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.3	1.3	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
82.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
85°	0.6	0.0	0.0	0.6	0.0	0.6	0.6	0.6	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583777

CATALOG NUMBER: HCC8S10D010BZ-HM80520927-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	423.0	423.0	423.0	423.0	423.0	423.0	423.0	423.0
2.5°	414.7	414.7	414.1	414.7	413.5	414.1	413.5	413.5
5°	405.3	404.0	404.0	404.0	403.4	403.4	402.7	402.7
7.5°	393.9	393.3	392.6	392.0	391.4	390.8	390.8	390.8
10°	382.5	381.3	381.3	380.6	379.4	378.8	378.8	378.8
12.5°	369.3	368.5	367.9	367.9	365.4	366.0	365.4	365.4
15°	356.6	355.9	355.9	354.0	352.8	352.8	352.8	352.2
17.5°	343.3	342.7	342.1	340.8	339.4	339.4	338.8	339.4
20°	329.3	328.7	327.5	327.5	326.8	326.2	325.0	325.6
22.5°	315.5	314.2	313.6	313.6	313.0	313.0	311.7	311.7
25°	301.0	300.3	299.7	300.3	299.1	299.1	297.7	297.7
27.5°	285.7	285.1	285.1	285.1	284.5	285.1	284.5	284.5
30°	270.6	270.6	270.0	270.0	270.6	270.0	270.6	271.2
32.5°	254.1	254.1	254.8	254.8	255.4	255.4	255.4	255.4
35°	237.0	238.4	238.4	239.0	239.6	240.3	240.3	240.9
37.5°	221.3	221.9	222.5	223.2	224.4	224.4	224.4	224.4
40°	204.2	204.8	206.1	205.4	207.9	208.7	207.9	207.9
42.5°	186.6	187.8	188.4	189.7	190.3	191.6	192.2	192.2
45°	170.1	170.7	172.0	173.2	173.8	175.7	175.7	175.7
47.5°	153.0	154.2	154.9	156.1	156.7	158.7	159.3	158.7
50°	136.5	137.9	139.1	139.1	141.0	141.6	142.9	143.5
52.5°	120.8	121.4	122.6	123.3	124.5	125.8	126.5	127.1
55°	105.5	106.3	107.5	107.5	109.4	110.0	111.3	111.3
57.5°	91.7	92.3	93.5	92.9	94.2	95.4	95.4	94.8
60°	78.4	78.4	78.4	79.7	80.3	80.9	81.6	81.6
62.5°	64.4	65.7	66.4	66.4	67.1	67.7	67.7	67.1
65°	51.8	53.1	53.7	53.7	54.3	54.3	54.3	55.1
67.5°	39.2	39.2	39.2	39.8	39.2	39.2	39.2	39.2
70°	24.6	24.6	24.6	24.6	24.0	24.6	24.6	25.2
72.5°	13.2	13.2	13.2	13.2	13.2	13.2	13.2	13.2
75°	5.6	5.6	5.6	6.4	5.6	5.6	5.6	5.6
77.5°	2.5	1.9	2.5	2.5	1.9	1.9	1.9	1.9
80°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
82.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
85°	0.0	0.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)