

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583778

Luminaire Tested: **HCC8W10D010BZ-HM80520927-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583778  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W10D010BZ-HM80520927-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 859.9 lumens  
Efficiency: N/A  
Efficacy: 86.9 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583778  
CATALOG NUMBER: HCC8W10D010BZ-HM80520927-81WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583778

CATALOG NUMBER: HCC8W10D010BZ-HM80520927-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	14367	14367	14367
5°	14870	14288	13719
10°	15202	14034	12948
15°	15419	13565	12093
20°	15371	12906	11226
25°	14994	12068	10303
30°	14204	11099	9454
35°	12923	10043	8594
40°	11352	8932	7761
45°	9895	7858	6921
50°	8616	6884	6097
55°	7683	6048	5306
60°	6975	5298	4521
65°	6268	4611	4108
70°	5581	3931	3706
75°	4897	3312	3169
80°	4155	2681	2788
85°	3149	1981	2264



TEST NUMBER: P583778  
 CATALOG NUMBER: HCC8W10D010BZ-HM80520927-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.6	5.1
10°-20°	120.3	14.0
20°-30°	166.9	19.4
30°-40°	172.6	20.1
40°-50°	144.5	16.8
50°-60°	104.9	12.2
60°-70°	66.2	7.7
70°-80°	32.8	3.8
80°-90°	8.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	330.8	38.5
0°-40°	503.4	58.5
0°-60°	752.8	87.5
0°-90°	859.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	859.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	466	466	466	466	466	
5°	480	475	462	449	443	46
15°	483	465	425	391	379	136
25°	441	412	355	316	303	202
35°	343	318	267	236	228	214
45°	227	210	180	162	159	176
55°	143	130	112	103	99	129
65°	86	75	63	56	56	86
75°	41	34	28	27	27	44
85°	9	7	6	6	6	11
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583778

CATALOG NUMBER: HCC8W10D010BZ-HM80520927-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9
2.5°	473.6	473.6	474.2	473.6	473.6	473.6	472.9	472.9	472.3	472.3	470.9
5°	480.4	479.2	480.4	479.2	479.2	479.2	478.6	477.3	476.7	475.4	474.8
7.5°	483.7	483.0	483.0	482.4	482.4	481.8	481.2	480.4	477.9	477.3	475.4
10°	485.5	484.9	484.9	484.3	483.0	483.0	481.8	481.2	477.9	476.7	474.2
12.5°	484.9	484.9	484.9	484.3	482.4	481.8	480.4	478.6	476.1	473.6	470.9
15°	483.0	483.0	481.8	481.2	479.2	477.9	477.3	474.2	471.7	468.4	464.7
17.5°	476.7	476.7	476.1	474.8	472.9	471.7	470.3	467.2	464.7	459.6	455.8
20°	468.4	467.8	467.2	465.3	463.4	462.8	460.8	456.5	453.3	449.5	444.5
22.5°	456.5	455.8	455.2	453.9	450.8	449.5	448.2	445.1	439.5	435.6	429.2
25°	440.7	440.7	439.5	437.5	434.3	433.1	431.2	428.0	423.0	417.2	412.2
27.5°	422.3	421.7	419.7	418.5	416.0	414.1	411.0	407.1	402.1	397.6	391.4
30°	398.9	398.9	397.6	395.8	392.6	391.4	388.8	384.4	379.4	373.6	369.3
32.5°	372.4	372.4	370.5	369.3	367.3	364.2	363.5	358.4	354.0	349.7	344.6
35°	343.3	343.9	342.7	340.2	336.9	336.9	335.7	331.3	326.2	321.8	318.0
37.5°	314.2	312.3	311.7	310.5	308.6	306.0	304.7	302.8	298.5	295.2	289.6
40°	282.0	282.6	281.4	280.1	279.5	277.5	276.9	273.7	270.6	266.8	264.3
42.5°	252.9	252.9	252.9	251.6	250.4	248.5	247.9	245.9	242.1	239.6	235.8
45°	226.9	225.0	225.0	224.4	223.8	222.5	220.7	219.4	216.8	214.9	210.5
47.5°	201.7	202.3	201.7	201.1	199.2	198.6	197.8	195.3	192.8	190.9	187.8
50°	179.6	180.8	179.6	179.6	178.3	177.7	176.3	174.5	172.6	169.5	166.2
52.5°	161.2	161.2	160.6	160.0	158.1	156.7	156.1	155.5	152.4	149.9	147.4
55°	142.9	143.5	143.5	141.6	141.0	139.7	139.1	137.1	135.9	132.1	130.3
57.5°	127.1	126.5	127.1	125.8	124.5	123.3	122.6	121.4	119.5	117.0	114.4
60°	113.1	111.9	111.9	111.3	110.0	109.4	108.1	106.3	104.3	101.8	99.9
62.5°	99.3	98.7	98.0	97.4	96.0	95.4	94.8	92.9	91.0	89.2	87.3
65°	85.9	85.9	85.3	84.1	83.4	82.8	82.2	80.9	78.4	77.2	75.2
67.5°	73.9	73.3	73.3	72.1	70.8	70.2	70.2	68.9	67.1	65.1	63.8
70°	61.9	62.6	61.9	61.3	60.1	60.1	58.8	58.2	55.7	55.1	53.1
72.5°	51.2	51.2	50.6	50.6	49.3	48.7	48.7	47.4	46.2	44.8	43.6
75°	41.1	41.1	41.1	40.5	39.8	38.6	38.6	38.0	36.7	35.5	34.1
77.5°	32.2	31.6	31.6	31.0	30.3	29.7	29.7	29.1	27.8	27.2	26.0
80°	23.4	22.7	22.7	22.7	21.5	22.1	21.5	20.9	20.2	19.6	19.0
82.5°	15.1	15.7	15.7	15.1	14.5	14.5	14.5	13.9	13.9	13.2	12.6
85°	8.9	8.9	8.9	8.9	8.2	8.2	8.2	7.6	7.6	7.6	7.0
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.1	3.1	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583778

CATALOG NUMBER: HCC8W10D010BZ-HM80520927-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9
2.5°	470.9	469.7	469.1	468.4	468.4	467.8	467.2	465.9	465.9	464.7	464.1
5°	473.6	471.7	470.3	469.1	468.4	467.2	465.9	464.1	463.4	461.6	459.6
7.5°	474.2	470.9	469.7	467.2	465.9	464.7	462.2	460.2	457.7	455.8	453.3
10°	471.7	469.1	465.9	462.8	462.2	460.2	456.5	453.9	450.8	448.2	444.5
12.5°	467.8	464.1	460.8	457.1	455.2	453.3	449.5	445.7	441.3	436.8	433.1
15°	461.6	457.1	452.7	448.2	445.7	443.8	439.5	435.0	430.6	424.9	421.1
17.5°	452.1	447.0	442.6	436.8	434.3	432.5	426.7	421.7	416.0	410.4	406.5
20°	440.1	433.7	428.6	422.3	420.5	417.2	411.6	405.9	399.5	393.3	388.8
22.5°	424.2	417.9	412.2	405.9	402.7	399.5	393.9	386.9	380.6	375.5	371.1
25°	405.9	400.1	393.3	387.5	383.8	380.0	373.6	367.9	362.3	354.7	350.3
27.5°	385.6	378.8	373.6	366.0	362.3	359.8	352.8	345.2	340.2	333.2	328.1
30°	362.9	356.5	350.9	343.3	339.4	336.9	330.7	323.7	318.7	311.7	306.6
32.5°	338.8	331.9	324.9	319.9	315.5	313.0	306.0	301.6	295.2	289.6	283.9
35°	313.0	306.0	301.0	294.0	291.5	289.0	283.2	277.5	271.9	266.8	262.4
37.5°	285.1	280.1	274.4	269.4	267.4	264.9	257.9	252.9	248.5	243.4	239.6
40°	257.9	253.5	249.8	244.7	241.5	239.6	234.5	230.2	225.0	221.9	218.2
42.5°	233.3	228.3	224.4	220.7	217.4	215.6	211.2	207.9	204.2	201.1	196.6
45°	207.3	204.8	200.4	197.2	195.3	192.8	189.7	185.8	182.7	180.2	177.1
47.5°	184.6	182.1	178.9	175.1	173.8	172.0	168.8	166.2	163.7	161.2	158.1
50°	163.7	160.6	158.1	155.5	154.2	152.4	149.2	148.0	146.0	143.5	141.6
52.5°	144.7	142.2	139.7	136.5	135.9	134.6	132.8	130.3	128.4	127.1	125.8
55°	127.7	125.1	123.3	120.8	120.1	118.9	116.4	115.0	113.8	112.5	111.3
57.5°	112.5	110.0	107.5	106.3	104.9	103.7	103.0	101.2	99.9	99.3	98.0
60°	98.7	96.0	94.2	92.3	91.7	91.0	89.8	88.5	87.3	85.9	85.3
62.5°	85.3	82.8	81.6	80.3	79.0	79.0	77.8	76.4	75.2	74.6	73.3
65°	73.3	72.1	70.2	68.3	67.7	67.7	65.7	65.1	64.4	63.2	61.9
67.5°	61.9	60.7	58.8	58.2	57.6	56.9	56.3	55.1	53.7	53.1	51.8
70°	51.8	50.6	49.3	48.7	48.1	47.4	46.2	45.6	44.2	43.6	43.0
72.5°	41.7	41.1	39.8	39.2	38.6	38.0	37.3	36.7	35.5	34.7	34.1
75°	33.5	32.9	31.6	31.0	30.3	30.3	29.7	28.5	27.8	27.8	27.2
77.5°	25.2	24.6	24.0	23.4	22.7	22.7	22.1	21.5	20.9	20.9	20.2
80°	18.4	17.7	17.1	17.1	17.1	16.5	15.7	15.7	15.1	15.1	14.5
82.5°	12.0	12.0	11.4	11.4	11.4	10.7	10.7	10.1	10.1	10.1	10.1
85°	7.0	7.0	7.0	6.4	6.4	6.4	6.4	6.4	6.4	5.6	6.4
87.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583778

CATALOG NUMBER: HCC8W10D010BZ-HM80520927-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9
2.5°	463.4	462.8	461.6	461.6	460.2	460.2	459.6	459.0	458.3	457.7	457.1
5°	459.0	456.5	455.2	454.6	453.3	452.7	450.8	449.5	448.8	447.6	446.3
7.5°	450.8	448.2	445.7	445.1	444.5	442.0	440.1	438.1	436.8	435.6	434.3
10°	441.3	438.7	435.6	434.3	433.1	430.0	427.4	425.5	423.0	420.5	419.7
12.5°	430.0	426.1	422.3	421.1	419.1	416.0	413.5	410.4	408.4	405.2	404.6
15°	416.6	412.2	409.0	405.9	404.6	401.5	397.0	394.5	390.8	389.4	386.3
17.5°	400.9	396.4	392.0	390.8	388.8	384.4	380.0	376.8	373.0	371.1	369.3
20°	384.4	378.8	374.3	373.0	370.5	366.7	362.3	359.2	355.9	352.2	350.3
22.5°	365.4	359.2	355.3	352.2	351.5	347.1	342.1	339.4	336.9	333.8	331.3
25°	344.6	338.8	334.4	331.9	330.7	326.8	323.1	319.9	316.1	314.2	311.1
27.5°	323.1	319.3	313.6	311.1	309.2	306.0	301.6	299.7	295.9	293.4	291.5
30°	302.2	296.5	293.4	290.2	288.2	285.1	281.4	279.5	276.2	273.7	271.9
32.5°	279.5	275.6	271.2	270.0	267.4	264.3	261.8	258.6	256.0	253.5	252.9
35°	258.6	253.5	249.1	247.9	245.9	242.8	241.5	239.6	236.4	235.8	233.3
37.5°	235.8	233.3	228.3	226.3	225.7	223.2	220.7	219.4	217.4	215.6	214.9
40°	214.3	211.2	208.7	206.7	205.4	203.6	201.1	200.4	199.2	196.6	196.0
42.5°	194.1	190.9	188.4	187.8	185.8	184.0	182.7	180.8	180.2	179.6	178.3
45°	174.5	172.6	170.1	169.5	168.8	166.2	165.0	163.7	162.5	161.8	160.6
47.5°	156.7	154.9	153.0	152.4	151.1	150.5	148.6	148.0	146.0	145.4	144.7
50°	139.7	138.5	137.1	136.5	135.3	134.6	133.4	132.1	130.9	130.3	129.6
52.5°	124.5	123.3	122.0	121.4	120.8	119.5	118.3	117.0	116.4	115.8	115.0
55°	110.0	108.8	108.1	107.5	106.9	106.3	104.3	103.7	103.0	102.4	101.2
57.5°	96.8	95.4	94.2	94.2	93.5	92.9	91.7	90.4	90.4	89.2	87.9
60°	84.7	83.4	82.2	81.6	80.9	79.7	79.0	78.4	77.8	77.2	75.8
62.5°	72.1	71.4	70.2	70.2	68.9	68.3	67.7	67.1	66.4	65.1	64.4
65°	61.3	60.7	59.4	58.8	58.8	58.2	56.9	56.3	55.7	55.7	55.1
67.5°	51.2	50.6	49.3	48.7	48.7	48.1	47.4	47.4	46.8	46.2	46.8
70°	42.3	41.1	41.1	40.5	40.5	39.8	39.2	39.2	39.2	39.8	39.8
72.5°	33.5	32.9	32.2	32.2	32.2	32.2	31.6	31.6	32.2	32.9	32.9
75°	26.6	26.0	26.0	26.0	25.2	25.2	26.0	26.0	26.6	26.6	26.6
77.5°	19.6	19.6	19.6	19.6	19.6	19.6	20.2	20.2	20.9	20.9	20.9
80°	14.5	14.5	14.5	14.5	14.5	15.1	15.1	15.1	15.1	15.1	15.7
82.5°	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.7	10.7	10.7	10.7
85°	5.6	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583778

CATALOG NUMBER: HCC8W10D010BZ-HM80520927-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	465.9	465.9	465.9	465.9	465.9	465.9	465.9	465.9
2.5°	456.5	456.5	456.5	457.1	455.8	455.8	455.8	455.8
5°	445.7	445.1	444.5	445.1	443.8	443.8	443.2	443.2
7.5°	432.5	431.8	431.2	431.2	430.0	430.0	429.2	428.6
10°	417.9	416.6	417.2	416.0	415.4	414.7	414.1	413.5
12.5°	402.1	400.9	400.1	398.9	397.6	397.0	397.6	396.4
15°	385.0	383.1	382.5	381.3	380.0	379.4	379.4	378.8
17.5°	366.0	364.8	364.2	362.9	362.3	361.0	360.4	359.8
20°	348.3	345.2	345.8	344.6	343.9	341.4	341.4	342.1
22.5°	328.7	326.8	325.6	324.3	323.7	322.4	322.4	321.8
25°	309.2	307.2	306.6	305.3	304.7	303.5	302.8	302.8
27.5°	290.2	287.6	287.6	286.4	285.1	284.5	283.9	283.2
30°	270.0	268.0	267.4	267.4	266.8	266.8	264.9	265.5
32.5°	251.0	249.8	249.1	247.9	247.9	247.3	247.3	245.3
35°	232.0	230.2	230.8	229.5	228.9	228.3	228.9	228.3
37.5°	213.7	212.4	212.4	211.2	211.2	210.5	209.9	211.2
40°	195.3	194.7	194.1	193.4	194.1	193.4	192.2	192.8
42.5°	177.1	177.1	176.3	176.3	175.7	175.7	175.7	175.7
45°	160.6	160.0	160.0	159.3	159.3	159.3	159.3	158.7
47.5°	144.1	143.5	143.5	143.5	142.9	142.9	142.2	142.9
50°	128.4	128.4	127.7	127.7	128.4	127.7	127.1	127.1
52.5°	113.8	113.8	113.1	113.1	112.5	111.9	112.5	112.5
55°	100.5	99.9	99.3	99.3	98.7	98.0	98.0	98.7
57.5°	87.9	87.3	86.7	86.7	85.3	84.7	84.7	84.7
60°	75.8	74.6	74.6	73.9	73.9	73.3	73.3	73.3
62.5°	64.4	63.8	63.8	63.8	63.8	63.2	63.2	63.2
65°	55.1	55.1	55.1	55.7	55.7	56.3	56.3	56.3
67.5°	47.4	48.1	48.1	48.1	48.7	48.7	48.7	48.1
70°	40.5	40.5	40.5	41.1	41.1	41.1	41.1	41.1
72.5°	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5
75°	26.6	27.2	27.2	27.2	26.6	27.2	27.2	26.6
77.5°	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9
80°	15.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7
82.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
85°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)