

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583796

Luminaire Tested: **HCC8S10D010BZ-HM80520930-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583796  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S10D010BZ-HM80520930-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 991.6 lumens  
Efficiency: N/A  
Efficacy: 100.2 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583796  
CATALOG NUMBER: HCC8S10D010BZ-HM80520930-81WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P583796

CATALOG NUMBER: HCC8S10D010BZ-HM80520930-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	15205	15205	15205
5°	15762	15152	14632
10°	16204	15020	14034
15°	16565	14755	13415
20°	16591	14179	12870
25°	16274	13388	12412
30°	15432	12416	11868
35°	14022	11308	11335
40°	12261	10148	10683
45°	10623	9040	9956
50°	9307	8026	9072
55°	8285	7113	8209
60°	7475	6389	7216
65°	6742	5618	6290
70°	6059	4733	4670
75°	5338	3753	3503
80°	4475	3108	3356
85°	3503	2724	2972



TEST NUMBER: P583796  
 CATALOG NUMBER: HCC8S10D010BZ-HM80520930-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.5	4.7
10°-20°	131.0	13.2
20°-30°	187.2	18.9
30°-40°	198.9	20.1
40°-50°	171.3	17.3
50°-60°	128.0	12.9
60°-70°	81.7	8.2
70°-80°	37.2	3.7
80°-90°	9.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.7	36.8
0°-40°	563.6	56.8
0°-60°	863.0	87.0
0°-90°	991.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	991.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	493	493	493	493	493	
5°	509	502	490	477	473	49
15°	519	501	462	431	420	146
25°	478	448	394	370	365	219
35°	372	347	300	293	301	232
45°	244	230	207	213	228	189
55°	154	142	132	144	153	139
65°	92	82	77	80	86	92
75°	45	38	32	29	29	48
85°	10	8	8	8	8	12
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583796

CATALOG NUMBER: HCC8S10D010BZ-HM80520930-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1
2.5°	502.1	500.8	501.4	500.8	501.4	501.4	500.0	500.0	500.0	500.0	497.9
5°	509.2	508.4	508.4	507.7	507.0	507.7	507.0	506.3	505.0	504.2	502.1
7.5°	513.3	513.3	513.3	513.3	512.7	511.9	511.2	509.8	508.4	507.0	505.6
10°	517.5	518.2	517.5	516.9	516.1	514.7	514.0	512.7	510.5	508.4	507.0
12.5°	519.6	519.6	518.9	518.9	517.5	516.9	514.7	512.7	510.5	508.4	505.0
15°	518.9	518.9	518.2	517.5	515.4	514.7	513.3	511.2	507.7	505.0	501.4
17.5°	514.7	514.0	512.7	512.7	509.8	509.2	507.7	505.0	501.4	497.1	493.1
20°	505.6	505.6	505.0	504.2	501.4	499.3	497.9	494.4	491.6	486.7	482.5
22.5°	493.1	494.4	493.1	491.6	488.1	487.4	485.2	481.0	477.0	471.3	466.4
25°	478.3	477.6	477.0	475.5	472.7	471.3	468.5	464.3	460.1	453.8	448.2
27.5°	459.4	456.6	456.6	453.8	451.7	449.5	448.2	444.0	438.4	433.4	426.5
30°	433.4	434.2	430.7	430.0	426.5	425.0	422.3	418.1	413.1	407.6	401.9
32.5°	405.4	403.4	403.4	400.6	397.7	395.7	395.0	390.0	385.8	380.3	374.7
35°	372.5	372.5	370.5	369.7	367.0	365.5	363.5	360.6	355.8	350.9	346.7
37.5°	340.3	339.0	338.2	336.8	334.8	332.6	332.6	327.8	327.1	321.4	315.9
40°	304.6	306.0	304.6	302.5	301.8	300.4	299.8	296.9	294.9	289.9	286.4
42.5°	274.5	273.1	273.1	272.4	269.6	269.6	268.2	266.8	263.4	261.9	257.7
45°	243.6	245.1	243.0	243.6	240.9	240.9	240.9	238.1	235.4	233.2	230.4
47.5°	217.1	217.8	217.8	215.6	215.0	215.0	213.6	212.2	210.1	207.3	205.2
50°	194.0	194.7	193.3	192.6	191.2	190.5	190.5	187.6	186.3	183.4	182.1
52.5°	173.0	173.0	172.2	172.2	170.2	170.2	168.8	166.7	165.3	163.8	160.3
55°	154.1	154.1	153.4	152.7	152.7	150.6	149.9	147.7	146.4	143.5	141.5
57.5°	135.8	136.5	135.8	135.1	134.5	133.8	132.3	130.3	128.9	126.8	125.4
60°	121.2	121.2	120.4	119.7	118.4	117.7	117.0	115.5	113.5	112.0	110.0
62.5°	107.1	106.5	105.8	105.1	103.6	103.6	102.3	100.8	98.7	97.4	95.9
65°	92.4	92.4	91.7	91.7	91.0	89.7	88.9	88.2	85.5	84.7	82.0
67.5°	79.1	79.8	78.5	78.5	77.0	77.0	76.3	74.3	73.6	72.1	70.7
70°	67.2	67.2	67.2	66.5	65.1	64.4	63.7	62.4	61.7	60.2	58.8
72.5°	55.3	55.3	54.6	54.6	54.0	53.2	52.5	51.1	51.1	49.8	48.3
75°	44.8	44.8	44.1	43.4	42.7	42.7	42.1	41.3	39.9	39.2	38.5
77.5°	34.3	34.3	34.3	33.7	32.9	32.9	32.9	31.5	30.2	30.2	29.4
80°	25.2	25.2	24.5	24.5	23.8	23.8	23.8	23.1	22.4	21.8	21.0
82.5°	16.8	16.8	16.8	16.8	16.1	16.1	16.1	15.4	14.7	14.7	14.7
85°	9.9	9.9	9.9	9.9	9.1	9.1	9.1	9.1	9.1	8.4	8.4
87.5°	4.2	3.5	4.2	3.5	4.2	3.5	4.2	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583796

CATALOG NUMBER: HCC8S10D010BZ-HM80520930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1
2.5°	498.6	497.9	497.1	496.5	496.5	495.8	494.4	493.7	493.1	492.3	492.3
5°	501.4	500.8	499.3	497.9	497.1	495.8	494.4	493.1	491.6	489.5	488.9
7.5°	503.5	501.4	500.0	497.1	496.5	495.1	493.1	490.9	488.1	485.2	483.2
10°	503.5	500.8	498.6	495.1	493.7	492.3	489.5	486.0	482.5	479.7	476.2
12.5°	502.1	498.6	495.1	491.6	489.5	487.4	483.2	479.7	475.5	471.3	468.5
15°	497.1	493.1	488.9	484.6	482.5	479.7	475.5	470.6	466.4	462.2	457.2
17.5°	488.1	483.9	479.0	474.1	471.3	469.1	462.9	459.4	453.0	448.8	444.7
20°	476.2	471.3	464.9	460.1	456.6	454.5	449.5	443.3	438.4	432.1	427.9
22.5°	460.8	454.5	448.2	443.3	439.8	436.9	430.7	424.4	420.2	414.6	409.6
25°	442.6	436.3	430.0	423.0	419.5	416.6	411.1	405.4	399.9	393.5	389.3
27.5°	420.8	413.8	408.3	401.9	398.5	394.3	388.0	382.4	376.7	372.5	367.0
30°	397.0	389.3	383.8	377.4	373.9	370.5	364.2	358.6	353.6	348.7	345.9
32.5°	368.4	362.8	357.1	350.9	348.1	345.9	339.7	334.0	328.4	324.2	322.1
35°	341.0	334.8	329.8	324.2	320.7	318.7	313.0	308.1	305.3	300.4	297.6
37.5°	312.3	307.5	301.8	296.2	294.1	292.0	287.9	283.0	278.7	275.3	273.8
40°	282.2	278.0	273.1	269.6	267.6	265.4	261.9	258.4	255.7	252.1	250.7
42.5°	253.5	250.7	246.5	242.3	240.2	239.6	235.4	232.5	231.1	229.7	228.3
45°	227.5	223.5	220.6	217.8	215.6	214.3	212.2	210.1	208.7	207.3	205.9
47.5°	202.4	198.9	196.0	194.0	191.8	191.2	189.8	187.6	186.3	186.3	186.3
50°	179.2	176.5	173.7	172.2	171.5	170.2	168.8	168.0	167.3	167.3	167.3
52.5°	159.0	156.1	154.1	152.7	152.7	151.2	149.9	149.2	149.2	149.2	149.2
55°	140.0	138.0	136.5	135.1	133.8	133.1	133.1	133.1	132.3	132.3	133.1
57.5°	123.2	121.9	119.7	118.4	117.7	117.7	117.0	116.2	117.0	117.7	118.4
60°	107.8	106.5	105.8	103.6	103.6	103.6	102.9	102.9	102.9	103.6	104.3
62.5°	93.9	93.2	91.7	91.0	90.4	90.4	89.7	89.7	89.7	89.7	90.4
65°	81.3	79.8	78.5	78.5	78.5	77.8	77.8	76.3	77.0	77.0	76.3
67.5°	69.4	67.9	67.2	66.5	65.9	65.9	65.1	64.4	63.7	63.7	63.7
70°	58.2	56.7	56.7	55.3	55.3	54.6	54.0	54.0	53.2	52.5	51.8
72.5°	46.9	46.3	45.6	44.8	44.8	44.8	44.1	43.4	42.7	42.1	40.6
75°	37.1	37.1	35.7	35.0	35.0	34.3	33.7	32.9	32.2	31.5	30.8
77.5°	28.7	28.0	26.6	26.0	26.0	26.0	25.2	24.5	23.8	23.1	22.4
80°	21.0	20.3	19.6	18.9	18.9	18.9	18.2	18.2	17.5	17.5	17.5
82.5°	14.1	14.1	13.3	13.3	13.3	13.3	12.6	12.6	12.6	12.6	12.6
85°	8.4	8.4	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583796

CATALOG NUMBER: HCC8S10D010BZ-HM80520930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1
2.5°	490.9	490.9	489.5	488.9	488.1	488.9	487.4	486.7	486.0	486.0	485.2
5°	486.7	486.0	483.2	482.5	481.8	481.0	479.7	478.3	477.0	476.2	475.5
7.5°	481.0	479.0	476.2	475.5	474.8	472.7	470.6	469.1	467.1	466.4	464.9
10°	473.3	470.6	468.5	466.4	464.9	462.9	460.8	458.7	455.9	455.2	453.0
12.5°	464.3	460.8	456.6	455.9	453.8	451.0	448.2	446.1	444.0	442.6	440.5
15°	453.0	449.5	445.3	443.3	441.1	439.1	435.6	432.7	430.7	428.6	426.5
17.5°	439.8	435.6	432.1	430.0	428.6	425.0	422.3	418.8	416.6	414.6	412.5
20°	423.7	420.2	415.3	413.1	412.5	409.6	406.2	404.7	401.9	399.9	398.5
22.5°	405.4	401.9	397.7	396.4	393.5	392.2	388.6	387.3	385.8	383.8	383.1
25°	385.1	381.6	378.1	377.4	375.4	373.9	371.9	369.7	369.7	367.7	367.7
27.5°	364.2	360.6	357.8	356.4	355.8	354.3	352.3	351.6	350.9	350.1	350.1
30°	341.7	337.5	336.2	335.5	334.8	333.3	332.6	331.3	332.0	332.6	332.0
32.5°	317.9	316.5	313.7	312.3	313.0	312.3	311.0	312.3	311.7	313.0	313.7
35°	294.9	293.4	292.0	292.0	290.6	290.6	290.6	291.4	292.7	293.4	294.9
37.5°	272.4	270.3	269.6	268.9	269.6	269.6	269.6	271.1	272.4	273.8	275.9
40°	248.6	247.3	247.3	247.3	247.3	249.3	248.6	250.0	251.5	253.5	255.7
42.5°	226.2	226.2	226.9	226.9	226.9	226.9	228.3	230.4	232.5	234.6	236.7
45°	205.2	205.2	205.2	206.6	206.6	207.3	210.1	211.4	212.9	215.0	217.1
47.5°	185.6	185.6	186.3	187.0	187.6	189.1	190.5	192.6	194.7	196.0	198.2
50°	167.3	168.0	169.5	170.9	170.9	171.5	173.7	175.1	176.5	178.6	179.2
52.5°	149.9	151.2	152.7	153.4	154.1	155.4	156.1	158.3	159.0	161.1	161.8
55°	133.8	134.5	136.5	137.3	137.3	138.7	140.0	141.5	143.5	143.5	145.0
57.5°	119.0	119.7	121.2	121.9	121.2	123.2	123.9	125.4	126.1	127.4	128.1
60°	104.3	105.8	106.5	106.5	107.1	107.8	109.3	109.3	110.7	112.0	112.0
62.5°	90.4	91.0	91.7	92.4	93.2	92.4	94.6	94.6	95.9	96.6	98.1
65°	77.0	77.8	77.8	78.5	78.5	79.1	79.1	79.8	80.5	82.0	82.6
67.5°	63.7	63.7	63.7	64.4	63.7	64.4	64.4	65.1	65.1	66.5	67.2
70°	51.8	51.1	50.4	50.4	50.4	50.4	49.8	50.4	50.4	51.1	51.1
72.5°	39.9	39.2	38.5	37.9	37.9	37.1	36.4	37.1	37.1	37.9	37.9
75°	30.2	28.7	28.7	28.7	28.0	28.0	28.0	28.7	28.7	28.7	29.4
77.5°	22.4	22.4	21.8	21.8	21.8	22.4	22.4	23.1	23.1	23.1	23.1
80°	16.8	17.5	17.5	17.5	17.5	18.2	18.2	18.2	18.2	18.9	18.9
82.5°	12.6	12.6	12.6	12.6	13.3	13.3	13.3	13.3	13.3	13.3	13.3
85°	7.7	8.4	8.4	7.7	8.4	8.4	8.4	8.4	8.4	8.4	8.4
87.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583796

CATALOG NUMBER: HCC8S10D010BZ-HM80520930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1
2.5°	484.6	484.6	484.6	484.6	483.9	483.9	483.9	483.2
5°	474.1	474.1	474.1	472.7	473.3	473.3	472.0	472.7
7.5°	463.6	462.9	462.2	462.2	461.4	460.8	460.1	460.8
10°	451.7	449.5	449.5	448.8	448.8	447.5	447.5	448.2
12.5°	438.4	436.9	436.9	436.3	435.6	434.9	434.2	434.2
15°	425.0	423.7	423.0	422.3	421.5	420.2	420.8	420.2
17.5°	411.8	409.6	409.6	408.9	408.3	406.9	406.9	406.2
20°	396.4	395.7	394.3	395.0	394.3	392.8	392.2	392.2
22.5°	380.9	380.9	380.3	380.3	379.6	378.9	378.1	378.1
25°	366.2	365.5	366.2	366.2	364.2	364.2	364.2	364.8
27.5°	349.4	350.1	349.4	349.4	349.4	349.4	350.1	349.4
30°	332.6	332.6	332.6	333.3	334.8	334.0	334.0	333.3
32.5°	314.4	315.2	315.2	315.9	316.5	317.9	317.9	318.7
35°	296.2	297.6	298.3	297.6	299.8	299.8	301.1	301.1
37.5°	277.3	278.0	279.5	280.1	281.5	282.2	283.0	283.0
40°	257.0	259.8	260.5	261.2	263.4	263.4	264.0	265.4
42.5°	238.1	240.9	241.6	242.3	243.6	245.8	245.1	246.5
45°	219.8	222.0	222.7	223.5	225.5	226.2	226.2	228.3
47.5°	200.3	201.7	202.4	203.7	205.2	206.6	207.9	207.3
50°	180.7	182.8	184.1	184.9	187.0	187.6	188.4	189.1
52.5°	163.1	164.6	165.3	166.0	168.0	168.8	169.5	170.9
55°	146.4	147.0	148.4	147.7	149.9	150.6	151.2	152.7
57.5°	129.6	130.3	130.9	130.9	132.3	133.8	134.5	135.1
60°	113.5	114.8	115.5	115.5	115.5	117.0	117.0	117.0
62.5°	98.7	98.7	99.4	99.4	100.8	100.8	100.8	100.8
65°	83.3	84.0	84.7	84.7	86.2	85.5	86.8	86.2
67.5°	67.2	67.2	68.6	68.6	67.9	68.6	68.6	68.6
70°	51.1	51.1	51.8	51.8	51.8	51.8	51.8	51.8
72.5°	37.9	37.9	37.9	38.5	37.9	37.9	38.5	37.9
75°	29.4	29.4	29.4	29.4	29.4	29.4	29.4	29.4
77.5°	23.1	23.1	23.8	23.8	23.8	23.8	23.8	23.8
80°	18.9	18.9	18.9	18.9	19.6	18.9	18.9	18.9
82.5°	14.1	13.3	14.1	13.3	14.1	14.1	14.1	14.1
85°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
87.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)