

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583794

Luminaire Tested: **HCC8W10D010SL-HM80520930-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583794
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W10D010SL-HM80520930-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 872.5 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583794
CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583794

CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	14444	14444	14444
5°	15044	14415	13809
10°	15543	14228	13132
15°	15937	13903	12450
20°	15968	13330	11833
25°	15699	12483	11221
30°	14859	11519	10696
35°	13548	10356	10040
40°	11782	9130	9270
45°	10104	7911	8486
50°	8630	6817	7623
55°	7570	5876	6623
60°	6741	5014	5569
65°	5983	4086	4444
70°	5301	3038	2524
75°	4420	1585	751
80°	3481	497	124
85°	2477	248	0



TEST NUMBER: P583794
 CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	5.1
10°-20°	123.7	14.2
20°-30°	175.1	20.1
30°-40°	183.2	21.0
40°-50°	152.8	17.5
50°-60°	108.4	12.4
60°-70°	62.4	7.2
70°-80°	20.1	2.3
80°-90°	2.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	342.9	39.3
0°-40°	526.1	60.3
0°-60°	787.3	90.2
0°-90°	872.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	872.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	468	468	468	468	468	
5°	486	480	466	452	446	47
15°	499	479	436	401	390	140
25°	461	427	367	338	330	211
35°	360	328	275	260	267	223
45°	232	213	181	183	195	180
55°	141	126	109	115	123	127
65°	82	69	56	56	61	82
75°	37	27	13	6	6	40
85°	7	4	1	0	0	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583794

CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	478.3	477.6	476.8	477.6	476.8	477.6	476.8	476.8	476.1	475.4	475.4
5°	486.0	485.2	485.2	485.2	484.5	483.8	483.8	483.1	481.8	481.0	479.6
7.5°	490.8	491.5	491.5	491.5	490.2	490.2	488.7	487.3	486.0	484.5	482.4
10°	496.4	496.4	495.7	495.0	493.7	492.9	492.2	490.8	488.7	486.0	483.8
12.5°	498.5	498.5	497.9	496.4	495.7	495.0	494.3	492.2	489.5	486.0	483.1
15°	499.2	497.9	497.1	496.4	495.0	492.9	492.9	490.2	486.6	482.4	478.9
17.5°	493.7	494.3	492.9	491.5	489.5	488.0	486.0	483.8	479.6	474.7	471.2
20°	486.6	486.0	485.2	483.1	480.3	479.6	477.6	474.1	470.5	464.9	460.0
22.5°	475.4	474.7	473.3	471.9	469.1	467.7	465.7	461.4	456.5	450.9	445.3
25°	461.4	460.0	458.0	455.1	453.0	451.6	448.8	444.6	439.0	432.7	427.1
27.5°	439.0	441.1	439.7	435.5	433.4	430.6	430.0	424.3	419.4	413.1	406.8
30°	417.3	417.3	415.2	413.1	409.6	407.5	404.7	400.5	395.6	387.9	383.0
32.5°	390.0	389.3	386.4	385.8	383.0	378.8	378.1	372.5	367.6	362.0	355.7
35°	359.9	358.4	355.7	353.6	352.2	350.1	348.0	343.1	338.2	332.6	328.4
37.5°	325.6	325.6	324.9	321.4	320.0	318.5	316.5	311.6	308.8	303.1	298.9
40°	292.7	292.0	289.9	289.2	287.8	285.7	284.3	281.5	277.3	273.1	268.9
42.5°	260.5	261.2	258.3	259.0	256.3	254.8	254.1	250.0	247.9	243.6	240.2
45°	231.7	231.0	229.7	229.0	227.5	226.1	224.8	222.6	219.1	214.9	212.9
47.5°	205.2	203.0	203.0	202.3	201.7	198.8	198.1	196.0	194.0	189.8	186.9
50°	179.9	179.9	179.9	179.2	177.2	176.5	175.0	173.0	170.8	168.0	163.8
52.5°	159.6	159.6	159.6	158.9	156.1	155.4	154.7	151.9	149.2	147.0	144.2
55°	140.8	141.5	140.8	139.3	137.3	137.3	135.1	133.8	130.9	128.9	126.1
57.5°	124.6	124.6	123.2	122.5	121.2	120.4	119.0	117.7	114.1	112.0	108.5
60°	109.3	108.5	108.5	107.1	105.8	104.3	103.6	101.6	100.1	96.6	93.9
62.5°	95.2	95.2	93.9	93.9	91.0	91.0	90.3	88.2	86.1	82.6	81.3
65°	82.0	82.0	81.3	80.5	78.4	77.8	77.0	74.9	72.8	70.7	68.6
67.5°	70.1	70.1	68.6	67.9	66.5	65.9	64.4	63.0	60.9	58.8	56.7
70°	58.8	58.1	57.5	56.7	55.3	54.6	53.2	51.8	49.8	48.3	46.2
72.5°	47.6	47.6	46.9	45.6	44.8	44.1	43.4	42.1	39.9	37.9	36.4
75°	37.1	37.1	37.1	35.7	34.3	33.7	33.7	32.2	30.8	28.7	27.3
77.5°	28.7	28.0	27.3	27.3	26.0	25.2	24.5	23.8	21.8	21.0	19.6
80°	19.6	20.3	19.6	18.9	18.2	17.5	17.5	16.1	15.4	14.1	12.6
82.5°	13.3	12.6	12.6	11.9	11.9	11.2	11.2	9.9	9.1	8.4	7.7
85°	7.0	7.0	6.3	6.3	6.3	5.6	5.6	4.9	4.9	4.2	3.5
87.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583794

CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	474.7	473.3	472.6	472.6	471.9	471.2	470.5	469.9	468.4	468.4	467.0
5°	478.3	476.8	476.1	474.1	472.6	472.6	469.9	469.1	467.0	465.7	464.2
7.5°	481.0	478.3	476.1	474.1	472.6	471.2	468.4	465.7	462.8	460.0	458.6
10°	481.0	478.3	474.7	471.2	469.9	468.4	464.9	460.7	457.2	454.4	450.9
12.5°	479.6	475.4	471.2	468.4	465.7	463.5	459.3	455.1	450.9	445.3	442.5
15°	475.4	469.9	465.7	460.7	458.6	455.1	451.6	445.3	440.4	435.5	432.0
17.5°	467.0	460.0	455.1	450.3	446.7	444.6	439.0	433.4	427.8	422.3	418.1
20°	454.4	448.1	442.5	436.2	433.4	430.6	423.6	418.1	412.4	406.2	401.9
22.5°	439.0	432.7	425.0	420.1	415.9	412.4	406.2	399.8	394.3	388.6	383.0
25°	420.1	413.8	406.8	399.1	396.3	392.8	385.8	379.5	373.2	366.9	362.0
27.5°	399.8	391.4	385.8	377.4	374.5	371.1	363.4	356.4	350.7	345.9	340.3
30°	375.3	369.0	361.3	353.6	350.7	347.3	341.0	334.6	329.1	323.5	317.9
32.5°	348.7	342.3	334.6	329.1	324.9	322.1	315.8	310.2	304.6	298.9	294.1
35°	320.7	313.7	308.1	302.4	298.9	295.5	289.2	284.3	280.1	275.1	270.2
37.5°	292.0	287.0	281.5	275.1	271.7	268.9	264.0	258.3	254.8	250.6	247.1
40°	264.0	258.3	253.5	247.9	245.1	242.9	238.1	233.9	230.3	226.8	224.8
42.5°	235.2	230.3	225.5	222.0	219.8	217.8	214.2	209.4	207.2	203.7	201.7
45°	208.7	204.5	201.0	196.0	194.6	193.3	189.1	185.6	183.4	181.4	179.9
47.5°	183.4	180.7	176.5	173.7	171.5	170.1	167.3	164.6	162.4	161.1	159.6
50°	161.8	158.2	155.4	152.7	151.2	149.2	146.3	145.0	143.5	142.1	142.1
52.5°	141.5	138.0	135.1	133.1	131.6	130.2	128.1	127.4	126.1	126.1	125.4
55°	122.5	120.4	117.7	114.8	114.1	113.5	112.0	110.6	110.0	109.3	110.0
57.5°	106.4	104.3	101.6	99.4	98.7	98.1	97.4	95.9	95.2	95.2	95.2
60°	91.7	89.7	87.5	85.5	85.5	84.0	83.3	82.6	82.0	81.3	81.3
62.5°	78.4	76.3	74.2	72.8	72.1	71.4	70.1	69.4	68.6	68.6	67.9
65°	66.5	63.7	63.0	60.9	60.2	59.5	58.8	57.5	56.7	56.0	55.3
67.5°	54.6	53.2	51.1	49.8	49.0	48.3	47.6	46.2	45.6	44.8	43.4
70°	44.1	42.7	41.3	39.9	39.2	38.5	37.1	35.7	35.0	33.7	31.5
72.5°	34.3	32.9	31.5	30.0	29.4	28.7	27.3	26.0	24.5	23.1	21.8
75°	26.0	24.5	22.4	21.0	20.3	20.3	18.2	16.8	15.4	13.3	11.9
77.5°	18.2	16.1	15.4	14.1	13.3	11.9	10.5	9.1	7.7	7.0	5.6
80°	11.9	10.5	9.1	8.4	7.7	7.0	6.3	4.9	3.5	2.8	2.0
82.5°	7.0	6.3	5.6	4.9	4.2	3.5	2.8	2.8	2.0	1.4	0.7
85°	3.5	2.8	2.0	2.0	1.4	1.4	1.4	0.7	0.7	0.7	0.7
87.5°	1.4	0.7	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583794

CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.3	465.7	464.9	464.2	464.2	462.8	462.8	462.2	460.7	460.0	460.0
5°	462.2	460.0	458.6	458.0	457.2	455.1	454.4	453.0	451.6	450.3	449.5
7.5°	455.8	452.3	450.9	450.3	448.1	446.1	444.6	442.5	440.4	438.2	437.6
10°	448.1	444.6	441.1	439.7	437.6	436.2	433.4	430.6	428.5	426.3	424.3
12.5°	438.2	434.2	430.6	429.2	427.1	424.3	420.1	418.7	415.2	413.8	411.0
15°	427.1	422.3	418.7	416.6	414.4	410.2	407.5	404.7	401.2	399.8	397.0
17.5°	413.1	407.5	404.0	401.9	400.5	397.0	392.8	389.3	385.8	384.4	382.2
20°	396.3	392.8	387.9	385.8	384.4	380.2	376.0	374.5	371.8	369.0	366.9
22.5°	377.4	373.9	369.0	366.9	366.2	362.6	359.2	357.1	355.0	352.9	350.7
25°	357.8	353.6	349.4	348.0	346.5	343.8	341.0	339.6	337.5	336.1	334.6
27.5°	336.8	332.6	329.1	326.9	325.6	323.5	322.1	320.7	319.3	317.9	317.2
30°	314.3	310.2	307.4	306.0	304.6	303.9	301.8	301.1	300.4	298.9	299.7
32.5°	292.0	288.5	285.7	283.6	283.6	282.1	281.5	281.5	280.8	280.8	280.8
35°	267.4	265.4	263.2	262.5	261.9	261.2	260.5	261.2	260.5	261.2	261.9
37.5°	245.1	242.9	241.6	240.9	240.2	240.9	240.2	240.2	240.9	242.2	242.9
40°	222.0	220.6	219.1	219.8	219.1	219.1	219.1	221.3	222.0	222.6	223.3
42.5°	200.3	198.8	198.1	198.1	198.8	198.1	199.5	200.3	201.7	203.7	205.2
45°	179.2	178.5	178.5	179.2	178.5	179.9	179.9	181.4	183.4	184.9	186.2
47.5°	159.6	159.6	159.6	160.3	160.3	161.1	162.4	163.1	164.6	166.0	167.3
50°	141.5	142.1	142.8	142.8	142.8	144.2	145.7	146.3	147.0	147.7	149.9
52.5°	125.4	126.1	126.1	126.7	127.4	128.1	128.9	130.2	130.9	132.3	133.1
55°	110.0	110.0	111.3	112.0	112.0	112.0	113.5	113.5	114.8	115.5	117.0
57.5°	95.2	95.9	95.9	96.6	96.6	97.4	98.1	98.7	99.4	100.1	100.8
60°	81.3	81.3	81.3	82.0	82.6	83.3	82.6	84.0	84.0	85.5	86.1
62.5°	67.9	68.6	68.6	68.6	68.6	68.6	68.6	69.4	70.1	70.7	71.4
65°	55.3	55.3	55.3	54.6	55.3	54.6	55.3	56.0	56.0	56.7	57.5
67.5°	42.7	42.7	41.3	41.3	42.1	42.1	42.1	42.1	41.3	42.7	42.7
70°	30.8	30.0	29.4	28.7	28.7	28.0	28.0	27.3	27.3	27.3	27.3
72.5°	20.3	18.9	17.5	16.8	16.1	16.1	14.7	14.1	14.7	14.7	14.7
75°	10.5	9.1	8.4	7.7	7.0	7.0	6.3	6.3	6.3	6.3	6.3
77.5°	4.2	3.5	2.8	2.8	2.0	2.0	2.0	2.0	2.0	2.0	2.0
80°	1.4	1.4	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
85°	0.7	0.0	0.0	0.7	0.0	0.7	0.7	0.7	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583794

CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	459.3	459.3	458.6	459.3	458.0	458.6	458.0	458.0
5°	448.8	447.4	447.4	447.4	446.7	446.7	446.1	446.1
7.5°	436.2	435.5	434.8	434.2	433.4	432.7	432.7	432.7
10°	423.6	422.3	422.3	421.5	420.1	419.4	419.4	419.4
12.5°	408.9	408.2	407.5	407.5	404.7	405.4	404.7	404.7
15°	394.9	394.3	394.3	392.1	390.6	390.6	390.6	390.0
17.5°	380.2	379.5	378.8	377.4	376.0	376.0	375.3	376.0
20°	364.8	364.1	362.6	362.6	362.0	361.3	359.9	360.6
22.5°	349.4	348.0	347.3	347.3	346.5	346.5	345.2	345.2
25°	333.3	332.6	331.9	332.6	331.2	331.2	329.8	329.8
27.5°	316.5	315.8	315.8	315.8	315.0	315.8	315.0	315.0
30°	299.7	299.7	298.9	298.9	299.7	298.9	299.7	300.4
32.5°	281.5	281.5	282.1	282.1	282.8	282.8	282.8	282.8
35°	262.5	264.0	264.0	264.7	265.4	266.1	266.1	266.7
37.5°	245.1	245.8	246.4	247.1	248.6	248.6	248.6	248.6
40°	226.1	226.8	228.3	227.5	230.3	231.0	230.3	230.3
42.5°	206.5	207.9	208.7	210.1	210.7	212.2	212.9	212.9
45°	188.4	189.1	190.4	191.8	192.6	194.6	194.6	194.6
47.5°	169.5	170.8	171.5	173.0	173.7	175.7	176.5	175.7
50°	151.2	152.7	154.1	154.1	156.1	156.9	158.2	158.9
52.5°	133.8	134.4	135.8	136.5	138.0	139.3	140.0	140.8
55°	117.0	117.7	119.0	119.0	121.2	121.9	123.2	123.2
57.5°	101.6	102.2	103.6	102.9	104.3	105.8	105.8	105.1
60°	86.8	86.8	86.8	88.2	88.9	89.7	90.3	90.3
62.5°	71.4	72.8	73.6	73.6	74.2	74.9	74.9	74.2
65°	57.5	58.8	59.5	59.5	60.2	60.2	60.2	60.9
67.5°	43.4	43.4	43.4	44.1	43.4	43.4	43.4	43.4
70°	27.3	27.3	27.3	27.3	26.6	27.3	27.3	28.0
72.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7
75°	6.3	6.3	6.3	7.0	6.3	6.3	6.3	6.3
77.5°	2.8	2.0	2.8	2.8	2.0	2.0	2.0	2.0
80°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
85°	0.0	0.7	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)