

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583795

Luminaire Tested: **HCC8W10D010SL-HM80520930-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W10D010SL-HM80520930-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 952.4 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583795
CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583795

CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	15912	15912	15912
5°	16471	15821	15192
10°	16840	15543	14341
15°	17076	15020	13389
20°	17025	14291	12430
25°	16604	13365	11412
30°	15735	12291	10472
35°	14312	11124	9516
40°	12571	9894	8598
45°	10959	8700	7662
50°	9537	7623	6755
55°	8505	6699	5876
60°	7734	5871	5014
65°	6946	5115	4546
70°	6185	4355	4111
75°	5433	3670	3503
80°	4617	2983	3108
85°	3503	2229	2477



TEST NUMBER: P583795
 CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.3	5.1
10°-20°	133.2	14.0
20°-30°	184.9	19.4
30°-40°	191.1	20.1
40°-50°	160.0	16.8
50°-60°	116.2	12.2
60°-70°	73.3	7.7
70°-80°	36.3	3.8
80°-90°	9.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.4	38.5
0°-40°	557.5	58.5
0°-60°	833.7	87.5
0°-90°	952.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	952.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	516	516	516	516	516	
5°	532	526	511	497	491	51
15°	535	515	470	433	419	151
25°	488	456	393	350	335	224
35°	380	352	296	262	253	237
45°	251	233	200	180	176	194
55°	158	144	125	114	109	143
65°	95	83	70	62	62	95
75°	46	38	31	29	29	49
85°	10	8	6	7	7	12
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583795

CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0
2.5°	524.4	524.4	525.2	524.4	524.4	524.4	523.7	523.7	523.0	523.0	521.7
5°	532.1	530.7	532.1	530.7	530.7	530.7	530.1	528.6	527.9	526.5	525.9
7.5°	535.6	534.9	534.9	534.2	534.2	533.6	532.8	532.1	529.4	528.6	526.5
10°	537.8	537.1	537.1	536.3	534.9	534.9	533.6	532.8	529.4	527.9	525.2
12.5°	537.1	537.1	537.1	536.3	534.2	533.6	532.1	530.1	527.2	524.4	521.7
15°	534.9	534.9	533.6	532.8	530.7	529.4	528.6	525.2	522.3	518.8	514.6
17.5°	527.9	527.9	527.2	525.9	523.7	522.3	520.9	517.5	514.6	509.0	504.8
20°	518.8	518.2	517.5	515.3	513.3	512.5	510.4	505.6	502.1	497.9	492.2
22.5°	505.6	504.8	504.1	502.7	499.2	497.9	496.4	492.9	486.6	482.4	475.4
25°	488.0	488.0	486.6	484.5	481.0	479.6	477.6	474.1	468.4	462.2	456.5
27.5°	467.7	467.0	464.9	463.5	460.7	458.6	455.1	450.9	445.3	440.4	433.4
30°	441.9	441.9	440.4	438.2	434.8	433.4	430.6	425.7	420.1	413.8	408.9
32.5°	412.4	412.4	410.2	408.9	406.8	403.3	402.5	397.0	392.1	387.2	381.6
35°	380.2	380.9	379.5	376.7	373.2	373.2	371.8	366.9	361.3	356.4	352.2
37.5°	348.0	345.9	345.2	343.8	341.7	338.8	337.5	335.4	330.4	326.9	320.7
40°	312.3	313.0	311.6	310.1	309.5	307.4	306.6	303.1	299.7	295.5	292.7
42.5°	280.1	280.1	280.1	278.6	277.3	275.1	274.4	272.4	268.2	265.4	261.2
45°	251.3	249.3	249.3	248.6	247.9	246.4	244.4	242.9	240.2	238.1	233.2
47.5°	223.3	224.1	223.3	222.6	220.6	219.8	219.1	216.4	213.6	211.4	207.9
50°	198.8	200.3	198.8	198.8	197.5	196.8	195.3	193.3	191.1	187.6	184.1
52.5°	178.5	178.5	177.9	177.2	175.0	173.7	173.0	172.2	168.8	166.0	163.1
55°	158.2	158.9	158.9	156.9	156.1	154.7	154.1	151.9	150.5	146.3	144.2
57.5°	140.8	140.0	140.8	139.3	138.0	136.5	135.8	134.4	132.3	129.6	126.7
60°	125.4	123.9	123.9	123.2	121.9	121.2	119.7	117.7	115.5	112.7	110.6
62.5°	110.0	109.3	108.5	107.8	106.4	105.8	105.1	102.9	100.8	98.7	96.6
65°	95.2	95.2	94.5	93.2	92.4	91.7	91.0	89.7	86.8	85.5	83.3
67.5°	82.0	81.3	81.3	79.8	78.4	77.8	77.8	76.3	74.2	72.1	70.7
70°	68.6	69.4	68.6	67.9	66.5	66.5	65.1	64.4	61.7	60.9	58.8
72.5°	56.7	56.7	56.0	56.0	54.6	54.0	54.0	52.5	51.1	49.8	48.3
75°	45.6	45.6	45.6	44.8	44.1	42.7	42.7	42.1	40.6	39.2	37.9
77.5°	35.7	35.0	35.0	34.3	33.7	32.9	32.9	32.2	30.8	30.0	28.7
80°	26.0	25.2	25.2	25.2	23.8	24.5	23.8	23.1	22.4	21.8	21.0
82.5°	16.8	17.5	17.5	16.8	16.1	16.1	16.1	15.4	15.4	14.7	14.1
85°	9.9	9.9	9.9	9.9	9.1	9.1	9.1	8.4	8.4	8.4	7.7
87.5°	4.2	4.2	4.2	4.2	4.2	4.2	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583795

CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0
2.5°	521.7	520.2	519.5	518.8	518.8	518.2	517.5	516.0	516.0	514.6	514.0
5°	524.4	522.3	520.9	519.5	518.8	517.5	516.0	514.0	513.3	511.1	509.0
7.5°	525.2	521.7	520.2	517.5	516.0	514.6	511.8	509.8	506.9	504.8	502.1
10°	522.3	519.5	516.0	512.5	511.8	509.8	505.6	502.7	499.2	496.4	492.2
12.5°	518.2	514.0	510.4	506.2	504.1	502.1	497.9	493.7	488.7	483.8	479.6
15°	511.1	506.2	501.4	496.4	493.7	491.5	486.6	481.8	476.8	470.5	466.3
17.5°	500.6	495.0	490.2	483.8	481.0	478.9	472.6	467.0	460.7	454.4	450.1
20°	487.3	480.3	474.7	467.7	465.7	462.2	455.8	449.5	442.5	435.5	430.6
22.5°	469.9	462.8	456.5	449.5	446.1	442.5	436.2	428.5	421.5	415.9	411.0
25°	449.5	443.2	435.5	429.2	425.0	420.8	413.8	407.5	401.2	392.8	387.9
27.5°	427.1	419.4	413.8	405.4	401.2	398.3	390.6	382.2	376.7	369.0	363.4
30°	401.9	394.9	388.6	380.2	376.0	373.2	366.1	358.4	352.9	345.2	339.6
32.5°	375.3	367.6	359.9	354.2	349.4	346.5	338.8	334.0	326.9	320.7	314.3
35°	346.5	338.8	333.3	325.6	322.7	320.0	313.7	307.4	301.1	295.5	290.5
37.5°	315.8	310.1	303.9	298.2	296.2	293.4	285.7	280.1	275.1	269.6	265.4
40°	285.7	280.8	276.6	270.9	267.4	265.4	259.8	254.8	249.3	245.8	241.6
42.5°	258.3	252.8	248.6	244.4	240.9	238.7	233.9	230.3	226.1	222.6	217.8
45°	229.7	226.8	222.0	218.4	216.4	213.6	210.1	205.9	202.3	199.5	196.0
47.5°	204.5	201.7	198.1	194.0	192.6	190.4	186.9	184.1	181.4	178.5	175.0
50°	181.4	177.9	175.0	172.2	170.8	168.8	165.3	163.8	161.8	158.9	156.9
52.5°	160.3	157.6	154.7	151.2	150.5	149.2	147.0	144.2	142.1	140.8	139.3
55°	141.5	138.6	136.5	133.8	133.1	131.6	128.9	127.4	126.1	124.6	123.2
57.5°	124.6	121.9	119.0	117.7	116.2	114.8	114.1	112.0	110.6	110.0	108.5
60°	109.3	106.4	104.3	102.2	101.6	100.8	99.4	98.1	96.6	95.2	94.5
62.5°	94.5	91.7	90.3	88.9	87.5	87.5	86.1	84.7	83.3	82.6	81.3
65°	81.3	79.8	77.8	75.6	74.9	74.9	72.8	72.1	71.4	70.1	68.6
67.5°	68.6	67.2	65.1	64.4	63.7	63.0	62.3	60.9	59.5	58.8	57.5
70°	57.5	56.0	54.6	54.0	53.2	52.5	51.1	50.4	49.0	48.3	47.6
72.5°	46.2	45.6	44.1	43.4	42.7	42.1	41.3	40.6	39.2	38.5	37.9
75°	37.1	36.4	35.0	34.3	33.7	33.7	32.9	31.5	30.8	30.8	30.0
77.5°	28.0	27.3	26.6	26.0	25.2	25.2	24.5	23.8	23.1	23.1	22.4
80°	20.3	19.6	18.9	18.9	18.9	18.2	17.5	17.5	16.8	16.8	16.1
82.5°	13.3	13.3	12.6	12.6	12.6	11.9	11.9	11.2	11.2	11.2	11.2
85°	7.7	7.7	7.7	7.0	7.0	7.0	7.0	7.0	7.0	6.3	7.0
87.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583795

CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0
2.5°	513.3	512.5	511.1	511.1	509.8	509.8	509.0	508.3	507.6	506.9	506.2
5°	508.3	505.6	504.1	503.4	502.1	501.4	499.2	497.9	497.1	495.7	494.3
7.5°	499.2	496.4	493.7	492.9	492.2	489.5	487.3	485.2	483.8	482.4	481.0
10°	488.7	486.0	482.4	481.0	479.6	476.1	473.3	471.2	468.4	465.7	464.9
12.5°	476.1	471.9	467.7	466.3	464.2	460.7	458.0	454.4	452.3	448.8	448.1
15°	461.4	456.5	453.0	449.5	448.1	444.6	439.7	436.9	432.7	431.3	427.8
17.5°	443.9	439.0	434.2	432.7	430.6	425.7	420.8	417.3	413.1	411.0	408.9
20°	425.7	419.4	414.4	413.1	410.2	406.2	401.2	397.7	394.1	390.0	387.9
22.5°	404.7	397.7	393.5	390.0	389.3	384.4	378.8	376.0	373.2	369.7	366.9
25°	381.6	375.3	370.3	367.6	366.1	362.0	357.8	354.2	350.1	348.0	344.5
27.5°	357.8	353.6	347.3	344.5	342.3	338.8	334.0	331.9	327.7	324.9	322.7
30°	334.6	328.4	324.9	321.4	319.3	315.8	311.6	309.5	306.0	303.1	301.1
32.5°	309.5	305.3	300.4	298.9	296.2	292.7	289.9	286.3	283.6	280.8	280.1
35°	286.3	280.8	275.9	274.4	272.4	268.9	267.4	265.4	261.9	261.2	258.3
37.5°	261.2	258.3	252.8	250.6	250.0	247.1	244.4	242.9	240.9	238.7	238.1
40°	237.4	233.9	231.0	229.0	227.5	225.5	222.6	222.0	220.6	217.8	217.1
42.5°	214.9	211.4	208.7	207.9	205.9	203.7	202.3	200.3	199.5	198.8	197.5
45°	193.3	191.1	188.4	187.6	186.9	184.1	182.7	181.4	179.9	179.2	177.9
47.5°	173.7	171.5	169.5	168.8	167.3	166.6	164.6	163.8	161.8	161.1	160.3
50°	154.7	153.4	151.9	151.2	149.9	149.2	147.7	146.3	145.0	144.2	143.5
52.5°	138.0	136.5	135.1	134.4	133.8	132.3	130.9	129.6	128.9	128.1	127.4
55°	121.9	120.4	119.7	119.0	118.3	117.7	115.5	114.8	114.1	113.5	112.0
57.5°	107.1	105.8	104.3	104.3	103.6	102.9	101.6	100.1	100.1	98.7	97.4
60°	93.9	92.4	91.0	90.3	89.7	88.2	87.5	86.8	86.1	85.5	84.0
62.5°	79.8	79.1	77.8	77.8	76.3	75.6	74.9	74.2	73.6	72.1	71.4
65°	67.9	67.2	65.9	65.1	65.1	64.4	63.0	62.3	61.7	61.7	60.9
67.5°	56.7	56.0	54.6	54.0	54.0	53.2	52.5	52.5	51.8	51.1	51.8
70°	46.9	45.6	45.6	44.8	44.8	44.1	43.4	43.4	43.4	44.1	44.1
72.5°	37.1	36.4	35.7	35.7	35.7	35.7	35.0	35.0	35.7	36.4	36.4
75°	29.4	28.7	28.7	28.7	28.0	28.0	28.7	28.7	29.4	29.4	29.4
77.5°	21.8	21.8	21.8	21.8	21.8	21.8	22.4	22.4	23.1	23.1	23.1
80°	16.1	16.1	16.1	16.1	16.1	16.8	16.8	16.8	16.8	16.8	17.5
82.5°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.9	11.9	11.9	11.9
85°	6.3	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583795

CATALOG NUMBER: HCC8W10D010SL-HM80520930-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0
2.5°	505.6	505.6	505.6	506.2	504.8	504.8	504.8	504.8
5°	493.7	492.9	492.2	492.9	491.5	491.5	490.8	490.8
7.5°	478.9	478.2	477.6	477.6	476.1	476.1	475.4	474.7
10°	462.8	461.4	462.2	460.7	460.0	459.3	458.6	458.0
12.5°	445.3	443.9	443.2	441.9	440.4	439.7	440.4	439.0
15°	426.3	424.3	423.6	422.1	420.8	420.1	420.1	419.4
17.5°	405.4	404.0	403.3	401.9	401.2	399.8	399.1	398.3
20°	385.8	382.2	383.0	381.6	380.9	378.1	378.1	378.8
22.5°	364.1	362.0	360.6	359.2	358.4	357.1	357.1	356.4
25°	342.3	340.3	339.6	338.1	337.5	336.1	335.4	335.4
27.5°	321.4	318.5	318.5	317.2	315.8	315.0	314.3	313.7
30°	298.9	296.9	296.2	296.2	295.5	295.5	293.4	294.1
32.5°	278.0	276.6	275.9	274.4	274.4	273.8	273.8	271.7
35°	257.0	254.8	255.5	254.1	253.5	252.8	253.5	252.8
37.5°	236.7	235.2	235.2	233.9	233.9	233.2	232.5	233.9
40°	216.4	215.6	214.9	214.2	214.9	214.2	212.9	213.6
42.5°	196.0	196.0	195.3	195.3	194.6	194.6	194.6	194.6
45°	177.9	177.2	177.2	176.5	176.5	176.5	176.5	175.7
47.5°	159.6	158.9	158.9	158.9	158.2	158.2	157.6	158.2
50°	142.1	142.1	141.5	141.5	142.1	141.5	140.8	140.8
52.5°	126.1	126.1	125.4	125.4	124.6	123.9	124.6	124.6
55°	111.3	110.6	110.0	110.0	109.3	108.5	108.5	109.3
57.5°	97.4	96.6	95.9	95.9	94.5	93.9	93.9	93.9
60°	84.0	82.6	82.6	82.0	82.0	81.3	81.3	81.3
62.5°	71.4	70.7	70.7	70.7	70.7	70.1	70.1	70.1
65°	60.9	60.9	60.9	61.7	61.7	62.3	62.3	62.3
67.5°	52.5	53.2	53.2	53.2	54.0	54.0	54.0	53.2
70°	44.8	44.8	44.8	45.6	45.6	45.6	45.6	45.6
72.5°	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1
75°	29.4	30.0	30.0	30.0	29.4	30.0	30.0	29.4
77.5°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
80°	17.5	17.5	17.5	17.5	17.5	17.5	17.5	17.5
82.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)