

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583811

Luminaire Tested: **HCC8S10D010MW-HM80520935-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583811
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S10D010MW-HM80520935-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 921.4 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583811
CATALOG NUMBER: HCC8S10D010MW-HM80520935-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583811

CATALOG NUMBER: HCC8S10D010MW-HM80520935-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	15252	15252	15252
5°	15883	15220	14582
10°	16414	15024	13868
15°	16830	14682	13146
20°	16864	14074	12496
25°	16580	13181	11847
30°	15692	12163	11294
35°	14309	10939	10604
40°	12438	9645	9794
45°	10671	8351	8962
50°	9115	7201	8050
55°	7989	6204	7000
60°	7117	5292	5884
65°	6311	4312	4692
70°	5599	3201	2669
75°	4670	1680	786
80°	3676	533	124
85°	2654	248	0



TEST NUMBER: P583811
 CATALOG NUMBER: HCC8S10D010MW-HM80520935-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.6	5.1
10°-20°	130.6	14.2
20°-30°	184.9	20.1
30°-40°	193.5	21.0
40°-50°	161.4	17.5
50°-60°	114.4	12.4
60°-70°	65.9	7.2
70°-80°	21.2	2.3
80°-90°	2.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.2	39.3
0°-40°	555.6	60.3
0°-60°	831.4	90.2
0°-90°	921.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	921.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	495	495	495	495	495	
5°	513	506	492	477	471	49
15°	527	506	460	424	412	148
25°	487	451	387	356	348	222
35°	380	347	291	275	282	236
45°	245	225	192	194	206	190
55°	149	133	115	121	130	134
65°	86	72	59	59	64	86
75°	39	29	14	7	7	42
85°	8	4	1	0	0	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583811

CATALOG NUMBER: HCC8S10D010MW-HM80520935-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	505.1	504.2	503.5	504.2	503.5	504.2	503.5	503.5	502.8	502.1	502.1
5°	513.1	512.4	512.4	512.4	511.7	511.0	511.0	510.2	508.7	508.0	506.5
7.5°	518.3	519.0	519.0	519.0	517.6	517.6	516.1	514.7	513.1	511.7	509.4
10°	524.2	524.2	523.5	522.7	521.3	520.6	519.9	518.3	516.1	513.1	511.0
12.5°	526.5	526.5	525.8	524.2	523.5	522.7	522.0	519.9	516.9	513.1	510.2
15°	527.2	525.8	525.0	524.2	522.7	520.6	520.6	517.6	513.9	509.4	505.8
17.5°	521.3	522.0	520.6	519.0	516.9	515.4	513.1	511.0	506.5	501.4	497.6
20°	513.9	513.1	512.4	510.2	507.2	506.5	504.2	500.6	496.9	491.0	485.8
22.5°	502.1	501.4	499.8	498.3	495.5	493.9	491.7	487.3	482.1	476.2	470.2
25°	487.3	485.8	483.6	480.7	478.4	477.0	473.9	469.5	463.6	457.0	451.0
27.5°	463.6	465.9	464.3	459.9	457.7	454.7	454.0	448.1	442.9	436.2	429.6
30°	440.7	440.7	438.5	436.2	432.6	430.3	427.4	423.0	417.8	409.6	404.5
32.5°	411.8	411.1	408.2	407.5	404.5	400.0	399.3	393.4	388.2	382.2	375.6
35°	380.1	378.6	375.6	373.5	371.9	369.7	367.5	362.3	357.1	351.2	346.8
37.5°	343.8	343.8	343.1	339.4	337.9	336.4	334.3	329.0	326.1	320.2	315.8
40°	309.0	308.3	306.1	305.4	303.9	301.7	300.3	297.3	292.8	288.4	283.9
42.5°	275.0	275.9	272.9	273.6	270.6	269.1	268.4	264.0	261.8	257.3	253.6
45°	244.7	244.0	242.6	241.8	240.3	238.8	237.4	235.1	231.4	227.1	224.8
47.5°	216.6	214.4	214.4	213.7	213.0	210.0	209.3	207.0	204.8	200.4	197.4
50°	190.0	190.0	190.0	189.3	187.0	186.3	184.9	182.6	180.4	177.4	173.0
52.5°	168.6	168.6	168.6	167.8	164.9	164.2	163.5	160.5	157.5	155.3	152.3
55°	148.6	149.4	148.6	147.1	145.0	145.0	142.7	141.2	138.2	136.1	133.1
57.5°	131.6	131.6	130.2	129.5	127.9	127.2	125.7	124.2	120.6	118.3	114.6
60°	115.4	114.6	114.6	113.1	111.7	110.2	109.4	107.2	105.8	102.0	99.0
62.5°	100.6	100.6	99.0	99.0	96.2	96.2	95.4	93.2	91.0	87.3	85.8
65°	86.5	86.5	85.8	85.0	82.8	82.1	81.4	79.1	76.9	74.6	72.5
67.5°	73.9	73.9	72.5	71.8	70.2	69.5	68.0	66.6	64.3	62.1	59.9
70°	62.1	61.4	60.6	59.9	58.4	57.7	56.3	54.7	52.5	51.0	48.8
72.5°	50.2	50.2	49.5	48.1	47.4	46.6	45.8	44.4	42.2	39.9	38.5
75°	39.2	39.2	39.2	37.7	36.2	35.5	35.5	34.0	32.6	30.3	28.8
77.5°	30.3	29.6	28.8	28.8	27.4	26.6	25.8	25.1	23.0	22.2	20.7
80°	20.7	21.4	20.7	20.0	19.2	18.5	18.5	16.9	16.2	14.8	13.3
82.5°	14.1	13.3	13.3	12.6	12.6	11.8	11.8	10.3	9.6	8.9	8.2
85°	7.5	7.5	6.6	6.6	6.6	5.9	5.9	5.2	5.2	4.4	3.7
87.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583811

CATALOG NUMBER: HCC8S10D010MW-HM80520935-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	501.4	499.8	499.1	499.1	498.3	497.6	496.9	496.2	494.6	494.6	493.2
5°	505.1	503.5	502.8	500.6	499.1	499.1	496.2	495.5	493.2	491.7	490.3
7.5°	508.0	505.1	502.8	500.6	499.1	497.6	494.6	491.7	488.7	485.8	484.3
10°	508.0	505.1	501.4	497.6	496.2	494.6	491.0	486.6	482.8	479.8	476.2
12.5°	506.5	502.1	497.6	494.6	491.7	489.5	485.0	480.7	476.2	470.2	467.3
15°	502.1	496.2	491.7	486.6	484.3	480.7	477.0	470.2	465.1	459.9	456.3
17.5°	493.2	485.8	480.7	475.4	471.8	469.5	463.6	457.7	451.8	445.8	441.5
20°	479.8	473.2	467.3	460.6	457.7	454.7	447.4	441.5	435.5	428.9	424.4
22.5°	463.6	457.0	448.8	443.7	439.2	435.5	428.9	422.3	416.3	410.4	404.5
25°	443.7	437.0	429.6	421.4	418.5	414.8	407.5	400.7	394.1	387.4	382.2
27.5°	422.3	413.4	407.5	398.6	395.6	391.9	383.8	376.3	370.5	365.3	359.4
30°	396.3	389.7	381.5	373.5	370.5	366.7	360.1	353.4	347.5	341.6	335.7
32.5°	368.2	361.6	353.4	347.5	343.1	340.2	333.4	327.5	321.7	315.8	310.6
35°	338.6	331.3	325.4	319.4	315.8	312.0	305.4	300.3	295.8	290.6	285.5
37.5°	308.3	303.1	297.3	290.6	286.9	283.9	278.7	272.9	269.1	264.7	261.1
40°	278.7	272.9	267.7	261.8	258.8	256.6	251.5	247.0	243.3	239.6	237.4
42.5°	248.5	243.3	238.1	234.4	232.2	229.9	226.2	221.0	218.9	215.2	213.0
45°	220.3	215.9	212.3	207.0	205.5	204.1	199.7	195.9	193.8	191.5	190.0
47.5°	193.8	190.8	186.3	183.4	181.1	179.7	176.7	173.8	171.5	170.1	168.6
50°	170.8	167.1	164.2	161.2	159.7	157.5	154.6	153.0	151.6	150.1	150.1
52.5°	149.4	145.7	142.7	140.5	139.1	137.5	135.3	134.6	133.1	133.1	132.3
55°	129.5	127.2	124.2	121.3	120.6	119.8	118.3	116.8	116.1	115.4	116.1
57.5°	112.4	110.2	107.2	105.1	104.2	103.5	102.8	101.3	100.6	100.6	100.6
60°	96.9	94.6	92.4	90.1	90.1	88.7	88.0	87.3	86.5	85.8	85.8
62.5°	82.8	80.7	78.4	76.9	76.2	75.4	73.9	73.2	72.5	72.5	71.8
65°	70.2	67.3	66.6	64.3	63.6	62.9	62.1	60.6	59.9	59.1	58.4
67.5°	57.7	56.3	54.0	52.5	51.8	51.0	50.2	48.8	48.1	47.4	45.8
70°	46.6	45.1	43.6	42.2	41.3	40.6	39.2	37.7	37.0	35.5	33.3
72.5°	36.2	34.7	33.3	31.9	31.0	30.3	28.8	27.4	25.8	24.4	23.0
75°	27.4	25.8	23.7	22.2	21.4	21.4	19.2	17.8	16.2	14.1	12.6
77.5°	19.2	16.9	16.2	14.8	14.1	12.6	11.1	9.6	8.2	7.5	5.9
80°	12.6	11.1	9.6	8.9	8.2	7.5	6.6	5.2	3.7	3.0	2.2
82.5°	7.5	6.6	5.9	5.2	4.4	3.7	3.0	3.0	2.2	1.4	0.7
85°	3.7	3.0	2.2	2.2	1.4	1.4	1.4	0.7	0.7	0.7	0.7
87.5°	1.4	0.7	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583811

CATALOG NUMBER: HCC8S10D010MW-HM80520935-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.5	491.7	491.0	490.3	490.3	488.7	488.7	488.0	486.6	485.8	485.8
5°	488.0	485.8	484.3	483.6	482.8	480.7	479.8	478.4	477.0	475.4	474.7
7.5°	481.4	477.7	476.2	475.4	473.2	471.1	469.5	467.3	465.1	462.9	462.2
10°	473.2	469.5	465.9	464.3	462.2	460.6	457.7	454.7	452.6	450.3	448.1
12.5°	462.9	458.4	454.7	453.3	451.0	448.1	443.7	442.2	438.5	437.0	434.0
15°	451.0	445.8	442.2	439.9	437.8	433.3	430.3	427.4	423.7	422.3	419.3
17.5°	436.2	430.3	426.6	424.4	423.0	419.3	414.8	411.1	407.5	405.9	403.8
20°	418.5	414.8	409.6	407.5	405.9	401.5	397.0	395.6	392.6	389.7	387.4
22.5°	398.6	394.9	389.7	387.4	386.7	383.1	379.4	377.1	374.9	372.6	370.5
25°	377.8	373.5	369.0	367.5	366.0	363.0	360.1	358.7	356.4	355.0	353.4
27.5°	355.7	351.2	347.5	345.3	343.8	341.6	340.2	338.6	337.2	335.7	335.0
30°	332.0	327.5	324.7	323.1	321.7	320.9	318.7	317.9	317.2	315.8	316.5
32.5°	308.3	304.6	301.7	299.4	299.4	298.0	297.3	297.3	296.5	296.5	296.5
35°	282.5	280.2	278.0	277.3	276.6	275.9	275.0	275.9	275.0	275.9	276.6
37.5°	258.8	256.6	255.1	254.3	253.6	254.3	253.6	253.6	254.3	255.8	256.6
40°	234.4	232.9	231.4	232.2	231.4	231.4	231.4	233.7	234.4	235.1	235.8
42.5°	211.4	210.0	209.3	209.3	210.0	209.3	210.7	211.4	213.0	215.2	216.6
45°	189.3	188.6	188.6	189.3	188.6	190.0	190.0	191.5	193.8	195.2	196.6
47.5°	168.6	168.6	168.6	169.4	169.4	170.1	171.5	172.2	173.8	175.3	176.7
50°	149.4	150.1	150.9	150.9	150.9	152.3	153.9	154.6	155.3	156.0	158.2
52.5°	132.3	133.1	133.1	133.8	134.6	135.3	136.1	137.5	138.2	139.8	140.5
55°	116.1	116.1	117.6	118.3	118.3	118.3	119.8	119.8	121.3	122.0	123.4
57.5°	100.6	101.3	101.3	102.0	102.0	102.8	103.5	104.2	105.1	105.8	106.5
60°	85.8	85.8	85.8	86.5	87.3	88.0	87.3	88.7	88.7	90.1	91.0
62.5°	71.8	72.5	72.5	72.5	72.5	72.5	72.5	73.2	73.9	74.6	75.4
65°	58.4	58.4	58.4	57.7	58.4	57.7	58.4	59.1	59.1	59.9	60.6
67.5°	45.1	45.1	43.6	43.6	44.4	44.4	44.4	44.4	43.6	45.1	45.1
70°	32.6	31.9	31.0	30.3	30.3	29.6	29.6	28.8	28.8	28.8	28.8
72.5°	21.4	20.0	18.5	17.8	16.9	16.9	15.5	14.8	15.5	15.5	15.5
75°	11.1	9.6	8.9	8.2	7.5	7.5	6.6	6.6	6.6	6.6	6.6
77.5°	4.4	3.7	3.0	3.0	2.2	2.2	2.2	2.2	2.2	2.2	2.2
80°	1.4	1.4	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
85°	0.7	0.0	0.0	0.7	0.0	0.7	0.7	0.7	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583811

CATALOG NUMBER: HCC8S10D010MW-HM80520935-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	485.0	485.0	484.3	485.0	483.6	484.3	483.6	483.6
5°	473.9	472.5	472.5	472.5	471.8	471.8	471.1	471.1
7.5°	460.6	459.9	459.2	458.4	457.7	457.0	457.0	457.0
10°	447.4	445.8	445.8	445.1	443.7	442.9	442.9	442.9
12.5°	431.9	431.0	430.3	430.3	427.4	428.2	427.4	427.4
15°	417.1	416.3	416.3	414.1	412.6	412.6	412.6	411.8
17.5°	401.5	400.7	400.0	398.6	397.0	397.0	396.3	397.0
20°	385.2	384.5	383.1	383.1	382.2	381.5	380.1	380.8
22.5°	369.0	367.5	366.7	366.7	366.0	366.0	364.6	364.6
25°	351.9	351.2	350.5	351.2	349.8	349.8	348.2	348.2
27.5°	334.3	333.4	333.4	333.4	332.7	333.4	332.7	332.7
30°	316.5	316.5	315.8	315.8	316.5	315.8	316.5	317.2
32.5°	297.3	297.3	298.0	298.0	298.7	298.7	298.7	298.7
35°	277.3	278.7	278.7	279.5	280.2	281.0	281.0	281.7
37.5°	258.8	259.5	260.2	261.1	262.5	262.5	262.5	262.5
40°	238.8	239.6	241.0	240.3	243.3	244.0	243.3	243.3
42.5°	218.2	219.6	220.3	221.8	222.6	224.1	224.8	224.8
45°	198.9	199.7	201.1	202.7	203.4	205.5	205.5	205.5
47.5°	179.0	180.4	181.1	182.6	183.4	185.6	186.3	185.6
50°	159.7	161.2	162.6	162.6	164.9	165.6	167.1	167.8
52.5°	141.2	142.0	143.4	144.2	145.7	147.1	147.8	148.6
55°	123.4	124.2	125.7	125.7	127.9	128.6	130.2	130.2
57.5°	107.2	107.9	109.4	108.7	110.2	111.7	111.7	110.9
60°	91.7	91.7	91.7	93.2	93.9	94.6	95.4	95.4
62.5°	75.4	76.9	77.6	77.6	78.4	79.1	79.1	78.4
65°	60.6	62.1	62.9	62.9	63.6	63.6	63.6	64.3
67.5°	45.8	45.8	45.8	46.6	45.8	45.8	45.8	45.8
70°	28.8	28.8	28.8	28.8	28.1	28.8	28.8	29.6
72.5°	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5
75°	6.6	6.6	6.6	7.5	6.6	6.6	6.6	6.6
77.5°	3.0	2.2	3.0	3.0	2.2	2.2	2.2	2.2
80°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
85°	0.0	0.7	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)