

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583812

Luminaire Tested: **HCC8S10D010SL-HM80520935-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583812  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S10D010SL-HM80520935-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1005.8 lumens  
Efficiency: N/A  
Efficacy: 101.6 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583812  
CATALOG NUMBER: HCC8S10D010SL-HM80520935-81WWW

### Luminous Intensity Polar Plot





TEST NUMBER: P583812

CATALOG NUMBER: HCC8S10D010SL-HM80520935-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	16806	16806	16806
5°	17393	16709	16044
10°	17779	16414	15142
15°	18034	15863	14139
20°	17980	15092	13126
25°	17536	14113	12051
30°	16614	12982	11059
35°	15114	11745	10051
40°	13276	10446	9077
45°	11574	9188	8094
50°	10074	8050	7129
55°	8984	7075	6204
60°	8159	6204	5292
65°	7340	5392	4794
70°	6537	4598	4337
75°	5731	3884	3693
80°	4866	3161	3285
85°	3644	2335	2654



TEST NUMBER: P583812  
 CATALOG NUMBER: HCC8S10D010SL-HM80520935-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.0	5.1
10°-20°	140.6	14.0
20°-30°	195.2	19.4
30°-40°	201.8	20.1
40°-50°	169.0	16.8
50°-60°	122.7	12.2
60°-70°	77.4	7.7
70°-80°	38.4	3.8
80°-90°	9.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	386.9	38.5
0°-40°	588.7	58.5
0°-60°	880.4	87.5
0°-90°	1005.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1005.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	545	545	545	545	545	
5°	562	555	540	525	518	54
15°	565	543	497	457	443	159
25°	515	482	415	370	354	236
35°	402	372	312	277	267	250
45°	265	246	211	190	186	205
55°	167	152	132	121	115	151
65°	101	88	74	65	66	100
75°	48	40	33	31	31	52
85°	10	8	7	8	8	13
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583812

CATALOG NUMBER: HCC8S10D010SL-HM80520935-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	553.9	553.9	554.6	553.9	553.9	553.9	553.0	553.0	552.3	552.3	550.9
5°	561.9	560.5	561.9	560.5	560.5	560.5	559.8	558.2	557.5	556.0	555.3
7.5°	565.7	564.9	564.9	564.2	564.2	563.4	562.7	561.9	559.1	558.2	556.0
10°	567.8	567.1	567.1	566.4	564.9	564.9	563.4	562.7	559.1	557.5	554.6
12.5°	567.1	567.1	567.1	566.4	564.2	563.4	561.9	559.8	556.8	553.9	550.9
15°	564.9	564.9	563.4	562.7	560.5	559.1	558.2	554.6	551.6	547.9	543.4
17.5°	557.5	557.5	556.8	555.3	553.0	551.6	550.2	546.4	543.4	537.5	533.1
20°	547.9	547.2	546.4	544.3	542.0	541.3	539.0	533.8	530.2	525.8	519.9
22.5°	533.8	533.1	532.4	530.9	527.2	525.8	524.2	520.6	513.9	509.4	502.1
25°	515.4	515.4	513.9	511.7	508.0	506.5	504.2	500.6	494.6	488.0	482.1
27.5°	493.9	493.2	491.0	489.5	486.6	484.3	480.7	476.2	470.2	465.1	457.7
30°	466.6	466.6	465.1	462.9	459.2	457.7	454.7	449.5	443.7	437.0	431.9
32.5°	435.5	435.5	433.3	431.9	429.6	425.9	425.1	419.3	414.1	408.9	403.0
35°	401.5	402.2	400.7	397.9	394.1	394.1	392.6	387.4	381.5	376.3	371.9
37.5°	367.5	365.3	364.6	363.0	360.8	357.8	356.4	354.2	349.1	345.3	338.6
40°	329.8	330.6	329.0	327.5	326.8	324.7	323.8	320.2	316.5	312.0	309.0
42.5°	295.8	295.8	295.8	294.2	292.8	290.6	289.8	287.6	283.2	280.2	275.9
45°	265.4	263.2	263.2	262.5	261.8	260.2	258.1	256.6	253.6	251.5	246.2
47.5°	235.8	236.6	235.8	235.1	232.9	232.2	231.4	228.5	225.5	223.3	219.6
50°	210.0	211.4	210.0	210.0	208.5	207.8	206.3	204.1	201.8	198.2	194.5
52.5°	188.6	188.6	187.8	187.0	184.9	183.4	182.6	181.9	178.3	175.3	172.2
55°	167.1	167.8	167.8	165.6	164.9	163.4	162.6	160.5	159.0	154.6	152.3
57.5°	148.6	147.8	148.6	147.1	145.7	144.2	143.4	142.0	139.8	136.8	133.8
60°	132.3	130.9	130.9	130.2	128.6	127.9	126.5	124.2	122.0	119.0	116.8
62.5°	116.1	115.4	114.6	113.8	112.4	111.7	110.9	108.7	106.5	104.2	102.0
65°	100.6	100.6	99.8	98.3	97.6	96.9	96.2	94.6	91.7	90.1	88.0
67.5°	86.5	85.8	85.8	84.3	82.8	82.1	82.1	80.7	78.4	76.2	74.6
70°	72.5	73.2	72.5	71.8	70.2	70.2	68.8	68.0	65.0	64.3	62.1
72.5°	59.9	59.9	59.1	59.1	57.7	57.0	57.0	55.4	54.0	52.5	51.0
75°	48.1	48.1	48.1	47.4	46.6	45.1	45.1	44.4	42.9	41.3	39.9
77.5°	37.7	37.0	37.0	36.2	35.5	34.7	34.7	34.0	32.6	31.9	30.3
80°	27.4	26.6	26.6	26.6	25.1	25.8	25.1	24.4	23.7	23.0	22.2
82.5°	17.8	18.5	18.5	17.8	16.9	16.9	16.9	16.2	16.2	15.5	14.8
85°	10.3	10.3	10.3	10.3	9.6	9.6	9.6	8.9	8.9	8.9	8.2
87.5°	4.4	4.4	4.4	4.4	4.4	4.4	3.7	3.7	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583812

CATALOG NUMBER: HCC8S10D010SL-HM80520935-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	550.9	549.4	548.6	547.9	547.9	547.2	546.4	545.0	545.0	543.4	542.7
5°	553.9	551.6	550.2	548.6	547.9	546.4	545.0	542.7	542.0	539.8	537.5
7.5°	554.6	550.9	549.4	546.4	545.0	543.4	540.5	538.3	535.4	533.1	530.2
10°	551.6	548.6	545.0	541.3	540.5	538.3	533.8	530.9	527.2	524.2	519.9
12.5°	547.2	542.7	539.0	534.6	532.4	530.2	525.8	521.3	516.1	511.0	506.5
15°	539.8	534.6	529.5	524.2	521.3	519.0	513.9	508.7	503.5	496.9	492.5
17.5°	528.6	522.7	517.6	511.0	508.0	505.8	499.1	493.2	486.6	479.8	475.4
20°	514.6	507.2	501.4	493.9	491.7	488.0	481.4	474.7	467.3	459.9	454.7
22.5°	496.2	488.7	482.1	474.7	471.1	467.3	460.6	452.6	445.1	439.2	434.0
25°	474.7	468.1	459.9	453.3	448.8	444.4	437.0	430.3	423.7	414.8	409.6
27.5°	451.0	442.9	437.0	428.2	423.7	420.7	412.6	403.8	397.9	389.7	383.8
30°	424.4	417.0	410.4	401.5	397.0	394.1	386.7	378.6	372.6	364.6	358.7
32.5°	396.3	388.2	380.1	374.2	369.0	366.0	357.8	352.7	345.3	338.6	332.0
35°	366.0	357.8	351.9	343.8	340.9	337.9	331.3	324.7	317.9	312.0	306.9
37.5°	333.4	327.5	320.9	315.0	312.8	309.8	301.7	295.8	290.6	284.6	280.2
40°	301.7	296.5	292.1	286.2	282.5	280.2	274.3	269.1	263.2	259.5	255.1
42.5°	272.9	267.0	262.5	258.1	254.3	252.2	247.0	243.3	238.8	235.1	229.9
45°	242.6	239.6	234.4	230.7	228.5	225.5	221.8	217.4	213.7	210.7	207.0
47.5°	215.9	213.0	209.3	204.8	203.4	201.1	197.4	194.5	191.5	188.6	184.9
50°	191.5	187.8	184.9	181.9	180.4	178.3	174.5	173.0	170.8	167.8	165.6
52.5°	169.4	166.4	163.4	159.7	159.0	157.5	155.3	152.3	150.1	148.6	147.1
55°	149.4	146.4	144.2	141.2	140.5	139.0	136.1	134.6	133.1	131.6	130.2
57.5°	131.6	128.6	125.7	124.2	122.7	121.3	120.6	118.3	116.8	116.1	114.6
60°	115.4	112.4	110.2	107.9	107.2	106.5	105.1	103.5	102.0	100.6	99.8
62.5°	99.8	96.9	95.4	93.9	92.4	92.4	91.0	89.4	88.0	87.3	85.8
65°	85.8	84.3	82.1	79.8	79.1	79.1	76.9	76.2	75.4	73.9	72.5
67.5°	72.5	71.0	68.8	68.0	67.3	66.6	65.7	64.3	62.9	62.1	60.6
70°	60.6	59.1	57.7	57.0	56.3	55.4	54.0	53.2	51.8	51.0	50.2
72.5°	48.8	48.1	46.6	45.8	45.1	44.4	43.6	42.9	41.3	40.6	39.9
75°	39.2	38.5	37.0	36.2	35.5	35.5	34.7	33.3	32.6	32.6	31.9
77.5°	29.6	28.8	28.1	27.4	26.6	26.6	25.8	25.1	24.4	24.4	23.7
80°	21.4	20.7	20.0	20.0	20.0	19.2	18.5	18.5	17.8	17.8	16.9
82.5°	14.1	14.1	13.3	13.3	13.3	12.6	12.6	11.8	11.8	11.8	11.8
85°	8.2	8.2	8.2	7.5	7.5	7.5	7.5	7.5	7.5	6.6	7.5
87.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.0	3.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583812

CATALOG NUMBER: HCC8S10D010SL-HM80520935-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	542.0	541.3	539.8	539.8	538.3	538.3	537.5	536.8	536.1	535.4	534.6
5°	536.8	533.8	532.4	531.6	530.2	529.5	527.2	525.8	525.0	523.5	522.0
7.5°	527.2	524.2	521.3	520.6	519.9	516.9	514.6	512.4	511.0	509.4	508.0
10°	516.1	513.1	509.4	508.0	506.5	502.8	499.8	497.6	494.6	491.7	491.0
12.5°	502.8	498.3	493.9	492.5	490.2	486.6	483.6	479.8	477.7	473.9	473.2
15°	487.3	482.1	478.4	474.7	473.2	469.5	464.3	461.4	457.0	455.4	451.8
17.5°	468.8	463.6	458.4	457.0	454.7	449.5	444.4	440.7	436.2	434.0	431.9
20°	449.5	442.9	437.8	436.2	433.3	428.9	423.7	420.0	416.3	411.8	409.6
22.5°	427.4	420.0	415.5	411.8	411.1	405.9	400.0	397.0	394.1	390.4	387.4
25°	403.0	396.3	391.1	388.2	386.7	382.2	377.8	374.2	369.7	367.5	363.8
27.5°	377.8	373.5	366.7	363.8	361.6	357.8	352.7	350.5	346.1	343.1	340.9
30°	353.4	346.8	343.1	339.4	337.2	333.4	329.0	326.8	323.1	320.2	317.9
32.5°	326.8	322.4	317.2	315.8	312.8	309.0	306.1	302.4	299.4	296.5	295.8
35°	302.4	296.5	291.4	289.8	287.6	283.9	282.5	280.2	276.6	275.9	272.9
37.5°	275.9	272.9	267.0	264.7	264.0	261.0	258.1	256.6	254.3	252.2	251.5
40°	250.6	247.0	244.0	241.8	240.3	238.1	235.1	234.4	232.9	229.9	229.2
42.5°	227.1	223.3	220.3	219.6	217.4	215.2	213.7	211.4	210.7	210.0	208.5
45°	204.1	201.8	198.9	198.2	197.4	194.5	193.0	191.5	190.0	189.3	187.8
47.5°	183.4	181.1	179.0	178.3	176.7	176.0	173.8	173.0	170.8	170.1	169.4
50°	163.4	161.9	160.5	159.7	158.2	157.5	156.0	154.6	153.0	152.3	151.6
52.5°	145.7	144.2	142.7	142.0	141.2	139.8	138.2	136.8	136.1	135.3	134.6
55°	128.6	127.2	126.5	125.7	125.0	124.2	122.0	121.3	120.6	119.8	118.3
57.5°	113.1	111.7	110.2	110.2	109.4	108.7	107.2	105.8	105.8	104.2	102.8
60°	99.0	97.6	96.2	95.4	94.6	93.2	92.4	91.7	91.0	90.1	88.7
62.5°	84.3	83.5	82.1	82.1	80.7	79.8	79.1	78.4	77.6	76.2	75.4
65°	71.8	71.0	69.5	68.8	68.8	68.0	66.6	65.7	65.0	65.0	64.3
67.5°	59.9	59.1	57.7	57.0	57.0	56.3	55.4	55.4	54.7	54.0	54.7
70°	49.5	48.1	48.1	47.4	47.4	46.6	45.8	45.8	45.8	46.6	46.6
72.5°	39.2	38.5	37.7	37.7	37.7	37.7	37.0	37.0	37.7	38.5	38.5
75°	31.0	30.3	30.3	30.3	29.6	29.6	30.3	30.3	31.0	31.0	31.0
77.5°	23.0	23.0	23.0	23.0	23.0	23.0	23.7	23.7	24.4	24.4	24.4
80°	16.9	16.9	16.9	16.9	16.9	17.8	17.8	17.8	17.8	17.8	18.5
82.5°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	12.6	12.6	12.6	12.6
85°	6.6	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
87.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583812

CATALOG NUMBER: HCC8S10D010SL-HM80520935-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	533.8	533.8	533.8	534.6	533.1	533.1	533.1	533.1
5°	521.3	520.6	519.9	520.6	519.0	519.0	518.3	518.3
7.5°	505.8	505.1	504.2	504.2	502.8	502.8	502.1	501.4
10°	488.7	487.3	488.0	486.6	485.8	485.0	484.3	483.6
12.5°	470.2	468.8	468.1	466.6	465.1	464.3	465.1	463.6
15°	450.3	448.1	447.4	445.8	444.4	443.7	443.7	442.9
17.5°	428.2	426.6	425.9	424.4	423.7	422.3	421.4	420.7
20°	407.5	403.8	404.5	403.0	402.2	399.3	399.3	400.0
22.5°	384.5	382.2	380.8	379.4	378.6	377.1	377.1	376.3
25°	361.6	359.4	358.7	357.1	356.4	355.0	354.2	354.2
27.5°	339.4	336.4	336.4	335.0	333.4	332.7	332.0	331.3
30°	315.8	313.5	312.8	312.8	312.0	312.0	309.8	310.6
32.5°	293.5	292.1	291.4	289.8	289.8	289.1	289.1	286.9
35°	271.4	269.1	269.8	268.4	267.7	267.0	267.7	267.0
37.5°	249.9	248.5	248.5	247.0	247.0	246.2	245.4	247.0
40°	228.5	227.8	227.1	226.2	227.1	226.2	224.8	225.5
42.5°	207.0	207.0	206.3	206.3	205.5	205.5	205.5	205.5
45°	187.8	187.0	187.0	186.3	186.3	186.3	186.3	185.6
47.5°	168.6	167.8	167.8	167.8	167.1	167.1	166.4	167.1
50°	150.1	150.1	149.4	149.4	150.1	149.4	148.6	148.6
52.5°	133.1	133.1	132.3	132.3	131.6	130.9	131.6	131.6
55°	117.6	116.8	116.1	116.1	115.4	114.6	114.6	115.4
57.5°	102.8	102.0	101.3	101.3	99.8	99.0	99.0	99.0
60°	88.7	87.3	87.3	86.5	86.5	85.8	85.8	85.8
62.5°	75.4	74.6	74.6	74.6	74.6	73.9	73.9	73.9
65°	64.3	64.3	64.3	65.0	65.0	65.7	65.7	65.7
67.5°	55.4	56.3	56.3	56.3	57.0	57.0	57.0	56.3
70°	47.4	47.4	47.4	48.1	48.1	48.1	48.1	48.1
72.5°	39.2	39.2	39.2	39.2	39.2	39.2	39.2	39.2
75°	31.0	31.9	31.9	31.9	31.0	31.9	31.9	31.0
77.5°	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4
80°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5
82.5°	12.6	12.6	12.6	12.6	12.6	12.6	12.6	12.6
85°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
87.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)