

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583847

Luminaire Tested: **HCC8W15D010MB-HM80520827-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583847  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W15D010MB-HM80520827-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1513.7 lumens  
Efficiency: N/A  
Efficacy: 108.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583847  
CATALOG NUMBER: HCC8W15D010MB-HM80520827-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583847

CATALOG NUMBER: HCC8W15D010MB-HM80520827-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	23207	23207	23207
5°	24058	23129	22340
10°	24736	22930	21424
15°	25290	22522	20476
20°	25330	21645	19643
25°	24844	20442	18951
30°	23565	18957	18120
35°	21412	17264	17305
40°	18718	15494	16307
45°	16223	13798	15198
50°	14210	12257	13845
55°	12645	10865	12526
60°	11409	9757	11015
65°	10295	8581	9595
70°	9259	7222	7141
75°	8149	5731	5349
80°	6819	4759	5132
85°	5272	4175	4529



TEST NUMBER: P583847  
 CATALOG NUMBER: HCC8W15D010MB-HM80520827-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.0	4.7
10°-20°	200.0	13.2
20°-30°	285.8	18.9
30°-40°	303.7	20.1
40°-50°	261.5	17.3
50°-60°	195.5	12.9
60°-70°	124.7	8.2
70°-80°	56.8	3.7
80°-90°	14.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.8	36.8
0°-40°	860.5	56.8
0°-60°	1317.4	87.0
0°-90°	1513.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1513.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	753	753	753	753	753	
5°	777	766	747	728	722	74
15°	792	765	706	657	641	223
25°	730	684	601	564	557	334
35°	569	529	459	447	460	354
45°	372	352	316	325	348	289
55°	235	216	202	219	233	211
65°	141	125	118	123	132	141
75°	68	59	48	44	45	73
85°	15	13	12	13	13	18
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583847

CATALOG NUMBER: HCC8W15D010MB-HM80520827-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6
2.5°	766.5	764.3	765.4	764.3	765.4	765.4	763.4	763.4	763.4	763.4	760.1
5°	777.2	776.1	776.1	775.1	774.0	775.1	774.0	772.9	770.8	769.8	766.5
7.5°	783.6	783.6	783.6	783.6	782.5	781.4	780.5	778.3	776.1	774.0	771.9
10°	790.0	791.1	790.0	789.0	787.9	785.8	784.7	782.5	779.4	776.1	774.0
12.5°	793.3	793.3	792.2	792.2	790.0	789.0	785.8	782.5	779.4	776.1	770.8
15°	792.2	792.2	791.1	790.0	786.9	785.8	783.6	780.5	775.1	770.8	765.4
17.5°	785.8	784.7	782.5	782.5	778.3	777.2	775.1	770.8	765.4	759.0	752.6
20°	771.9	771.9	770.8	769.8	765.4	762.3	760.1	754.8	750.5	743.0	736.6
22.5°	752.6	754.8	752.6	750.5	745.2	744.1	740.8	734.4	728.1	719.5	712.0
25°	730.2	729.1	728.1	725.9	721.7	719.5	715.2	708.8	702.4	692.8	684.2
27.5°	701.3	697.1	697.1	692.8	689.5	686.4	684.2	677.8	669.3	661.8	651.1
30°	661.8	662.9	657.4	656.4	651.1	648.9	644.7	638.3	630.7	622.1	613.7
32.5°	619.0	615.8	615.8	611.5	607.2	604.1	603.0	595.5	589.0	580.4	571.9
35°	568.8	568.8	565.5	564.4	560.2	558.0	554.9	550.6	543.1	535.6	529.2
37.5°	519.6	517.4	516.3	514.2	511.0	507.8	507.8	500.3	499.2	490.7	482.1
40°	465.0	467.2	465.0	461.9	460.8	458.6	457.5	453.3	450.1	442.6	437.3
42.5°	419.1	416.9	416.9	415.8	411.6	411.6	409.5	407.3	402.0	399.8	393.4
45°	372.0	374.2	371.0	372.0	367.8	367.8	367.8	363.4	359.2	356.0	351.7
47.5°	331.4	332.5	332.5	329.3	328.2	328.2	326.1	323.9	320.8	316.4	313.2
50°	296.2	297.2	295.1	294.0	291.9	290.8	290.8	286.5	284.4	280.0	278.0
52.5°	264.0	264.0	263.1	263.1	259.8	259.8	257.6	254.5	252.3	250.2	244.9
55°	235.2	235.2	234.1	233.0	233.0	229.8	228.8	225.6	223.4	219.2	215.9
57.5°	207.4	208.5	207.4	206.3	205.2	204.2	202.1	198.8	196.7	193.5	191.4
60°	185.0	185.0	183.9	182.8	180.6	179.5	178.6	176.4	173.2	171.1	167.9
62.5°	163.5	162.6	161.5	160.4	158.2	158.2	156.0	154.0	150.7	148.6	146.4
65°	141.1	141.1	140.0	140.0	138.9	136.9	135.8	134.7	130.4	129.4	125.1
67.5°	120.9	121.8	119.8	119.8	117.6	117.6	116.5	113.3	112.3	110.1	108.0
70°	102.7	102.7	102.7	101.6	99.4	98.3	97.2	95.2	94.1	91.9	89.8
72.5°	84.5	84.5	83.4	83.4	82.3	81.2	80.1	78.1	78.1	75.9	73.7
75°	68.4	68.4	67.4	66.3	65.2	65.2	64.1	63.0	61.0	59.9	58.8
77.5°	52.4	52.4	52.4	51.3	50.2	50.2	50.2	48.1	45.9	45.9	44.9
80°	38.4	38.4	37.5	37.5	36.4	36.4	36.4	35.3	34.2	33.1	32.1
82.5°	25.7	25.7	25.7	25.7	24.6	24.6	24.6	23.5	22.4	22.4	22.4
85°	14.9	14.9	14.9	14.9	13.9	13.9	13.9	13.9	13.9	12.8	12.8
87.5°	6.4	5.3	6.4	5.3	6.4	5.3	6.4	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583847

CATALOG NUMBER: HCC8W15D010MB-HM80520827-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6
2.5°	761.2	760.1	759.0	757.9	757.9	756.9	754.8	753.7	752.6	751.6	751.6
5°	765.4	764.3	762.3	760.1	759.0	756.9	754.8	752.6	750.5	747.2	746.3
7.5°	768.7	765.4	763.4	759.0	757.9	755.8	752.6	749.4	745.2	740.8	737.7
10°	768.7	764.3	761.2	755.8	753.7	751.6	747.2	741.9	736.6	732.3	727.0
12.5°	766.5	761.2	755.8	750.5	747.2	744.1	737.7	732.3	725.9	719.5	715.2
15°	759.0	752.6	746.3	739.7	736.6	732.3	725.9	718.4	712.0	705.5	698.1
17.5°	745.2	738.8	731.2	723.7	719.5	716.3	706.6	701.3	691.7	685.3	678.9
20°	727.0	719.5	709.9	702.4	697.1	693.8	686.4	676.7	669.3	659.6	653.2
22.5°	703.5	693.8	684.2	676.7	671.4	667.1	657.4	647.8	641.4	632.9	625.4
25°	675.6	666.0	656.4	645.8	640.3	636.1	627.6	619.0	610.5	600.8	594.4
27.5°	642.5	631.8	623.2	613.7	608.3	601.9	592.3	583.7	575.1	568.8	560.2
30°	606.1	594.4	585.9	576.2	570.9	565.5	555.9	547.3	539.8	532.4	528.2
32.5°	562.4	553.8	545.3	535.6	531.3	528.2	518.5	510.0	501.4	495.0	491.8
35°	520.7	511.0	503.6	495.0	489.6	486.5	477.9	470.4	466.1	458.6	454.4
37.5°	476.8	469.3	460.8	452.2	449.0	445.8	439.3	431.9	425.5	420.2	418.0
40°	430.8	424.4	416.9	411.6	408.4	405.1	399.8	394.5	390.2	384.9	382.7
42.5°	387.0	382.7	376.3	369.9	366.7	365.6	359.2	354.9	352.8	350.7	348.5
45°	347.4	341.0	336.8	332.5	329.3	327.2	323.9	320.8	318.6	316.4	314.3
47.5°	309.0	303.7	299.3	296.2	292.9	291.9	289.7	286.5	284.4	284.4	284.4
50°	273.7	269.4	265.1	263.1	262.0	259.8	257.6	256.5	255.5	255.5	255.5
52.5°	242.7	238.3	235.2	233.0	233.0	230.9	228.8	227.7	227.7	227.7	227.7
55°	213.8	210.6	208.5	206.3	204.2	203.2	203.2	203.2	202.1	202.1	203.2
57.5°	188.1	186.1	182.8	180.6	179.5	179.5	178.6	177.5	178.6	179.5	180.6
60°	164.6	162.6	161.5	158.2	158.2	158.2	157.1	157.1	157.1	158.2	159.3
62.5°	143.3	142.2	140.0	138.9	137.9	137.9	136.9	136.9	136.9	136.9	137.9
65°	124.0	121.8	119.8	119.8	119.8	118.7	118.7	116.5	117.6	117.6	116.5
67.5°	105.8	103.8	102.7	101.6	100.5	100.5	99.4	98.3	97.2	97.2	97.2
70°	88.7	86.6	86.6	84.5	84.5	83.4	82.3	82.3	81.2	80.1	79.2
72.5°	71.6	70.6	69.5	68.4	68.4	68.4	67.4	66.3	65.2	64.1	62.1
75°	56.6	56.6	54.5	53.5	53.5	52.4	51.3	50.2	49.2	48.1	47.0
77.5°	43.9	42.8	40.6	39.5	39.5	39.5	38.4	37.5	36.4	35.3	34.2
80°	32.1	31.0	29.9	28.9	28.9	28.9	27.8	27.8	26.8	26.8	26.8
82.5°	21.3	21.3	20.4	20.4	20.4	20.4	19.3	19.3	19.3	19.3	19.3
85°	12.8	12.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583847

CATALOG NUMBER: HCC8W15D010MB-HM80520827-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6
2.5°	749.4	749.4	747.2	746.3	745.2	746.3	744.1	743.0	741.9	741.9	740.8
5°	743.0	741.9	737.7	736.6	735.5	734.4	732.3	730.2	728.1	727.0	725.9
7.5°	734.4	731.2	727.0	725.9	724.8	721.7	718.4	716.3	713.1	712.0	709.9
10°	722.6	718.4	715.2	712.0	709.9	706.6	703.5	700.2	696.0	694.9	691.7
12.5°	708.8	703.5	697.1	696.0	692.8	688.5	684.2	680.9	677.8	675.6	672.4
15°	691.7	686.4	680.0	676.7	673.5	670.3	664.9	660.7	657.4	654.3	651.1
17.5°	671.4	664.9	659.6	656.4	654.3	648.9	644.7	639.3	636.1	632.9	629.7
20°	646.8	641.4	634.0	630.7	629.7	625.4	620.1	617.9	613.7	610.5	608.3
22.5°	619.0	613.7	607.2	605.2	600.8	598.6	593.3	591.2	589.0	585.9	584.8
25°	588.0	582.6	577.3	576.2	573.0	570.9	567.7	564.4	564.4	561.3	561.3
27.5°	555.9	550.6	546.3	544.2	543.1	540.9	537.8	536.7	535.6	534.5	534.5
30°	521.8	515.3	513.2	512.1	511.0	508.9	507.8	505.6	506.7	507.8	506.7
32.5°	485.4	483.2	479.0	476.8	477.9	476.8	474.6	476.8	475.7	477.9	479.0
35°	450.1	447.9	445.8	445.8	443.7	443.7	443.7	444.8	446.8	447.9	450.1
37.5°	415.8	412.7	411.6	410.5	411.6	411.6	411.6	413.7	415.8	418.0	421.3
40°	379.6	377.4	377.4	377.4	377.4	380.5	379.6	381.6	383.8	387.0	390.2
42.5°	345.4	345.4	346.4	346.4	346.4	346.4	348.5	351.7	354.9	358.1	361.4
45°	313.2	313.2	313.2	315.3	315.3	316.4	320.8	322.8	325.0	328.2	331.4
47.5°	283.3	283.3	284.4	285.5	286.5	288.6	290.8	294.0	297.2	299.3	302.6
50°	255.5	256.5	258.7	260.9	260.9	262.0	265.1	267.3	269.4	272.6	273.7
52.5°	228.8	230.9	233.0	234.1	235.2	237.4	238.3	241.6	242.7	245.9	246.9
55°	204.2	205.2	208.5	209.5	209.5	211.7	213.8	215.9	219.2	219.2	221.2
57.5°	181.7	182.8	185.0	186.1	185.0	188.1	189.2	191.4	192.4	194.6	195.7
60°	159.3	161.5	162.6	162.6	163.5	164.6	166.8	166.8	168.9	171.1	171.1
62.5°	137.9	138.9	140.0	141.1	142.2	141.1	144.4	144.4	146.4	147.5	149.7
65°	117.6	118.7	118.7	119.8	119.8	120.9	120.9	121.8	122.9	125.1	126.2
67.5°	97.2	97.2	97.2	98.3	97.2	98.3	98.3	99.4	99.4	101.6	102.7
70°	79.2	78.1	77.0	77.0	77.0	77.0	75.9	77.0	77.0	78.1	78.1
72.5°	61.0	59.9	58.8	57.7	57.7	56.6	55.6	56.6	56.6	57.7	57.7
75°	45.9	43.9	43.9	43.9	42.8	42.8	42.8	43.9	43.9	43.9	44.9
77.5°	34.2	34.2	33.1	33.1	33.1	34.2	34.2	35.3	35.3	35.3	35.3
80°	25.7	26.8	26.8	26.8	26.8	27.8	27.8	27.8	27.8	28.9	28.9
82.5°	19.3	19.3	19.3	19.3	20.4	20.4	20.4	20.4	20.4	20.4	20.4
85°	11.8	12.8	12.8	11.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P583847

CATALOG NUMBER: HCC8W15D010MB-HM80520827-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	752.6	752.6	752.6	752.6	752.6	752.6	752.6	752.6
2.5°	739.7	739.7	739.7	739.7	738.8	738.8	738.8	737.7
5°	723.7	723.7	723.7	721.7	722.6	722.6	720.6	721.7
7.5°	707.7	706.6	705.5	705.5	704.6	703.5	702.4	703.5
10°	689.5	686.4	686.4	685.3	685.3	683.1	683.1	684.2
12.5°	669.3	667.1	667.1	666.0	664.9	663.8	662.9	662.9
15°	648.9	646.8	645.8	644.7	643.6	641.4	642.5	641.4
17.5°	628.6	625.4	625.4	624.3	623.2	621.2	621.2	620.1
20°	605.2	604.1	601.9	603.0	601.9	599.7	598.6	598.6
22.5°	581.5	581.5	580.4	580.4	579.5	578.4	577.3	577.3
25°	559.1	558.0	559.1	559.1	555.9	555.9	555.9	557.0
27.5°	533.5	534.5	533.5	533.5	533.5	533.5	534.5	533.5
30°	507.8	507.8	507.8	508.9	511.0	510.0	510.0	508.9
32.5°	480.1	481.0	481.0	482.1	483.2	485.4	485.4	486.5
35°	452.2	454.4	455.4	454.4	457.5	457.5	459.7	459.7
37.5°	423.3	424.4	426.6	427.7	429.8	430.8	431.9	431.9
40°	392.3	396.6	397.7	398.7	402.0	402.0	403.1	405.1
42.5°	363.4	367.8	368.9	369.9	372.0	375.2	374.2	376.3
45°	335.7	338.8	339.9	341.0	344.3	345.4	345.4	348.5
47.5°	305.7	307.9	309.0	311.1	313.2	315.3	317.5	316.4
50°	275.8	279.1	281.1	282.2	285.5	286.5	287.6	288.6
52.5°	249.1	251.2	252.3	253.4	256.5	257.6	258.7	260.9
55°	223.4	224.5	226.7	225.6	228.8	229.8	230.9	233.0
57.5°	197.7	198.8	199.9	199.9	202.1	204.2	205.2	206.3
60°	173.2	175.3	176.4	176.4	176.4	178.6	178.6	178.6
62.5°	150.7	150.7	151.8	151.8	154.0	154.0	154.0	154.0
65°	127.2	128.3	129.4	129.4	131.5	130.4	132.6	131.5
67.5°	102.7	102.7	104.7	104.7	103.8	104.7	104.7	104.7
70°	78.1	78.1	79.2	79.2	79.2	79.2	79.2	79.2
72.5°	57.7	57.7	57.7	58.8	57.7	57.7	58.8	57.7
75°	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9
77.5°	35.3	35.3	36.4	36.4	36.4	36.4	36.4	36.4
80°	28.9	28.9	28.9	28.9	29.9	28.9	28.9	28.9
82.5°	21.3	20.4	21.3	20.4	21.3	21.3	21.3	21.3
85°	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)