

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583864

Luminaire Tested: **HCC8W15D010BZ-HM80520830-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583864
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W15D010BZ-HM80520830-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1505.5 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583864
CATALOG NUMBER: HCC8W15D010BZ-HM80520830-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583864

CATALOG NUMBER: HCC8W15D010BZ-HM80520830-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	23081	23081	23081
5°	23928	23005	22216
10°	24605	22805	21308
15°	25150	22404	20364
20°	25192	21527	19538
25°	24712	20333	18846
30°	23436	18854	18021
35°	21292	17170	17211
40°	18617	15409	16222
45°	16140	13724	15119
50°	14128	12190	13768
55°	12575	10806	12462
60°	11348	9707	10953
65°	10244	8537	9537
70°	9205	7195	7096
75°	8114	5695	5326
80°	6801	4724	5097
85°	5272	4140	4529



TEST NUMBER: P583864

CATALOG NUMBER: HCC8W15D010BZ-HM80520830-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.6	4.7
10°-20°	198.9	13.2
20°-30°	284.3	18.9
30°-40°	302.0	20.1
40°-50°	260.0	17.3
50°-60°	194.4	12.9
60°-70°	124.0	8.2
70°-80°	56.4	3.7
80°-90°	14.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.8	36.8
0°-40°	855.8	56.8
0°-60°	1310.3	87.0
0°-90°	1505.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1505.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	748	748	748	748	748	
5°	773	762	743	724	718	74
15°	788	761	702	654	638	222
25°	726	680	598	561	554	332
35°	566	526	456	444	457	352
45°	370	350	315	323	347	288
55°	234	215	201	218	232	210
65°	140	124	117	122	131	140
75°	68	58	48	44	45	72
85°	15	13	12	13	13	18
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583864

CATALOG NUMBER: HCC8W15D010BZ-HM80520830-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5
2.5°	762.4	760.2	761.3	760.2	761.3	761.3	759.2	759.2	759.2	759.2	756.0
5°	773.0	771.9	771.9	770.8	769.8	770.8	769.8	768.8	766.6	765.5	762.4
7.5°	779.4	779.4	779.4	779.4	778.3	777.2	776.1	774.1	771.9	769.8	767.7
10°	785.8	786.9	785.8	784.7	783.6	781.6	780.5	778.3	775.2	771.9	769.8
12.5°	788.9	788.9	787.8	787.8	785.8	784.7	781.6	778.3	775.2	771.9	766.6
15°	787.8	787.8	786.9	785.8	782.5	781.6	779.4	776.1	770.8	766.6	761.3
17.5°	781.6	780.5	778.3	778.3	774.1	773.0	770.8	766.6	761.3	754.9	748.5
20°	767.7	767.7	766.6	765.5	761.3	758.1	756.0	750.7	746.4	739.0	732.6
22.5°	748.5	750.7	748.5	746.4	741.1	740.0	736.9	730.5	724.1	715.5	708.2
25°	726.3	725.2	724.1	721.9	717.7	715.5	711.3	704.9	698.5	689.0	680.5
27.5°	697.5	693.2	693.2	689.0	685.8	682.6	680.5	674.1	665.6	658.2	647.6
30°	658.2	659.3	654.0	652.9	647.6	645.4	641.2	634.8	627.3	618.8	610.3
32.5°	615.6	612.5	612.5	608.2	603.9	600.7	599.7	592.3	585.9	577.3	568.9
35°	565.6	565.6	562.5	561.4	557.2	555.0	551.9	547.6	540.2	532.7	526.3
37.5°	516.7	514.7	513.6	511.4	508.3	505.0	505.0	497.7	496.6	488.0	479.6
40°	462.5	464.6	462.5	459.3	458.3	456.1	455.1	450.8	447.7	440.2	434.9
42.5°	416.8	414.6	414.6	413.6	409.3	409.3	407.3	405.1	399.8	397.7	391.3
45°	370.1	372.1	369.0	370.1	365.7	365.7	365.7	361.5	357.3	354.0	349.8
47.5°	329.6	330.7	330.7	327.5	326.4	326.4	324.3	322.2	319.0	314.7	311.5
50°	294.5	295.6	293.4	292.5	290.3	289.2	289.2	285.0	282.8	278.6	276.4
52.5°	262.6	262.6	261.6	261.6	258.4	258.4	256.3	253.0	250.9	248.8	243.5
55°	233.9	233.9	232.8	231.8	231.8	228.6	227.5	224.4	222.2	218.0	214.7
57.5°	206.3	207.4	206.3	205.2	204.1	203.0	201.0	197.7	195.7	192.4	190.3
60°	184.0	184.0	182.9	181.8	179.7	178.6	177.6	175.4	172.2	170.1	166.9
62.5°	162.7	161.6	160.5	159.5	157.4	157.4	155.2	153.2	149.9	147.9	145.7
65°	140.4	140.4	139.3	139.3	138.2	136.0	135.1	134.0	129.8	128.7	124.4
67.5°	120.1	121.2	119.1	119.1	117.0	117.0	115.9	112.7	111.7	109.5	107.4
70°	102.1	102.1	102.1	101.0	98.9	97.8	96.8	94.6	93.6	91.5	89.3
72.5°	84.0	84.0	82.9	82.9	81.8	80.9	79.8	77.6	77.6	75.4	73.4
75°	68.1	68.1	67.0	65.9	64.8	64.8	63.7	62.8	60.6	59.5	58.4
77.5°	52.1	52.1	52.1	51.1	50.0	50.0	50.0	47.8	45.7	45.7	44.7
80°	38.3	38.3	37.2	37.2	36.2	36.2	36.2	35.1	34.0	33.0	31.9
82.5°	25.5	25.5	25.5	25.5	24.5	24.5	24.5	23.4	22.3	22.3	22.3
85°	14.9	14.9	14.9	14.9	13.9	13.9	13.9	13.9	13.9	12.8	12.8
87.5°	6.4	5.3	6.4	5.3	6.4	5.3	6.4	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583864

CATALOG NUMBER: HCC8W15D010BZ-HM80520830-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5
2.5°	757.1	756.0	754.9	753.8	753.8	752.8	750.7	749.6	748.5	747.5	747.5
5°	761.3	760.2	758.1	756.0	754.9	752.8	750.7	748.5	746.4	743.2	742.2
7.5°	764.5	761.3	759.2	754.9	753.8	751.7	748.5	745.4	741.1	736.9	733.6
10°	764.5	760.2	757.1	751.7	749.6	747.5	743.2	737.9	732.6	728.3	723.0
12.5°	762.4	757.1	751.7	746.4	743.2	740.0	733.6	728.3	721.9	715.5	711.3
15°	754.9	748.5	742.2	735.8	732.6	728.3	721.9	714.6	708.2	701.8	694.3
17.5°	741.1	734.7	727.3	719.9	715.5	712.4	702.9	697.5	687.9	681.5	675.2
20°	723.0	715.5	706.0	698.5	693.2	690.1	682.6	673.1	665.6	656.0	649.6
22.5°	699.6	690.1	680.5	673.1	667.7	663.5	654.0	644.3	637.9	629.5	622.0
25°	672.0	662.4	652.9	642.3	636.8	632.6	624.2	615.6	607.1	597.6	591.2
27.5°	639.0	628.4	619.9	610.3	605.0	598.6	589.0	580.6	572.0	565.6	557.2
30°	602.9	591.2	582.6	573.1	567.8	562.5	552.9	544.4	536.9	529.5	525.3
32.5°	559.2	550.8	542.2	532.7	528.4	525.3	515.7	507.2	498.6	492.2	489.1
35°	517.8	508.3	500.8	492.2	486.9	483.8	475.3	467.9	463.6	456.1	451.9
37.5°	474.2	466.8	458.3	449.7	446.6	443.4	437.1	429.6	423.2	417.9	415.7
40°	428.5	422.1	414.6	409.3	406.2	403.0	397.7	392.3	388.1	382.8	380.7
42.5°	384.9	380.7	374.3	367.9	364.8	363.7	357.3	353.1	350.9	348.7	346.7
45°	345.6	339.2	335.0	330.7	327.5	325.4	322.2	319.0	316.9	314.7	312.6
47.5°	307.3	302.0	297.8	294.5	291.4	290.3	288.1	285.0	282.8	282.8	282.8
50°	272.2	268.0	263.7	261.6	260.5	258.4	256.3	255.2	254.1	254.1	254.1
52.5°	241.4	237.1	233.9	231.8	231.8	229.7	227.5	226.4	226.4	226.4	226.4
55°	212.7	209.4	207.4	205.2	203.0	202.1	202.1	202.1	201.0	201.0	202.1
57.5°	187.1	185.0	181.8	179.7	178.6	178.6	177.6	176.5	177.6	178.6	179.7
60°	163.8	161.6	160.5	157.4	157.4	157.4	156.3	156.3	156.3	157.4	158.5
62.5°	142.4	141.5	139.3	138.2	137.1	137.1	136.0	136.0	136.0	136.0	137.1
65°	123.4	121.2	119.1	119.1	119.1	118.0	118.0	115.9	117.0	117.0	115.9
67.5°	105.3	103.1	102.1	101.0	99.9	99.9	98.9	97.8	96.8	96.8	96.8
70°	88.2	86.2	86.2	84.0	84.0	82.9	81.8	81.8	80.9	79.8	78.7
72.5°	71.2	70.1	69.2	68.1	68.1	68.1	67.0	65.9	64.8	63.7	61.7
75°	56.4	56.4	54.2	53.1	53.1	52.1	51.1	50.0	48.9	47.8	46.8
77.5°	43.6	42.5	40.4	39.3	39.3	39.3	38.3	37.2	36.2	35.1	34.0
80°	31.9	30.8	29.8	28.7	28.7	28.7	27.6	27.6	26.6	26.6	26.6
82.5°	21.2	21.2	20.2	20.2	20.2	20.2	19.2	19.2	19.2	19.2	19.2
85°	12.8	12.8	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583864

CATALOG NUMBER: HCC8W15D010BZ-HM80520830-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5
2.5°	745.4	745.4	743.2	742.2	741.1	742.2	740.0	739.0	737.9	737.9	736.9
5°	739.0	737.9	733.6	732.6	731.6	730.5	728.3	726.3	724.1	723.0	721.9
7.5°	730.5	727.3	723.0	721.9	721.0	717.7	714.6	712.4	709.3	708.2	706.0
10°	718.8	714.6	711.3	708.2	706.0	702.9	699.6	696.5	692.2	691.2	687.9
12.5°	704.9	699.6	693.2	692.2	689.0	684.8	680.5	677.3	674.1	672.0	668.8
15°	687.9	682.6	676.2	673.1	669.9	666.7	661.3	657.1	654.0	650.7	647.6
17.5°	667.7	661.3	656.0	652.9	650.7	645.4	641.2	635.9	632.6	629.5	626.2
20°	643.2	637.9	630.6	627.3	626.2	622.0	616.7	614.6	610.3	607.1	605.0
22.5°	615.6	610.3	603.9	601.8	597.6	595.4	590.1	588.0	585.9	582.6	581.7
25°	584.8	579.5	574.2	573.1	570.0	567.8	564.5	561.4	561.4	558.3	558.3
27.5°	552.9	547.6	543.3	541.2	540.2	538.0	534.8	533.8	532.7	531.6	531.6
30°	518.9	512.5	510.3	509.4	508.3	506.1	505.0	503.0	504.1	505.0	504.1
32.5°	482.7	480.6	476.3	474.2	475.3	474.2	472.1	474.2	473.2	475.3	476.3
35°	447.7	445.5	443.4	443.4	441.3	441.3	441.3	442.4	444.4	445.5	447.7
37.5°	413.6	410.4	409.3	408.3	409.3	409.3	409.3	411.5	413.6	415.7	419.0
40°	377.4	375.4	375.4	375.4	375.4	378.5	377.4	379.6	381.7	384.9	388.1
42.5°	343.4	343.4	344.5	344.5	344.5	344.5	346.7	349.8	353.1	356.2	359.3
45°	311.5	311.5	311.5	313.7	313.7	314.7	319.0	321.1	323.2	326.4	329.6
47.5°	281.7	281.7	282.8	283.9	285.0	287.0	289.2	292.5	295.6	297.8	300.9
50°	254.1	255.2	257.3	259.4	259.4	260.5	263.7	265.8	268.0	271.1	272.2
52.5°	227.5	229.7	231.8	232.8	233.9	236.1	237.1	240.3	241.4	244.5	245.6
55°	203.0	204.1	207.4	208.3	208.3	210.5	212.7	214.7	218.0	218.0	220.2
57.5°	180.8	181.8	184.0	185.0	184.0	187.1	188.2	190.3	191.4	193.5	194.6
60°	158.5	160.5	161.6	161.6	162.7	163.8	165.9	165.9	168.0	170.1	170.1
62.5°	137.1	138.2	139.3	140.4	141.5	140.4	143.5	143.5	145.7	146.8	148.8
65°	117.0	118.0	118.0	119.1	119.1	120.1	120.1	121.2	122.3	124.4	125.4
67.5°	96.8	96.8	96.8	97.8	96.8	97.8	97.8	98.9	98.9	101.0	102.1
70°	78.7	77.6	76.5	76.5	76.5	76.5	75.4	76.5	76.5	77.6	77.6
72.5°	60.6	59.5	58.4	57.4	57.4	56.4	55.3	56.4	56.4	57.4	57.4
75°	45.7	43.6	43.6	43.6	42.5	42.5	42.5	43.6	43.6	43.6	44.7
77.5°	34.0	34.0	33.0	33.0	33.0	34.0	34.0	35.1	35.1	35.1	35.1
80°	25.5	26.6	26.6	26.6	26.6	27.6	27.6	27.6	27.6	28.7	28.7
82.5°	19.2	19.2	19.2	19.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2
85°	11.7	12.8	12.8	11.7	12.8	12.8	12.8	12.8	12.8	12.8	12.8
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583864

CATALOG NUMBER: HCC8W15D010BZ-HM80520830-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5
2.5°	735.8	735.8	735.8	735.8	734.7	734.7	734.7	733.6
5°	719.9	719.9	719.9	717.7	718.8	718.8	716.6	717.7
7.5°	703.8	702.9	701.8	701.8	700.7	699.6	698.5	699.6
10°	685.8	682.6	682.6	681.5	681.5	679.4	679.4	680.5
12.5°	665.6	663.5	663.5	662.4	661.3	660.3	659.3	659.3
15°	645.4	643.2	642.3	641.2	640.1	637.9	639.0	637.9
17.5°	625.2	622.0	622.0	620.9	619.9	617.8	617.8	616.7
20°	601.8	600.7	598.6	599.7	598.6	596.5	595.4	595.4
22.5°	578.4	578.4	577.3	577.3	576.4	575.3	574.2	574.2
25°	556.1	555.0	556.1	556.1	552.9	552.9	552.9	553.9
27.5°	530.6	531.6	530.6	530.6	530.6	530.6	531.6	530.6
30°	505.0	505.0	505.0	506.1	508.3	507.2	507.2	506.1
32.5°	477.4	478.5	478.5	479.6	480.6	482.7	482.7	483.8
35°	449.7	451.9	453.0	451.9	455.1	455.1	457.2	457.2
37.5°	421.0	422.1	424.3	425.4	427.4	428.5	429.6	429.6
40°	390.2	394.5	395.5	396.6	399.8	399.8	400.9	403.0
42.5°	361.5	365.7	366.8	367.9	370.1	373.2	372.1	374.3
45°	333.9	337.0	338.1	339.2	342.3	343.4	343.4	346.7
47.5°	304.1	306.2	307.3	309.4	311.5	313.7	315.8	314.7
50°	274.4	277.5	279.7	280.8	283.9	285.0	286.1	287.0
52.5°	247.7	249.9	250.9	252.0	255.2	256.3	257.3	259.4
55°	222.2	223.3	225.5	224.4	227.5	228.6	229.7	231.8
57.5°	196.7	197.7	198.8	198.8	201.0	203.0	204.1	205.2
60°	172.2	174.4	175.4	175.4	175.4	177.6	177.6	177.6
62.5°	149.9	149.9	151.0	151.0	153.2	153.2	153.2	153.2
65°	126.5	127.6	128.7	128.7	130.7	129.8	131.8	130.7
67.5°	102.1	102.1	104.2	104.2	103.1	104.2	104.2	104.2
70°	77.6	77.6	78.7	78.7	78.7	78.7	78.7	78.7
72.5°	57.4	57.4	57.4	58.4	57.4	57.4	58.4	57.4
75°	44.7	44.7	44.7	44.7	44.7	44.7	44.7	44.7
77.5°	35.1	35.1	36.2	36.2	36.2	36.2	36.2	36.2
80°	28.7	28.7	28.7	28.7	29.8	28.7	28.7	28.7
82.5°	21.2	20.2	21.2	20.2	21.2	21.2	21.2	21.2
85°	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)