

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583855

Luminaire Tested: **HCC8W15D010SL-HM80520830-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583855  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W15D010SL-HM80520830-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1514.0 lumens  
Efficiency: N/A  
Efficacy: 108.1 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583855  
CATALOG NUMBER: HCC8W15D010SL-HM80520830-81RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P583855

CATALOG NUMBER: HCC8W15D010SL-HM80520830-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	24564	24564	24564
5°	24890	24460	24231
10°	25144	24210	23847
15°	25396	23700	23225
20°	25268	22823	22301
25°	24681	21459	21166
30°	23440	19922	19844
35°	21337	18175	18336
40°	18710	16271	16870
45°	16144	14474	15490
50°	14133	12708	14032
55°	12521	10924	12349
60°	11280	9183	10231
65°	10164	7377	7836
70°	8917	5364	4310
75°	7613	2788	1132
80°	5860	746	195
85°	3750	0	0



TEST NUMBER: P583855  
 CATALOG NUMBER: HCC8W15D010SL-HM80520830-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.2	5.0
10°-20°	211.3	14.0
20°-30°	299.9	19.8
30°-40°	315.7	20.9
40°-50°	268.6	17.7
50°-60°	194.1	12.8
60°-70°	110.4	7.3
70°-80°	34.8	2.3
80°-90°	4.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	586.3	38.7
0°-40°	902.0	59.6
0°-60°	1364.6	90.1
0°-90°	1514.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1514.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	797	797	797	797	797	
5°	804	800	790	785	783	77
15°	796	775	742	728	728	224
25°	725	689	631	620	622	332
35°	567	534	483	480	487	353
45°	370	356	332	340	355	288
55°	233	216	203	215	230	210
65°	139	120	101	100	107	138
75°	64	49	23	11	10	69
85°	11	6	0	0	0	14
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583855

CATALOG NUMBER: HCC8W15D010SL-HM80520830-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6
2.5°	800.8	801.9	799.8	799.8	801.9	799.8	800.8	800.8	799.8	799.8	798.8
5°	804.1	803.0	803.0	803.0	804.1	801.9	800.8	801.9	799.8	799.8	799.8
7.5°	805.2	805.2	804.1	803.0	803.0	803.0	801.9	800.8	799.8	797.7	796.6
10°	803.0	803.0	804.1	801.9	801.9	799.8	799.8	797.7	797.7	795.5	792.4
12.5°	800.8	799.8	799.8	797.7	797.7	795.5	795.5	792.4	791.3	788.1	784.9
15°	795.5	794.5	792.4	791.3	790.2	789.2	787.0	786.0	782.8	778.6	775.3
17.5°	784.9	783.9	782.8	780.7	778.6	777.5	776.4	773.2	768.9	765.8	760.5
20°	770.0	768.9	768.9	765.8	764.7	761.6	760.5	756.3	753.0	746.6	742.4
22.5°	749.9	750.8	748.8	746.6	744.4	741.3	739.1	734.9	729.6	723.2	717.9
25°	725.4	726.4	724.3	722.2	719.0	716.9	714.7	708.3	703.0	695.5	689.1
27.5°	694.6	694.6	694.6	692.4	687.1	686.0	683.8	677.5	670.1	663.7	657.3
30°	658.3	657.3	657.3	654.1	652.0	647.7	644.6	639.3	633.8	626.5	619.0
32.5°	614.8	615.8	612.6	610.5	607.3	607.3	603.1	598.8	592.4	584.9	577.6
35°	566.8	567.9	565.9	564.8	559.5	558.4	557.3	552.0	547.8	542.4	533.9
37.5°	517.9	516.9	515.9	515.9	512.6	510.6	508.4	505.3	498.9	494.5	490.3
40°	464.8	464.8	464.8	463.7	462.6	460.6	459.5	457.3	453.1	448.9	445.6
42.5°	416.9	416.9	415.8	414.8	412.7	413.7	411.6	409.5	405.2	402.0	399.9
45°	370.2	370.2	370.2	371.1	369.1	365.8	365.8	363.8	361.6	359.5	356.3
47.5°	328.6	331.9	329.7	328.6	329.7	325.5	325.5	323.3	321.3	319.1	314.9
50°	294.6	294.6	294.6	292.5	291.4	291.4	288.2	286.1	285.0	282.9	278.6
52.5°	263.8	261.6	261.6	260.5	259.6	257.4	257.4	255.2	251.0	248.8	245.7
55°	232.9	232.9	231.8	230.8	229.7	228.7	227.6	224.4	222.3	219.1	215.9
57.5°	205.2	207.4	206.3	204.2	202.1	202.1	199.9	197.9	194.6	191.5	188.2
60°	182.9	181.8	181.8	180.8	178.7	177.6	176.5	173.4	170.1	167.0	163.8
62.5°	159.5	159.5	159.5	157.4	155.3	154.2	153.2	151.0	146.8	143.6	141.5
65°	139.3	138.2	137.2	136.2	135.1	132.9	131.8	129.8	126.5	123.4	120.1
67.5°	119.2	118.1	118.1	117.0	113.8	112.8	112.8	109.5	106.4	103.1	100.0
70°	98.9	98.9	98.9	96.8	95.7	94.7	93.6	91.5	88.3	85.1	81.9
72.5°	81.9	80.9	80.9	79.8	76.5	75.6	74.5	72.3	69.2	67.0	64.8
75°	63.9	63.9	62.8	61.7	60.6	59.5	58.4	56.4	53.1	50.0	48.9
77.5°	48.9	47.8	47.8	46.8	44.7	43.6	43.6	41.5	38.3	36.2	34.0
80°	33.0	34.0	33.0	31.9	30.8	29.8	28.7	27.6	25.5	23.4	21.3
82.5°	20.2	21.3	20.2	20.2	19.2	18.1	18.1	15.9	14.9	13.9	12.8
85°	10.6	10.6	10.6	10.6	9.5	9.5	9.5	8.6	7.5	6.4	6.4
87.5°	3.1	4.2	3.1	3.1	3.1	3.1	3.1	3.1	2.2	2.2	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583855

CATALOG NUMBER: HCC8W15D010SL-HM80520830-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6
2.5°	799.8	798.8	797.7	797.7	797.7	797.7	797.7	796.6	795.5	795.5	795.5
5°	797.7	797.7	797.7	796.6	795.5	795.5	793.4	792.4	791.3	790.2	789.2
7.5°	795.5	793.4	792.4	791.3	790.2	790.2	788.1	786.0	786.0	783.9	781.7
10°	789.2	788.1	786.0	783.9	782.8	781.7	779.6	776.4	775.3	773.2	771.1
12.5°	781.7	779.6	777.5	773.2	772.2	771.1	766.9	763.6	761.6	760.5	755.2
15°	772.2	767.9	764.7	759.4	758.3	756.3	753.0	749.9	745.5	742.4	740.2
17.5°	755.2	750.8	745.5	740.2	738.1	738.1	732.8	728.5	723.2	721.1	716.9
20°	734.9	729.6	725.4	719.0	715.8	712.6	709.4	703.0	698.8	695.5	690.2
22.5°	711.6	704.1	698.8	692.4	687.1	683.8	678.5	673.2	667.9	664.7	660.5
25°	681.8	675.4	666.8	660.5	657.3	653.0	646.6	641.3	636.0	630.7	628.5
27.5°	648.8	640.2	632.9	625.4	622.1	619.0	611.5	605.2	600.9	595.6	593.5
30°	612.6	604.1	595.6	589.2	586.0	580.7	576.5	569.0	563.7	559.5	554.2
32.5°	571.2	564.8	557.3	547.8	545.6	541.4	535.0	531.8	525.4	522.2	517.9
35°	526.5	522.2	514.8	507.3	504.2	502.0	496.7	490.3	486.1	482.8	480.7
37.5°	483.9	478.6	471.2	465.9	463.7	460.6	454.2	450.9	446.7	444.5	440.3
40°	438.1	432.8	427.5	424.4	421.1	419.1	414.8	411.6	407.3	404.2	403.1
42.5°	393.6	390.3	386.1	381.9	380.8	377.5	375.5	372.2	369.1	368.0	364.8
45°	353.1	349.9	345.7	341.4	340.3	338.2	337.2	333.9	331.9	331.9	331.9
47.5°	312.7	309.4	305.2	303.2	304.1	299.9	299.9	298.8	296.8	296.8	297.8
50°	276.5	272.3	271.2	269.1	266.9	264.9	265.9	262.7	262.7	264.9	263.8
52.5°	242.4	238.2	237.1	235.1	234.0	234.0	232.9	232.9	231.8	232.9	232.9
55°	211.6	208.5	206.3	204.2	203.2	203.2	203.2	202.1	201.0	203.2	204.2
57.5°	184.0	182.9	180.8	177.6	176.5	175.4	174.5	174.5	174.5	174.5	175.4
60°	159.5	157.4	155.3	152.1	152.1	151.0	150.0	148.9	148.9	148.9	148.9
62.5°	138.2	135.1	131.8	129.8	128.7	127.6	126.5	124.5	124.5	124.5	124.5
65°	117.0	113.8	111.7	109.5	107.4	107.4	105.3	104.2	102.1	101.1	98.9
67.5°	96.8	94.7	92.5	89.3	88.3	87.2	85.1	84.0	80.9	79.8	78.7
70°	78.7	75.6	73.4	71.2	70.3	68.1	65.9	63.9	61.7	59.5	57.5
72.5°	61.7	58.4	56.4	54.2	52.1	52.1	48.9	46.8	43.6	41.5	38.3
75°	45.8	42.5	40.4	37.2	36.2	35.1	31.9	29.8	26.6	23.4	21.3
77.5°	30.8	28.7	26.6	23.4	21.3	21.3	18.1	15.9	13.9	10.6	9.5
80°	19.2	17.0	14.9	12.8	12.8	10.6	9.5	7.5	5.3	4.2	3.1
82.5°	10.6	9.5	8.6	6.4	6.4	5.3	4.2	3.1	2.2	1.1	1.1
85°	5.3	4.2	3.1	3.1	2.2	2.2	2.2	1.1	1.1	0.0	0.0
87.5°	2.2	1.1	1.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583855

CATALOG NUMBER: HCC8W15D010SL-HM80520830-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6
2.5°	794.5	794.5	793.4	793.4	793.4	792.4	793.4	792.4	792.4	792.4	793.4
5°	790.2	788.1	788.1	787.0	787.0	786.0	787.0	786.0	784.9	783.9	784.9
7.5°	781.7	779.6	778.6	777.5	777.5	777.5	776.4	775.3	776.4	773.2	775.3
10°	770.0	768.9	766.9	765.8	764.7	765.8	764.7	762.5	762.5	762.5	761.6
12.5°	755.2	753.0	751.9	750.8	748.8	748.8	749.9	747.7	747.7	745.5	745.5
15°	737.1	734.9	732.8	732.8	730.7	730.7	729.6	729.6	728.5	727.5	727.5
17.5°	714.7	711.6	709.4	710.5	709.4	708.3	708.3	706.3	705.2	706.3	706.3
20°	688.2	686.0	683.8	684.9	682.8	681.8	682.8	679.6	680.7	680.7	680.7
22.5°	658.3	657.3	654.1	654.1	652.0	650.9	652.0	652.0	653.0	652.0	652.0
25°	625.4	623.2	621.2	621.2	620.1	619.0	620.1	621.2	620.1	621.2	621.2
27.5°	590.3	587.1	587.1	584.9	584.9	586.0	584.9	586.0	587.1	587.1	589.2
30°	552.0	550.9	549.8	548.8	548.8	549.8	549.8	549.8	550.9	553.1	553.1
32.5°	515.9	513.7	511.5	511.5	513.7	512.6	513.7	513.7	515.9	515.9	517.9
35°	476.5	476.5	474.4	475.4	475.4	475.4	475.4	477.5	479.7	480.7	482.8
37.5°	440.3	437.2	438.1	438.1	439.2	438.1	441.4	441.4	443.6	443.6	445.6
40°	401.0	401.0	402.0	401.0	402.0	402.0	404.2	406.3	407.3	409.5	410.5
42.5°	363.8	365.8	363.8	364.8	365.8	366.9	368.0	369.1	373.3	375.5	378.6
45°	329.7	330.8	331.9	332.9	331.9	333.9	335.0	337.2	340.3	341.4	342.5
47.5°	296.8	297.8	298.8	299.9	299.9	302.1	303.2	305.2	307.4	308.5	309.4
50°	264.9	266.9	268.0	268.0	269.1	271.2	273.3	273.3	275.5	278.6	279.7
52.5°	236.1	236.1	238.2	239.3	240.4	240.4	243.5	244.6	245.7	247.9	249.9
55°	204.2	207.4	208.5	208.5	210.6	212.7	213.8	214.9	214.9	219.1	219.1
57.5°	176.5	177.6	179.8	179.8	179.8	182.9	182.9	185.1	186.2	187.1	189.3
60°	148.9	151.0	151.0	152.1	151.0	153.2	154.2	156.3	157.4	158.5	159.5
62.5°	123.4	123.4	124.5	124.5	124.5	124.5	126.5	126.5	128.7	129.8	130.9
65°	98.9	98.9	98.9	98.9	98.9	98.9	98.9	98.9	100.0	100.0	102.1
67.5°	76.5	75.6	73.4	74.5	73.4	73.4	72.3	72.3	73.4	73.4	75.6
70°	55.3	54.2	52.1	52.1	51.1	50.0	48.9	47.8	46.8	46.8	46.8
72.5°	36.2	34.0	30.8	29.8	29.8	27.6	25.5	24.5	24.5	24.5	24.5
75°	18.1	15.9	13.9	12.8	12.8	10.6	11.7	10.6	10.6	10.6	10.6
77.5°	7.5	5.3	4.2	4.2	4.2	3.1	3.1	3.1	3.1	3.1	3.1
80°	2.2	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
82.5°	1.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583855

CATALOG NUMBER: HCC8W15D010SL-HM80520830-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	796.6	796.6	796.6	796.6	796.6	796.6	796.6	796.6
2.5°	792.4	792.4	790.2	791.3	791.3	791.3	791.3	791.3
5°	782.8	783.9	782.8	783.9	783.9	782.8	782.8	782.8
7.5°	773.2	774.3	773.2	774.3	774.3	774.3	773.2	773.2
10°	761.6	761.6	761.6	761.6	761.6	760.5	761.6	761.6
12.5°	745.5	745.5	745.5	746.6	746.6	745.5	745.5	744.4
15°	728.5	726.4	727.5	728.5	727.5	727.5	727.5	727.5
17.5°	705.2	706.3	705.2	705.2	705.2	705.2	706.3	705.2
20°	680.7	680.7	681.8	680.7	680.7	680.7	680.7	679.6
22.5°	653.0	652.0	652.0	653.0	653.0	652.0	653.0	653.0
25°	622.1	623.2	622.1	622.1	623.2	623.2	623.2	622.1
27.5°	589.2	590.3	591.3	590.3	590.3	590.3	591.3	592.4
30°	555.1	557.3	555.1	555.1	557.3	556.2	557.3	557.3
32.5°	519.0	522.2	520.1	522.2	522.2	523.3	522.2	523.3
35°	482.8	486.1	486.1	486.1	487.1	488.1	488.1	487.1
37.5°	448.9	449.9	449.9	452.0	453.1	454.2	454.2	453.1
40°	413.7	415.8	416.9	416.9	416.9	419.1	421.1	419.1
42.5°	379.7	380.8	381.9	381.9	383.9	385.0	386.1	386.1
45°	346.7	348.8	349.9	351.0	352.1	354.1	353.1	355.2
47.5°	312.7	315.8	316.9	318.0	320.2	321.3	322.2	323.3
50°	281.8	284.0	284.0	286.1	289.3	289.3	291.4	292.5
52.5°	251.0	252.1	253.2	254.1	256.3	258.5	258.5	260.5
55°	221.2	222.3	222.3	223.4	224.4	228.7	229.7	229.7
57.5°	190.4	190.4	192.6	193.5	194.6	196.8	196.8	196.8
60°	160.6	161.7	161.7	162.7	163.8	165.9	167.0	165.9
62.5°	130.9	131.8	131.8	132.9	135.1	136.2	135.1	135.1
65°	103.1	104.2	104.2	105.3	107.4	107.4	106.4	107.4
67.5°	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6
70°	47.8	46.8	45.8	46.8	46.8	46.8	45.8	47.8
72.5°	23.4	24.5	24.5	24.5	24.5	24.5	24.5	23.4
75°	10.6	10.6	9.5	9.5	9.5	10.6	10.6	9.5
77.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
80°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)