

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593566

Luminaire Tested: **HCC8W15D010BZ-HM80520850-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W15D010BZ-HM80520850-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1682.7 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593566
CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593566

CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	25798	25798	25798
5°	26744	25714	24831
10°	27498	25491	23816
15°	28112	25038	22765
20°	28159	24060	21839
25°	27617	22725	21064
30°	26196	21076	20143
35°	23802	19191	19236
40°	20807	17225	18130
45°	18037	15337	16894
50°	15793	13624	15394
55°	14059	12075	13930
60°	12680	10848	12242
65°	11448	9537	10667
70°	10287	8042	7934
75°	9055	6374	5945
80°	7600	5292	5700
85°	5873	4599	5024



TEST NUMBER: P593566
 CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.9	4.7
10°-20°	222.3	13.2
20°-30°	317.7	18.9
30°-40°	337.6	20.1
40°-50°	290.6	17.3
50°-60°	217.3	12.9
60°-70°	138.6	8.2
70°-80°	63.1	3.7
80°-90°	16.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	618.9	36.8
0°-40°	956.5	56.8
0°-60°	1464.5	87.0
0°-90°	1682.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1682.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	837	837	837	837	837	
5°	864	852	831	809	802	83
15°	881	851	784	731	713	248
25°	812	761	668	627	619	372
35°	632	588	510	497	511	394
45°	414	391	352	361	387	321
55°	262	240	225	244	259	235
65°	157	139	131	137	146	156
75°	76	65	54	49	50	81
85°	17	14	13	14	14	20
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593566

CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	852.1	849.8	851.0	849.8	851.0	851.0	848.6	848.6	848.6	848.6	844.9
5°	864.0	862.8	862.8	861.6	860.4	861.6	860.4	859.3	856.9	855.7	852.1
7.5°	871.1	871.1	871.1	871.1	869.9	868.8	867.6	865.2	862.8	860.4	858.1
10°	878.2	879.4	878.2	877.1	875.9	873.5	872.3	869.9	866.4	862.8	860.4
12.5°	881.8	881.8	880.6	880.6	878.2	877.1	873.5	869.9	866.4	862.8	856.9
15°	880.6	880.6	879.4	878.2	874.7	873.5	871.1	867.6	861.6	856.9	851.0
17.5°	873.5	872.3	869.9	869.9	865.2	864.0	861.6	856.9	851.0	843.7	836.6
20°	858.1	858.1	856.9	855.7	851.0	847.4	844.9	839.0	834.3	825.9	818.8
22.5°	836.6	839.0	836.6	834.3	828.3	827.1	823.6	816.5	809.3	799.8	791.4
25°	811.7	810.5	809.3	807.0	802.2	799.8	795.1	787.9	780.8	770.1	760.6
27.5°	779.6	774.8	774.8	770.1	766.5	763.0	760.6	753.5	744.0	735.7	723.7
30°	735.7	736.9	730.8	729.7	723.7	721.4	716.6	709.5	701.2	691.7	682.2
32.5°	688.1	684.6	684.6	679.7	675.0	671.4	670.2	661.9	654.8	645.3	635.8
35°	632.3	632.3	628.6	627.4	622.7	620.3	616.8	612.0	603.7	595.4	588.3
37.5°	577.6	575.1	574.1	571.7	568.0	564.5	564.5	556.2	555.0	545.5	536.0
40°	516.9	519.4	516.9	513.5	512.2	509.8	508.6	503.9	500.3	492.0	486.1
42.5°	465.9	463.4	463.4	462.4	457.5	457.5	455.1	452.8	446.8	444.5	437.3
45°	413.6	416.0	412.4	413.6	408.9	408.9	408.9	404.0	399.3	395.7	391.0
47.5°	368.4	369.6	369.6	366.1	364.9	364.9	362.5	360.1	356.6	351.7	348.2
50°	329.2	330.4	328.0	326.8	324.4	323.3	323.3	318.5	316.1	311.4	309.0
52.5°	293.5	293.5	292.3	292.3	288.8	288.8	286.4	282.8	280.5	278.1	272.2
55°	261.5	261.5	260.3	259.1	259.1	255.5	254.4	250.8	248.4	243.7	240.0
57.5°	230.5	231.7	230.5	229.3	228.2	227.0	224.6	221.0	218.7	215.1	212.7
60°	205.6	205.6	204.4	203.2	200.9	199.7	198.5	196.1	192.6	190.1	186.5
62.5°	181.8	180.6	179.4	178.2	175.9	175.9	173.5	171.1	167.6	165.2	162.8
65°	156.9	156.9	155.7	155.7	154.5	152.1	151.0	149.8	145.0	143.8	139.1
67.5°	134.2	135.4	133.2	133.2	130.7	130.7	129.5	125.9	124.8	122.4	120.0
70°	114.1	114.1	114.1	112.9	110.5	109.3	108.1	105.8	104.6	102.2	99.8
72.5°	93.9	93.9	92.7	92.7	91.5	90.4	89.2	86.8	86.8	84.4	82.1
75°	76.0	76.0	74.8	73.6	72.5	72.5	71.3	70.1	67.7	66.5	65.3
77.5°	58.2	58.2	58.2	57.0	55.9	55.9	55.9	53.5	51.1	51.1	49.9
80°	42.8	42.8	41.6	41.6	40.4	40.4	40.4	39.2	38.1	36.9	35.7
82.5°	28.6	28.6	28.6	28.6	27.4	27.4	27.4	26.1	24.9	24.9	24.9
85°	16.6	16.6	16.6	16.6	15.4	15.4	15.4	15.4	15.4	14.2	14.2
87.5°	7.1	5.9	7.1	5.9	7.1	5.9	7.1	5.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593566

CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	846.2	844.9	843.7	842.7	842.7	841.5	839.0	837.8	836.6	835.4	835.4
5°	851.0	849.8	847.4	844.9	843.7	841.5	839.0	836.6	834.3	830.7	829.5
7.5°	854.5	851.0	848.6	843.7	842.7	840.2	836.6	833.1	828.3	823.6	820.0
10°	854.5	849.8	846.2	840.2	837.8	835.4	830.7	824.8	818.8	814.1	808.2
12.5°	852.1	846.2	840.2	834.3	830.7	827.1	820.0	814.1	807.0	799.8	795.1
15°	843.7	836.6	829.5	822.4	818.8	814.1	807.0	798.7	791.4	784.3	776.0
17.5°	828.3	821.2	812.9	804.6	799.8	796.3	785.5	779.6	768.9	761.8	754.7
20°	808.2	799.8	789.2	780.8	774.8	771.3	763.0	752.3	744.0	733.2	726.1
22.5°	782.0	771.3	760.6	752.3	746.4	741.6	730.8	720.2	713.1	703.6	695.3
25°	751.1	740.4	729.7	717.8	711.9	707.1	697.6	688.1	678.7	667.9	660.8
27.5°	714.2	702.4	692.9	682.2	676.2	669.1	658.4	648.9	639.4	632.3	622.7
30°	673.8	660.8	651.3	640.6	634.7	628.6	618.0	608.5	600.2	591.9	587.1
32.5°	625.2	615.6	606.1	595.4	590.7	587.1	576.4	566.8	557.4	550.2	546.7
35°	578.8	568.0	559.7	550.2	544.3	540.7	531.3	523.0	518.2	509.8	505.1
37.5°	530.1	521.8	512.2	502.7	499.1	495.6	488.5	480.1	473.0	467.1	464.6
40°	479.0	471.8	463.4	457.5	453.9	450.4	444.5	438.5	433.8	427.9	425.5
42.5°	430.2	425.5	418.4	411.1	407.7	406.4	399.3	394.5	392.2	389.8	387.4
45°	386.2	379.1	374.4	369.6	366.1	363.7	360.1	356.6	354.1	351.7	349.5
47.5°	343.4	337.5	332.8	329.2	325.6	324.4	322.1	318.5	316.1	316.1	316.1
50°	304.3	299.4	294.7	292.3	291.1	288.8	286.4	285.2	284.0	284.0	284.0
52.5°	269.8	265.0	261.5	259.1	259.1	256.7	254.4	253.2	253.2	253.2	253.2
55°	237.7	234.1	231.7	229.3	227.0	225.8	225.8	225.8	224.6	224.6	225.8
57.5°	209.2	206.8	203.2	200.9	199.7	199.7	198.5	197.3	198.5	199.7	200.9
60°	183.0	180.6	179.4	175.9	175.9	175.9	174.7	174.7	174.7	175.9	177.1
62.5°	159.3	158.1	155.7	154.5	153.3	153.3	152.1	152.1	152.1	152.1	153.3
65°	137.9	135.4	133.2	133.2	133.2	131.9	131.9	129.5	130.7	130.7	129.5
67.5°	117.6	115.3	114.1	112.9	111.7	111.7	110.5	109.3	108.1	108.1	108.1
70°	98.7	96.3	96.3	93.9	93.9	92.7	91.5	91.5	90.4	89.2	88.0
72.5°	79.7	78.4	77.2	76.0	76.0	76.0	74.8	73.6	72.5	71.3	68.9
75°	63.0	63.0	60.6	59.4	59.4	58.2	57.0	55.9	54.7	53.5	52.3
77.5°	48.7	47.6	45.2	44.0	44.0	44.0	42.8	41.6	40.4	39.2	38.1
80°	35.7	34.5	33.3	32.1	32.1	32.1	30.8	30.8	29.8	29.8	29.8
82.5°	23.7	23.7	22.5	22.5	22.5	22.5	21.4	21.4	21.4	21.4	21.4
85°	14.2	14.2	13.0	13.0	13.0	13.0	13.0	13.0	13.0	13.0	13.0
87.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593566

CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	833.1	833.1	830.7	829.5	828.3	829.5	827.1	825.9	824.8	824.8	823.6
5°	825.9	824.8	820.0	818.8	817.6	816.5	814.1	811.7	809.3	808.2	807.0
7.5°	816.5	812.9	808.2	807.0	805.8	802.2	798.7	796.3	792.6	791.4	789.2
10°	803.4	798.7	795.1	791.4	789.2	785.5	782.0	778.4	773.7	772.5	768.9
12.5°	787.9	782.0	774.8	773.7	770.1	765.3	760.6	757.0	753.5	751.1	747.6
15°	768.9	763.0	755.9	752.3	748.7	745.2	739.1	734.4	730.8	727.3	723.7
17.5°	746.4	739.1	733.2	729.7	727.3	721.4	716.6	710.7	707.1	703.6	700.0
20°	719.0	713.1	704.7	701.2	700.0	695.3	689.3	687.0	682.2	678.7	676.2
22.5°	688.1	682.2	675.0	672.6	667.9	665.5	659.6	657.2	654.8	651.3	650.1
25°	653.6	647.7	641.8	640.6	637.0	634.7	631.1	627.4	627.4	623.9	623.9
27.5°	618.0	612.0	607.3	604.9	603.7	601.3	597.8	596.6	595.4	594.2	594.2
30°	580.0	572.9	570.4	569.2	568.0	565.7	564.5	562.1	563.3	564.5	563.3
32.5°	539.6	537.2	532.4	530.1	531.3	530.1	527.7	530.1	528.9	531.3	532.4
35°	500.3	497.9	495.6	495.6	493.2	493.2	493.2	494.4	496.8	497.9	500.3
37.5°	462.4	458.7	457.5	456.3	457.5	457.5	457.5	459.9	462.4	464.6	468.3
40°	421.9	419.5	419.5	419.5	419.5	423.1	421.9	424.3	426.7	430.2	433.8
42.5°	383.9	383.9	385.0	385.0	385.0	385.0	387.4	391.0	394.5	398.1	401.7
45°	348.2	348.2	348.2	350.5	350.5	351.7	356.6	358.8	361.3	364.9	368.4
47.5°	315.0	315.0	316.1	317.3	318.5	320.9	323.3	326.8	330.4	332.8	336.3
50°	284.0	285.2	287.6	289.9	289.9	291.1	294.7	297.2	299.4	303.1	304.3
52.5°	254.4	256.7	259.1	260.3	261.5	263.8	265.0	268.6	269.8	273.3	274.5
55°	227.0	228.2	231.7	232.9	232.9	235.3	237.7	240.0	243.7	243.7	246.1
57.5°	202.1	203.2	205.6	206.8	205.6	209.2	210.4	212.7	213.9	216.3	217.5
60°	177.1	179.4	180.6	180.6	181.8	183.0	185.4	185.4	187.7	190.1	190.1
62.5°	153.3	154.5	155.7	156.9	158.1	156.9	160.4	160.4	162.8	164.0	166.4
65°	130.7	131.9	131.9	133.2	133.2	134.2	134.2	135.4	136.6	139.1	140.3
67.5°	108.1	108.1	108.1	109.3	108.1	109.3	109.3	110.5	110.5	112.9	114.1
70°	88.0	86.8	85.6	85.6	85.6	85.6	84.4	85.6	85.6	86.8	86.8
72.5°	67.7	66.5	65.3	64.2	64.2	63.0	61.8	63.0	63.0	64.2	64.2
75°	51.1	48.7	48.7	48.7	47.6	47.6	47.6	48.7	48.7	48.7	49.9
77.5°	38.1	38.1	36.9	36.9	36.9	38.1	38.1	39.2	39.2	39.2	39.2
80°	28.6	29.8	29.8	29.8	29.8	30.8	30.8	30.8	30.8	32.1	32.1
82.5°	21.4	21.4	21.4	21.4	22.5	22.5	22.5	22.5	22.5	22.5	22.5
85°	13.0	14.2	14.2	13.0	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593566

CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	822.4	822.4	822.4	822.4	821.2	821.2	821.2	820.0
5°	804.6	804.6	804.6	802.2	803.4	803.4	801.0	802.2
7.5°	786.7	785.5	784.3	784.3	783.1	782.0	780.8	782.0
10°	766.5	763.0	763.0	761.8	761.8	759.4	759.4	760.6
12.5°	744.0	741.6	741.6	740.4	739.1	738.1	736.9	736.9
15°	721.4	719.0	717.8	716.6	715.4	713.1	714.2	713.1
17.5°	698.8	695.3	695.3	694.1	692.9	690.5	690.5	689.3
20°	672.6	671.4	669.1	670.2	669.1	666.7	665.5	665.5
22.5°	646.5	646.5	645.3	645.3	644.1	643.0	641.8	641.8
25°	621.5	620.3	621.5	621.5	618.0	618.0	618.0	619.1
27.5°	593.0	594.2	593.0	593.0	593.0	593.0	594.2	593.0
30°	564.5	564.5	564.5	565.7	568.0	566.8	566.8	565.7
32.5°	533.6	534.8	534.8	536.0	537.2	539.6	539.6	540.7
35°	502.7	505.1	506.2	505.1	508.6	508.6	511.0	511.0
37.5°	470.7	471.8	474.2	475.4	477.8	479.0	480.1	480.1
40°	436.2	440.9	442.1	443.3	446.8	446.8	448.0	450.4
42.5°	404.0	408.9	410.1	411.1	413.6	417.2	416.0	418.4
45°	373.2	376.7	377.9	379.1	382.7	383.9	383.9	387.4
47.5°	339.9	342.2	343.4	345.8	348.2	350.5	352.9	351.7
50°	306.7	310.2	312.6	313.8	317.3	318.5	319.7	320.9
52.5°	276.9	279.3	280.5	281.6	285.2	286.4	287.6	289.9
55°	248.4	249.6	252.0	250.8	254.4	255.5	256.7	259.1
57.5°	219.9	221.0	222.2	222.2	224.6	227.0	228.2	229.3
60°	192.6	194.8	196.1	196.1	196.1	198.5	198.5	198.5
62.5°	167.6	167.6	168.7	168.7	171.1	171.1	171.1	171.1
65°	141.5	142.7	143.8	143.8	146.2	145.0	147.4	146.2
67.5°	114.1	114.1	116.5	116.5	115.3	116.5	116.5	116.5
70°	86.8	86.8	88.0	88.0	88.0	88.0	88.0	88.0
72.5°	64.2	64.2	64.2	65.3	64.2	64.2	65.3	64.2
75°	49.9	49.9	49.9	49.9	49.9	49.9	49.9	49.9
77.5°	39.2	39.2	40.4	40.4	40.4	40.4	40.4	40.4
80°	32.1	32.1	32.1	32.1	33.3	32.1	32.1	32.1
82.5°	23.7	22.5	23.7	22.5	23.7	23.7	23.7	23.7
85°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)