

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593564

Luminaire Tested: **HCC8W15D010MB-HM80520850-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593564  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W15D010MB-HM80520850-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1480.7 lumens  
Efficiency: N/A  
Efficacy: 105.8 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593564  
CATALOG NUMBER: HCC8W15D010MB-HM80520850-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593564

CATALOG NUMBER: HCC8W15D010MB-HM80520850-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	24512	24512	24512
5°	25525	24457	23429
10°	26377	24148	22288
15°	27046	23592	21127
20°	27099	22613	20080
25°	26641	21183	19040
30°	25217	19548	18149
35°	22989	17576	17042
40°	19994	15498	15735
45°	17151	13423	14404
50°	14646	11571	12938
55°	12838	9962	11247
60°	11428	8505	9454
65°	10149	6939	7545
70°	8998	5139	4283
75°	7506	2681	1275
80°	5913	835	213
85°	4210	425	0



TEST NUMBER: P593564  
 CATALOG NUMBER: HCC8W15D010MB-HM80520850-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.9	5.1
10°-20°	209.9	14.2
20°-30°	297.1	20.1
30°-40°	310.9	21.0
40°-50°	259.3	17.5
50°-60°	183.9	12.4
60°-70°	105.9	7.2
70°-80°	34.1	2.3
80°-90°	4.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.0	39.3
0°-40°	892.9	60.3
0°-60°	1336.0	90.2
0°-90°	1480.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1480.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	795	795	795	795	795	
5°	825	814	790	766	757	79
15°	847	813	739	681	662	238
25°	783	725	623	573	560	357
35°	611	557	467	442	453	379
45°	393	361	308	311	330	305
55°	239	214	185	195	209	216
65°	139	116	95	95	103	139
75°	63	46	22	11	11	68
85°	12	6	1	0	0	15
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593564

CATALOG NUMBER: HCC8W15D010MB-HM80520850-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9
2.5°	811.6	810.4	809.2	810.4	809.2	810.4	809.2	809.2	808.0	806.9	806.9
5°	824.6	823.5	823.5	823.5	822.3	821.1	821.1	819.9	817.5	816.3	814.0
7.5°	832.9	834.1	834.1	834.1	831.8	831.8	829.4	827.0	824.6	822.3	818.7
10°	842.4	842.4	841.2	840.1	837.7	836.5	835.3	832.9	829.4	824.6	821.1
12.5°	846.0	846.0	844.8	842.4	841.2	840.1	838.9	835.3	830.6	824.6	819.9
15°	847.2	844.8	843.6	842.4	840.1	836.5	836.5	831.8	825.8	818.7	812.8
17.5°	837.7	838.9	836.5	834.1	830.6	828.2	824.6	821.1	814.0	805.7	799.6
20°	825.8	824.6	823.5	819.9	815.2	814.0	810.4	804.5	798.4	789.0	780.7
22.5°	806.9	805.7	803.3	800.8	796.1	793.7	790.1	783.0	774.7	765.2	755.8
25°	783.0	780.7	777.1	772.4	768.8	766.4	761.7	754.6	745.1	734.3	724.8
27.5°	745.1	748.5	746.3	739.0	735.5	730.7	729.6	720.1	711.8	701.1	690.3
30°	708.2	708.2	704.6	701.1	695.2	691.5	686.8	679.6	671.3	658.3	650.0
32.5°	661.8	660.7	655.9	654.7	650.0	642.9	641.7	632.1	623.8	614.3	603.6
35°	610.7	608.4	603.6	600.1	597.7	594.1	590.6	582.3	573.9	564.4	557.3
37.5°	552.5	552.5	551.3	545.4	543.0	540.7	537.1	528.8	524.1	514.5	507.4
40°	496.7	495.5	491.9	490.8	488.4	484.8	482.5	477.7	470.6	463.4	456.3
42.5°	442.0	443.2	438.5	439.7	434.9	432.5	431.3	424.2	420.7	413.6	407.5
45°	393.3	392.1	389.7	388.6	386.2	383.8	381.4	377.9	371.9	364.8	361.3
47.5°	348.1	344.6	344.6	343.4	342.2	337.4	336.3	332.7	329.1	322.0	317.3
50°	305.3	305.3	305.3	304.1	300.6	299.4	297.0	293.5	289.9	285.2	278.0
52.5°	270.9	270.9	270.9	269.7	265.0	263.8	262.6	257.9	253.0	249.6	244.7
55°	238.8	240.0	238.8	236.4	232.9	232.9	229.3	226.9	222.2	218.6	213.9
57.5°	211.5	211.5	209.2	208.0	205.6	204.4	202.0	199.7	193.6	190.1	184.1
60°	185.3	184.1	184.1	181.8	179.4	177.0	175.8	172.3	169.9	164.0	159.2
62.5°	161.6	161.6	159.2	159.2	154.5	154.5	153.3	149.7	146.2	140.3	137.9
65°	139.1	139.1	137.9	136.6	133.0	131.9	130.7	127.1	123.6	120.0	116.4
67.5°	118.8	118.8	116.4	115.3	112.9	111.7	109.3	106.9	103.4	99.8	96.3
70°	99.8	98.6	97.5	96.3	93.9	92.7	90.3	88.0	84.4	81.9	78.4
72.5°	80.9	80.9	79.7	77.2	76.0	74.8	73.6	71.3	67.7	64.1	61.8
75°	63.0	63.0	63.0	60.6	58.2	57.0	57.0	54.7	52.3	48.7	46.4
77.5°	48.7	47.5	46.4	46.4	44.0	42.8	41.6	40.4	36.9	35.7	33.3
80°	33.3	34.5	33.3	32.1	30.8	29.8	29.8	27.4	26.1	23.7	21.3
82.5°	22.5	21.3	21.3	20.2	20.2	19.0	19.0	16.6	15.4	14.2	13.0
85°	11.9	11.9	10.7	10.7	10.7	9.5	9.5	8.3	8.3	7.1	5.9
87.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593564

CATALOG NUMBER: HCC8W15D010MB-HM80520850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9
2.5°	805.7	803.3	802.0	802.0	800.8	799.6	798.4	797.3	794.9	794.9	792.5
5°	811.6	809.2	808.0	804.5	802.0	802.0	797.3	796.1	792.5	790.1	787.8
7.5°	816.3	811.6	808.0	804.5	802.0	799.6	794.9	790.1	785.4	780.7	778.3
10°	816.3	811.6	805.7	799.6	797.3	794.9	789.0	781.8	775.9	771.2	765.2
12.5°	814.0	806.9	799.6	794.9	790.1	786.6	779.5	772.4	765.2	755.8	751.0
15°	806.9	797.3	790.1	781.8	778.3	772.4	766.4	755.8	747.3	739.0	733.1
17.5°	792.5	780.7	772.4	764.1	758.1	754.6	745.1	735.5	726.0	716.5	709.4
20°	771.2	760.5	751.0	740.2	735.5	730.7	718.9	709.4	699.9	689.1	682.0
22.5°	745.1	734.3	721.3	713.0	705.8	699.9	689.1	678.5	669.0	659.5	650.0
25°	713.0	702.3	690.3	677.3	672.5	666.6	654.7	644.1	633.3	622.6	614.3
27.5°	678.5	664.2	654.7	640.5	635.8	629.7	616.7	604.8	595.3	587.0	577.4
30°	636.8	626.2	613.1	600.1	595.3	589.4	578.6	567.9	558.5	549.0	539.5
32.5°	591.8	581.1	567.9	558.5	551.3	546.6	535.9	526.3	516.8	507.4	499.1
35°	544.2	532.4	522.8	513.3	507.4	501.4	490.8	482.5	475.3	466.9	458.6
37.5°	495.5	487.2	477.7	466.9	461.0	456.3	448.0	438.5	432.5	425.4	419.5
40°	448.0	438.5	430.2	420.7	415.8	412.4	404.0	396.9	390.9	385.0	381.4
42.5°	399.2	390.9	382.6	376.7	373.1	369.6	363.5	355.2	351.7	345.8	342.2
45°	354.1	346.9	341.0	332.7	330.3	328.0	320.8	314.9	311.4	307.8	305.3
47.5°	311.4	306.6	299.4	294.6	291.1	288.7	284.0	279.2	275.7	273.3	270.9
50°	274.5	268.6	263.8	259.1	256.7	253.0	248.4	245.9	243.5	241.2	241.2
52.5°	240.0	234.1	229.3	225.8	223.4	221.0	217.5	216.3	213.9	213.9	212.7
55°	208.0	204.4	199.7	194.8	193.6	192.4	190.1	187.7	186.5	185.3	186.5
57.5°	180.6	177.0	172.3	168.7	167.5	166.4	165.2	162.8	161.6	161.6	161.6
60°	155.7	152.1	148.6	145.0	145.0	142.6	141.3	140.3	139.1	137.9	137.9
62.5°	133.0	129.5	125.9	123.6	122.4	121.2	118.8	117.6	116.4	116.4	115.3
65°	112.9	108.1	106.9	103.4	102.2	101.0	99.8	97.5	96.3	95.1	93.9
67.5°	92.7	90.3	86.8	84.4	83.1	81.9	80.9	78.4	77.2	76.0	73.6
70°	74.8	72.5	70.1	67.7	66.5	65.3	63.0	60.6	59.4	57.0	53.5
72.5°	58.2	55.8	53.5	51.1	49.9	48.7	46.4	44.0	41.6	39.2	36.9
75°	44.0	41.6	38.1	35.7	34.5	34.5	30.8	28.6	26.1	22.5	20.2
77.5°	30.8	27.4	26.1	23.7	22.5	20.2	17.8	15.4	13.0	11.9	9.5
80°	20.2	17.8	15.4	14.2	13.0	11.9	10.7	8.3	5.9	4.7	3.6
82.5°	11.9	10.7	9.5	8.3	7.1	5.9	4.7	4.7	3.6	2.4	1.2
85°	5.9	4.7	3.6	3.6	2.4	2.4	2.4	1.2	1.2	1.2	1.2
87.5°	2.4	1.2	1.2	1.2	1.2	1.2	1.2	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593564

CATALOG NUMBER: HCC8W15D010MB-HM80520850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9
2.5°	791.3	790.1	789.0	787.8	787.8	785.4	785.4	784.2	781.8	780.7	780.7
5°	784.2	780.7	778.3	777.1	775.9	772.4	771.2	768.8	766.4	764.1	762.9
7.5°	773.5	767.6	765.2	764.1	760.5	756.9	754.6	751.0	747.3	743.8	742.6
10°	760.5	754.6	748.5	746.3	742.6	740.2	735.5	730.7	727.2	723.6	720.1
12.5°	743.8	736.7	730.7	728.4	724.8	720.1	713.0	710.6	704.6	702.3	697.5
15°	724.8	716.5	710.6	707.0	703.5	696.2	691.5	686.8	680.8	678.5	673.7
17.5°	701.1	691.5	685.6	682.0	679.6	673.7	666.6	660.7	654.7	652.4	648.8
20°	672.5	666.6	658.3	654.7	652.4	645.2	638.0	635.8	630.9	626.2	622.6
22.5°	640.5	634.6	626.2	622.6	621.4	615.5	609.6	606.0	602.4	598.9	595.3
25°	607.2	600.1	593.0	590.6	588.2	583.5	578.6	576.4	572.7	570.3	567.9
27.5°	571.5	564.4	558.5	554.9	552.5	549.0	546.6	544.2	541.9	539.5	538.3
30°	533.6	526.3	521.6	519.2	516.8	515.7	512.1	510.9	509.7	507.4	508.5
32.5°	495.5	489.6	484.8	481.3	481.3	478.9	477.7	477.7	476.5	476.5	476.5
35°	453.9	450.3	446.8	445.6	444.4	443.2	442.0	443.2	442.0	443.2	444.4
37.5°	415.8	412.4	409.9	408.7	407.5	408.7	407.5	407.5	408.7	411.1	412.4
40°	376.7	374.3	371.9	373.1	371.9	371.9	371.9	375.5	376.7	377.9	379.1
42.5°	339.8	337.4	336.3	336.3	337.4	336.3	338.6	339.8	342.2	345.8	348.1
45°	304.1	303.1	303.1	304.1	303.1	305.3	305.3	307.8	311.4	313.7	316.1
47.5°	270.9	270.9	270.9	272.1	272.1	273.3	275.7	276.9	279.2	281.6	284.0
50°	240.0	241.2	242.4	242.4	242.4	244.7	247.1	248.4	249.6	250.8	254.3
52.5°	212.7	213.9	213.9	215.1	216.3	217.5	218.6	221.0	222.2	224.6	225.8
55°	186.5	186.5	188.9	190.1	190.1	190.1	192.4	192.4	194.8	196.1	198.5
57.5°	161.6	162.8	162.8	164.0	164.0	165.2	166.4	167.5	168.7	169.9	171.1
60°	137.9	137.9	137.9	139.1	140.3	141.3	140.3	142.6	142.6	145.0	146.2
62.5°	115.3	116.4	116.4	116.4	116.4	116.4	116.4	117.6	118.8	120.0	121.2
65°	93.9	93.9	93.9	92.7	93.9	92.7	93.9	95.1	95.1	96.3	97.5
67.5°	72.5	72.5	70.1	70.1	71.3	71.3	71.3	71.3	70.1	72.5	72.5
70°	52.3	51.1	49.9	48.7	48.7	47.5	47.5	46.4	46.4	46.4	46.4
72.5°	34.5	32.1	29.8	28.6	27.4	27.4	24.9	23.7	24.9	24.9	24.9
75°	17.8	15.4	14.2	13.0	11.9	11.9	10.7	10.7	10.7	10.7	10.7
77.5°	7.1	5.9	4.7	4.7	3.6	3.6	3.6	3.6	3.6	3.6	3.6
80°	2.4	2.4	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
82.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
85°	1.2	0.0	0.0	1.2	0.0	1.2	1.2	1.2	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593564

CATALOG NUMBER: HCC8W15D010MB-HM80520850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9
2.5°	779.5	779.5	778.3	779.5	777.1	778.3	777.1	777.1
5°	761.7	759.3	759.3	759.3	758.1	758.1	756.9	756.9
7.5°	740.2	739.0	737.9	736.7	735.5	734.3	734.3	734.3
10°	718.9	716.5	716.5	715.3	713.0	711.8	711.8	711.8
12.5°	694.0	692.8	691.5	691.5	686.8	687.9	686.8	686.8
15°	670.2	669.0	669.0	665.4	663.0	663.0	663.0	661.8
17.5°	645.2	644.1	642.9	640.5	638.0	638.0	636.8	638.0
20°	619.1	617.9	615.5	615.5	614.3	613.1	610.7	611.9
22.5°	593.0	590.6	589.4	589.4	588.2	588.2	585.8	585.8
25°	565.6	564.4	563.2	564.4	562.0	562.0	559.6	559.6
27.5°	537.1	535.9	535.9	535.9	534.7	535.9	534.7	534.7
30°	508.5	508.5	507.4	507.4	508.5	507.4	508.5	509.7
32.5°	477.7	477.7	478.9	478.9	480.1	480.1	480.1	480.1
35°	445.6	448.0	448.0	449.1	450.3	451.5	451.5	452.7
37.5°	415.8	417.1	418.3	419.5	421.9	421.9	421.9	421.9
40°	383.8	385.0	387.4	386.2	390.9	392.1	390.9	390.9
42.5°	350.5	352.9	354.1	356.4	357.6	360.1	361.3	361.3
45°	319.7	320.8	323.2	325.6	326.8	330.3	330.3	330.3
47.5°	287.5	289.9	291.1	293.5	294.6	298.2	299.4	298.2
50°	256.7	259.1	261.4	261.4	265.0	266.2	268.6	269.7
52.5°	226.9	228.1	230.5	231.7	234.1	236.4	237.6	238.8
55°	198.5	199.7	202.0	202.0	205.6	206.8	209.2	209.2
57.5°	172.3	173.5	175.8	174.7	177.0	179.4	179.4	178.2
60°	147.4	147.4	147.4	149.7	150.9	152.1	153.3	153.3
62.5°	121.2	123.6	124.7	124.7	125.9	127.1	127.1	125.9
65°	97.5	99.8	101.0	101.0	102.2	102.2	102.2	103.4
67.5°	73.6	73.6	73.6	74.8	73.6	73.6	73.6	73.6
70°	46.4	46.4	46.4	46.4	45.2	46.4	46.4	47.5
72.5°	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9
75°	10.7	10.7	10.7	11.9	10.7	10.7	10.7	10.7
77.5°	4.7	3.6	4.7	4.7	3.6	3.6	3.6	3.6
80°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
82.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
85°	0.0	1.2	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)