

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583906

Luminaire Tested: **HCC8S15D010SL-HM80520927-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010SL-HM80520927-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1236.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583906
CATALOG NUMBER: HCC8S15D010SL-HM80520927-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P583906

CATALOG NUMBER: HCC8S15D010SL-HM80520927-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20053	20053	20053
5°	20318	19972	19780
10°	20525	19764	19467
15°	20735	19346	18957
20°	20628	18633	18206
25°	20146	17519	17281
30°	19135	16262	16201
35°	17418	14839	14971
40°	15276	13280	13771
45°	13174	11814	12647
50°	11537	10372	11451
55°	10220	8914	10080
60°	9208	7499	8350
65°	8303	6020	6399
70°	7276	4382	3516
75°	6207	2288	929
80°	4777	622	142
85°	3078	0	0



TEST NUMBER: P583906

CATALOG NUMBER: HCC8S15D010SL-HM80520927-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	5.0
10°-20°	172.5	14.0
20°-30°	244.8	19.8
30°-40°	257.7	20.9
40°-50°	219.2	17.7
50°-60°	158.4	12.8
60°-70°	90.1	7.3
70°-80°	28.4	2.3
80°-90°	3.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	478.7	38.7
0°-40°	736.4	59.6
0°-60°	1114.0	90.1
0°-90°	1236.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1236.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	650	650	650	650	650	
5°	656	653	645	641	639	63
15°	650	633	606	595	594	183
25°	592	563	515	506	508	271
35°	463	436	394	392	398	288
45°	302	291	271	278	290	235
55°	190	176	166	175	188	171
65°	114	98	82	82	88	113
75°	52	40	19	9	8	56
85°	9	5	0	0	0	11
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583906

CATALOG NUMBER: HCC8S15D010SL-HM80520927-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3
2.5°	653.8	654.7	652.9	652.9	654.7	652.9	653.8	653.8	652.9	652.9	652.0
5°	656.4	655.5	655.5	655.5	656.4	654.7	653.8	654.7	652.9	652.9	652.9
7.5°	657.2	657.2	656.4	655.5	655.5	655.5	654.7	653.8	652.9	651.2	650.3
10°	655.5	655.5	656.4	654.7	654.7	652.9	652.9	651.2	651.2	649.5	646.8
12.5°	653.8	652.9	652.9	651.2	651.2	649.5	649.5	646.8	646.0	643.3	640.8
15°	649.5	648.5	646.8	646.0	645.2	644.2	642.5	641.7	639.0	635.5	633.0
17.5°	640.8	639.9	639.0	637.3	635.5	634.7	633.8	631.2	627.7	625.2	620.8
20°	628.6	627.7	627.7	625.2	624.3	621.7	620.8	617.3	614.7	609.5	606.0
22.5°	612.1	613.0	611.3	609.5	607.8	605.2	603.5	600.0	595.6	590.4	586.1
25°	592.1	593.0	591.3	589.5	587.0	585.1	583.5	578.3	573.9	567.8	562.6
27.5°	567.0	567.0	567.0	565.3	560.9	560.0	558.3	553.1	546.9	541.8	536.6
30°	537.4	536.6	536.6	533.9	532.2	528.8	526.1	521.8	517.4	511.4	505.4
32.5°	501.9	502.7	500.1	498.4	495.7	495.7	492.2	488.9	483.6	477.5	471.5
35°	462.7	463.7	461.9	461.0	456.7	455.9	455.0	450.7	447.2	442.8	435.8
37.5°	422.8	422.0	421.1	421.1	418.5	416.8	415.0	412.5	407.2	403.7	400.3
40°	379.5	379.5	379.5	378.6	377.6	376.0	375.1	373.3	369.8	366.4	363.8
42.5°	340.3	340.3	339.4	338.6	336.9	337.8	336.0	334.3	330.8	328.2	326.4
45°	302.1	302.1	302.1	303.1	301.2	298.7	298.7	296.9	295.2	293.4	290.9
47.5°	268.2	270.9	269.2	268.2	269.2	265.7	265.7	263.9	262.2	260.5	257.0
50°	240.5	240.5	240.5	238.7	237.9	237.9	235.3	233.5	232.7	231.0	227.5
52.5°	215.3	213.6	213.6	212.7	211.8	210.2	210.2	208.3	204.8	203.2	200.5
55°	190.1	190.1	189.3	188.5	187.5	186.7	185.8	183.2	181.5	178.8	176.3
57.5°	167.6	169.3	168.5	166.7	165.0	165.0	163.3	161.5	158.9	156.3	153.6
60°	149.3	148.5	148.5	147.6	145.8	145.0	144.1	141.5	138.9	136.3	133.8
62.5°	130.3	130.3	130.3	128.5	126.8	125.9	125.1	123.3	119.8	117.2	115.4
65°	113.8	112.9	111.9	111.1	110.3	108.6	107.6	105.9	103.3	100.7	98.1
67.5°	97.2	96.4	96.4	95.6	92.9	92.1	92.1	89.4	86.9	84.2	81.6
70°	80.7	80.7	80.7	79.0	78.1	77.2	76.4	74.7	72.1	69.4	66.9
72.5°	66.9	66.0	66.0	65.1	62.5	61.7	60.7	59.0	56.4	54.7	53.0
75°	52.1	52.1	51.2	50.4	49.5	48.6	47.7	46.0	43.4	40.8	39.9
77.5°	39.9	39.0	39.0	38.2	36.5	35.5	35.5	33.9	31.2	29.5	27.8
80°	26.9	27.8	26.9	26.0	25.2	24.3	23.5	22.5	20.8	19.2	17.4
82.5°	16.5	17.4	16.5	16.5	15.7	14.7	14.7	13.0	12.2	11.3	10.4
85°	8.7	8.7	8.7	8.7	7.8	7.8	7.8	7.0	6.0	5.2	5.2
87.5°	2.7	3.5	2.7	2.7	2.7	2.7	2.7	2.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583906

CATALOG NUMBER: HCC8S15D010SL-HM80520927-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3
2.5°	652.9	652.0	651.2	651.2	651.2	651.2	651.2	650.3	649.5	649.5	649.5
5°	651.2	651.2	651.2	650.3	649.5	649.5	647.7	646.8	646.0	645.2	644.2
7.5°	649.5	647.7	646.8	646.0	645.2	645.2	643.3	641.7	641.7	639.9	638.2
10°	644.2	643.3	641.7	639.9	639.0	638.2	636.5	633.8	633.0	631.2	629.5
12.5°	638.2	636.5	634.7	631.2	630.3	629.5	626.0	623.3	621.7	620.8	616.5
15°	630.3	626.8	624.3	620.0	619.0	617.3	614.7	612.1	608.6	606.0	604.3
17.5°	616.5	613.0	608.6	604.3	602.6	602.6	598.2	594.8	590.4	588.6	585.1
20°	600.0	595.6	592.1	587.0	584.3	581.8	579.1	573.9	570.4	567.8	563.5
22.5°	580.8	574.8	570.4	565.3	560.9	558.3	553.9	549.6	545.3	542.6	539.2
25°	556.6	551.3	544.4	539.2	536.6	533.1	527.9	523.6	519.2	514.9	513.1
27.5°	529.6	522.7	516.6	510.6	507.9	505.4	499.2	494.0	490.6	486.2	484.5
30°	500.1	493.2	486.2	481.0	478.4	474.0	470.6	464.5	460.2	456.7	452.4
32.5°	466.2	461.0	455.0	447.2	445.4	442.0	436.7	434.2	428.9	426.3	422.8
35°	429.8	426.3	420.2	414.2	411.5	409.8	405.5	400.3	396.8	394.2	392.5
37.5°	395.0	390.7	384.6	380.3	378.6	376.0	370.8	368.1	364.6	362.9	359.5
40°	357.8	353.4	349.1	346.4	343.8	342.1	338.6	336.0	332.6	329.9	329.1
42.5°	321.3	318.6	315.2	311.7	310.9	308.2	306.4	303.9	301.2	300.4	297.8
45°	288.2	285.7	282.2	278.7	277.9	276.1	275.2	272.6	270.9	270.9	270.9
47.5°	255.2	252.7	249.2	247.5	248.4	244.9	244.9	244.0	242.2	242.2	243.0
50°	225.7	222.3	221.4	219.7	218.0	216.2	217.0	214.5	214.5	216.2	215.3
52.5°	198.0	194.5	193.6	191.8	191.0	191.0	190.1	190.1	189.3	190.1	190.1
55°	172.8	170.1	168.5	166.7	165.8	165.8	165.8	165.0	164.1	165.8	166.7
57.5°	150.3	149.3	147.6	145.0	144.1	143.3	142.4	142.4	142.4	142.4	143.3
60°	130.3	128.5	126.8	124.1	124.1	123.3	122.4	121.6	121.6	121.6	121.6
62.5°	112.9	110.3	107.6	105.9	105.1	104.2	103.3	101.6	101.6	101.6	101.6
65°	95.6	92.9	91.2	89.4	87.7	87.7	85.9	85.1	83.4	82.5	80.7
67.5°	79.0	77.2	75.6	72.9	72.1	71.2	69.4	68.6	66.0	65.1	64.2
70°	64.2	61.7	59.9	58.2	57.4	55.6	53.9	52.1	50.4	48.6	46.9
72.5°	50.4	47.7	46.0	44.2	42.5	42.5	39.9	38.2	35.5	33.9	31.2
75°	37.4	34.7	33.0	30.4	29.5	28.7	26.0	24.3	21.7	19.2	17.4
77.5°	25.2	23.5	21.7	19.2	17.4	17.4	14.7	13.0	11.3	8.7	7.8
80°	15.7	13.9	12.2	10.4	10.4	8.7	7.8	6.0	4.3	3.5	2.7
82.5°	8.7	7.8	7.0	5.2	5.2	4.3	3.5	2.7	1.7	0.8	0.8
85°	4.3	3.5	2.7	2.7	1.7	1.7	1.7	0.8	0.8	0.0	0.0
87.5°	1.7	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583906

CATALOG NUMBER: HCC8S15D010SL-HM80520927-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3
2.5°	648.5	648.5	647.7	647.7	647.7	646.8	647.7	646.8	646.8	646.8	647.7
5°	645.2	643.3	643.3	642.5	642.5	641.7	642.5	641.7	640.8	639.9	640.8
7.5°	638.2	636.5	635.5	634.7	634.7	634.7	633.8	633.0	633.8	631.2	633.0
10°	628.6	627.7	626.0	625.2	624.3	625.2	624.3	622.5	622.5	622.5	621.7
12.5°	616.5	614.7	613.8	613.0	611.3	611.3	612.1	610.3	610.3	608.6	608.6
15°	601.7	600.0	598.2	598.2	596.5	596.5	595.6	595.6	594.8	593.8	593.8
17.5°	583.5	580.8	579.1	580.0	579.1	578.3	578.3	576.5	575.6	576.5	576.5
20°	561.8	560.0	558.3	559.1	557.4	556.6	557.4	554.8	555.6	555.6	555.6
22.5°	537.4	536.6	533.9	533.9	532.2	531.4	532.2	532.2	533.1	532.2	532.2
25°	510.6	508.8	507.1	507.1	506.2	505.4	506.2	507.1	506.2	507.1	507.1
27.5°	481.9	479.2	479.2	477.5	477.5	478.4	477.5	478.4	479.2	479.2	481.0
30°	450.7	449.7	448.9	448.0	448.0	448.9	448.9	448.9	449.7	451.5	451.5
32.5°	421.1	419.3	417.7	417.7	419.3	418.5	419.3	419.3	421.1	421.1	422.8
35°	389.0	389.0	387.3	388.1	388.1	388.1	388.1	389.8	391.6	392.5	394.2
37.5°	359.5	356.8	357.8	357.8	358.6	357.8	360.3	360.3	362.1	362.1	363.8
40°	327.3	327.3	328.2	327.3	328.2	328.2	329.9	331.6	332.6	334.3	335.1
42.5°	296.9	298.7	296.9	297.8	298.7	299.6	300.4	301.2	304.7	306.4	309.1
45°	269.2	270.0	270.9	271.7	270.9	272.6	273.5	275.2	277.9	278.7	279.6
47.5°	242.2	243.0	244.0	244.9	244.9	246.5	247.5	249.2	250.9	251.8	252.7
50°	216.2	218.0	218.8	218.8	219.7	221.4	223.2	223.2	224.9	227.5	228.3
52.5°	192.8	192.8	194.5	195.3	196.2	196.2	198.8	199.7	200.5	202.3	204.0
55°	166.7	169.3	170.1	170.1	172.0	173.6	174.5	175.3	175.3	178.8	178.8
57.5°	144.1	145.0	146.8	146.8	146.8	149.3	149.3	151.1	152.0	152.8	154.6
60°	121.6	123.3	123.3	124.1	123.3	125.1	125.9	127.6	128.5	129.4	130.3
62.5°	100.7	100.7	101.6	101.6	101.6	101.6	103.3	103.3	105.1	105.9	106.8
65°	80.7	80.7	80.7	80.7	80.7	80.7	80.7	80.7	81.6	81.6	83.4
67.5°	62.5	61.7	59.9	60.7	59.9	59.9	59.0	59.0	59.9	59.9	61.7
70°	45.2	44.2	42.5	42.5	41.7	40.8	39.9	39.0	38.2	38.2	38.2
72.5°	29.5	27.8	25.2	24.3	24.3	22.5	20.8	20.0	20.0	20.0	20.0
75°	14.7	13.0	11.3	10.4	10.4	8.7	9.5	8.7	8.7	8.7	8.7
77.5°	6.0	4.3	3.5	3.5	3.5	2.7	2.7	2.7	2.7	2.7	2.7
80°	1.7	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
82.5°	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583906

CATALOG NUMBER: HCC8S15D010SL-HM80520927-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3
2.5°	646.8	646.8	645.2	646.0	646.0	646.0	646.0	646.0
5°	639.0	639.9	639.0	639.9	639.9	639.0	639.0	639.0
7.5°	631.2	632.0	631.2	632.0	632.0	632.0	631.2	631.2
10°	621.7	621.7	621.7	621.7	621.7	620.8	621.7	621.7
12.5°	608.6	608.6	608.6	609.5	609.5	608.6	608.6	607.8
15°	594.8	593.0	593.8	594.8	593.8	593.8	593.8	593.8
17.5°	575.6	576.5	575.6	575.6	575.6	575.6	576.5	575.6
20°	555.6	555.6	556.6	555.6	555.6	555.6	555.6	554.8
22.5°	533.1	532.2	532.2	533.1	533.1	532.2	533.1	533.1
25°	507.9	508.8	507.9	507.9	508.8	508.8	508.8	507.9
27.5°	481.0	481.9	482.7	481.9	481.9	481.9	482.7	483.6
30°	453.2	455.0	453.2	453.2	455.0	454.0	455.0	455.0
32.5°	423.7	426.3	424.5	426.3	426.3	427.2	426.3	427.2
35°	394.2	396.8	396.8	396.8	397.7	398.5	398.5	397.7
37.5°	366.4	367.3	367.3	369.0	369.8	370.8	370.8	369.8
40°	337.8	339.4	340.3	340.3	340.3	342.1	343.8	342.1
42.5°	309.9	310.9	311.7	311.7	313.4	314.3	315.2	315.2
45°	283.1	284.7	285.7	286.5	287.4	289.1	288.2	290.0
47.5°	255.2	257.9	258.7	259.6	261.4	262.2	263.1	263.9
50°	230.0	231.8	231.8	233.5	236.2	236.2	237.9	238.7
52.5°	204.8	205.8	206.7	207.5	209.2	211.0	211.0	212.7
55°	180.6	181.5	181.5	182.3	183.2	186.7	187.5	187.5
57.5°	155.4	155.4	157.1	158.0	158.9	160.6	160.6	160.6
60°	131.1	131.9	131.9	132.8	133.8	135.4	136.3	135.4
62.5°	106.8	107.6	107.6	108.6	110.3	111.1	110.3	110.3
65°	84.2	85.1	85.1	85.9	87.7	87.7	86.9	87.7
67.5°	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.7
70°	39.0	38.2	37.4	38.2	38.2	38.2	37.4	39.0
72.5°	19.2	20.0	20.0	20.0	20.0	20.0	20.0	19.2
75°	8.7	8.7	7.8	7.8	7.8	8.7	8.7	7.8
77.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
80°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)